

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P953240

Luminaire Tested: **GALN-SB6D-835-U-SLL**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P953240
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GALN-SB6D-835-U-SLL
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(6) 80 CRI, 3500K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR LEFT OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 57031 lumens
Efficiency: N/A
Efficacy: 129.6 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B4 - U0 - G5


Input Watts (W): 440.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P953240
 CATALOG NUMBER: GALN-SB6D-835-U-SLL

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 17.4 fc
 Type IV - Short - N/A

REPORT NUMBER: P953240
CATALOG NUMBER: GALN-SB6D-835-U-SLL

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P953240
 CATALOG NUMBER: GALN-SB6D-835-U-SLL

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	14494.4	0.0	14494.4
	% Fixture	25.4	0.0	25.4
Street Side	Lumens	42536.6	0.0	42536.6
	% Fixture	74.6	0.0	74.6
Total	Lumens	57031.0	0.0	57031.0
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	777.9	1.4
10°-20°	2442.1	4.3
20°-30°	3772.2	6.6
30°-40°	4780.4	8.4
40°-50°	7210.0	12.6
50°-60°	11648.9	20.4
60°-70°	14522.2	25.5
70°-80°	9522.9	16.7
80°-90°	2354.3	4.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	57031.0	100.0
0°-180°	57031.0	100.0




REPORT NUMBER: P953240
 CATALOG NUMBER: GALN-SB6D-835-U-SLL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	3836.0	6.7			
FM (30°-60°)	16634.7	29.2			
FH (60°-80°)	20126.5	35.3			G5
FVH (80°-90°)	1939.4	3.4			G5
BL (0°-30°)	3156.3	5.5	B4/5000		
BM (30°-60°)	7004.6	12.3	B4/8500		
BH (60°-80°)	3918.6	6.9	B4/5000		G4/5000
BVH (80°-90°)	414.9	0.7			G3/500
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G5

Type IV Short



REPORT NUMBER: P953240

CATALOG NUMBER: GALN-SB6D-835-U-SLL

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°
0°	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3
2.5°	8433.6	8465.5	8497.7	8543.1	8588.6	8615.6	8642.7	8656.3	8669.8	8663.8
5°	9068.5	9180.2	9292.1	9402.9	9513.9	9574.1	9634.3	9670.7	9707.4	9735.1
7.5°	9706.5	9888.3	10069.7	10233.1	10396.6	10495.0	10593.4	10646.6	10699.6	10725.2
10°	10195.5	10410.4	10625.3	10817.0	11008.6	11124.8	11240.4	11292.1	11343.6	11363.1
12.5°	10495.0	10727.9	10960.5	11133.8	11306.6	11390.8	11475.1	11503.4	11531.7	11534.7
15°	10677.0	10878.0	11078.8	11187.4	11296.3	11299.3	11302.4	11272.3	11242.2	11206.7
17.5°	10779.3	10915.1	11050.8	11052.9	11054.7	10932.8	10810.9	10699.3	10587.3	10508.5
20°	10892.2	10939.4	10987.0	10844.0	10701.1	10432.1	10163.0	9967.1	9771.2	9650.8
22.5°	11023.1	10961.1	10899.1	10603.0	10306.9	9911.2	9515.4	9270.5	9025.5	8892.5
25°	11191.6	10996.0	10800.4	10350.8	9901.2	9420.6	8940.0	8682.5	8425.5	8299.7
27.5°	11420.3	11070.6	10720.7	10125.1	9529.9	8997.2	8464.6	8211.2	7958.1	7839.2
30°	11728.8	11207.3	10686.0	9953.0	9219.9	8665.0	8110.1	7875.1	7640.0	7529.3
32.5°	12092.9	11378.8	10665.0	9835.6	9006.3	8484.7	7963.2	7778.8	7594.0	7514.2
35°	12535.3	11661.4	10787.8	9923.5	9059.5	8697.2	8335.2	8292.1	8249.1	8242.5
37.5°	13280.1	12252.1	11224.1	10438.7	9653.3	9629.8	9606.3	9803.1	9999.9	10102.2
40°	14405.6	13287.6	12169.6	11585.5	11001.4	11413.7	11826.0	12304.5	12782.9	13021.3
42.5°	15898.2	14788.9	13679.7	13343.3	13006.8	13906.0	14805.2	15675.5	16545.8	17056.8
45°	17741.4	16745.0	15748.3	15599.9	15451.3	16891.8	18332.7	19762.7	21193.0	22061.2
47.5°	20046.5	19077.2	18107.6	18077.5	18047.4	20125.6	22203.3	24296.8	26390.1	27619.4
50°	23067.8	21870.4	20673.3	20678.5	20683.6	23361.9	26040.1	28803.6	31567.0	33237.8
52.5°	26536.1	25086.2	23636.6	23490.0	23343.2	26542.4	29741.6	33160.8	36579.6	38582.3
55°	30228.5	28796.1	27363.6	26792.2	26220.7	29781.3	33341.6	37417.7	41493.8	43875.7
57.5°	33586.9	32806.9	32026.5	30880.3	29734.4	33329.6	36924.8	41541.7	46158.3	49111.9
60°	35616.7	36828.2	38040.0	36616.6	35193.2	38595.6	41997.9	46941.0	51884.1	55076.3
62.5°	34586.0	37896.5	41207.0	41046.6	40885.9	44002.7	47119.7	51822.7	56525.3	59475.9
65°	32523.1	35630.2	38737.3	39352.1	39966.6	43927.5	47888.6	52448.9	57008.9	59521.1
67.5°	29759.0	32714.2	35669.3	35957.6	36245.6	40372.6	44499.2	49079.1	53659.0	55627.0
70°	26438.3	29652.5	32867.0	32995.8	33124.9	36815.6	40505.9	44447.2	48388.1	49482.0
72.5°	22481.0	26169.5	29858.3	29951.0	30043.4	32930.8	35818.3	38770.1	41721.6	41832.4
75°	17475.0	21292.7	25110.3	25453.0	25795.8	28042.2	30288.7	32366.6	34444.5	33887.8
77.5°	12485.6	16049.2	19613.2	20103.7	20594.2	22302.0	24009.8	25483.4	26957.4	26000.4
80°	8171.8	11169.9	14167.8	14777.5	15387.2	16677.0	17966.2	18740.2	19513.9	17974.6
82.5°	4750.2	6799.8	8849.8	9530.8	10212.1	11099.8	11987.6	12310.5	12633.1	11423.3
85°	2090.0	3177.8	4265.7	4845.0	5424.3	6153.7	6882.9	7066.2	7249.4	6280.4
87.5°	647.0	1012.6	1378.3	1701.5	2024.7	2389.4	2754.1	2769.8	2785.1	2338.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P953240
 CATALOG NUMBER: GALN-SB6D-835-U-SLL

CANDELA DISTRIBUTION (continued):

50°		55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
7842.3	0°	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3
8669.8	2.5°	8656.3	8642.7	8615.6	8588.6	8543.1	8497.7	8465.5	8433.6	8368.9	8304.2
9707.4	5°	9670.7	9634.3	9574.1	9513.9	9402.9	9292.1	9180.2	9068.5	8925.6	8782.7
10699.6	7.5°	10646.6	10593.4	10495.0	10396.6	10233.1	10069.7	9888.3	9706.5	9470.6	9235.0
11343.6	10°	11292.1	11240.4	11124.8	11008.6	10817.0	10625.3	10410.4	10195.5	9897.3	9599.1
11531.7	12.5°	11503.4	11475.1	11390.8	11306.6	11133.8	10960.5	10727.9	10495.0	10167.2	9839.8
11242.2	15°	11272.3	11302.4	11299.3	11296.3	11187.4	11078.8	10878.0	10677.0	10335.5	9993.9
10587.3	17.5°	10699.3	10810.9	10932.8	11054.7	11052.9	11050.8	10915.1	10779.3	10433.0	10086.6
9771.2	20°	9967.1	10163.0	10432.1	10701.1	10844.0	10987.0	10939.4	10892.2	10532.3	10172.1
9025.5	22.5°	9270.5	9515.4	9911.2	10306.9	10603.0	10899.1	10961.1	11023.1	10655.4	10287.3
8425.5	25°	8682.5	8940.0	9420.6	9901.2	10350.8	10800.4	10996.0	11191.6	10831.1	10470.9
7958.1	27.5°	8211.2	8464.6	8997.2	9529.9	10125.1	10720.7	11070.6	11420.3	11076.7	10732.7
7640.0	30°	7875.1	8110.1	8665.0	9219.9	9953.0	10686.0	11207.3	11728.8	11396.5	11064.6
7594.0	32.5°	7778.8	7963.2	8484.7	9006.3	9835.6	10665.0	11378.8	12092.9	11764.0	11435.4
8249.1	35°	8292.1	8335.2	8697.2	9059.5	9923.5	10787.8	11661.4	12535.3	12220.5	11905.4
9999.9	37.5°	9803.1	9606.3	9629.8	9653.3	10438.7	11224.1	12252.1	13280.1	12878.6	12477.2
12782.9	40°	12304.5	11826.0	11413.7	11001.4	11585.5	12169.6	13287.6	14405.6	13820.5	13235.5
16545.8	42.5°	15675.5	14805.2	13906.0	13006.8	13343.3	13679.7	14788.9	15898.2	15053.8	14209.3
21193.0	45°	19762.7	18332.7	16891.8	15451.3	15599.9	15748.3	16745.0	17741.4	16602.3	15463.3
26390.1	47.5°	24296.8	22203.3	20125.6	18047.4	18077.5	18107.6	19077.2	20046.5	18443.4	16840.1
31567.0	50°	28803.6	26040.1	23361.9	20683.6	20678.5	20673.3	21870.4	23067.8	20651.1	18234.0
36579.6	52.5°	33160.8	29741.6	26542.4	23343.2	23490.0	23636.6	25086.2	26536.1	22970.0	19404.0
41493.8	55°	37417.7	33341.6	29781.3	26220.7	26792.2	27363.6	28796.1	30228.5	25026.0	19823.8
46158.3	57.5°	41541.7	36924.8	33329.6	29734.4	30880.3	32026.5	32806.9	33586.9	26483.1	19379.3
51884.1	60°	46941.0	41997.9	38595.6	35193.2	36616.6	38040.0	36828.2	35616.7	26847.2	18077.5
56525.3	62.5°	51822.7	47119.7	44002.7	40885.9	41046.6	41207.0	37896.5	34586.0	25314.0	16042.0
57008.9	65°	52448.9	47888.6	43927.5	39966.6	39352.1	38737.3	35630.2	32523.1	23144.6	13766.1
53659.0	67.5°	49079.1	44499.2	40372.6	36245.6	35957.6	35669.3	32714.2	29759.0	20562.9	11366.8
48388.1	70°	44447.2	40505.9	36815.6	33124.9	32995.8	32867.0	29652.5	26438.3	17745.9	9053.5
41721.6	72.5°	38770.1	35818.3	32930.8	30043.4	29951.0	29858.3	26169.5	22481.0	14692.0	6903.3
34444.5	75°	32366.6	30288.7	28042.2	25795.8	25453.0	25110.3	21292.7	17475.0	11191.3	4907.6
26957.4	77.5°	25483.4	24009.8	22302.0	20594.2	20103.7	19613.2	16049.2	12485.6	7832.9	3180.2
19513.9	80°	18740.2	17966.2	16677.0	15387.2	14777.5	14167.8	11169.9	8171.8	5046.6	1921.4
12633.1	82.5°	12310.5	11987.6	11099.8	10212.1	9530.8	8849.8	6799.8	4750.2	2920.8	1091.8
7249.4	85°	7066.2	6882.9	6153.7	5424.3	4845.0	4265.7	3177.8	2090.0	1313.9	538.1
2785.1	87.5°	2769.8	2754.1	2389.4	2024.7	1701.5	1378.3	1012.6	647.0	430.3	213.7
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P953240
 CATALOG NUMBER: GALN-SB6D-835-U-SLL

CANDELA DISTRIBUTION (continued):

105°		110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
7842.3	0°	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3
8235.3	2.5°	8166.7	8097.4	8028.2	7962.0	7895.8	7831.7	7760.4	7702.6	7645.1	7593.1
8640.0	5°	8497.7	8354.1	8210.9	8077.0	7943.1	7816.7	7691.8	7582.9	7473.6	7382.1
9017.1	7.5°	8799.2	8587.1	8374.9	8188.0	8001.1	7828.7	7667.1	7522.1	7377.3	7256.9
9311.1	10°	9023.4	8765.8	8507.9	8287.0	8065.5	7852.8	7679.1	7526.3	7373.4	7253.0
9513.6	12.5°	9187.4	8883.5	8579.5	8329.5	8079.4	7855.8	7694.2	7569.0	7444.4	7364.4
9640.0	15°	9286.1	8936.1	8586.2	8296.7	8007.2	7759.5	7630.1	7570.2	7510.6	7521.5
9700.5	17.5°	9314.4	8908.2	8501.9	8153.7	7805.5	7514.2	7434.5	7456.5	7478.1	7609.3
9747.7	20°	9323.4	8831.1	8338.8	7907.3	7475.7	7136.6	7115.5	7217.8	7320.1	7547.9
9811.5	22.5°	9335.5	8736.6	8137.8	7618.1	7098.4	6712.3	6753.5	6904.9	7056.2	7316.2
9927.1	25°	9383.0	8643.3	7903.9	7295.2	6686.7	6291.0	6402.3	6576.8	6751.4	6985.2
10107.7	27.5°	9482.3	8581.0	7679.8	6999.9	6320.1	5959.9	6095.4	6263.9	6432.4	6624.7
10341.5	30°	9618.3	8551.8	7484.7	6753.2	6021.6	5719.2	5825.4	5959.0	6093.2	6252.7
10585.5	32.5°	9735.7	8515.7	7295.2	6540.4	5785.4	5541.6	5588.9	5668.0	5747.2	5874.5
10863.6	35°	9821.8	8447.7	7074.3	6331.3	5588.3	5385.2	5365.6	5387.3	5409.2	5506.4
11175.1	37.5°	9872.9	8331.3	6789.6	6085.1	5380.6	5203.1	5131.5	5107.4	5083.3	5153.1
11570.5	40°	9905.1	8170.9	6436.9	5791.4	5145.9	4984.9	4875.1	4820.6	4766.1	4816.4
12087.8	42.5°	9966.2	8005.4	6045.1	5467.3	4889.5	4741.2	4602.7	4530.5	4458.3	4499.2
12768.5	45°	10073.7	7851.6	5629.8	5123.0	4616.3	4465.8	4331.9	4261.5	4191.4	4225.7
13493.7	47.5°	10147.4	7724.6	5301.8	4850.7	4399.6	4205.5	4090.2	4031.3	3972.3	4004.8
14166.6	50°	10099.2	7586.2	5073.1	4669.8	4266.6	4011.4	3877.5	3825.1	3773.1	3823.6
14603.6	52.5°	9802.8	7352.3	4902.2	4550.7	4199.5	3906.1	3718.9	3667.1	3615.7	3691.8
14507.3	55°	9190.4	6964.7	4739.1	4464.3	4189.6	3916.6	3634.6	3552.8	3471.2	3579.3
13829.6	57.5°	8280.1	6418.2	4556.1	4362.0	4167.9	3927.1	3584.1	3464.9	3345.7	3461.9
12568.4	60°	7059.2	5708.7	4358.1	4205.5	4052.9	3894.0	3536.5	3382.2	3227.5	3329.5
10863.0	62.5°	5684.0	4859.4	4034.9	3933.5	3832.4	3812.8	3481.2	3288.0	3095.1	3159.8
9123.0	65°	4480.3	4095.4	3710.5	3662.6	3614.8	3617.2	3364.4	3159.2	2953.6	2978.6
7418.5	67.5°	3470.3	3361.1	3251.6	3278.3	3304.8	3298.2	3156.2	2985.2	2814.3	2806.5
5841.1	70°	2628.6	2659.9	2690.9	2814.9	2938.6	2938.6	2891.9	2770.4	2648.8	2621.7
4465.5	72.5°	2027.7	2121.9	2216.4	2392.1	2567.5	2597.0	2597.6	2514.3	2430.9	2391.2
3241.0	75°	1574.5	1659.9	1745.4	1942.2	2139.0	2275.0	2263.6	2199.5	2135.1	2097.2
2196.2	77.5°	1212.1	1270.2	1328.6	1519.7	1710.8	1935.0	1929.0	1877.5	1826.0	1787.5
1415.0	80°	908.8	932.9	957.0	1118.9	1280.5	1548.3	1547.4	1504.4	1461.0	1428.8
870.3	82.5°	649.4	653.6	658.4	777.6	896.8	1125.5	1138.1	1117.1	1096.0	1073.1
465.2	85°	392.7	390.6	388.2	475.5	562.7	732.8	749.3	726.7	704.2	678.6
192.9	87.5°	172.1	170.0	167.9	203.4	239.2	310.0	331.0	322.0	313.0	308.2
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P953240
 CATALOG NUMBER: GALN-SB6D-835-U-SLL

CANDELA DISTRIBUTION (continued):

160°		165°	170°	175°	180°	185°	190°	195°	200°	205°	210°
7842.3	0°	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3
7541.3	2.5°	7495.9	7450.4	7404.7	7359.3	7324.1	7288.5	7260.0	7231.4	7209.1	7186.8
7290.9	5°	7210.3	7129.6	7056.5	6983.1	6926.8	6870.2	6830.8	6791.4	6763.4	6735.4
7136.6	7.5°	7035.2	6933.4	6843.8	6754.4	6687.3	6620.5	6573.5	6526.6	6494.4	6462.5
7132.7	10°	7023.4	6913.9	6813.1	6712.3	6632.2	6551.9	6499.5	6446.5	6416.1	6385.7
7284.9	12.5°	7198.9	7113.4	7009.0	6904.9	6802.5	6700.2	6632.5	6564.8	6530.8	6497.1
7532.3	15°	7510.0	7487.8	7397.2	7306.6	7160.9	7015.3	6912.4	6809.5	6762.2	6715.3
7740.5	17.5°	7810.4	7879.9	7806.7	7733.9	7541.0	7348.1	7196.5	7044.8	6975.0	6904.9
7776.0	20°	7922.0	8068.0	8034.2	8000.2	7779.7	7559.4	7373.4	7187.7	7098.4	7008.7
7576.8	22.5°	7766.7	7956.6	7977.1	7997.2	7786.6	7575.9	7384.5	7192.8	7098.7	7004.2
7219.3	25°	7406.2	7593.1	7662.9	7732.4	7559.7	7387.2	7216.9	7047.2	6965.3	6883.8
6816.7	27.5°	6966.5	7116.4	7194.0	7272.0	7148.9	7026.1	6894.0	6761.9	6707.1	6652.1
6412.2	30°	6536.5	6661.1	6724.3	6787.5	6693.9	6600.0	6505.5	6410.4	6382.4	6354.2
6002.1	32.5°	6121.2	6240.7	6310.8	6381.2	6295.2	6208.8	6133.3	6057.7	6039.4	6021.0
5603.3	35°	5721.3	5839.6	5923.8	6008.1	5946.7	5885.6	5815.8	5746.3	5718.3	5690.6
5222.7	37.5°	5340.3	5458.3	5562.4	5666.5	5638.2	5609.9	5545.9	5481.5	5430.6	5380.0
4866.7	40°	4980.4	5094.2	5213.9	5334.0	5340.9	5347.5	5293.1	5238.6	5164.6	5091.1
4540.4	42.5°	4648.2	4756.2	4885.6	5015.0	5049.6	5084.2	5038.2	4992.4	4900.7	4808.9
4260.6	45°	4362.9	4465.2	4599.4	4733.6	4783.3	4832.9	4791.4	4750.2	4645.2	4540.4
4037.0	47.5°	4137.2	4237.1	4369.5	4501.9	4559.1	4616.3	4587.4	4558.5	4465.2	4371.9
3874.5	50°	3969.0	4063.2	4181.7	4300.3	4373.7	4447.2	4445.3	4444.1	4369.5	4294.9
3767.7	52.5°	3854.3	3940.7	4051.1	4161.9	4248.8	4335.8	4351.5	4367.1	4306.3	4245.5
3687.0	55°	3780.3	3873.6	3970.5	4067.1	4159.2	4251.5	4273.2	4294.9	4241.9	4189.0
3578.1	57.5°	3687.6	3797.1	3892.8	3988.8	4081.8	4174.5	4196.5	4218.4	4164.9	4111.3
3431.2	60°	3557.0	3682.8	3780.0	3877.5	3970.8	4064.1	4088.1	4112.2	4059.9	4007.8
3224.5	62.5°	3371.0	3517.9	3621.7	3725.5	3811.0	3896.5	3919.6	3942.8	3895.5	3848.3
3003.3	65°	3160.4	3317.8	3417.1	3516.4	3591.6	3666.8	3690.6	3714.1	3668.6	3623.2
2798.7	67.5°	2943.7	3089.1	3183.2	3277.1	3342.1	3407.1	3430.3	3453.2	3411.4	3369.8
2594.6	70°	2722.2	2849.8	2931.1	3012.3	3071.0	3129.7	3151.9	3174.2	3140.2	3106.2
2351.8	72.5°	2452.3	2552.5	2625.9	2699.3	2756.8	2814.3	2840.8	2867.3	2839.0	2810.7
2059.0	75°	2133.6	2208.2	2274.7	2341.2	2393.6	2446.0	2473.7	2501.3	2487.5	2473.7
1749.0	77.5°	1809.8	1870.3	1927.5	1984.6	2039.7	2094.5	2120.4	2146.2	2127.0	2107.1
1396.3	80°	1446.9	1497.1	1545.3	1593.4	1635.3	1676.8	1711.1	1745.4	1737.0	1728.8
1050.2	82.5°	1046.0	1041.8	1025.0	1008.1	1097.2	1186.3	1244.6	1303.0	1299.4	1295.5
653.0	85°	631.4	609.4	562.7	516.1	599.5	683.1	755.3	827.6	821.5	815.5
303.3	87.5°	302.4	301.5	266.0	230.2	265.1	300.3	329.5	358.7	351.5	343.7
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P953240
 CATALOG NUMBER: GALN-SB6D-835-U-SLL

CANDELA DISTRIBUTION (continued):

215°		220°	225°	230°	235°	240°	245°	250°	255°	260°	265°
7842.3	0°	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3
7166.4	2.5°	7145.6	7120.0	7145.6	7166.4	7186.8	7209.1	7231.4	7260.0	7288.5	7324.1
6714.1	5°	6692.7	6671.6	6692.7	6714.1	6735.4	6763.4	6791.4	6830.8	6870.2	6926.8
6443.2	7.5°	6424.3	6409.8	6424.3	6443.2	6462.5	6494.4	6526.6	6573.5	6620.5	6687.3
6369.5	10°	6353.2	6346.6	6353.2	6369.5	6385.7	6416.1	6446.5	6499.5	6551.9	6632.2
6483.3	12.5°	6469.4	6467.0	6469.4	6483.3	6497.1	6530.8	6564.8	6632.5	6700.2	6802.5
6697.2	15°	6679.2	6677.7	6679.2	6697.2	6715.3	6762.2	6809.5	6912.4	7015.3	7160.9
6882.0	17.5°	6858.8	6855.2	6858.8	6882.0	6904.9	6975.0	7044.8	7196.5	7348.1	7541.0
6980.1	20°	6951.5	6942.5	6951.5	6980.1	7008.7	7098.4	7187.7	7373.4	7559.4	7779.7
6972.6	22.5°	6941.0	6927.4	6941.0	6972.6	7004.2	7098.7	7192.8	7384.5	7575.9	7786.6
6854.0	25°	6824.5	6807.1	6824.5	6854.0	6883.8	6965.3	7047.2	7216.9	7387.2	7559.7
6638.5	27.5°	6625.0	6620.5	6625.0	6638.5	6652.1	6707.1	6761.9	6894.0	7026.1	7148.9
6354.2	30°	6354.2	6358.7	6354.2	6354.2	6354.2	6382.4	6410.4	6505.5	6600.0	6693.9
6023.4	32.5°	6026.1	6030.7	6026.1	6023.4	6021.0	6039.4	6057.7	6133.3	6208.8	6295.2
5684.6	35°	5678.6	5675.6	5678.6	5684.6	5690.6	5718.3	5746.3	5815.8	5885.6	5946.7
5353.3	37.5°	5326.5	5311.4	5326.5	5353.3	5380.0	5430.6	5481.5	5545.9	5609.9	5638.2
5041.2	40°	4991.8	4962.3	4991.8	5041.2	5091.1	5164.6	5238.6	5293.1	5347.5	5340.9
4736.3	42.5°	4663.8	4616.3	4663.8	4736.3	4808.9	4900.7	4992.4	5038.2	5084.2	5049.6
4455.3	45°	4370.1	4315.3	4370.1	4455.3	4540.4	4645.2	4750.2	4791.4	4832.9	4783.3
4293.1	47.5°	4214.5	4161.9	4214.5	4293.1	4371.9	4465.2	4558.5	4587.4	4616.3	4559.1
4222.1	50°	4149.2	4098.7	4149.2	4222.1	4294.9	4369.5	4444.1	4445.3	4447.2	4373.7
4180.2	52.5°	4115.2	4068.6	4115.2	4180.2	4245.5	4306.3	4367.1	4351.5	4335.8	4248.8
4131.8	55°	4074.6	4032.5	4074.6	4131.8	4189.0	4241.9	4294.9	4273.2	4251.5	4159.2
4054.7	57.5°	3997.9	3954.2	3997.9	4054.7	4111.3	4164.9	4218.4	4196.5	4174.5	4081.8
3949.4	60°	3891.0	3845.9	3891.0	3949.4	4007.8	4059.9	4112.2	4088.1	4064.1	3970.8
3786.9	62.5°	3725.5	3671.4	3725.5	3786.9	3848.3	3895.5	3942.8	3919.6	3896.5	3811.0
3563.6	65°	3504.3	3457.7	3504.3	3563.6	3623.2	3668.6	3714.1	3690.6	3666.8	3591.6
3314.5	67.5°	3259.1	3216.9	3259.1	3314.5	3369.8	3411.4	3453.2	3430.3	3407.1	3342.1
3053.2	70°	3000.3	2952.1	3000.3	3053.2	3106.2	3140.2	3174.2	3151.9	3129.7	3071.0
2760.1	72.5°	2709.9	2663.2	2709.9	2760.1	2810.7	2839.0	2867.3	2840.8	2814.3	2756.8
2431.2	75°	2388.8	2344.3	2388.8	2431.2	2473.7	2487.5	2501.3	2473.7	2446.0	2393.6
2064.4	77.5°	2021.7	1986.1	2021.7	2064.4	2107.1	2127.0	2146.2	2120.4	2094.5	2039.7
1671.4	80°	1613.6	1546.8	1613.6	1671.4	1728.8	1737.0	1745.4	1711.1	1676.8	1635.3
1247.1	82.5°	1198.3	1155.6	1198.3	1247.1	1295.5	1299.4	1303.0	1244.6	1186.3	1097.2
777.6	85°	739.7	701.2	739.7	777.6	815.5	821.5	827.6	755.3	683.1	599.5
324.4	87.5°	304.5	285.9	304.5	324.4	343.7	351.5	358.7	329.5	300.3	265.1
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P953240
 CATALOG NUMBER: GALN-SB6D-835-U-SLL

CANDELA DISTRIBUTION (continued):

270°		275°	280°	285°	290°	295°	300°	305°	310°	315°	320°
7842.3	0°	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3
7359.3	2.5°	7404.7	7450.4	7495.9	7541.3	7593.1	7645.1	7702.6	7760.4	7831.7	7895.8
6983.1	5°	7056.5	7129.6	7210.3	7290.9	7382.1	7473.6	7582.9	7691.8	7816.7	7943.1
6754.4	7.5°	6843.8	6933.4	7035.2	7136.6	7256.9	7377.3	7522.1	7667.1	7828.7	8001.1
6712.3	10°	6813.1	6913.9	7023.4	7132.7	7253.0	7373.4	7526.3	7679.1	7852.8	8065.5
6904.9	12.5°	7009.0	7113.4	7198.9	7284.9	7364.4	7444.4	7569.0	7694.2	7855.8	8079.4
7306.6	15°	7397.2	7487.8	7510.0	7532.3	7521.5	7510.6	7570.2	7630.1	7759.5	8007.2
7733.9	17.5°	7806.7	7879.9	7810.4	7740.5	7609.3	7478.1	7456.5	7434.5	7514.2	7805.5
8000.2	20°	8034.2	8068.0	7922.0	7776.0	7547.9	7320.1	7217.8	7115.5	7136.6	7475.7
7997.2	22.5°	7977.1	7956.6	7766.7	7576.8	7316.2	7056.2	6904.9	6753.5	6712.3	7098.4
7732.4	25°	7662.9	7593.1	7406.2	7219.3	6985.2	6751.4	6576.8	6402.3	6291.0	6686.7
7272.0	27.5°	7194.0	7116.4	6966.5	6816.7	6624.7	6432.4	6263.9	6095.4	5959.9	6320.1
6787.5	30°	6724.3	6661.1	6536.5	6412.2	6252.7	6093.2	5959.0	5825.4	5719.2	6021.6
6381.2	32.5°	6310.8	6240.7	6121.2	6002.1	5874.5	5747.2	5668.0	5588.9	5541.6	5785.4
6008.1	35°	5923.8	5839.6	5721.3	5603.3	5506.4	5409.2	5387.3	5365.6	5385.2	5588.3
5666.5	37.5°	5562.4	5458.3	5340.3	5222.7	5153.1	5083.3	5107.4	5131.5	5203.1	5380.6
5334.0	40°	5213.9	5094.2	4980.4	4866.7	4816.4	4766.1	4820.6	4875.1	4984.9	5145.9
5015.0	42.5°	4885.6	4756.2	4648.2	4540.4	4499.2	4458.3	4530.5	4602.7	4741.2	4889.5
4733.6	45°	4599.4	4465.2	4362.9	4260.6	4225.7	4191.4	4261.5	4331.9	4465.8	4616.3
4501.9	47.5°	4369.5	4237.1	4137.2	4037.0	4004.8	3972.3	4031.3	4090.2	4205.5	4399.6
4300.3	50°	4181.7	4063.2	3969.0	3874.5	3823.6	3773.1	3825.1	3877.5	4011.4	4266.6
4161.9	52.5°	4051.1	3940.7	3854.3	3767.7	3691.8	3615.7	3667.1	3718.9	3906.1	4199.5
4067.1	55°	3970.5	3873.6	3780.3	3687.0	3579.3	3471.2	3552.8	3634.6	3916.6	4189.6
3988.8	57.5°	3892.8	3797.1	3687.6	3578.1	3461.9	3345.7	3464.9	3584.1	3927.1	4167.9
3877.5	60°	3780.0	3682.8	3557.0	3431.2	3329.5	3227.5	3382.2	3536.5	3894.0	4052.9
3725.5	62.5°	3621.7	3517.9	3371.0	3224.5	3159.8	3095.1	3288.0	3481.2	3812.8	3832.4
3516.4	65°	3417.1	3317.8	3160.4	3003.3	2978.6	2953.6	3159.2	3364.4	3617.2	3614.8
3277.1	67.5°	3183.2	3089.1	2943.7	2798.7	2806.5	2814.3	2985.2	3156.2	3298.2	3304.8
3012.3	70°	2931.1	2849.8	2722.2	2594.6	2621.7	2648.8	2770.4	2891.9	2938.6	2938.6
2699.3	72.5°	2625.9	2552.5	2452.3	2351.8	2391.2	2430.9	2514.3	2597.6	2597.0	2567.5
2341.2	75°	2274.7	2208.2	2133.6	2059.0	2097.2	2135.1	2199.5	2263.6	2275.0	2139.0
1984.6	77.5°	1927.5	1870.3	1809.8	1749.0	1787.5	1826.0	1877.5	1929.0	1935.0	1710.8
1593.4	80°	1545.3	1497.1	1446.9	1396.3	1428.8	1461.0	1504.4	1547.4	1548.3	1280.5
1008.1	82.5°	1025.0	1041.8	1046.0	1050.2	1073.1	1096.0	1117.1	1138.1	1125.5	896.8
516.1	85°	562.7	609.4	631.4	653.0	678.6	704.2	726.7	749.3	732.8	562.7
230.2	87.5°	266.0	301.5	302.4	303.3	308.2	313.0	322.0	331.0	310.0	239.2
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P953240
 CATALOG NUMBER: GALN-SB6D-835-U-SLL

CANDELA DISTRIBUTION (continued):

325°		330°	335°	340°	345°	350°	355°	360°
7842.3	0°	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3	7842.3
7962.0	2.5°	8028.2	8097.4	8166.7	8235.3	8304.2	8368.9	8433.6
8077.0	5°	8210.9	8354.1	8497.7	8640.0	8782.7	8925.6	9068.5
8188.0	7.5°	8374.9	8587.1	8799.2	9017.1	9235.0	9470.6	9706.5
8287.0	10°	8507.9	8765.8	9023.4	9311.1	9599.1	9897.3	10195.5
8329.5	12.5°	8579.5	8883.5	9187.4	9513.6	9839.8	10167.2	10495.0
8296.7	15°	8586.2	8936.1	9286.1	9640.0	9993.9	10335.5	10677.0
8153.7	17.5°	8501.9	8908.2	9314.4	9700.5	10086.6	10433.0	10779.3
7907.3	20°	8338.8	8831.1	9323.4	9747.7	10172.1	10532.3	10892.2
7618.1	22.5°	8137.8	8736.6	9335.5	9811.5	10287.3	10655.4	11023.1
7295.2	25°	7903.9	8643.3	9383.0	9927.1	10470.9	10831.1	11191.6
6999.9	27.5°	7679.8	8581.0	9482.3	10107.7	10732.7	11076.7	11420.3
6753.2	30°	7484.7	8551.8	9618.3	10341.5	11064.6	11396.5	11728.8
6540.4	32.5°	7295.2	8515.7	9735.7	10585.5	11435.4	11764.0	12092.9
6331.3	35°	7074.3	8447.7	9821.8	10863.6	11905.4	12220.5	12535.3
6085.1	37.5°	6789.6	8331.3	9872.9	11175.1	12477.2	12878.6	13280.1
5791.4	40°	6436.9	8170.9	9905.1	11570.5	13235.5	13820.5	14405.6
5467.3	42.5°	6045.1	8005.4	9966.2	12087.8	14209.3	15053.8	15898.2
5123.0	45°	5629.8	7851.6	10073.7	12768.5	15463.3	16602.3	17741.4
4850.7	47.5°	5301.8	7724.6	10147.4	13493.7	16840.1	18443.4	20046.5
4669.8	50°	5073.1	7586.2	10099.2	14166.6	18234.0	20651.1	23067.8
4550.7	52.5°	4902.2	7352.3	9802.8	14603.6	19404.0	22970.0	26536.1
4464.3	55°	4739.1	6964.7	9190.4	14507.3	19823.8	25026.0	30228.5
4362.0	57.5°	4556.1	6418.2	8280.1	13829.6	19379.3	26483.1	33586.9
4205.5	60°	4358.1	5708.7	7059.2	12568.4	18077.5	26847.2	35616.7
3933.5	62.5°	4034.9	4859.4	5684.0	10863.0	16042.0	25314.0	34586.0
3662.6	65°	3710.5	4095.4	4480.3	9123.0	13766.1	23144.6	32523.1
3278.3	67.5°	3251.6	3361.1	3470.3	7418.5	11366.8	20562.9	29759.0
2814.9	70°	2690.9	2659.9	2628.6	5841.1	9053.5	17745.9	26438.3
2392.1	72.5°	2216.4	2121.9	2027.7	4465.5	6903.3	14692.0	22481.0
1942.2	75°	1745.4	1659.9	1574.5	3241.0	4907.6	11191.3	17475.0
1519.7	77.5°	1328.6	1270.2	1212.1	2196.2	3180.2	7832.9	12485.6
1118.9	80°	957.0	932.9	908.8	1415.0	1921.4	5046.6	8171.8
777.6	82.5°	658.4	653.6	649.4	870.3	1091.8	2920.8	4750.2
475.5	85°	388.2	390.6	392.7	465.2	538.1	1313.9	2090.0
203.4	87.5°	167.9	170.0	172.1	192.9	213.7	430.3	647.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)