

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P944072

Luminaire Tested: **GALN-SB8D-835-U-SL4**

Issue Date: 1/21/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P944072  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2405-108-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: GALN-SB8D-835-U-SL4  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(8) 80 CRI, 3500K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND TYPE IV SPILL  
LIGHT ELIMINATOR OPTICS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 75656 lumens  
Efficiency: N/A  
Efficacy: 129.3 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')  
IES Classification: Type IV - Medium  
BUG Rating: B5 - U0 - G5  
  
Input Watts (W): 584.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P944072  
 CATALOG NUMBER: GALN-SB8D-835-U-SL4

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 17.9 fc  
 Type IV - Medium - N/A

REPORT NUMBER: P944072  
CATALOG NUMBER: GALN-SB8D-835-U-SL4

### Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral      - - - Horizontal Cone Through 75-Deg Vertical

REPORT NUMBER: P944072

CATALOG NUMBER: GALN-SB8D-835-U-SL4

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	23440.8	0.0	23440.8
	% Fixture	31.0	0.0	31.0
<b>Street Side</b>	Lumens	52215.2	0.0	52215.2
	% Fixture	69.0	0.0	69.0
<b>Total</b>	Lumens	75656.0	0.0	75656.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	863.6	1.1
10°-20°	2899.4	3.8
20°-30°	5294.1	7.0
30°-40°	7508.5	9.9
40°-50°	10138.7	13.4
50°-60°	13639.2	18.0
60°-70°	17311.3	22.9
70°-80°	15711.1	20.8
80°-90°	2290.2	3.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	75656.0	100.0
0°-180°	75656.0	100.0

**Coefficient of Utilization**



REPORT NUMBER: P944072


CATALOG NUMBER: GALN-SB8D-835-U-SL4

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	3979.6	5.3			
FM (30°-60°)	18571.9	24.5			
FH (60°-80°)	27688.9	36.6			G5
FVH (80°-90°)	1974.9	2.6			G5
BL (0°-30°)	5077.5	6.7	B5		
BM (30°-60°)	12714.5	16.8	B5		
BH (60°-80°)	5333.5	7.0	B5		G5
BVH (80°-90°)	315.3	0.4			G3/500
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B5-U0-G5**

Type IV Medium



REPORT NUMBER: P944072  
 CATALOG NUMBER: GALN-SB8D-835-U-SL4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	40°	45°	55°	65°	75°
0°	8651.4	8651.4	8651.4	8651.4	8651.4	8651.4	8651.4	8651.4	8651.4	8651.4
2.5°	8518.9	8567.1	8555.1	8539.0	8539.0	8543.0	8539.0	8567.1	8595.2	8623.3
5°	8607.2	8655.4	8631.3	8611.2	8595.2	8591.2	8579.1	8575.1	8591.2	8627.3
7.5°	8779.8	8827.9	8791.8	8755.7	8723.6	8707.5	8691.5	8667.4	8655.4	8675.4
10°	8972.4	9020.5	8976.4	8912.2	8860.0	8840.0	8823.9	8799.8	8783.8	8795.8
12.5°	9165.0	9213.1	9153.0	9064.7	8996.5	8984.4	8964.4	8956.3	8952.3	8948.3
15°	9345.6	9385.7	9309.4	9205.1	9132.9	9112.8	9092.8	9104.8	9124.9	9148.9
17.5°	9486.0	9526.1	9413.8	9277.3	9209.1	9201.1	9189.1	9229.2	9285.4	9345.6
20°	9614.4	9654.5	9510.1	9325.5	9245.2	9245.2	9249.3	9333.5	9413.8	9502.1
22.5°	9795.0	9827.1	9650.5	9397.7	9281.4	9289.4	9321.5	9405.8	9506.1	9626.4
25°	10063.8	10087.9	9871.2	9534.2	9401.7	9425.8	9453.9	9494.0	9590.3	9730.8
27.5°	10497.2	10517.3	10232.4	9774.9	9574.3	9614.4	9654.5	9626.4	9670.6	9791.0
30°	11107.1	11119.2	10758.0	10152.1	9867.2	9887.3	9895.3	9778.9	9694.7	9791.0
32.5°	11829.4	11825.4	11396.0	10609.6	10200.3	10180.2	10112.0	9883.3	9686.6	9770.9
35°	12949.0	12904.8	12351.1	11251.6	10577.5	10453.1	10292.6	9999.6	9726.8	9750.8
37.5°	14802.8	14666.4	13900.0	12302.9	11139.2	10822.2	10585.5	10188.2	9815.0	9742.8
40°	16893.4	16720.9	15878.2	13743.5	11981.9	11472.3	11091.1	10457.1	9959.5	9778.9
42.5°	19373.3	19128.5	18221.6	15440.8	13049.3	12310.9	11737.1	10798.2	10172.2	9895.3
45°	22418.9	22093.9	20809.8	17354.9	14393.5	13410.4	12644.0	11315.8	10497.2	10120.0
47.5°	25496.6	25576.9	23751.1	19545.8	16006.6	14766.7	13779.6	12094.3	10970.7	10481.2
50°	28767.0	28823.2	26676.4	21973.5	17836.4	16299.6	15055.6	12965.0	11628.8	10994.8
52.5°	31319.1	31327.1	29332.8	24513.5	19742.4	17984.9	16432.0	13960.2	12391.2	11676.9
55°	32916.1	32896.1	31194.7	26917.1	21933.4	19754.5	17956.8	15091.7	13322.1	12479.5
57.5°	34075.8	34015.6	32478.7	28983.7	24268.8	21845.1	19682.3	16375.8	14421.6	13434.5
60°	34517.2	34481.1	33349.5	30769.3	26724.5	24156.4	21672.6	17812.3	15669.6	14562.1
62.5°	34685.7	34753.9	34204.2	32498.8	29352.8	26716.5	23859.5	19529.8	17074.0	15838.1
65°	35279.6	35404.0	35291.6	34762.0	32322.2	29714.0	26760.6	21572.2	18606.9	17206.4
67.5°	36455.3	36579.7	36627.9	37470.5	35949.7	33449.8	30380.1	24116.3	20400.5	18626.9
70°	36427.2	36391.1	37241.8	39625.3	40492.1	38622.2	35259.5	27246.2	22539.3	19806.6
72.5°	33156.9	32868.0	34878.3	39601.3	44272.0	44023.2	41218.4	31282.9	24385.1	19951.1
75°	24874.7	24104.2	27655.5	35688.9	44902.0	47088.9	45006.4	33786.9	23947.7	17627.8
77.5°	10637.6	9863.2	14048.4	26419.6	40187.1	44019.2	41531.4	29477.2	19116.5	11656.9
80°	2784.8	2780.8	4245.4	11977.9	27330.4	32506.8	28518.2	19036.2	10922.5	4165.2
82.5°	1151.6	1123.6	1560.9	4658.7	13354.2	18241.7	14887.1	8490.9	3944.5	1127.6
85°	429.4	425.3	758.4	1609.1	4710.9	7523.8	5445.2	2170.9	983.1	549.7
87.5°	120.4	116.4	164.5	557.8	1147.6	1741.5	930.9	357.1	276.9	216.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P944072  
 CATALOG NUMBER: GALN-SB8D-835-U-SL4

**CANDELA DISTRIBUTION (continued):**

85°		90°	95°	105°	115°	125°	135°	145°	155°	165°	175°
8651.4	0°	8651.4	8651.4	8651.4	8651.4	8651.4	8651.4	8651.4	8651.4	8651.4	8651.4
8667.4	2.5°	8679.5	8699.5	8735.6	8763.7	8799.8	8840.0	8896.1	8932.3	8968.4	8992.4
8687.5	5°	8715.6	8759.7	8852.0	8944.3	9052.6	9153.0	9269.3	9353.6	9421.8	9441.9
8759.7	7.5°	8795.8	8868.0	9024.5	9181.0	9353.6	9518.1	9686.6	9831.1	9947.5	9991.6
8888.1	10°	8936.3	9032.6	9253.3	9474.0	9702.7	9955.5	10172.2	10380.8	10545.4	10613.6
9040.6	12.5°	9112.8	9233.2	9522.1	9827.1	10144.1	10493.2	10774.1	11030.9	11235.5	11327.8
9253.3	15°	9341.5	9498.0	9867.2	10276.5	10742.0	11227.5	11584.6	11869.5	12098.3	12210.6
9474.0	17.5°	9590.3	9799.0	10264.5	10882.4	11548.5	12186.5	12603.9	12812.5	13049.3	13157.6
9678.6	20°	9831.1	10087.9	10754.0	11652.9	12539.7	13217.8	13554.9	13611.1	13627.1	13639.1
9871.2	22.5°	10079.9	10425.0	11368.0	12623.9	13574.9	14044.4	14092.6	13851.8	13514.7	13358.3
10059.8	25°	10352.7	10810.2	12170.5	13695.3	14465.8	14521.9	14152.8	13566.9	12928.9	12636.0
10212.3	27.5°	10617.6	11255.6	13133.5	14718.6	15107.8	14614.2	13819.7	12989.1	12218.6	11909.7
10320.6	30°	10882.4	11765.2	14196.9	15613.4	15400.7	14385.5	13294.0	12367.1	11592.7	11267.6
10416.9	32.5°	11151.3	12359.1	15420.8	16259.4	15348.5	13900.0	12640.0	11668.9	10986.8	10645.7
10501.2	35°	11456.2	13089.4	16580.4	16612.5	14999.4	13185.7	11777.3	10834.3	10240.4	9967.5
10601.5	37.5°	11853.5	14016.3	17603.7	16700.8	14389.5	12138.4	10705.9	9847.1	9357.6	9233.2
10750.0	40°	12347.1	15131.9	18386.2	16560.4	13486.7	10866.4	9534.2	8848.0	8571.1	8599.2
10950.6	42.5°	12989.1	16379.8	18935.9	16199.2	12230.7	9554.2	8506.9	8201.9	8334.4	8446.7
11251.6	45°	13823.7	17675.9	19277.0	15585.3	10810.2	8442.7	7901.0	7973.2	8073.5	8085.6
11737.1	47.5°	14891.1	18988.1	19501.7	14658.4	9361.6	7660.2	7515.8	7531.8	7511.8	7427.5
12463.4	50°	16223.3	20264.1	19702.3	13430.5	8129.7	7170.7	6978.1	6921.9	6645.0	6372.2
13430.5	52.5°	17740.1	21435.8	19786.6	11905.7	7170.7	6761.4	6448.4	6095.3	5577.6	5493.4
14646.3	55°	19425.4	22519.2	19569.9	10031.7	6364.1	6235.7	5762.2	5336.9	5280.7	5208.5
16247.4	57.5°	21439.8	23686.9	19128.5	7941.1	5537.5	5621.8	5160.3	5208.5	5108.2	4995.8
18305.9	60°	23642.8	24894.7	18354.1	6035.1	4682.8	4855.4	5003.8	4999.8	4971.7	4879.4
20476.8	62.5°	25625.1	25689.3	16829.2	4622.6	3932.4	4261.5	4666.8	4662.7	4638.7	4586.5
22743.9	65°	26804.8	25568.9	14285.2	3639.5	3314.5	3771.9	4209.3	4241.4	4245.4	4241.4
24449.3	67.5°	26596.1	24160.4	10794.1	2897.2	2804.9	3274.4	3755.9	3800.0	3832.1	3840.1
24666.0	70°	24236.7	21066.6	7038.3	2311.3	2351.4	2837.0	3326.5	3370.7	3398.8	3430.9
21403.7	72.5°	18891.8	15489.0	4028.7	1869.9	1954.2	2459.8	2901.2	2953.3	2969.4	3029.6
14895.1	75°	11512.4	9108.8	2174.9	1472.7	1605.1	2102.7	2479.8	2540.0	2568.1	2640.4
7315.1	77.5°	5473.3	3944.5	1239.9	1147.6	1292.1	1717.4	2094.6	2162.8	2086.6	2126.7
2018.4	80°	1849.9	1464.6	782.5	874.8	987.1	1340.2	1677.3	1745.5	1585.0	1577.0
670.1	82.5°	646.0	593.9	497.6	581.8	638.0	959.0	1268.0	1356.3	1179.7	1175.7
301.0	85°	252.8	240.8	276.9	317.0	381.2	589.9	834.6	878.8	726.3	585.9
88.3	87.5°	52.2	56.2	68.2	72.2	116.4	204.6	301.0	369.2	292.9	248.8
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END O

180°  
8651.4  
8976.4  
9449.9  
9995.6  
10617.6  
11327.8  
12202.6  
13153.6  
13671.2  
13402.4  
12680.1  
11945.8  
11303.8  
10689.8  
10027.7  
9321.5  
8695.5  
8551.0  
8165.8  
7491.7  
6408.3  
5521.5  
5220.5  
4975.7  
4847.3  
4566.4  
4241.4  
3848.2  
3446.9  
3053.7  
2648.4  
2094.6  
1560.9  
1119.5  
577.8  
228.7  
0.0

F REPORT)