

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P956095

Luminaire Tested: **GALN-SB8D-835-U-SLL-HSS**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P956095
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GALN-SB8D-835-U-SLL-HSS
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(8) 80 CRI, 3500K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR LEFT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 58249 lumens
Efficiency: N/A
Efficacy: 99.6 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B4 - U0 - G5


Input Watts (W): 584.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P956095
 CATALOG NUMBER: GALN-SB8D-835-U-SLL-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 21.2 fc
 Type IV - Short - N/A

REPORT NUMBER: P956095
CATALOG NUMBER: GALN-SB8D-835-U-SLL-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P956095
 CATALOG NUMBER: GALN-SB8D-835-U-SLL-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	11578.1	0.0	11578.1
	% Fixture	19.9	0.0	19.9
Street Side	Lumens	46670.9	0.0	46670.9
	% Fixture	80.1	0.0	80.1
Total	Lumens	58249.0	0.0	58249.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	794.1	1.4
10°-20°	2380.4	4.1
20°-30°	3506.9	6.0
30°-40°	4505.4	7.7
40°-50°	7286.5	12.5
50°-60°	12777.6	21.9
60°-70°	15988.3	27.4
70°-80°	9342.8	16.0
80°-90°	1666.9	2.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	58249.0	100.0
0°-180°	58249.0	100.0

Coefficient of Utilization



REPORT NUMBER: P956095


CATALOG NUMBER: GALN-SB8D-835-U-SLL-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	3897.5	6.7			
FM (30°-60°)	18279.2	31.4			
FH (60°-80°)	22905.3	39.3			G5
FVH (80°-90°)	1588.8	2.7			G5
BL (0°-30°)	2783.9	4.8	B4/5000		
BM (30°-60°)	6290.3	10.8	B4/8500		
BH (60°-80°)	2425.8	4.2	B3/2500		G3/2500
BVH (80°-90°)	78.1	0.1			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G5

Type IV Short



REPORT NUMBER: P956095
 CATALOG NUMBER: GALN-SB8D-835-U-SLL-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	8065.6	8065.6	8065.6	8065.6	8065.6	8065.6	8065.6	8065.6	8065.6	8065.6
2.5°	9036.7	9104.9	9257.4	9337.7	9462.1	9470.1	9470.1	9361.7	9357.7	9137.0
5°	10100.1	10260.6	10621.7	10994.9	11075.2	11095.2	11055.1	10838.4	10677.9	10248.6
7.5°	11155.4	11464.4	12014.2	12511.7	12672.3	12672.3	12576.0	12222.8	11893.8	11271.8
10°	12030.2	12419.5	13165.8	13723.6	13908.2	13868.1	13671.4	13226.0	12772.6	12018.2
12.5°	12608.1	13045.4	13864.0	14313.5	14502.1	14397.7	14173.0	13739.6	13262.1	12467.6
15°	12897.0	13354.4	14064.7	14301.4	14249.3	14140.9	14112.8	13904.2	13543.0	12800.7
17.5°	13021.4	13446.7	13940.3	13791.8	13350.4	13266.1	13547.0	13811.9	13723.6	13089.6
20°	13137.7	13494.9	13643.3	12985.3	12214.8	12138.6	12676.3	13430.7	13815.9	13358.4
22.5°	13298.2	13518.9	13214.0	12134.5	11303.9	11127.3	11721.2	12856.8	13844.0	13699.5
25°	13518.9	13579.1	12740.5	11328.0	10493.3	10316.8	10870.5	12218.8	13795.8	14068.7
27.5°	13783.8	13659.4	12287.0	10653.8	9847.3	9682.8	10236.5	11604.9	13659.4	14437.9
30°	14128.9	13763.7	11837.6	10132.2	9385.8	9265.4	9799.1	11075.2	13490.9	14907.4
32.5°	14478.0	13807.9	11420.3	9827.2	9281.5	9325.6	9763.0	10790.3	13306.3	15356.8
35°	14855.2	13948.3	11215.6	10128.2	10152.3	10537.5	10718.0	11055.1	13278.2	15966.7
37.5°	15368.8	14261.3	11460.4	11624.9	12459.6	13258.1	13109.6	12351.2	13603.2	16877.6
40°	16107.2	14811.1	12527.8	14173.0	15886.5	17182.6	16616.8	14706.7	14598.4	18189.8
42.5°	17182.6	15685.8	14421.8	17286.9	20192.1	22326.9	20810.1	17744.4	16339.9	20063.7
45°	18771.6	17102.3	16713.1	20573.4	25501.0	28863.7	25709.7	20982.7	18779.7	22900.8
47.5°	20974.6	19184.9	18859.9	24036.4	31953.5	36303.3	31142.9	23984.2	21556.5	26769.0
50°	23899.9	21989.9	20894.4	27824.4	39028.0	43887.4	36572.2	26881.4	24738.6	31496.1
52.5°	27760.2	25902.3	23265.9	31431.9	46303.1	51311.0	42025.5	29425.5	28687.1	36981.5
55°	33024.9	31789.0	26508.2	34874.8	53574.2	58778.7	47266.2	31825.1	33903.7	43498.2
57.5°	39557.7	40440.5	31183.1	38867.5	60111.0	66475.2	52530.9	35179.8	40677.2	50785.3
60°	43771.1	51945.0	40135.5	44770.2	67538.6	75178.8	59745.8	41560.0	47795.8	53397.6
62.5°	42751.8	55604.6	50857.6	52306.2	74368.3	81506.9	66816.3	47968.4	49136.1	49549.4
65°	39625.9	52651.3	48670.6	53770.8	76097.7	81864.1	68706.3	47141.8	41680.4	40452.5
67.5°	35324.2	49148.1	43474.1	49886.5	72971.8	76872.2	65187.1	41700.5	32210.3	30356.4
70°	30681.5	45271.8	40063.3	45528.6	67012.9	68172.6	59204.1	36676.5	23691.3	20501.1
72.5°	26275.5	41235.0	37727.9	41062.4	59063.6	56664.0	51415.3	32234.4	17250.8	14787.0
75°	21769.2	35280.1	34401.3	35757.6	48610.4	44633.8	42719.7	26688.8	13539.0	10698.0
77.5°	16797.4	27567.6	29590.0	28635.0	34216.7	33153.3	33113.2	20055.7	9891.4	7138.7
80°	11496.5	19213.0	23117.4	20200.2	22206.5	21664.8	24939.2	13454.7	7174.8	4297.7
82.5°	6757.5	11697.2	16091.1	9779.1	12279.0	12604.0	14851.2	6544.8	4221.4	991.1
85°	2740.7	4618.7	6292.0	3828.2	5922.8	4995.9	5637.9	1837.8	1175.7	24.1
87.5°	690.2	1476.7	1035.3	429.4	686.2	630.0	497.6	224.7	48.2	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P956095
 CATALOG NUMBER: GALN-SB8D-835-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

90°		95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
8065.6	0°	8065.6	8065.6	8065.6	8065.6	8065.6	8065.6	8065.6	8065.6	8065.6	8065.6
9112.9	2.5°	8956.5	8864.2	8635.4	8406.7	8222.1	7973.3	7808.8	7612.2	7423.6	7255.0
10156.3	5°	9903.5	9598.5	9181.2	8800.0	8410.7	8033.5	7660.3	7267.1	6905.9	6685.2
11039.1	7.5°	10673.9	10136.2	9582.4	9096.9	8627.4	8186.0	7692.4	7214.9	6649.1	6348.2
11713.2	10°	11247.7	10541.5	9815.2	9257.4	8783.9	8354.5	7937.2	7455.7	6773.5	6396.3
12122.5	12.5°	11624.9	10786.3	9935.6	9297.5	8767.9	8434.8	8250.2	8061.6	7383.5	6942.1
12423.5	15°	11885.8	10958.8	10019.8	9205.2	8555.2	8310.4	8495.0	8711.7	8278.3	7768.7
12736.5	17.5°	12170.7	11183.5	10055.9	8956.5	8141.9	8037.5	8515.1	9016.6	8996.6	8491.0
13033.4	20°	12471.6	11380.2	10031.9	8555.2	7640.3	7732.6	8342.5	8924.4	9169.1	8896.3
13374.5	22.5°	12780.6	11568.8	9939.6	8033.5	7170.8	7459.7	8069.6	8579.3	8868.2	8783.9
13791.8	25°	13169.8	11833.6	9803.1	7471.7	6781.5	7182.8	7752.6	8165.9	8366.6	8362.6
14241.2	27.5°	13635.3	12186.7	9730.9	7018.3	6504.7	6869.8	7375.4	7744.6	7885.0	7885.0
14799.0	30°	14177.0	12604.0	9650.7	6721.4	6344.2	6544.8	6938.0	7299.2	7439.6	7439.6
15409.0	32.5°	14778.9	13005.3	9458.0	6540.8	6223.8	6227.8	6476.6	6805.6	6974.2	6998.2
16171.4	35°	15501.2	13434.7	9036.7	6396.3	6083.3	5918.8	6039.2	6312.1	6512.7	6564.9
17258.8	37.5°	16448.3	13960.3	8434.8	6183.6	5866.6	5593.8	5621.9	5830.5	6051.2	6131.5
18759.6	40°	17720.3	14578.3	7808.8	5878.7	5561.7	5236.6	5224.6	5377.1	5593.8	5682.1
20790.0	42.5°	19401.6	15320.7	7210.9	5585.7	5192.5	4859.4	4839.4	4959.8	5148.4	5240.6
23470.6	45°	21552.5	16231.6	6697.3	5357.0	4831.3	4502.3	4494.3	4594.6	4759.1	4855.4
26901.5	47.5°	24542.0	17142.5	6348.2	5236.6	4546.4	4209.4	4225.4	4313.7	4462.2	4530.4
31343.6	50°	28438.3	17419.3	6171.6	5236.6	4394.0	3948.5	4028.8	4101.0	4213.4	4253.5
36668.5	52.5°	32178.2	16504.4	6011.1	5268.7	4414.0	3727.8	3900.4	3952.6	4048.9	4064.9
41604.2	55°	34012.0	14189.1	5790.4	5276.8	4538.4	3539.2	3796.1	3892.4	3928.5	3924.5
44469.3	57.5°	33382.0	11472.4	5417.2	5244.7	4622.7	3418.9	3667.7	3852.2	3876.3	3840.2
43923.5	60°	31171.0	8446.8	5132.3	5007.9	4590.6	3382.7	3471.0	3764.0	3800.1	3751.9
39718.2	62.5°	27463.2	5862.6	4911.6	4486.3	4450.1	3370.7	3162.0	3571.3	3659.6	3591.4
31925.4	65°	21620.7	4141.2	4229.4	3932.5	4145.2	3306.5	2841.0	3338.6	3459.0	3354.7
23161.6	67.5°	14630.5	2989.5	3426.9	3563.3	3651.6	3162.0	2608.3	3073.8	3234.3	3097.8
14863.2	70°	7901.1	2098.7	2263.2	3001.5	3101.9	2913.3	2399.6	2804.9	2989.5	2841.0
10565.6	72.5°	4666.8	1508.8	1585.0	2411.7	2584.2	2564.1	2166.9	2491.9	2716.6	2540.1
7291.2	75°	2572.2	1019.2	1131.6	1749.6	2098.7	1978.3	1861.9	2110.7	2339.4	2166.9
4570.5	77.5°	1151.7	609.9	786.5	1147.6	1649.2	1356.3	1440.6	1645.2	1857.9	1677.3
2544.1	80°	445.4	341.1	521.7	626.0	1199.8	750.4	926.9	1211.8	1364.3	1219.9
553.8	82.5°	56.2	152.5	224.7	244.8	698.2	397.3	537.7	762.4	750.4	650.1
0.0	85°	0.0	28.1	32.1	16.1	301.0	144.5	176.6	248.8	232.7	176.6
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	8.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P956095
 CATALOG NUMBER: GALN-SB8D-835-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

185°		195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
8065.6	0°	8065.6	8065.6	8065.6	8065.6	8065.6	8065.6	8065.6	8065.6	8065.6	8065.6
7222.9	2.5°	7026.3	6881.9	6809.6	6749.4	6805.6	6837.7	6837.7	6974.2	7054.4	7086.5
6544.8	5°	6191.7	5922.8	5742.2	5633.9	5670.0	5710.1	5754.3	5926.8	6043.2	6119.4
6075.3	7.5°	5533.6	5124.3	4871.5	4739.1	4759.1	4787.2	4823.3	4991.9	5108.2	5208.5
5987.0	10°	5208.5	4630.7	4297.7	4137.1	4109.1	4093.0	4081.0	4181.3	4269.6	4349.8
6348.2	12.5°	5224.6	4418.0	4012.7	3816.1	3731.9	3635.5	3559.3	3575.4	3631.5	3731.9
6994.2	15°	5429.2	4349.8	3864.3	3619.5	3479.1	3366.7	3274.4	3254.3	3274.4	3290.5
7732.6	17.5°	5706.1	4341.8	3735.9	3430.9	3286.4	3194.1	3109.9	3081.8	3085.8	3105.9
8222.1	20°	5926.8	4317.7	3591.4	3250.3	3121.9	3041.7	2957.4	2929.3	2937.3	2941.3
8270.3	22.5°	6043.2	4281.6	3430.9	3069.8	2961.4	2881.2	2804.9	2800.9	2800.9	2825.0
8009.4	25°	6043.2	4205.4	3286.4	2897.2	2800.9	2728.7	2636.4	2652.4	2660.5	2692.6
7604.2	27.5°	5898.7	4060.9	3170.1	2748.7	2648.4	2576.2	2491.9	2512.0	2524.0	2560.1
7202.9	30°	5714.2	3888.4	3037.6	2608.3	2491.9	2439.8	2367.5	2375.5	2391.6	2431.7
6829.7	32.5°	5517.5	3683.7	2929.3	2467.8	2351.5	2311.3	2231.1	2243.1	2259.2	2303.3
6460.5	35°	5300.8	3442.9	2800.9	2339.4	2223.1	2191.0	2098.7	2106.7	2130.8	2178.9
6063.3	37.5°	5072.1	3246.3	2672.5	2215.0	2094.7	2062.6	1966.2	1974.3	2002.4	2058.5
5645.9	40°	4847.4	3053.7	2536.1	2082.6	1962.2	1934.1	1829.8	1837.8	1869.9	1930.1
5224.6	42.5°	4602.6	2905.2	2359.5	1946.2	1817.8	1789.7	1693.4	1705.4	1741.5	1801.7
4835.4	45°	4309.7	2808.9	2162.9	1817.8	1673.3	1645.2	1556.9	1581.0	1621.2	1681.3
4502.3	47.5°	4008.7	2768.8	1998.3	1681.3	1524.8	1500.8	1428.5	1468.7	1512.8	1561.0
4217.4	50°	3719.8	2716.6	1829.8	1552.9	1396.4	1372.4	1324.2	1376.4	1420.5	1464.7
4012.7	52.5°	3390.8	2604.3	1677.3	1440.6	1288.1	1280.1	1256.0	1304.1	1344.3	1384.4
3836.2	55°	3049.7	2423.7	1544.9	1340.3	1195.8	1203.8	1191.8	1231.9	1264.0	1300.1
3675.7	57.5°	2752.7	2195.0	1440.6	1231.9	1115.5	1139.6	1123.6	1143.6	1163.7	1207.8
3483.1	60°	2451.8	1922.1	1324.2	1103.5	1035.3	1063.4	1019.2	1015.2	1023.3	1035.3
3198.2	62.5°	2046.5	1637.2	1179.7	991.1	947.0	959.0	874.8	810.6	810.6	822.6
2800.9	65°	1645.2	1372.4	1019.2	862.7	826.6	818.6	698.2	609.9	601.9	638.0
2339.4	67.5°	1352.3	1139.6	858.7	718.3	694.2	702.2	614.0	525.7	517.6	557.8
1906.1	70°	1119.6	918.9	686.2	553.8	577.8	614.0	525.7	441.4	429.4	465.5
1548.9	72.5°	890.8	718.3	525.7	409.3	477.5	521.7	429.4	349.1	341.1	373.2
1195.8	75°	654.1	513.6	357.1	296.9	369.2	409.3	313.0	248.8	236.8	264.8
798.5	77.5°	405.3	288.9	224.7	176.6	252.8	272.9	164.5	144.5	140.4	160.5
485.5	80°	188.6	124.4	108.3	60.2	92.3	108.3	68.2	76.2	80.3	96.3
244.8	82.5°	52.2	20.1	4.0	0.0	0.0	32.1	16.1	32.1	40.1	60.2
20.1	85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	8.0	20.1	36.1
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	16.1
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P956095
 CATALOG NUMBER: GALN-SB8D-835-U-SLL-HSS

CANDELA DISTRIBUTION (continued):

285°		295°	305°	315°	325°	335°	345°	355°	360°
8065.6	0°	8065.6	8065.6	8065.6	8065.6	8065.6	8065.6	8065.6	8065.6
7311.2	2.5°	7479.8	7640.3	7897.1	8161.9	8422.8	8687.6	8944.4	9036.7
6468.5	5°	6785.6	7154.7	7664.3	8210.1	8771.9	9341.7	9863.3	10100.1
5597.8	7.5°	6011.1	6540.8	7307.2	8161.9	9056.8	9951.6	10774.2	11155.4
4735.0	10°	5184.5	5854.6	6729.4	7885.0	9169.1	10405.1	11536.6	12030.2
3976.6	12.5°	4398.0	5100.2	6067.3	7451.7	9080.8	10665.9	12026.2	12608.1
3442.9	15°	3739.9	4361.9	5405.2	6938.0	8795.9	10681.9	12258.9	12897.0
3146.0	17.5°	3246.3	3651.6	4731.0	6368.2	8422.8	10533.5	12339.2	13021.4
2985.5	20°	3001.5	3113.9	3856.3	5637.9	8073.6	10393.0	12419.5	13137.7
2857.1	22.5°	2857.1	2885.2	3154.0	4694.9	7656.3	10348.9	12559.9	13298.2
2740.7	25°	2740.7	2748.7	2821.0	3719.8	7018.3	10320.8	12776.6	13518.9
2620.3	27.5°	2624.3	2624.3	2664.5	2997.5	6151.5	10200.4	13057.5	13783.8
2499.9	30°	2508.0	2508.0	2536.1	2652.4	5136.3	9963.7	13394.6	14128.9
2379.6	32.5°	2387.6	2387.6	2411.7	2495.9	4101.0	9666.7	13703.5	14478.0
2255.2	35°	2267.2	2259.2	2291.3	2379.6	3262.4	9289.5	14012.5	14855.2
2130.8	37.5°	2138.8	2134.8	2166.9	2267.2	2816.9	8852.1	14245.3	15368.8
2006.4	40°	2002.4	2002.4	2038.5	2146.8	2688.5	8302.4	14614.4	16107.2
1878.0	42.5°	1878.0	1869.9	1910.1	2042.5	2592.2	7776.7	15276.5	17182.6
1761.6	45°	1757.6	1741.5	1777.6	1942.2	2423.7	7592.1	16512.5	18771.6
1649.2	47.5°	1645.2	1605.1	1637.2	1821.8	2271.2	8282.3	18534.9	20974.6
1548.9	50°	1552.9	1476.7	1504.8	1701.4	2154.8	9779.1	21159.2	23899.9
1456.6	52.5°	1456.6	1356.3	1372.4	1552.9	2050.5	11203.6	24004.3	27760.2
1364.3	55°	1356.3	1244.0	1252.0	1404.5	1902.0	11416.3	26781.1	33024.9
1260.0	57.5°	1244.0	1139.6	1139.6	1268.0	1793.7	9895.4	28915.9	39557.7
1131.6	60°	1119.6	1051.3	1031.3	1159.7	1890.0	6982.2	29164.6	43771.1
967.1	62.5°	983.1	947.0	918.9	1055.4	1962.2	4137.1	27162.3	42751.8
762.4	65°	826.6	818.6	798.5	1159.7	1653.3	2443.8	23318.1	39625.9
650.1	67.5°	694.2	682.2	682.2	1215.9	1256.0	1536.9	18217.9	35324.2
553.8	70°	597.9	553.8	553.8	918.9	762.4	1063.4	12720.4	30681.5
457.5	72.5°	501.6	453.4	421.3	734.3	569.8	778.5	7949.3	26275.5
349.1	75°	401.3	365.2	325.0	485.5	425.4	589.9	4618.7	21769.2
220.7	77.5°	288.9	272.9	228.7	357.1	309.0	425.4	2748.7	16797.4
136.4	80°	148.5	152.5	144.5	204.7	208.7	288.9	1565.0	11496.5
88.3	82.5°	88.3	68.2	76.2	100.3	120.4	164.5	589.9	6757.5
64.2	85°	56.2	36.1	36.1	48.2	60.2	64.2	180.6	2740.7
32.1	87.5°	28.1	12.0	16.1	24.1	20.1	16.1	8.0	690.2
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)