

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P947214

Luminaire Tested: **GALN-SB2C-850-U-SLR-HSS**

Issue Date: 1/21/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P947214  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: GALN-SB2C-850-U-SLR-HSS  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(2) 80 CRI, 5000K, 615mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT  
ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10933 lumens  
Efficiency: N/A  
Efficacy: 108.4 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G3  
  
Input Watts (W): 100.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P947214  
 CATALOG NUMBER: GALN-SB2C-850-U-SLR-HSS

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 3.4 fc  
 Type IV - Short - N/A

REPORT NUMBER: P947214  
CATALOG NUMBER: GALN-SB2C-850-U-SLR-HSS

### Luminous Intensity Polar Plot



REPORT NUMBER: P947214

CATALOG NUMBER: GALN-SB2C-850-U-SLR-HSS

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1531.1	0.0	1531.1
	% Fixture	14.0	0.0	14.0
<b>Street Side</b>	Lumens	9401.9	0.0	9401.9
	% Fixture	86.0	0.0	86.0
<b>Total</b>	Lumens	10933.0	0.0	10933.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	149.0	1.4
10°-20°	446.8	4.1
20°-30°	658.2	6.0
30°-40°	845.6	7.7
40°-50°	1367.6	12.5
50°-60°	2398.3	21.9
60°-70°	3000.9	27.4
70°-80°	1753.6	16.0
80°-90°	312.9	2.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10933.0	100.0
0°-180°	10933.0	100.0

**Coefficient of Utilization**



REPORT NUMBER: P947214


CATALOG NUMBER: GALN-SB2C-850-U-SLR-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	852.7	7.8			
FM (30°-60°)	3831.9	35.0			
FH (60°-80°)	4416.4	40.4			G2/5000
FVH (80°-90°)	300.8	2.8			G3/500
BL (0°-30°)	401.3	3.7	B1/500		
BM (30°-60°)	779.7	7.1	B1/1000		
BH (60°-80°)	338.1	3.1	B1/500		G1/500
BVH (80°-90°)	12.0	0.1			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G3**

Type IV Short



REPORT NUMBER: P947214  
 CATALOG NUMBER: GALN-SB2C-850-U-SLR-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	1513.9	1513.9	1513.9	1513.9	1513.9	1513.9	1513.9	1513.9	1513.9	1513.9
2.5°	1710.4	1681.1	1663.8	1620.8	1577.9	1543.2	1496.5	1465.7	1428.8	1393.4
5°	1906.3	1858.8	1801.6	1723.3	1651.7	1578.6	1507.8	1437.8	1364.0	1296.2
7.5°	2072.0	2003.4	1902.5	1798.6	1707.4	1619.3	1536.5	1443.8	1354.2	1248.0
10°	2198.5	2111.1	1978.6	1842.3	1737.6	1648.7	1568.1	1489.8	1399.4	1271.4
12.5°	2275.3	2181.9	2024.5	1864.8	1745.1	1645.7	1583.2	1548.5	1513.1	1385.8
15°	2331.8	2230.9	2056.9	1880.7	1727.8	1605.8	1559.8	1594.5	1635.1	1553.8
17.5°	2390.6	2284.4	2099.1	1887.4	1681.1	1528.2	1508.6	1598.2	1692.4	1688.6
20°	2446.3	2340.9	2136.0	1882.9	1605.8	1434.0	1451.4	1565.8	1675.0	1721.0
22.5°	2510.3	2398.8	2171.4	1865.6	1507.8	1345.9	1400.1	1514.6	1610.3	1664.5
25°	2588.6	2471.9	2221.1	1840.0	1402.4	1272.9	1348.2	1455.1	1532.7	1570.4
27.5°	2673.0	2559.3	2287.4	1826.4	1317.3	1220.9	1289.4	1384.3	1453.6	1480.0
30°	2777.7	2660.9	2365.7	1811.4	1261.6	1190.8	1228.4	1302.2	1370.0	1396.4
32.5°	2892.2	2773.9	2441.0	1775.2	1227.7	1168.2	1168.9	1215.6	1277.4	1309.0
35°	3035.3	2909.5	2521.6	1696.1	1200.6	1141.8	1110.9	1133.5	1184.7	1222.4
37.5°	3239.4	3087.2	2620.3	1583.2	1160.6	1101.1	1049.9	1055.2	1094.4	1135.8
40°	3521.1	3326.0	2736.3	1465.7	1103.4	1043.9	982.9	980.6	1009.2	1049.9
42.5°	3902.2	3641.6	2875.6	1353.4	1048.4	974.6	912.1	908.3	930.9	966.3
45°	4405.3	4045.3	3046.6	1257.0	1005.5	906.8	845.1	843.5	862.4	893.3
47.5°	5049.2	4606.4	3217.5	1191.5	982.9	853.3	790.1	793.1	809.7	837.5
50°	5883.0	5337.7	3269.5	1158.4	982.9	824.7	741.1	756.2	769.7	790.8
52.5°	6882.5	6039.7	3097.8	1128.2	988.9	828.5	699.7	732.1	741.9	759.9
55°	7808.9	6383.9	2663.2	1086.8	990.4	851.8	664.3	712.5	730.6	737.4
57.5°	8346.6	6265.6	2153.3	1016.8	984.4	867.7	641.7	688.4	723.0	727.6
60°	8244.2	5850.6	1585.4	963.3	940.0	861.6	634.9	651.5	706.5	713.3
62.5°	7454.9	5154.7	1100.4	921.9	842.0	835.3	632.7	593.5	670.3	686.9
65°	5992.2	4058.1	777.3	793.8	738.1	778.0	620.6	533.2	626.6	649.2
67.5°	4347.3	2746.1	561.1	643.2	668.8	685.4	593.5	489.6	576.9	607.1
70°	2789.7	1483.0	393.9	424.8	563.4	582.2	546.8	450.4	526.5	561.1
72.5°	1983.1	875.9	283.2	297.5	452.7	485.0	481.3	406.7	467.7	509.9
75°	1368.5	482.8	191.3	212.4	328.4	393.9	371.3	349.5	396.2	439.1
77.5°	857.9	216.2	114.5	147.6	215.4	309.6	254.6	270.4	308.8	348.7
80°	477.5	83.6	64.0	97.9	117.5	225.2	140.8	174.0	227.5	256.1
82.5°	103.9	10.5	28.6	42.2	45.9	131.1	74.6	100.9	143.1	140.8
85°	0.0	0.0	5.3	6.0	3.0	56.5	27.1	33.1	46.7	43.7
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P947214  
 CATALOG NUMBER: GALN-SB2C-850-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

90°		95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
1513.9	0°	1513.9	1513.9	1513.9	1513.9	1513.9	1513.9	1513.9	1513.9	1513.9	1513.9
1361.7	2.5°	1355.7	1318.8	1291.7	1278.1	1266.8	1277.4	1283.4	1283.4	1309.0	1324.1
1254.8	5°	1228.4	1162.1	1111.7	1077.8	1057.4	1064.2	1071.8	1080.0	1112.4	1134.3
1191.5	7.5°	1140.3	1038.6	961.8	914.3	889.5	893.3	898.5	905.3	936.9	958.8
1200.6	10°	1123.7	977.6	869.2	806.6	776.5	771.2	768.2	766.0	784.8	801.4
1303.0	12.5°	1191.5	980.6	829.2	753.2	716.3	700.4	682.4	668.1	671.1	681.6
1458.1	15°	1312.8	1019.0	816.4	725.3	679.4	653.0	631.9	614.6	610.8	614.6
1593.7	17.5°	1451.4	1071.0	814.9	701.2	644.0	616.8	599.5	583.7	578.4	579.2
1669.8	20°	1543.2	1112.4	810.4	674.1	610.1	586.0	570.9	555.1	549.8	551.3
1648.7	22.5°	1552.3	1134.3	803.6	644.0	576.2	555.8	540.8	526.5	525.7	525.7
1569.6	25°	1503.3	1134.3	789.3	616.8	543.8	525.7	512.2	494.8	497.8	499.4
1480.0	27.5°	1427.3	1107.2	762.2	595.0	515.9	497.1	483.5	467.7	471.5	473.7
1396.4	30°	1351.9	1072.5	729.8	570.1	489.6	467.7	457.9	444.4	445.9	448.9
1313.5	32.5°	1281.9	1035.6	691.4	549.8	463.2	441.4	433.8	418.8	421.0	424.0
1232.2	35°	1212.6	994.9	646.2	525.7	439.1	417.3	411.2	393.9	395.4	399.9
1150.8	37.5°	1138.0	952.0	609.3	501.6	415.7	393.2	387.1	369.1	370.6	375.8
1066.5	40°	1059.7	909.8	573.2	476.0	390.9	368.3	363.0	343.4	345.0	351.0
983.6	42.5°	980.6	863.9	545.3	442.9	365.3	341.2	335.9	317.8	320.1	326.9
911.3	45°	907.6	808.9	527.2	406.0	341.2	314.1	308.8	292.2	296.7	304.3
850.3	47.5°	845.1	752.4	519.7	375.1	315.6	286.2	281.7	268.1	275.7	283.9
798.4	50°	791.6	698.2	509.9	343.4	291.5	262.1	257.6	248.5	258.3	266.6
763.0	52.5°	753.2	636.4	488.8	314.8	270.4	241.8	240.3	235.7	244.8	252.3
736.6	55°	720.0	572.4	454.9	290.0	251.6	224.4	226.0	223.7	231.2	237.2
720.8	57.5°	689.9	516.7	412.0	270.4	231.2	209.4	213.9	210.9	214.7	218.4
704.2	60°	653.8	460.2	360.8	248.5	207.1	194.3	199.6	191.3	190.6	192.1
674.1	62.5°	600.3	384.1	307.3	221.4	186.0	177.7	180.0	164.2	152.1	152.1
629.6	65°	525.7	308.8	257.6	191.3	161.9	155.2	153.6	131.1	114.5	113.0
581.4	67.5°	439.1	253.8	213.9	161.2	134.8	130.3	131.8	115.2	98.7	97.2
533.2	70°	357.8	210.1	172.5	128.8	103.9	108.5	115.2	98.7	82.8	80.6
476.8	72.5°	290.7	167.2	134.8	98.7	76.8	89.6	97.9	80.6	65.5	64.0
406.7	75°	224.4	122.8	96.4	67.0	55.7	69.3	76.8	58.7	46.7	44.4
314.8	77.5°	149.9	76.1	54.2	42.2	33.1	47.4	51.2	30.9	27.1	26.4
229.0	80°	91.1	35.4	23.3	20.3	11.3	17.3	20.3	12.8	14.3	15.1
122.0	82.5°	45.9	9.8	3.8	0.8	0.0	0.0	6.0	3.0	6.0	7.5
33.1	85°	3.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.5	3.8
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P947214  
 CATALOG NUMBER: GALN-SB2C-850-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

185°		195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
1513.9	0°	1513.9	1513.9	1513.9	1513.9	1513.9	1513.9	1513.9	1513.9	1513.9	1513.9
1330.1	2.5°	1372.3	1403.9	1434.0	1482.2	1531.9	1580.9	1630.6	1678.8	1696.1	1708.9
1148.6	5°	1214.1	1273.6	1342.9	1438.6	1541.0	1646.4	1753.4	1851.3	1895.7	1925.9
977.6	7.5°	1050.7	1128.2	1227.7	1371.5	1531.9	1699.9	1867.9	2022.3	2093.8	2151.8
816.4	10°	888.7	973.1	1098.9	1263.1	1480.0	1721.0	1953.0	2165.4	2258.0	2331.1
700.4	12.5°	746.4	825.5	957.3	1138.8	1398.6	1704.4	2001.9	2257.2	2366.5	2448.6
617.6	15°	646.2	702.0	818.7	1014.5	1302.2	1650.9	2004.9	2300.9	2420.7	2506.5
583.0	17.5°	590.5	609.3	685.4	888.0	1195.3	1580.9	1977.1	2316.0	2444.0	2523.9
552.1	20°	560.4	563.4	584.5	723.8	1058.2	1515.4	1950.7	2331.1	2465.9	2532.9
530.2	22.5°	536.3	536.3	541.5	592.0	881.2	1437.0	1942.4	2357.4	2496.0	2537.4
505.4	25°	514.4	514.4	515.9	529.5	698.2	1317.3	1937.2	2398.1	2537.4	2548.7
480.5	27.5°	491.8	492.6	492.6	500.1	562.6	1154.6	1914.6	2450.8	2587.1	2563.8
456.4	30°	469.2	470.7	470.7	476.0	497.8	964.1	1870.1	2514.1	2651.9	2583.4
432.3	32.5°	446.6	448.1	448.1	452.7	468.5	769.7	1814.4	2572.1	2717.4	2591.7
409.0	35°	423.3	425.5	424.0	430.1	446.6	612.3	1743.6	2630.1	2788.2	2618.0
386.4	37.5°	399.9	401.4	400.7	406.7	425.5	528.7	1661.5	2673.8	2884.6	2676.8
362.3	40°	376.6	375.8	375.8	382.6	402.9	504.6	1558.3	2743.0	3023.2	2779.9
338.2	42.5°	352.5	352.5	351.0	358.5	383.4	486.5	1459.6	2867.3	3225.1	2944.1
315.6	45°	330.6	329.9	326.9	333.7	364.5	454.9	1425.0	3099.3	3523.3	3210.0
293.0	47.5°	309.6	308.8	301.3	307.3	341.9	426.3	1554.5	3478.9	3936.8	3600.9
274.9	50°	290.7	291.5	277.2	282.4	319.3	404.5	1835.5	3971.5	4485.9	4127.4
259.8	52.5°	273.4	273.4	254.6	257.6	291.5	384.9	2102.8	4505.5	5210.4	4861.7
244.0	55°	256.1	254.6	233.5	235.0	263.6	357.0	2142.8	5026.7	6198.6	5966.6
226.7	57.5°	236.5	233.5	213.9	213.9	238.0	336.7	1857.3	5427.3	7424.7	7590.4
194.3	60°	212.4	210.1	197.3	193.6	217.7	354.7	1310.5	5474.0	8215.6	9749.8
154.4	62.5°	181.5	184.5	177.7	172.5	198.1	368.3	776.5	5098.2	8024.3	10436.7
119.8	65°	143.1	155.2	153.6	149.9	217.7	310.3	458.7	4376.7	7437.5	9882.3
104.7	67.5°	122.0	130.3	128.0	128.0	228.2	235.7	288.5	3419.4	6630.2	9224.8
87.4	70°	103.9	112.2	103.9	103.9	172.5	143.1	199.6	2387.5	5758.7	8497.3
70.0	72.5°	85.9	94.1	85.1	79.1	137.8	107.0	146.1	1492.0	4931.8	7739.6
49.7	75°	65.5	75.3	68.5	61.0	91.1	79.8	110.7	866.9	4085.9	6621.9
30.1	77.5°	41.4	54.2	51.2	42.9	67.0	58.0	79.8	515.9	3152.8	5174.3
18.1	80°	25.6	27.9	28.6	27.1	38.4	39.2	54.2	293.7	2157.8	3606.2
11.3	82.5°	16.6	16.6	12.8	14.3	18.8	22.6	30.9	110.7	1268.3	2195.5
6.8	85°	12.1	10.5	6.8	6.8	9.0	11.3	12.1	33.9	514.4	866.9
3.0	87.5°	6.0	5.3	2.3	3.0	4.5	3.8	3.0	1.5	129.5	277.2
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P947214  
 CATALOG NUMBER: GALN-SB2C-850-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

285°		295°	305°	315°	325°	335°	345°	355°	360°
1513.9	0°	1513.9	1513.9	1513.9	1513.9	1513.9	1513.9	1513.9	1513.9
1737.6	2.5°	1752.6	1776.0	1777.5	1777.5	1757.1	1756.4	1715.0	1710.4
1993.6	5°	2063.7	2078.7	2082.5	2075.0	2034.3	2004.2	1923.6	1906.3
2255.0	7.5°	2348.4	2378.5	2378.5	2360.4	2294.2	2232.4	2115.7	2072.0
2471.1	10°	2575.8	2610.5	2603.0	2566.0	2482.4	2397.3	2255.7	2198.5
2602.2	12.5°	2686.6	2722.0	2702.4	2660.2	2578.9	2489.2	2340.1	2275.3
2639.9	15°	2684.3	2674.5	2654.2	2648.9	2609.7	2541.9	2402.6	2331.8
2616.5	17.5°	2588.6	2505.8	2490.0	2542.7	2592.4	2575.8	2456.8	2390.6
2560.8	20°	2437.3	2292.6	2278.3	2379.3	2520.9	2593.2	2507.3	2446.3
2480.2	22.5°	2277.6	2121.7	2088.5	2200.0	2413.2	2598.4	2571.3	2510.3
2391.3	25°	2126.2	1969.5	1936.4	2040.3	2293.4	2589.4	2640.6	2588.6
2306.2	27.5°	1999.7	1848.3	1817.4	1921.3	2178.2	2563.8	2709.9	2673.0
2221.8	30°	1901.8	1761.7	1739.1	1839.2	2078.7	2532.2	2798.0	2777.7
2143.5	32.5°	1844.5	1742.1	1750.4	1832.5	2025.3	2497.5	2882.4	2892.2
2105.1	35°	1901.0	1905.5	1977.8	2011.7	2075.0	2492.2	2996.9	3035.3
2151.1	37.5°	2181.9	2338.6	2488.5	2460.6	2318.3	2553.2	3167.8	3239.4
2351.4	40°	2660.2	2981.8	3225.1	3118.9	2760.4	2740.0	3414.1	3521.1
2706.9	42.5°	3244.7	3789.9	4190.6	3905.9	3330.5	3066.9	3765.8	3902.2
3137.0	45°	3861.5	4786.4	5417.5	4825.6	3938.3	3524.8	4298.3	4405.3
3539.9	47.5°	4511.5	5997.5	6813.9	5845.3	4501.7	4046.0	5024.4	5049.2
3921.8	50°	5222.5	7325.3	8237.4	6864.4	5045.5	4643.3	5911.6	5883.0
4366.9	52.5°	5899.6	8690.8	9630.8	7887.9	5523.0	5384.4	6941.2	6882.5
4975.4	55°	6545.8	10055.6	11032.4	8871.6	5973.4	6363.5	8164.4	7808.9
5852.9	57.5°	7295.2	11282.5	12477.0	9859.7	6603.0	7634.9	9532.1	8346.6
7533.2	60°	8403.1	12676.6	14110.6	11213.9	7800.6	8971.0	10022.4	8244.2
9545.7	62.5°	9817.6	13958.5	15298.4	12541.0	9003.4	9222.6	9300.1	7454.9
9135.2	65°	10092.5	14283.1	15365.4	12895.8	8848.2	7823.2	7592.7	5992.2
8159.8	67.5°	9363.4	13696.4	14428.5	12235.2	7826.9	6045.7	5697.7	4347.3
7519.6	70°	8545.5	12577.9	12795.6	11112.3	6884.0	4446.7	3847.9	2789.7
7081.3	72.5°	7707.2	11085.9	10635.5	9650.4	6050.2	3237.9	2775.4	1983.1
6456.9	75°	6711.5	9123.9	8377.5	8018.2	5009.3	2541.2	2007.9	1368.5
5553.9	77.5°	5374.6	6422.3	6222.7	6215.2	3764.3	1856.6	1339.9	857.9
4339.0	80°	3791.5	4168.0	4066.4	4680.9	2525.4	1346.7	806.6	477.5
3020.2	82.5°	1835.5	2304.7	2365.7	2787.5	1228.4	792.3	186.0	103.9
1181.0	85°	718.5	1111.7	937.7	1058.2	345.0	220.7	4.5	0.0
194.3	87.5°	80.6	128.8	118.2	93.4	42.2	9.0	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)