

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P950069

Luminaire Tested: **GALN-SB4C-850-U-SLL**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P950069
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GALN-SB4C-850-U-SLL
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(4) 80 CRI, 5000K, 615mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR LEFT OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 28607 lumens
Efficiency: N/A
Efficacy: 142.5 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U0 - G5


Input Watts (W): 200.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P950069
 CATALOG NUMBER: GALN-SB4C-850-U-SLL

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 8.7 fc
 Type IV - Short - N/A

REPORT NUMBER: P950069
CATALOG NUMBER: GALN-SB4C-850-U-SLL

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P950069
 CATALOG NUMBER: GALN-SB4C-850-U-SLL

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	7270.5	0.0	7270.5
	% Fixture	25.4	0.0	25.4
Street Side	Lumens	21336.5	0.0	21336.5
	% Fixture	74.6	0.0	74.6
Total	Lumens	28607.0	0.0	28607.0
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	390.2	1.4
10°-20°	1225.0	4.3
20°-30°	1892.2	6.6
30°-40°	2397.9	8.4
40°-50°	3616.6	12.6
50°-60°	5843.1	20.4
60°-70°	7284.4	25.5
70°-80°	4776.7	16.7
80°-90°	1180.9	4.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	28607.0	100.0
0°-180°	28607.0	100.0



REPORT NUMBER: P950069


CATALOG NUMBER: GALN-SB4C-850-U-SLL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1924.1	6.7			
FM (30°-60°)	8344.0	29.2			
FH (60°-80°)	10095.5	35.3			G4/12000
FVH (80°-90°)	972.8	3.4			G5
BL (0°-30°)	1583.2	5.5	B3/2500		
BM (30°-60°)	3513.5	12.3	B3/5000		
BH (60°-80°)	1965.6	6.9	B3/2500		G3/2500
BVH (80°-90°)	208.1	0.7			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G5

Type IV Short



REPORT NUMBER: P950069
 CATALOG NUMBER: GALN-SB4C-850-U-SLL

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°
0°	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7
2.5°	4230.3	4246.3	4262.5	4285.3	4308.1	4321.6	4335.2	4342.0	4348.8	4345.8
5°	4548.8	4604.8	4661.0	4716.5	4772.2	4802.4	4832.6	4850.9	4869.3	4883.2
7.5°	4868.8	4960.0	5051.0	5133.0	5215.0	5264.3	5313.7	5340.4	5367.0	5379.8
10°	5114.1	5221.9	5329.7	5425.8	5522.0	5580.3	5638.2	5664.2	5690.0	5699.8
12.5°	5264.3	5381.2	5497.8	5584.8	5671.4	5713.7	5756.0	5770.1	5784.3	5785.8
15°	5355.6	5456.5	5557.2	5611.6	5666.3	5667.8	5669.3	5654.2	5639.1	5621.3
17.5°	5407.0	5475.0	5543.1	5544.2	5545.1	5483.9	5422.8	5366.8	5310.7	5271.1
20°	5463.6	5487.3	5511.1	5439.4	5367.7	5232.8	5097.8	4999.6	4901.3	4840.9
22.5°	5529.2	5498.1	5467.0	5318.5	5170.0	4971.5	4773.0	4650.1	4527.2	4460.5
25°	5613.8	5515.6	5417.5	5192.0	4966.5	4725.4	4484.4	4355.2	4226.2	4163.2
27.5°	5728.5	5553.1	5377.5	5078.8	4780.2	4513.0	4245.9	4118.8	3991.8	3932.2
30°	5883.2	5621.6	5360.2	4992.5	4624.7	4346.4	4068.1	3950.2	3832.3	3776.7
32.5°	6065.9	5707.7	5349.6	4933.6	4517.6	4256.0	3994.4	3901.9	3809.2	3769.2
35°	6287.7	5849.4	5411.2	4977.7	4544.3	4362.6	4181.0	4159.4	4137.8	4134.5
37.5°	6661.3	6145.7	5630.1	5236.1	4842.1	4830.3	4818.6	4917.3	5016.0	5067.3
40°	7225.9	6665.1	6104.3	5811.4	5518.4	5725.2	5932.0	6172.0	6412.0	6531.5
42.5°	7974.6	7418.2	6861.8	6693.0	6524.3	6975.3	7426.3	7862.9	8299.4	8555.7
45°	8899.1	8399.4	7899.4	7825.0	7750.4	8473.0	9195.8	9913.1	10630.5	11066.0
47.5°	10055.4	9569.2	9082.9	9067.8	9052.7	10095.1	11137.3	12187.4	13237.4	13854.0
50°	11570.9	10970.3	10369.8	10372.4	10375.0	11718.4	13061.8	14448.0	15834.2	16672.2
52.5°	13310.6	12583.3	11856.2	11782.7	11709.0	13313.8	14918.5	16633.6	18348.5	19353.1
55°	15162.7	14444.2	13725.7	13439.1	13152.4	14938.4	16724.3	18768.9	20813.5	22008.2
57.5°	16847.3	16456.1	16064.7	15489.7	14914.9	16718.3	18521.6	20837.5	23153.2	24634.7
60°	17865.5	18473.2	19081.1	18367.1	17653.1	19359.7	21066.3	23545.8	26025.3	27626.5
62.5°	17348.5	19009.1	20669.6	20589.2	20508.6	22071.9	23635.5	25994.5	28353.3	29833.4
65°	16313.7	17872.3	19430.8	19739.2	20047.4	22034.2	24021.1	26308.6	28595.9	29856.0
67.5°	14927.3	16409.6	17891.9	18036.5	18181.0	20251.1	22321.0	24618.3	26915.6	27902.8
70°	13261.6	14873.8	16486.3	16550.9	16615.6	18466.8	20317.9	22294.9	24271.7	24820.4
72.5°	11276.6	13126.8	14977.1	15023.6	15069.9	16518.3	17966.6	19447.3	20927.8	20983.3
75°	8765.6	10680.5	12595.4	12767.3	12939.3	14066.1	15192.9	16235.2	17277.5	16998.3
77.5°	6262.8	8050.4	9838.0	10084.1	10330.1	11186.8	12043.4	12782.6	13521.9	13041.9
80°	4099.0	5602.9	7106.6	7412.5	7718.3	8365.2	9011.9	9400.1	9788.2	9016.1
82.5°	2382.7	3410.8	4439.1	4780.7	5122.4	5567.7	6013.0	6175.0	6336.8	5730.0
85°	1048.3	1594.0	2139.7	2430.3	2720.8	3086.7	3452.5	3544.4	3636.3	3150.3
87.5°	324.5	507.9	691.3	853.5	1015.6	1198.5	1381.5	1389.3	1397.0	1172.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P950069
 CATALOG NUMBER: GALN-SB4C-850-U-SLL

CANDELA DISTRIBUTION (continued):

50°		55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
3933.7	0°	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7
4348.8	2.5°	4342.0	4335.2	4321.6	4308.1	4285.3	4262.5	4246.3	4230.3	4197.9	4165.4
4869.3	5°	4850.9	4832.6	4802.4	4772.2	4716.5	4661.0	4604.8	4548.8	4477.1	4405.4
5367.0	7.5°	5340.4	5313.7	5264.3	5215.0	5133.0	5051.0	4960.0	4868.8	4750.5	4632.3
5690.0	10°	5664.2	5638.2	5580.3	5522.0	5425.8	5329.7	5221.9	5114.1	4964.5	4814.9
5784.3	12.5°	5770.1	5756.0	5713.7	5671.4	5584.8	5497.8	5381.2	5264.3	5099.9	4935.7
5639.1	15°	5654.2	5669.3	5667.8	5666.3	5611.6	5557.2	5456.5	5355.6	5184.3	5013.0
5310.7	17.5°	5366.8	5422.8	5483.9	5545.1	5544.2	5543.1	5475.0	5407.0	5233.2	5059.5
4901.3	20°	4999.6	5097.8	5232.8	5367.7	5439.4	5511.1	5487.3	5463.6	5283.0	5102.3
4527.2	22.5°	4650.1	4773.0	4971.5	5170.0	5318.5	5467.0	5498.1	5529.2	5344.8	5160.2
4226.2	25°	4355.2	4484.4	4725.4	4966.5	5192.0	5417.5	5515.6	5613.8	5432.9	5252.2
3991.8	27.5°	4118.8	4245.9	4513.0	4780.2	5078.8	5377.5	5553.1	5728.5	5556.1	5383.6
3832.3	30°	3950.2	4068.1	4346.4	4624.7	4992.5	5360.2	5621.6	5883.2	5716.6	5550.1
3809.2	32.5°	3901.9	3994.4	4256.0	4517.6	4933.6	5349.6	5707.7	6065.9	5900.9	5736.0
4137.8	35°	4159.4	4181.0	4362.6	4544.3	4977.7	5411.2	5849.4	6287.7	6129.9	5971.8
5016.0	37.5°	4917.3	4818.6	4830.3	4842.1	5236.1	5630.1	6145.7	6661.3	6460.0	6258.6
6412.0	40°	6172.0	5932.0	5725.2	5518.4	5811.4	6104.3	6665.1	7225.9	6932.4	6639.0
8299.4	42.5°	7862.9	7426.3	6975.3	6524.3	6693.0	6861.8	7418.2	7974.6	7551.0	7127.5
10630.5	45°	9913.1	9195.8	8473.0	7750.4	7825.0	7899.4	8399.4	8899.1	8327.8	7756.5
13237.4	47.5°	12187.4	11137.3	10095.1	9052.7	9067.8	9082.9	9569.2	10055.4	9251.3	8447.1
15834.2	50°	14448.0	13061.8	11718.4	10375.0	10372.4	10369.8	10970.3	11570.9	10358.7	9146.3
18348.5	52.5°	16633.6	14918.5	13313.8	11709.0	11782.7	11856.2	12583.3	13310.6	11521.9	9733.1
20813.5	55°	18768.9	16724.3	14938.4	13152.4	13439.1	13725.7	14444.2	15162.7	12553.2	9943.7
23153.2	57.5°	20837.5	18521.6	16718.3	14914.9	15489.7	16064.7	16456.1	16847.3	13284.0	9720.8
26025.3	60°	23545.8	21066.3	19359.7	17653.1	18367.1	19081.1	18473.2	17865.5	13466.7	9067.8
28353.3	62.5°	25994.5	23635.5	22071.9	20508.6	20589.2	20669.6	19009.1	17348.5	12697.6	8046.7
28595.9	65°	26308.6	24021.1	22034.2	20047.4	19739.2	19430.8	17872.3	16313.7	11609.4	6905.1
26915.6	67.5°	24618.3	22321.0	20251.1	18181.0	18036.5	17891.9	16409.6	14927.3	10314.4	5701.6
24271.7	70°	22294.9	20317.9	18466.8	16615.6	16550.9	16486.3	14873.8	13261.6	8901.4	4541.3
20927.8	72.5°	19447.3	17966.6	16518.3	15069.9	15023.6	14977.1	13126.8	11276.6	7369.6	3462.8
17277.5	75°	16235.2	15192.9	14066.1	12939.3	12767.3	12595.4	10680.5	8765.6	5613.6	2461.7
13521.9	77.5°	12782.6	12043.4	11186.8	10330.1	10084.1	9838.0	8050.4	6262.8	3929.0	1595.2
9788.2	80°	9400.1	9011.9	8365.2	7718.3	7412.5	7106.6	5602.9	4099.0	2531.4	963.8
6336.8	82.5°	6175.0	6013.0	5567.7	5122.4	4780.7	4439.1	3410.8	2382.7	1465.1	547.6
3636.3	85°	3544.4	3452.5	3086.7	2720.8	2430.3	2139.7	1594.0	1048.3	659.0	269.9
1397.0	87.5°	1389.3	1381.5	1198.5	1015.6	853.5	691.3	507.9	324.5	215.9	107.2
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P950069
 CATALOG NUMBER: GALN-SB4C-850-U-SLL

CANDELA DISTRIBUTION (continued):

105°		110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
3933.7	0°	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7
4130.8	2.5°	4096.4	4061.7	4027.0	3993.8	3960.6	3928.4	3892.7	3863.7	3834.8	3808.7
4333.9	5°	4262.5	4190.5	4118.6	4051.4	3984.3	3920.9	3858.2	3803.6	3748.8	3702.9
4523.0	7.5°	4413.7	4307.3	4200.9	4107.1	4013.4	3926.9	3845.9	3773.1	3700.5	3640.1
4670.5	10°	4526.2	4397.0	4267.6	4156.8	4045.7	3939.0	3851.9	3775.2	3698.5	3638.2
4772.1	12.5°	4608.4	4456.0	4303.5	4178.1	4052.7	3940.5	3859.4	3796.6	3734.2	3694.0
4835.5	15°	4658.0	4482.4	4306.9	4161.6	4016.4	3892.2	3827.3	3797.3	3767.4	3772.8
4865.8	17.5°	4672.1	4468.4	4264.6	4089.9	3915.3	3769.2	3729.2	3740.2	3751.1	3816.9
4889.5	20°	4676.7	4429.7	4182.8	3966.3	3749.9	3579.7	3569.2	3620.5	3671.8	3786.1
4921.5	22.5°	4682.7	4382.3	4081.9	3821.3	3560.6	3366.9	3387.6	3463.5	3539.4	3669.9
4979.5	25°	4706.6	4335.5	3964.7	3659.3	3354.1	3155.6	3211.4	3299.0	3386.5	3503.8
5070.0	27.5°	4756.4	4304.3	3852.2	3511.2	3170.2	2989.5	3057.5	3142.0	3226.5	3323.0
5187.3	30°	4824.6	4289.6	3754.4	3387.4	3020.5	2868.8	2922.1	2989.1	3056.4	3136.4
5309.8	32.5°	4883.5	4271.5	3659.3	3280.7	2902.0	2779.7	2803.4	2843.1	2882.8	2946.7
5449.2	35°	4926.6	4237.4	3548.5	3175.8	2803.1	2701.2	2691.4	2702.3	2713.3	2762.0
5605.5	37.5°	4952.3	4179.0	3405.7	3052.3	2699.0	2609.9	2574.0	2561.9	2549.8	2584.8
5803.8	40°	4968.5	4098.5	3228.8	2905.0	2581.2	2500.5	2445.4	2418.0	2390.7	2415.9
6063.3	42.5°	4999.1	4015.5	3032.2	2742.4	2452.6	2378.2	2308.8	2272.5	2236.3	2256.8
6404.7	45°	5053.0	3938.4	2823.9	2569.7	2315.5	2240.1	2172.9	2137.6	2102.4	2119.6
6768.5	47.5°	5090.0	3874.7	2659.4	2433.1	2206.9	2109.5	2051.7	2022.1	1992.5	2008.8
7106.0	50°	5065.8	3805.3	2544.7	2342.4	2140.1	2012.1	1945.0	1918.7	1892.6	1917.9
7325.2	52.5°	4917.1	3688.0	2458.9	2282.6	2106.5	1959.3	1865.4	1839.5	1813.6	1851.8
7276.9	55°	4610.0	3493.5	2377.1	2239.3	2101.5	1964.6	1823.2	1782.1	1741.2	1795.4
6937.0	57.5°	4153.3	3219.4	2285.4	2188.0	2090.6	1969.9	1797.8	1738.0	1678.2	1736.5
6304.3	60°	3540.9	2863.5	2186.0	2109.5	2033.0	1953.3	1773.9	1696.5	1618.9	1670.1
5448.9	62.5°	2851.1	2437.5	2023.9	1973.0	1922.3	1912.5	1746.2	1649.3	1552.5	1585.0
4576.1	65°	2247.3	2054.3	1861.2	1837.2	1813.2	1814.4	1687.6	1584.7	1481.6	1494.1
3721.2	67.5°	1740.7	1685.9	1631.0	1644.4	1657.7	1654.4	1583.1	1497.4	1411.7	1407.7
2929.9	70°	1318.5	1334.2	1349.8	1412.0	1474.0	1474.0	1450.6	1389.6	1328.6	1315.1
2239.9	72.5°	1017.1	1064.3	1111.7	1199.9	1287.9	1302.7	1303.0	1261.2	1219.4	1199.4
1625.7	75°	789.8	832.6	875.5	974.2	1072.9	1141.2	1135.4	1103.3	1071.0	1052.0
1101.6	77.5°	608.0	637.2	666.4	762.3	858.1	970.6	967.6	941.8	916.0	896.6
709.8	80°	455.9	467.9	480.0	561.2	642.3	776.6	776.2	754.6	732.9	716.7
436.5	82.5°	325.7	327.9	330.3	390.1	449.8	564.5	570.9	560.3	549.8	538.3
233.4	85°	197.0	195.9	194.7	238.5	282.3	367.6	375.9	364.5	353.2	340.4
96.8	87.5°	86.3	85.3	84.2	102.0	120.0	155.5	166.0	161.5	157.0	154.6
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P950069
 CATALOG NUMBER: GALN-SB4C-850-U-SLL

CANDELA DISTRIBUTION (continued):

160°		165°	170°	175°	180°	185°	190°	195°	200°	205°	210°
3933.7	0°	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7
3782.8	2.5°	3760.0	3737.2	3714.2	3691.4	3673.8	3656.0	3641.6	3627.3	3616.1	3604.9
3657.2	5°	3616.7	3576.3	3539.6	3502.8	3474.5	3446.1	3426.4	3406.6	3392.6	3378.5
3579.7	7.5°	3528.9	3477.8	3432.9	3388.0	3354.4	3320.9	3297.3	3273.8	3257.6	3241.6
3577.8	10°	3523.0	3468.0	3417.5	3366.9	3326.7	3286.4	3260.2	3233.6	3218.4	3203.1
3654.2	12.5°	3611.0	3568.1	3515.7	3463.5	3412.2	3360.9	3326.9	3292.9	3275.9	3259.0
3778.2	15°	3767.1	3755.9	3710.5	3665.0	3592.0	3518.9	3467.3	3415.7	3392.0	3368.4
3882.7	17.5°	3917.7	3952.6	3915.9	3879.4	3782.6	3685.9	3609.8	3533.7	3498.7	3463.5
3900.5	20°	3973.7	4046.9	4030.0	4013.0	3902.3	3791.8	3698.5	3605.4	3560.6	3515.6
3800.6	22.5°	3895.8	3991.1	4001.3	4011.4	3905.8	3800.1	3704.1	3608.0	3560.7	3513.3
3621.2	25°	3715.0	3808.7	3843.7	3878.6	3792.0	3705.5	3620.0	3534.9	3493.8	3452.9
3419.3	27.5°	3494.4	3569.6	3608.6	3647.7	3585.9	3524.3	3458.1	3391.8	3364.3	3336.7
3216.4	30°	3278.7	3341.2	3372.9	3404.6	3357.7	3310.6	3263.2	3215.5	3201.5	3187.3
3010.7	32.5°	3070.4	3130.4	3165.5	3200.9	3157.7	3114.4	3076.5	3038.6	3029.4	3020.2
2810.7	35°	2869.8	2929.1	2971.4	3013.7	2982.9	2952.2	2917.2	2882.4	2868.3	2854.4
2619.7	37.5°	2678.7	2737.9	2790.1	2842.4	2828.2	2814.0	2781.8	2749.5	2724.0	2698.7
2441.1	40°	2498.2	2555.3	2615.3	2675.6	2679.0	2682.3	2655.0	2627.7	2590.6	2553.7
2277.5	42.5°	2331.5	2385.7	2450.6	2515.6	2532.9	2550.3	2527.2	2504.2	2458.2	2412.2
2137.1	45°	2188.4	2239.8	2307.1	2374.4	2399.3	2424.2	2403.4	2382.7	2330.0	2277.5
2025.0	47.5°	2075.2	2125.3	2191.8	2258.2	2286.9	2315.5	2301.1	2286.6	2239.8	2193.0
1943.5	50°	1990.9	2038.1	2097.6	2157.0	2193.9	2230.7	2229.8	2229.2	2191.8	2154.3
1889.9	52.5°	1933.3	1976.7	2032.1	2087.6	2131.2	2174.9	2182.7	2190.6	2160.1	2129.6
1849.4	55°	1896.2	1943.0	1991.6	2040.1	2086.3	2132.6	2143.5	2154.3	2127.8	2101.2
1794.8	57.5°	1849.7	1904.7	1952.7	2000.8	2047.5	2094.0	2105.0	2116.0	2089.1	2062.3
1721.1	60°	1784.2	1847.3	1896.1	1945.0	1991.8	2038.6	2050.6	2062.7	2036.4	2010.3
1617.4	62.5°	1690.9	1764.6	1816.7	1868.7	1911.6	1954.5	1966.1	1977.7	1954.0	1930.3
1506.5	65°	1585.3	1664.2	1714.0	1763.8	1801.6	1839.3	1851.2	1863.0	1840.2	1817.4
1403.8	67.5°	1476.6	1549.5	1596.7	1643.8	1676.4	1709.0	1720.7	1732.1	1711.1	1690.3
1301.5	70°	1365.5	1429.5	1470.2	1511.0	1540.4	1569.9	1581.0	1592.2	1575.1	1558.1
1179.7	72.5°	1230.1	1280.3	1317.2	1354.0	1382.8	1411.7	1425.0	1438.2	1424.0	1409.9
1032.8	75°	1070.2	1107.7	1141.0	1174.4	1200.6	1226.9	1240.8	1254.7	1247.7	1240.8
877.3	77.5°	907.8	938.1	966.8	995.5	1023.1	1050.6	1063.6	1076.6	1066.9	1056.9
700.4	80°	725.8	751.0	775.1	799.3	820.3	841.1	858.3	875.5	871.3	867.2
526.8	82.5°	524.7	522.6	514.1	505.7	550.4	595.0	624.3	653.6	651.8	649.8
327.6	85°	316.7	305.7	282.3	258.9	300.7	342.7	378.9	415.1	412.1	409.1
152.2	87.5°	151.7	151.3	133.4	115.5	133.0	150.6	165.3	179.9	176.3	172.4
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P950069
 CATALOG NUMBER: GALN-SB4C-850-U-SLL

CANDELA DISTRIBUTION (continued):

215°		220°	225°	230°	235°	240°	245°	250°	255°	260°	265°
3933.7	0°	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7
3594.7	2.5°	3584.3	3571.4	3584.3	3594.7	3604.9	3616.1	3627.3	3641.6	3656.0	3673.8
3367.8	5°	3357.1	3346.5	3357.1	3367.8	3378.5	3392.6	3406.6	3426.4	3446.1	3474.5
3232.0	7.5°	3222.4	3215.2	3222.4	3232.0	3241.6	3257.6	3273.8	3297.3	3320.9	3354.4
3195.0	10°	3186.8	3183.5	3186.8	3195.0	3203.1	3218.4	3233.6	3260.2	3286.4	3326.7
3252.0	12.5°	3245.1	3243.9	3245.1	3252.0	3259.0	3275.9	3292.9	3326.9	3360.9	3412.2
3359.4	15°	3350.3	3349.5	3350.3	3359.4	3368.4	3392.0	3415.7	3467.3	3518.9	3592.0
3452.0	17.5°	3440.4	3438.6	3440.4	3452.0	3463.5	3498.7	3533.7	3609.8	3685.9	3782.6
3501.2	20°	3486.9	3482.4	3486.9	3501.2	3515.6	3560.6	3605.4	3698.5	3791.8	3902.3
3497.5	22.5°	3481.6	3474.8	3481.6	3497.5	3513.3	3560.7	3608.0	3704.1	3800.1	3905.8
3438.0	25°	3423.2	3414.4	3423.2	3438.0	3452.9	3493.8	3534.9	3620.0	3705.5	3792.0
3329.9	27.5°	3323.1	3320.9	3323.1	3329.9	3336.7	3364.3	3391.8	3458.1	3524.3	3585.9
3187.3	30°	3187.3	3189.5	3187.3	3187.3	3187.3	3201.5	3215.5	3263.2	3310.6	3357.7
3021.4	32.5°	3022.7	3025.0	3022.7	3021.4	3020.2	3029.4	3038.6	3076.5	3114.4	3157.7
2851.4	35°	2848.4	2846.9	2848.4	2851.4	2854.4	2868.3	2882.4	2917.2	2952.2	2982.9
2685.2	37.5°	2671.8	2664.2	2671.8	2685.2	2698.7	2724.0	2749.5	2781.8	2814.0	2828.2
2528.7	40°	2503.9	2489.1	2503.9	2528.7	2553.7	2590.6	2627.7	2655.0	2682.3	2679.0
2375.8	42.5°	2339.4	2315.5	2339.4	2375.8	2412.2	2458.2	2504.2	2527.2	2550.3	2532.9
2234.8	45°	2192.1	2164.6	2192.1	2234.8	2277.5	2330.0	2382.7	2403.4	2424.2	2399.3
2153.4	47.5°	2114.0	2087.6	2114.0	2153.4	2193.0	2239.8	2286.6	2301.1	2315.5	2286.9
2117.8	50°	2081.3	2055.9	2081.3	2117.8	2154.3	2191.8	2229.2	2229.8	2230.7	2193.9
2096.8	52.5°	2064.2	2040.8	2064.2	2096.8	2129.6	2160.1	2190.6	2182.7	2174.9	2131.2
2072.5	55°	2043.8	2022.7	2043.8	2072.5	2101.2	2127.8	2154.3	2143.5	2132.6	2086.3
2033.9	57.5°	2005.3	1983.5	2005.3	2033.9	2062.3	2089.1	2116.0	2105.0	2094.0	2047.5
1981.0	60°	1951.8	1929.1	1951.8	1981.0	2010.3	2036.4	2062.7	2050.6	2038.6	1991.8
1899.5	62.5°	1868.7	1841.6	1868.7	1899.5	1930.3	1954.0	1977.7	1966.1	1954.5	1911.6
1787.5	65°	1757.8	1734.4	1757.8	1787.5	1817.4	1840.2	1863.0	1851.2	1839.3	1801.6
1662.5	67.5°	1634.8	1613.6	1634.8	1662.5	1690.3	1711.1	1732.1	1720.7	1709.0	1676.4
1531.5	70°	1505.0	1480.8	1505.0	1531.5	1558.1	1575.1	1592.2	1581.0	1569.9	1540.4
1384.5	72.5°	1359.3	1335.9	1359.3	1384.5	1409.9	1424.0	1438.2	1425.0	1411.7	1382.8
1219.5	75°	1198.2	1175.9	1198.2	1219.5	1240.8	1247.7	1254.7	1240.8	1226.9	1200.6
1035.5	77.5°	1014.1	996.3	1014.1	1035.5	1056.9	1066.9	1076.6	1063.6	1050.6	1023.1
838.4	80°	809.4	775.9	809.4	838.4	867.2	871.3	875.5	858.3	841.1	820.3
625.5	82.5°	601.1	579.6	601.1	625.5	649.8	651.8	653.6	624.3	595.0	550.4
390.1	85°	371.0	351.7	371.0	390.1	409.1	412.1	415.1	378.9	342.7	300.7
162.7	87.5°	152.8	143.4	152.8	162.7	172.4	176.3	179.9	165.3	150.6	133.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P950069
 CATALOG NUMBER: GALN-SB4C-850-U-SLL

CANDELA DISTRIBUTION (continued):

270°		275°	280°	285°	290°	295°	300°	305°	310°	315°	320°
3933.7	0°	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7
3691.4	2.5°	3714.2	3737.2	3760.0	3782.8	3808.7	3834.8	3863.7	3892.7	3928.4	3960.6
3502.8	5°	3539.6	3576.3	3616.7	3657.2	3702.9	3748.8	3803.6	3858.2	3920.9	3984.3
3388.0	7.5°	3432.9	3477.8	3528.9	3579.7	3640.1	3700.5	3773.1	3845.9	3926.9	4013.4
3366.9	10°	3417.5	3468.0	3523.0	3577.8	3638.2	3698.5	3775.2	3851.9	3939.0	4045.7
3463.5	12.5°	3515.7	3568.1	3611.0	3654.2	3694.0	3734.2	3796.6	3859.4	3940.5	4052.7
3665.0	15°	3710.5	3755.9	3767.1	3778.2	3772.8	3767.4	3797.3	3827.3	3892.2	4016.4
3879.4	17.5°	3915.9	3952.6	3917.7	3882.7	3816.9	3751.1	3740.2	3729.2	3769.2	3915.3
4013.0	20°	4030.0	4046.9	3973.7	3900.5	3786.1	3671.8	3620.5	3569.2	3579.7	3749.9
4011.4	22.5°	4001.3	3991.1	3895.8	3800.6	3669.9	3539.4	3463.5	3387.6	3366.9	3560.6
3878.6	25°	3843.7	3808.7	3715.0	3621.2	3503.8	3386.5	3299.0	3211.4	3155.6	3354.1
3647.7	27.5°	3608.6	3569.6	3494.4	3419.3	3323.0	3226.5	3142.0	3057.5	2989.5	3170.2
3404.6	30°	3372.9	3341.2	3278.7	3216.4	3136.4	3056.4	2989.1	2922.1	2868.8	3020.5
3200.9	32.5°	3165.5	3130.4	3070.4	3010.7	2946.7	2882.8	2843.1	2803.4	2779.7	2902.0
3013.7	35°	2971.4	2929.1	2869.8	2810.7	2762.0	2713.3	2702.3	2691.4	2701.2	2803.1
2842.4	37.5°	2790.1	2737.9	2678.7	2619.7	2584.8	2549.8	2561.9	2574.0	2609.9	2699.0
2675.6	40°	2615.3	2555.3	2498.2	2441.1	2415.9	2390.7	2418.0	2445.4	2500.5	2581.2
2515.6	42.5°	2450.6	2385.7	2331.5	2277.5	2256.8	2236.3	2272.5	2308.8	2378.2	2452.6
2374.4	45°	2307.1	2239.8	2188.4	2137.1	2119.6	2102.4	2137.6	2172.9	2240.1	2315.5
2258.2	47.5°	2191.8	2125.3	2075.2	2025.0	2008.8	1992.5	2022.1	2051.7	2109.5	2206.9
2157.0	50°	2097.6	2038.1	1990.9	1943.5	1917.9	1892.6	1918.7	1945.0	2012.1	2140.1
2087.6	52.5°	2032.1	1976.7	1933.3	1889.9	1851.8	1813.6	1839.5	1865.4	1959.3	2106.5
2040.1	55°	1991.6	1943.0	1896.2	1849.4	1795.4	1741.2	1782.1	1823.2	1964.6	2101.5
2000.8	57.5°	1952.7	1904.7	1849.7	1794.8	1736.5	1678.2	1738.0	1797.8	1969.9	2090.6
1945.0	60°	1896.1	1847.3	1784.2	1721.1	1670.1	1618.9	1696.5	1773.9	1953.3	2033.0
1868.7	62.5°	1816.7	1764.6	1690.9	1617.4	1585.0	1552.5	1649.3	1746.2	1912.5	1922.3
1763.8	65°	1714.0	1664.2	1585.3	1506.5	1494.1	1481.6	1584.7	1687.6	1814.4	1813.2
1643.8	67.5°	1596.7	1549.5	1476.6	1403.8	1407.7	1411.7	1497.4	1583.1	1654.4	1657.7
1511.0	70°	1470.2	1429.5	1365.5	1301.5	1315.1	1328.6	1389.6	1450.6	1474.0	1474.0
1354.0	72.5°	1317.2	1280.3	1230.1	1179.7	1199.4	1219.4	1261.2	1303.0	1302.7	1287.9
1174.4	75°	1141.0	1107.7	1070.2	1032.8	1052.0	1071.0	1103.3	1135.4	1141.2	1072.9
995.5	77.5°	966.8	938.1	907.8	877.3	896.6	916.0	941.8	967.6	970.6	858.1
799.3	80°	775.1	751.0	725.8	700.4	716.7	732.9	754.6	776.2	776.6	642.3
505.7	82.5°	514.1	522.6	524.7	526.8	538.3	549.8	560.3	570.9	564.5	449.8
258.9	85°	282.3	305.7	316.7	327.6	340.4	353.2	364.5	375.9	367.6	282.3
115.5	87.5°	133.4	151.3	151.7	152.2	154.6	157.0	161.5	166.0	155.5	120.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P950069
 CATALOG NUMBER: GALN-SB4C-850-U-SLL

CANDELA DISTRIBUTION (continued):

325°		330°	335°	340°	345°	350°	355°	360°
3933.7	0°	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7	3933.7
3993.8	2.5°	4027.0	4061.7	4096.4	4130.8	4165.4	4197.9	4230.3
4051.4	5°	4118.6	4190.5	4262.5	4333.9	4405.4	4477.1	4548.8
4107.1	7.5°	4200.9	4307.3	4413.7	4523.0	4632.3	4750.5	4868.8
4156.8	10°	4267.6	4397.0	4526.2	4670.5	4814.9	4964.5	5114.1
4178.1	12.5°	4303.5	4456.0	4608.4	4772.1	4935.7	5099.9	5264.3
4161.6	15°	4306.9	4482.4	4658.0	4835.5	5013.0	5184.3	5355.6
4089.9	17.5°	4264.6	4468.4	4672.1	4865.8	5059.5	5233.2	5407.0
3966.3	20°	4182.8	4429.7	4676.7	4889.5	5102.3	5283.0	5463.6
3821.3	22.5°	4081.9	4382.3	4682.7	4921.5	5160.2	5344.8	5529.2
3659.3	25°	3964.7	4335.5	4706.6	4979.5	5252.2	5432.9	5613.8
3511.2	27.5°	3852.2	4304.3	4756.4	5070.0	5383.6	5556.1	5728.5
3387.4	30°	3754.4	4289.6	4824.6	5187.3	5550.1	5716.6	5883.2
3280.7	32.5°	3659.3	4271.5	4883.5	5309.8	5736.0	5900.9	6065.9
3175.8	35°	3548.5	4237.4	4926.6	5449.2	5971.8	6129.9	6287.7
3052.3	37.5°	3405.7	4179.0	4952.3	5605.5	6258.6	6460.0	6661.3
2905.0	40°	3228.8	4098.5	4968.5	5803.8	6639.0	6932.4	7225.9
2742.4	42.5°	3032.2	4015.5	4999.1	6063.3	7127.5	7551.0	7974.6
2569.7	45°	2823.9	3938.4	5053.0	6404.7	7756.5	8327.8	8899.1
2433.1	47.5°	2659.4	3874.7	5090.0	6768.5	8447.1	9251.3	10055.4
2342.4	50°	2544.7	3805.3	5065.8	7106.0	9146.3	10358.7	11570.9
2282.6	52.5°	2458.9	3688.0	4917.1	7325.2	9733.1	11521.9	13310.6
2239.3	55°	2377.1	3493.5	4610.0	7276.9	9943.7	12553.2	15162.7
2188.0	57.5°	2285.4	3219.4	4153.3	6937.0	9720.8	13284.0	16847.3
2109.5	60°	2186.0	2863.5	3540.9	6304.3	9067.8	13466.7	17865.5
1973.0	62.5°	2023.9	2437.5	2851.1	5448.9	8046.7	12697.6	17348.5
1837.2	65°	1861.2	2054.3	2247.3	4576.1	6905.1	11609.4	16313.7
1644.4	67.5°	1631.0	1685.9	1740.7	3721.2	5701.6	10314.4	14927.3
1412.0	70°	1349.8	1334.2	1318.5	2929.9	4541.3	8901.4	13261.6
1199.9	72.5°	1111.7	1064.3	1017.1	2239.9	3462.8	7369.6	11276.6
974.2	75°	875.5	832.6	789.8	1625.7	2461.7	5613.6	8765.6
762.3	77.5°	666.4	637.2	608.0	1101.6	1595.2	3929.0	6262.8
561.2	80°	480.0	467.9	455.9	709.8	963.8	2531.4	4099.0
390.1	82.5°	330.3	327.9	325.7	436.5	547.6	1465.1	2382.7
238.5	85°	194.7	195.9	197.0	233.4	269.9	659.0	1048.3
102.0	87.5°	84.2	85.3	86.3	96.8	107.2	215.9	324.5
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)