

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P940191

Luminaire Tested: **GALN-SB3A-927-U-SL4-HSS**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P940191
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2405-108-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GALN-SB3A-927-U-SL4-HSS
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(3) 90 CRI, 2700K, 350mA LIGHTSQUARES WITH 26 LEDS EACH AND TYPE IV SPILL
LIGHT ELIMINATOR OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5719 lumens
Efficiency: N/A
Efficacy: 67.5 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 84.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P940191
CATALOG NUMBER: GALN-SB3A-927-U-SL4-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral - - - Horizontal Cone Through 72.5-Deg Vertical

REPORT NUMBER: P940191
 CATALOG NUMBER: GALN-SB3A-927-U-SL4-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	738.6	0.0	738.6
	% Fixture	12.9	0.0	12.9
Street Side	Lumens	4980.4	0.0	4980.4
	% Fixture	87.1	0.0	87.1
Total	Lumens	5719.0	0.0	5719.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.2	1.2
10°-20°	187.8	3.3
20°-30°	303.9	5.3
30°-40°	448.6	7.8
40°-50°	755.1	13.2
50°-60°	1172.4	20.5
60°-70°	1467.0	25.7
70°-80°	1201.1	21.0
80°-90°	113.9	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5719.0	100.0
0°-180°	5719.0	100.0

Coefficient of Utilization




REPORT NUMBER: P940191
 CATALOG NUMBER: GALN-SB3A-927-U-SL4-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	379.6	6.6			
FM (30°-60°)	1922.6	33.6			
FH (60°-80°)	2565.2	44.9			G2/5000
FVH (80°-90°)	113.0	2.0			G2/225
BL (0°-30°)	181.3	3.2	B1/500		
BM (30°-60°)	453.5	7.9	B1/1000		
BH (60°-80°)	102.9	1.8	B0/110		G0/110
BVH (80°-90°)	0.9	0.0			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short



REPORT NUMBER: P940191
 CATALOG NUMBER: GALN-SB3A-927-U-SL4-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	40°	45°	55°	65°	75°
0°	757.2	757.2	757.2	757.2	757.2	757.2	757.2	757.2	757.2	757.2
2.5°	780.1	783.1	781.4	777.9	777.1	775.3	773.2	772.3	769.3	766.7
5°	802.0	805.1	802.9	798.2	796.0	793.9	790.8	788.3	782.2	776.6
7.5°	826.2	828.7	826.2	819.3	815.8	813.2	808.9	805.1	798.2	790.0
10°	852.9	855.0	851.1	842.1	836.5	832.6	828.7	824.4	818.0	808.9
12.5°	877.8	880.4	874.4	863.6	857.2	853.3	849.0	845.5	839.1	830.5
15°	900.7	904.6	894.2	882.6	875.3	872.2	867.9	865.8	861.5	855.5
17.5°	917.9	920.5	909.7	895.9	887.8	885.6	882.6	883.9	883.0	880.0
20°	932.6	934.3	920.1	903.3	894.2	894.6	893.8	898.1	899.8	899.8
22.5°	950.6	951.1	933.0	911.9	901.1	904.1	905.4	910.2	913.6	917.0
25°	974.3	973.5	951.9	923.1	913.6	917.9	920.9	922.6	926.5	932.1
27.5°	1009.7	1007.1	979.5	941.2	930.0	933.8	939.4	938.6	936.9	941.2
30°	1054.5	1051.0	1014.4	966.6	956.2	959.7	961.4	953.7	941.2	945.0
32.5°	1125.5	1119.5	1068.7	995.0	979.1	983.0	980.8	964.9	946.3	950.2
35°	1249.1	1234.5	1162.6	1054.5	1004.9	1000.6	995.4	979.9	957.1	953.2
37.5°	1511.9	1486.1	1363.3	1170.3	1063.5	1035.5	1019.6	1004.1	968.7	953.2
40°	1808.2	1782.0	1640.3	1364.2	1160.8	1113.5	1075.6	1032.5	980.8	958.8
42.5°	2117.5	2088.7	1943.1	1604.5	1300.0	1202.6	1132.0	1055.3	1000.6	976.1
45°	2463.0	2426.8	2236.4	1855.2	1502.0	1350.8	1222.9	1102.3	1035.1	1006.6
47.5°	2827.4	2780.4	2528.9	2098.6	1719.5	1555.8	1389.1	1186.3	1085.9	1052.3
50°	3150.4	3103.9	2830.8	2353.1	1922.8	1751.0	1578.7	1302.6	1162.1	1116.9
52.5°	3382.6	3347.3	3105.6	2615.9	2134.3	1934.0	1750.5	1437.8	1258.6	1199.6
55°	3538.1	3505.8	3300.3	2864.9	2380.3	2135.6	1919.8	1584.7	1374.9	1298.7
57.5°	3632.4	3613.9	3441.2	3087.1	2624.1	2356.2	2113.6	1746.2	1511.9	1415.4
60°	3666.0	3651.0	3528.6	3299.0	2918.7	2621.1	2341.5	1928.4	1678.2	1548.1
62.5°	3576.4	3579.5	3591.5	3550.2	3229.3	2931.2	2614.6	2147.2	1862.5	1698.4
65°	3154.7	3179.7	3408.9	3828.4	3640.6	3319.7	2962.2	2414.3	2073.6	1869.4
67.5°	2612.0	2648.2	2933.3	3991.2	4079.1	3824.1	3446.4	2754.6	2325.1	2043.4
70°	1999.5	2038.3	2383.7	3957.2	4489.6	4375.5	4045.1	3187.5	2585.7	2164.0
72.5°	1427.0	1446.9	1719.1	3654.4	4658.0	4751.1	4486.2	3597.5	2718.8	2097.3
75°	1002.8	999.3	1179.8	2942.8	4395.7	4705.4	4331.5	3375.7	2460.4	1666.1
77.5°	436.8	437.6	589.3	1787.1	3508.4	4018.8	3600.6	2114.5	1715.2	883.0
80°	113.3	116.7	216.2	711.6	2112.4	2652.5	2195.9	929.5	792.6	215.4
82.5°	40.1	42.6	99.5	223.6	779.2	1216.4	977.8	297.2	206.8	61.6
85°	11.6	13.8	53.4	68.5	161.1	343.7	237.3	57.7	50.8	31.9
87.5°	0.0	1.7	10.8	9.5	9.5	6.5	12.1	6.5	8.2	3.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P940191
 CATALOG NUMBER: GALN-SB3A-927-U-SL4-HSS

CANDELA DISTRIBUTION (continued):

85°		90°	95°	105°	115°	125°	135°	145°	155°	165°	175°
757.2	0°	757.2	757.2	757.2	757.2	757.2	757.2	757.2	757.2	757.2	757.2
763.7	2.5°	761.1	758.1	751.6	744.8	738.3	732.3	730.5	724.1	721.1	721.5
769.7	5°	765.0	759.4	746.9	731.8	716.3	698.7	684.0	663.3	645.7	643.5
781.4	7.5°	775.3	766.3	746.0	716.8	678.0	629.3	584.1	539.3	513.9	500.1
798.6	10°	791.3	779.2	748.2	692.2	609.9	522.9	454.4	398.0	369.1	355.8
819.7	12.5°	810.2	796.9	751.6	650.4	522.1	407.9	333.8	299.4	293.3	292.5
845.5	15°	836.9	822.3	755.5	594.0	426.9	310.6	276.5	277.0	281.7	284.3
873.5	17.5°	866.7	852.0	749.9	525.1	333.0	265.3	264.5	268.4	275.2	277.8
899.4	20°	896.8	883.0	730.1	444.1	269.2	252.8	256.3	260.6	267.5	270.9
924.8	22.5°	927.8	915.8	698.7	357.9	242.9	243.8	248.1	252.4	260.2	264.0
949.8	25°	961.0	950.6	656.9	286.9	231.7	234.3	239.9	245.1	253.3	258.0
970.9	27.5°	994.6	986.8	609.5	239.5	221.4	224.4	230.9	237.8	246.0	251.6
989.4	30°	1031.2	1026.9	571.6	221.8	211.5	214.1	221.4	229.2	238.2	245.1
1007.9	32.5°	1068.7	1067.8	553.1	234.8	202.4	204.2	210.6	218.4	229.6	238.2
1023.4	35°	1105.7	1107.4	542.3	271.4	199.4	194.7	199.0	205.9	219.2	230.0
1041.1	37.5°	1153.1	1157.4	541.9	311.0	206.8	185.2	188.2	193.0	204.6	217.1
1068.7	40°	1223.7	1246.6	569.4	345.0	219.7	176.6	177.5	178.3	184.4	194.7
1105.3	42.5°	1317.6	1384.4	668.9	368.3	224.8	168.9	165.8	161.1	160.2	165.8
1155.2	45°	1434.4	1551.1	843.8	381.2	219.7	160.2	152.1	139.6	134.8	138.7
1222.9	47.5°	1571.8	1733.7	1051.0	384.2	211.1	149.5	134.8	118.5	114.6	115.9
1313.8	50°	1705.7	1870.7	1233.2	359.2	196.8	135.7	115.9	102.1	99.5	99.9
1421.0	52.5°	1824.2	1917.7	1284.9	300.2	177.9	118.9	99.5	90.0	88.3	88.3
1539.5	55°	1902.6	1866.8	1145.8	229.6	154.2	101.7	85.3	80.5	79.7	79.3
1671.7	57.5°	1918.9	1701.4	865.4	165.8	120.6	85.7	75.8	73.2	71.5	69.8
1807.4	60°	1860.4	1425.8	550.9	115.9	90.5	73.2	67.2	65.5	62.0	58.6
1934.9	62.5°	1733.7	1076.9	305.0	80.5	72.8	62.5	59.4	57.3	50.8	45.2
2036.1	65°	1563.6	715.9	134.8	62.9	59.4	52.6	50.8	47.8	40.1	33.6
2074.4	67.5°	1392.6	412.2	60.7	50.4	47.8	43.1	41.8	39.6	34.0	28.0
1976.7	70°	1197.5	208.9	41.8	40.1	37.0	32.7	34.0	33.6	28.0	22.8
1612.3	72.5°	891.6	103.8	31.4	30.2	26.7	23.3	28.0	27.6	22.0	17.2
994.1	75°	504.8	51.3	22.8	21.1	15.9	17.2	22.4	21.1	15.1	11.2
419.5	77.5°	200.3	26.3	15.1	12.9	9.5	11.6	16.4	14.2	7.8	4.7
80.1	80°	46.1	12.9	7.8	5.6	4.3	6.9	8.6	5.2	2.2	0.4
21.5	82.5°	12.9	5.6	2.6	2.2	2.2	2.6	2.2	0.9	0.0	0.0
5.6	85°	4.3	2.6	0.9	0.4	0.4	0.4	0.4	0.0	0.0	0.0
1.7	87.5°	1.7	0.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END O

<u>180°</u>
757.2
721.1
642.2
499.2
353.2
292.0
283.9
277.4
270.9
264.0
258.0
252.0
246.0
239.1
231.7
219.2
198.1
168.9
138.7
115.4
99.9
87.9
78.4
68.9
57.3
43.5
32.3
27.1
22.0
16.4
10.3
4.3
0.0
0.0
0.0
0.0
0.0

F REPORT)