

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P952936

Luminaire Tested: **GALN-SB6C-927-U-5MQ**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P952936
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GALN-SB6C-927-U-5MQ
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(6) 90 CRI, 2700K, 615mA LIGHTSQUARES WITH 26 LEDS EACH AND TYPE V MEDIUM OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 28950 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type V - Short
BUG Rating: B5 - U0 - G3


Input Watts (W): 300.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P952936
 CATALOG NUMBER: GALN-SB6C-927-U-5MQ

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 4.4 fc
 Type V - Short - N/A

REPORT NUMBER: P952936
CATALOG NUMBER: GALN-SB6C-927-U-5MQ

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P952936

CATALOG NUMBER: GALN-SB6C-927-U-5MQ

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	14475.0	0.0	14475.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	14475.0	0.0	14475.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	28950.0	0.0	28950.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	269.4	0.9
10°-20°	835.4	2.9
20°-30°	1493.0	5.2
30°-40°	2420.1	8.4
40°-50°	3941.9	13.6
50°-60°	6010.1	20.8
60°-70°	8941.1	30.9
70°-80°	4873.2	16.8
80°-90°	165.9	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	28950.0	100.0
0°-180°	28950.0	100.0

Coefficient of Utilization



REPORT NUMBER: P952936


CATALOG NUMBER: GALN-SB6C-927-U-5MQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1298.9	4.5			
FM (30°-60°)	6186.0	21.4			
FH (60°-80°)	6907.1	23.9			G3/7500
FVH (80°-90°)	83.0	0.3			G1/100
BL (0°-30°)	1298.9	4.5	B3/2500		
BM (30°-60°)	6186.0	21.4	B4/8500		
BH (60°-80°)	6907.1	23.9	B5		G3/7500
BVH (80°-90°)	83.0	0.3			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B5-U0-G3

Type V Short



REPORT NUMBER: P952936
 CATALOG NUMBER: GALN-SB6C-927-U-5MQ

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	2773.1	2773.1	2773.1	2773.1	2773.1	2773.1	2773.1	2773.1	2773.1	2773.1
2.5°	2786.2	2789.1	2783.3	2780.4	2777.5	2773.1	2774.6	2781.8	2787.6	2786.2
5°	2809.4	2812.4	2808.0	2806.5	2800.7	2799.3	2799.3	2806.5	2810.9	2808.0
7.5°	2835.6	2840.0	2832.7	2831.2	2828.3	2825.4	2824.0	2831.2	2835.6	2835.6
10°	2860.3	2864.7	2858.9	2854.5	2851.6	2851.6	2848.7	2854.5	2861.8	2860.3
12.5°	2886.5	2889.4	2883.6	2880.7	2880.7	2885.0	2880.7	2883.6	2889.4	2886.5
15°	2918.5	2919.9	2918.5	2922.8	2930.1	2944.6	2931.5	2928.6	2931.5	2924.3
17.5°	2962.1	2965.0	2970.8	2980.9	2991.1	3017.3	2994.0	2986.8	2986.8	2972.2
20°	3015.8	3020.2	3028.9	3046.4	3059.4	3084.1	3060.9	3050.7	3046.4	3027.5
22.5°	3072.5	3079.8	3092.9	3116.1	3139.4	3162.6	3139.4	3121.9	3108.8	3084.1
25°	3137.9	3146.6	3167.0	3204.8	3236.7	3270.2	3242.6	3207.7	3181.5	3146.6
27.5°	3230.9	3241.1	3265.8	3312.3	3353.0	3382.1	3355.9	3310.9	3274.5	3232.4
30°	3361.7	3371.9	3401.0	3450.4	3478.0	3496.9	3479.5	3444.6	3401.0	3353.0
32.5°	3530.3	3543.4	3575.4	3621.9	3627.7	3630.6	3624.8	3607.4	3575.4	3517.3
35°	3744.0	3758.5	3794.9	3832.6	3826.8	3832.6	3823.9	3818.1	3794.9	3728.0
37.5°	4005.6	4023.0	4060.8	4089.9	4075.4	4068.1	4069.6	4071.0	4057.9	3983.8
40°	4309.4	4332.6	4360.2	4390.8	4366.1	4344.2	4358.8	4370.4	4358.8	4283.2
42.5°	4621.9	4655.3	4684.3	4727.9	4707.6	4680.0	4700.3	4713.4	4688.7	4607.3
45°	4969.2	5001.2	5039.0	5104.4	5089.8	5060.8	5089.8	5092.8	5050.6	4954.7
47.5°	5328.2	5361.6	5418.3	5505.5	5499.7	5467.7	5505.5	5485.2	5431.4	5316.6
50°	5668.3	5714.8	5802.0	5924.1	5935.7	5896.5	5947.4	5908.1	5818.0	5674.1
52.5°	5988.1	6037.5	6175.5	6341.2	6383.4	6332.5	6400.8	6332.5	6197.3	6012.8
55°	6323.8	6379.0	6543.3	6759.8	6844.1	6806.3	6870.3	6767.1	6575.2	6351.4
57.5°	6719.1	6752.6	6948.8	7206.0	7348.5	7357.2	7386.2	7211.8	6979.3	6724.9
60°	7147.9	7194.4	7408.0	7716.2	7941.4	8014.1	7983.6	7724.9	7454.6	7162.4
62.5°	7697.3	7748.1	8003.9	8373.1	8729.2	8909.4	8790.2	8415.3	8081.0	7730.7
65°	8152.2	8208.9	8671.1	9329.5	9977.7	10339.6	10040.2	9349.8	8748.1	8253.9
67.5°	7822.3	7892.0	8617.3	9826.5	11438.4	12518.2	11493.6	9974.8	8796.1	8126.0
70°	6836.9	6902.3	7748.1	9226.3	11849.7	14215.8	12096.7	9498.0	7775.8	7025.8
72.5°	4539.0	4749.8	5605.8	7379.0	10580.8	13154.8	10685.5	7229.3	5200.3	4528.8
75°	1505.7	1674.3	2258.6	3825.4	7086.8	9838.1	6746.7	3385.0	1789.2	1287.7
77.5°	379.3	437.5	603.2	1094.4	2826.9	5601.5	2544.9	893.8	486.9	340.1
80°	184.6	203.5	290.7	364.8	707.8	1780.4	664.2	343.0	229.6	177.3
82.5°	101.7	103.2	164.2	206.4	263.1	460.7	273.2	200.6	132.3	107.6
85°	62.5	61.0	87.2	110.5	110.5	164.2	130.8	110.5	75.6	66.9
87.5°	24.7	24.7	32.0	34.9	30.5	42.1	33.4	36.3	29.1	27.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END C

90°
2773.1
2787.6
2809.4
2835.6
2860.3
2885.0
2924.3
2972.2
3027.5
3082.7
3145.2
3230.9
3353.0
3518.7
3728.0
3983.8
4283.2
4613.1
4964.9
5309.3
5671.2
5995.3
6320.9
6690.1
7115.9
7669.7
8172.5
8025.7
6925.5
4382.0
1218.0
303.8
162.8
107.6
69.8
29.1
0.0

OF REPORT)