

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1435123

Luminaire Tested: **GALN-SB6A-940-U-T3LG**

Issue Date: 03/24/202

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Report Generated By 670245763



**Test Information**

Test Method: LM-79-08  
 Report Number: P1435123  
 Test Lab: INNOVATION CENTER(G1)  
 Issue Date: 03/24/202  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: McGRAW-EDISON  
 Catalog Number: GALN-SB6A-940-U-T3LG  
 Description: GALLEON II AREA AND ROADWAY HIGH DENSITY LUMINAIRE 350mA 6xLight  
 Square PACKAGE 90CRI 4000K FIXTURE w/ TYPE III LOW GLARE  
 Light Source: (156) 4000K CCT, 90 CRI LEDS  
 Ballast/Driver: ELECTRONIC DRIVER  
 Luminaire Equipment:

| <u>Sample No.</u> | <u>Condition</u> | <u>Description</u> |
|-------------------|------------------|--------------------|
| a                 | good             | reflector          |
| b                 | good             | lens               |
| c                 | good             | housing            |
| d                 | good             | cord               |


**Summary**

Lumens per Lamp: N/A  
 Luminaire Lumens: 19228.6 lumens  
 Efficiency: N/A  
 Efficacy: 112.5 lumens/watt  
 Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
 IES Classification: Type III - Short  
 BUG Rating: B3 - U0 - G2  
  
 Input Watts (W): 170.9  
 Input Voltage (V): 120  
 Input Current (A<sub>in</sub>): NR  
 Voltage Rise (V): NR  
 Power Factor: 0.97  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 28.75 FT

REPORT NUMBER: P1435123  
 CATALOG NUMBER: GALN-SB6A-940-U-T3LG

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 11 fc  
 Type III - Short - N/A

REPORT NUMBER: P1435123  
CATALOG NUMBER: GALN-SB6A-940-U-T3LG

### Luminous Intensity Polar Plot



— Vertical Plane Through 79-Deg Lateral      - - - Horizontal Cone Through 53-Deg Vertical

REPORT NUMBER: P1435123  
 CATALOG NUMBER: GALN-SB6A-940-U-T3LG

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 4847.4   | 0.0    | 4847.4  |
|                    | % Fixture | 25.2     | 0.0    | 25.2    |
| <b>Street Side</b> | Lumens    | 14381.2  | 0.0    | 14381.2 |
|                    | % Fixture | 74.8     | 0.0    | 74.8    |
| <b>Total</b>       | Lumens    | 19228.6  | 0.0    | 19228.6 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 269.0   | 1.4       |
| 10°-20°   | 832.9   | 4.3       |
| 20°-30°   | 1592.4  | 8.3       |
| 30°-40°   | 2734.1  | 14.2      |
| 40°-50°   | 3829.6  | 19.9      |
| 50°-60°   | 4346.1  | 22.6      |
| 60°-70°   | 3811.3  | 19.8      |
| 70°-80°   | 1490.3  | 7.8       |
| 80°-90°   | 322.9   | 1.7       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 19228.6 | 100.0     |
| 0°-180°   | 19228.6 | 100.0     |




REPORT NUMBER: P1435123  
 CATALOG NUMBER: GALN-SB6A-940-U-T3LG

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 1528.5 | 7.9       |                         |      |         |
| FM (30°-60°)   | 8381.1 | 43.6      |                         |      |         |
| FH (60°-80°)   | 4315.0 | 22.4      |                         |      | G2/5000 |
| FVH (80°-90°)  | 156.6  | 0.8       |                         |      | G2/225  |
| BL (0°-30°)    | 1165.8 | 6.1       | B3/2500                 |      |         |
| BM (30°-60°)   | 2528.8 | 13.2      | B3/5000                 |      |         |
| BH (60°-80°)   | 986.5  | 5.1       | B2/1000                 |      | G2/1000 |
| BVH (80°-90°)  | 166.3  | 0.9       |                         |      | G2/225  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G2**  
 Type III Short





REPORT NUMBER: P1435123  
 CATALOG NUMBER: GALN-SB6A-940-U-T3LG

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°     | 79°     | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|---------|---------|--------|
| 0°    | 2822.8 | 2822.8 | 2822.8 | 2822.8 | 2822.8 | 2822.8 | 2822.8 | 2822.8 | 2822.8  | 2822.8  | 2822.8 |
| 2.5°  | 2827.1 | 2827.1 | 2810.0 | 2827.1 | 2818.5 | 2831.4 | 2839.9 | 2839.9 | 2857.1  | 2852.8  | 2852.8 |
| 5°    | 2780.0 | 2771.4 | 2767.1 | 2797.1 | 2814.2 | 2848.5 | 2887.1 | 2904.2 | 2934.2  | 2934.2  | 2938.5 |
| 7.5°  | 2655.7 | 2651.5 | 2672.9 | 2732.9 | 2788.5 | 2874.2 | 2955.6 | 3002.7 | 3049.8  | 3058.4  | 3058.4 |
| 10°   | 2578.6 | 2574.4 | 2600.1 | 2672.9 | 2762.8 | 2887.1 | 3015.6 | 3114.1 | 3191.2  | 3212.6  | 3212.6 |
| 12.5° | 2578.6 | 2578.6 | 2600.1 | 2672.9 | 2767.1 | 2917.0 | 3092.7 | 3259.7 | 3379.7  | 3405.4  | 3396.8 |
| 15°   | 2651.5 | 2647.2 | 2672.9 | 2750.0 | 2839.9 | 2981.3 | 3195.5 | 3418.2 | 3581.0  | 3628.1  | 3632.4 |
| 17.5° | 2728.6 | 2724.3 | 2762.8 | 2861.4 | 2968.4 | 3109.8 | 3328.3 | 3602.4 | 3833.7  | 3893.7  | 3906.5 |
| 20°   | 2848.5 | 2844.2 | 2891.3 | 2985.6 | 3118.4 | 3281.1 | 3508.2 | 3820.9 | 4142.1  | 4206.4  | 4223.5 |
| 22.5° | 2985.6 | 2989.9 | 3041.3 | 3156.9 | 3289.7 | 3503.9 | 3782.3 | 4129.3 | 4514.8  | 4613.3  | 4630.4 |
| 25°   | 3272.6 | 3259.7 | 3302.6 | 3383.9 | 3525.3 | 3782.3 | 4125.0 | 4501.9 | 4960.3  | 5080.2  | 5101.6 |
| 27.5° | 3653.8 | 3632.4 | 3679.5 | 3760.9 | 3863.7 | 4103.6 | 4497.6 | 4917.4 | 5470.0  | 5619.9  | 5624.2 |
| 30°   | 3996.5 | 3983.6 | 4047.9 | 4214.9 | 4322.0 | 4506.2 | 4926.0 | 5405.7 | 6099.7  | 6318.1  | 6326.7 |
| 32.5° | 4292.0 | 4287.7 | 4407.7 | 4621.9 | 4866.0 | 5063.1 | 5470.0 | 6022.6 | 6896.4  | 7149.1  | 7093.4 |
| 35°   | 4574.7 | 4587.6 | 4737.5 | 4960.3 | 5285.8 | 5679.9 | 6091.1 | 6720.8 | 7735.9  | 8040.1  | 7950.1 |
| 37.5° | 4861.7 | 4870.3 | 5067.3 | 5354.3 | 5697.0 | 6211.0 | 6763.6 | 7478.9 | 8464.1  | 8841.1  | 8644.0 |
| 40°   | 5127.3 | 5153.0 | 5418.6 | 5727.0 | 6172.5 | 6695.1 | 7311.9 | 8005.8 | 9025.3  | 9397.9  | 9183.8 |
| 42.5° | 5392.9 | 5431.4 | 5718.4 | 6142.5 | 6618.0 | 7162.0 | 7693.1 | 8327.1 | 9385.1  | 9800.6  | 9470.7 |
| 45°   | 5667.0 | 5692.7 | 6048.3 | 6489.5 | 7029.2 | 7530.3 | 7911.6 | 8532.7 | 9633.5  | 10083.3 | 9633.5 |
| 47.5° | 5851.2 | 5902.6 | 6292.4 | 6802.1 | 7341.9 | 7813.0 | 8087.2 | 8618.3 | 9792.0  | 10267.5 | 9693.5 |
| 50°   | 5924.0 | 5996.9 | 6416.6 | 6982.0 | 7598.9 | 8078.6 | 8224.3 | 8665.5 | 9967.6  | 10430.2 | 9680.6 |
| 52.5° | 5911.2 | 5979.7 | 6438.0 | 7063.4 | 7804.5 | 8322.8 | 8357.0 | 8716.9 | 10091.8 | 10485.9 | 9569.3 |
| 53°   | 5842.6 | 5936.9 | 6450.9 | 7067.7 | 7834.5 | 8387.0 | 8417.0 | 8721.1 | 10109.0 | 10563.0 | 9552.1 |
| 55°   | 5607.1 | 5658.5 | 6318.1 | 7063.4 | 7975.8 | 8626.9 | 8584.1 | 8849.6 | 10156.1 | 10511.6 | 9363.7 |
| 57.5° | 5392.9 | 5444.3 | 6018.3 | 6982.0 | 8091.5 | 8965.3 | 8853.9 | 8828.2 | 9899.1  | 10220.4 | 8888.2 |
| 60°   | 5255.8 | 5272.9 | 5757.0 | 6725.0 | 8044.3 | 9200.9 | 9029.5 | 8575.5 | 9265.1  | 9530.7  | 8052.9 |
| 62.5° | 5140.2 | 5135.9 | 5564.2 | 6356.7 | 7864.4 | 9235.2 | 9063.8 | 7950.1 | 8335.6  | 8378.5  | 6939.2 |
| 65°   | 4878.9 | 4848.9 | 5264.4 | 5941.2 | 7491.8 | 9080.9 | 8644.0 | 7003.5 | 7102.0  | 6960.6  | 5572.8 |
| 67.5° | 4360.6 | 4296.3 | 4664.7 | 5307.2 | 6733.6 | 8644.0 | 7843.0 | 5902.6 | 5598.5  | 5315.8  | 4197.8 |
| 70°   | 3122.6 | 3122.6 | 3418.2 | 4060.7 | 5405.7 | 7470.4 | 6733.6 | 4467.7 | 3855.1  | 3602.4  | 2805.7 |
| 72.5° | 1529.2 | 1567.7 | 1876.2 | 2398.7 | 3623.8 | 5422.9 | 5157.3 | 2895.6 | 2338.8  | 2214.6  | 1799.1 |
| 75°   | 651.1  | 655.4  | 801.0  | 1062.3 | 1837.6 | 3208.3 | 3229.7 | 1670.6 | 1499.2  | 1439.2  | 1190.8 |
| 77.5° | 454.0  | 462.6  | 526.9  | 625.4  | 873.8  | 1473.5 | 1679.1 | 1010.9 | 1006.6  | 963.8   | 848.1  |
| 80°   | 347.0  | 355.5  | 398.4  | 466.9  | 586.8  | 753.9  | 869.5  | 685.4  | 719.6   | 676.8   | 612.5  |
| 82.5° | 261.3  | 269.9  | 299.8  | 351.2  | 419.8  | 505.4  | 488.3  | 505.4  | 531.1   | 505.4   | 441.2  |
| 85°   | 175.6  | 179.9  | 201.3  | 244.2  | 269.9  | 304.1  | 304.1  | 368.4  | 385.5   | 376.9   | 347.0  |
| 87.5° | 90.0   | 90.0   | 107.1  | 128.5  | 137.1  | 141.4  | 124.2  | 162.8  | 184.2   | 201.3   | 162.8  |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0    |



REPORT NUMBER: P1435123  
 CATALOG NUMBER: GALN-SB6A-940-U-T3LG

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 2822.8 | 2822.8 | 2822.8 | 2822.8 | 2822.8 | 2822.8 | 2822.8 | 2822.8 | 2822.8 | 2822.8 | 2822.8 |
| 2.5°  | 2852.8 | 2857.1 | 2844.2 | 2839.9 | 2835.7 | 2814.2 | 2814.2 | 2792.8 | 2788.5 | 2792.8 | 2780.0 |
| 5°    | 2947.0 | 2938.5 | 2904.2 | 2878.5 | 2848.5 | 2788.5 | 2754.3 | 2707.2 | 2694.3 | 2681.4 | 2668.6 |
| 7.5°  | 3062.7 | 3049.8 | 2989.9 | 2921.3 | 2839.9 | 2724.3 | 2660.0 | 2582.9 | 2557.2 | 2535.8 | 2527.2 |
| 10°   | 3208.3 | 3182.6 | 3088.4 | 2942.7 | 2792.8 | 2651.5 | 2561.5 | 2467.3 | 2424.4 | 2415.9 | 2394.5 |
| 12.5° | 3396.8 | 3349.7 | 3174.0 | 2947.0 | 2750.0 | 2565.8 | 2467.3 | 2394.5 | 2377.3 | 2373.0 | 2351.6 |
| 15°   | 3606.7 | 3538.1 | 3255.4 | 2951.3 | 2694.3 | 2493.0 | 2433.0 | 2394.5 | 2394.5 | 2390.2 | 2377.3 |
| 17.5° | 3863.7 | 3752.3 | 3332.5 | 2934.2 | 2625.8 | 2471.6 | 2441.6 | 2407.3 | 2398.7 | 2403.0 | 2385.9 |
| 20°   | 4172.1 | 3987.9 | 3413.9 | 2912.8 | 2595.8 | 2475.8 | 2441.6 | 2394.5 | 2373.0 | 2368.8 | 2355.9 |
| 22.5° | 4527.6 | 4257.8 | 3503.9 | 2878.5 | 2595.8 | 2471.6 | 2415.9 | 2351.6 | 2308.8 | 2291.7 | 2274.5 |
| 25°   | 4934.6 | 4570.5 | 3598.1 | 2865.6 | 2604.3 | 2454.4 | 2364.5 | 2261.7 | 2193.1 | 2167.4 | 2154.6 |
| 27.5° | 5427.2 | 4900.3 | 3666.6 | 2878.5 | 2600.1 | 2415.9 | 2274.5 | 2141.7 | 2064.6 | 2021.8 | 2013.2 |
| 30°   | 5971.2 | 5255.8 | 3713.8 | 2899.9 | 2574.4 | 2343.1 | 2167.4 | 2017.5 | 1910.4 | 1859.0 | 1846.2 |
| 32.5° | 6613.7 | 5654.2 | 3760.9 | 2899.9 | 2510.1 | 2240.3 | 2043.2 | 1880.4 | 1769.1 | 1709.1 | 1700.5 |
| 35°   | 7324.7 | 6142.5 | 3803.7 | 2895.6 | 2433.0 | 2128.9 | 1919.0 | 1751.9 | 1636.3 | 1576.3 | 1572.0 |
| 37.5° | 7928.7 | 6510.9 | 3825.1 | 2852.8 | 2325.9 | 2000.4 | 1803.3 | 1636.3 | 1516.3 | 1452.1 | 1447.8 |
| 40°   | 8301.4 | 6665.1 | 3782.3 | 2767.1 | 2197.4 | 1867.6 | 1674.8 | 1520.6 | 1400.7 | 1323.6 | 1306.5 |
| 42.5° | 8442.7 | 6592.3 | 3645.2 | 2625.8 | 2043.2 | 1734.8 | 1567.7 | 1405.0 | 1246.5 | 1182.2 | 1169.4 |
| 45°   | 8395.6 | 6309.5 | 3354.0 | 2424.4 | 1871.9 | 1614.9 | 1473.5 | 1289.3 | 1186.5 | 1130.8 | 1126.6 |
| 47.5° | 8237.1 | 5872.6 | 2989.9 | 2171.7 | 1692.0 | 1507.8 | 1349.3 | 1259.3 | 1165.1 | 1105.1 | 1100.9 |
| 50°   | 7958.7 | 5405.7 | 2552.9 | 1884.7 | 1529.2 | 1396.4 | 1319.3 | 1246.5 | 1169.4 | 1122.3 | 1113.7 |
| 52.5° | 7603.2 | 4878.9 | 2150.3 | 1606.3 | 1387.8 | 1297.9 | 1289.3 | 1237.9 | 1178.0 | 1126.6 | 1105.1 |
| 53°   | 7521.8 | 4741.8 | 2073.2 | 1559.2 | 1366.4 | 1285.0 | 1280.8 | 1237.9 | 1169.4 | 1122.3 | 1105.1 |
| 55°   | 7132.0 | 4317.7 | 1829.0 | 1392.1 | 1259.3 | 1242.2 | 1280.8 | 1233.6 | 1148.0 | 1109.4 | 1096.6 |
| 57.5° | 6506.6 | 3760.9 | 1593.4 | 1237.9 | 1148.0 | 1190.8 | 1267.9 | 1216.5 | 1122.3 | 1053.7 | 1032.3 |
| 60°   | 5752.7 | 3122.6 | 1413.5 | 1135.1 | 1066.6 | 1126.6 | 1216.5 | 1156.5 | 1028.0 | 993.8  | 989.5  |
| 62.5° | 4853.2 | 2527.2 | 1276.5 | 1049.4 | 998.0  | 1058.0 | 1139.4 | 1036.6 | 942.4  | 916.7  | 908.1  |
| 65°   | 3790.9 | 2008.9 | 1169.4 | 985.2  | 929.5  | 976.6  | 1032.3 | 968.1  | 908.1  | 886.7  | 882.4  |
| 67.5° | 2818.5 | 1576.3 | 1083.7 | 929.5  | 861.0  | 891.0  | 955.2  | 938.1  | 886.7  | 873.8  | 869.5  |
| 70°   | 1944.7 | 1280.8 | 1006.6 | 878.1  | 775.3  | 809.6  | 908.1  | 920.9  | 869.5  | 861.0  | 856.7  |
| 72.5° | 1362.1 | 1083.7 | 925.2  | 822.4  | 706.8  | 741.0  | 886.7  | 886.7  | 831.0  | 843.8  | 835.3  |
| 75°   | 1023.7 | 912.4  | 831.0  | 753.9  | 621.1  | 672.5  | 856.7  | 848.1  | 792.4  | 848.1  | 826.7  |
| 77.5° | 771.0  | 736.8  | 719.6  | 668.2  | 544.0  | 595.4  | 796.7  | 779.6  | 706.8  | 711.1  | 672.5  |
| 80°   | 561.1  | 569.7  | 616.8  | 569.7  | 454.0  | 492.6  | 672.5  | 663.9  | 574.0  | 591.1  | 544.0  |
| 82.5° | 402.6  | 424.1  | 526.9  | 458.3  | 329.8  | 351.2  | 462.6  | 501.2  | 449.8  | 424.1  | 432.6  |
| 85°   | 304.1  | 317.0  | 424.1  | 338.4  | 205.6  | 231.3  | 317.0  | 359.8  | 351.2  | 325.5  | 329.8  |
| 87.5° | 128.5  | 145.6  | 197.0  | 158.5  | 119.9  | 119.9  | 197.0  | 252.7  | 227.0  | 192.8  | 201.3  |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

McGRAW-EDISON

Report Number: SP1-2106-271-4

Luminaire Tested: GFLD-SA1-A-940-U-WR-X-BK

Test Date: 06/15/2021

**Test Information**

Test Method: LM-79-08  
 Report Number: SP1-2106-271-4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry: 4π  
 Issue Date: 06/15/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: MCGRAW-EDISON  
 Catalog Number: **GFLD-SA1-A-940-U-WR-X-BK**  
 Description: MCGRAW EDISON

N6, BLACK

**Spectral Parameters**

CCT (K): 3952  
 CIE u': 0.2242  
 CIE v': 0.5064  
 Duv: 0.0032  
 CIE x: 0.3848  
 CIE y: 0.3864  
 CIE z: 0.2287  
 Peak Wavelength (nm): 614  
 Dominant Wavelength (nm): 577  
 Purity: 31.6  
 Rf: 92.2  
 Rg: 98.9

CRI (Ra): 92.2

|          |           |
|----------|-----------|
| R1: 92.0 | R9: 63.3  |
| R2: 93.7 | R10: 84.3 |
| R3: 94.4 | R11: 92.7 |
| R4: 93.1 | R12: 75.6 |
| R5: 91.2 | R13: 92.2 |
| R6: 91.1 | R14: 96.5 |
| R7: 95.4 |           |
| R8: 86.5 |           |

**Test Conditions**  
 Stabilization Time: 72M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 24.8/42%  
 Sphere Temperature (°C): 24.9



REPORT NUMBER: SP1-2106-271-4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 76INCH SPHERE IN0058  | 1/31/2021        | 7/31/2021            |
| Power Meter                    | XITRON 2801 IN0071    | 12/1/2020        | 12/1/2021            |
| AC Power Source                | CHROMA 61603 IN0063   | 12/1/2020        | 12/1/2021            |
| DC Power Source                | AGILENT E3634A IN0208 | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | ONSET IN0085          | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | ONSET IN0046          | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2106-271-4

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2106-271-4

**Photopic Flux vs. Wavelength**




#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 910           | NR            | 490    | 17463         | NR            | 620    | 33665         | NR            | 750    | 3275          | NR            | 880    | 1122          | NR            |
| 365    | 784           | NR            | 495    | 18986         | NR            | 625    | 33477         | NR            | 755    | 2901          | NR            | 885    | 1170          | NR            |
| 370    | 741           | NR            | 500    | 20627         | NR            | 630    | 32742         | NR            | 760    | 2665          | NR            | 890    | 751           | NR            |
| 375    | 805           | NR            | 505    | 21980         | NR            | 635    | 31767         | NR            | 765    | 2371          | NR            | 895    | 990           | NR            |
| 380    | 830           | NR            | 510    | 23346         | NR            | 640    | 30561         | NR            | 770    | 2039          | NR            | 900    | 982           | NR            |
| 385    | 690           | NR            | 515    | 24600         | NR            | 645    | 29699         | NR            | 775    | 1676          | NR            | 905    | 936           | NR            |
| 390    | 625           | NR            | 520    | 25854         | NR            | 650    | 28202         | NR            | 780    | 1616          | NR            | 910    | 888           | NR            |
| 395    | 599           | NR            | 525    | 26952         | NR            | 655    | 26484         | NR            | 785    | 1573          | NR            | 915    | 1068          | NR            |
| 400    | 568           | NR            | 530    | 28081         | NR            | 660    | 24930         | NR            | 790    | 1452          | NR            | 920    | 1179          | NR            |
| 405    | 577           | NR            | 535    | 28884         | NR            | 665    | 23070         | NR            | 795    | 1263          | NR            | 925    | 1008          | NR            |
| 410    | 720           | NR            | 540    | 29271         | NR            | 670    | 20926         | NR            | 800    | 1203          | NR            | 930    | 927           | NR            |
| 415    | 1084          | NR            | 545    | 29657         | NR            | 675    | 19011         | NR            | 805    | 1175          | NR            | 935    | 1185          | NR            |
| 420    | 1884          | NR            | 550    | 30152         | NR            | 680    | 17237         | NR            | 810    | 1108          | NR            | 940    | 1166          | NR            |
| 425    | 3574          | NR            | 555    | 30445         | NR            | 685    | 15540         | NR            | 815    | 1125          | NR            | 945    | 779           | NR            |
| 430    | 6636          | NR            | 560    | 30559         | NR            | 690    | 13894         | NR            | 820    | 988           | NR            | 950    | 905           | NR            |
| 435    | 12267         | NR            | 565    | 30663         | NR            | 695    | 12196         | NR            | 825    | 1070          | NR            | 955    | 1369          | NR            |
| 440    | 21326         | NR            | 570    | 30877         | NR            | 700    | 10840         | NR            | 830    | 1219          | NR            | 960    | 1280          | NR            |
| 445    | 30150         | NR            | 575    | 30916         | NR            | 705    | 9613          | NR            | 835    | 944           | NR            | 965    | 1177          | NR            |
| 450    | 29740         | NR            | 580    | 31248         | NR            | 710    | 8583          | NR            | 840    | 983           | NR            | 970    | 868           | NR            |
| 455    | 22827         | NR            | 585    | 31581         | NR            | 715    | 7631          | NR            | 845    | 1097          | NR            | 975    | 843           | NR            |
| 460    | 19023         | NR            | 590    | 32218         | NR            | 720    | 6779          | NR            | 850    | 856           | NR            | 980    | 744           | NR            |
| 465    | 16163         | NR            | 595    | 32417         | NR            | 725    | 5950          | NR            | 855    | 949           | NR            | 985    | 1113          | NR            |
| 470    | 13739         | NR            | 600    | 32976         | NR            | 730    | 5282          | NR            | 860    | 954           | NR            | 990    | 1002          | NR            |
| 475    | 13571         | NR            | 605    | 33620         | NR            | 735    | 4673          | NR            | 865    | 1019          | NR            | 995    | 1732          | NR            |
| 480    | 14597         | NR            | 610    | 33704         | NR            | 740    | 4087          | NR            | 870    | 1089          | NR            | 1000   | 1390          | NR            |
| 485    | 15964         | NR            | 615    | 33846         | NR            | 745    | 3658          | NR            | 875    | 1089          | NR            |        |               |               |

REPORT NUMBER: SP1-2106-271-4

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 3705.7**

**S/P: 1.75**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 910           | NR            | 490    | 17463         | NR            | 620    | 33665         | NR            | 750    | 3275          | NR            | 880    | 1122          | NR            |
| 365    | 784           | NR            | 495    | 18986         | NR            | 625    | 33477         | NR            | 755    | 2901          | NR            | 885    | 1170          | NR            |
| 370    | 741           | NR            | 500    | 20627         | NR            | 630    | 32742         | NR            | 760    | 2665          | NR            | 890    | 751           | NR            |
| 375    | 805           | NR            | 505    | 21980         | NR            | 635    | 31767         | NR            | 765    | 2371          | NR            | 895    | 990           | NR            |
| 380    | 830           | NR            | 510    | 23346         | NR            | 640    | 30561         | NR            | 770    | 2039          | NR            | 900    | 982           | NR            |
| 385    | 690           | NR            | 515    | 24600         | NR            | 645    | 29699         | NR            | 775    | 1676          | NR            | 905    | 936           | NR            |
| 390    | 625           | NR            | 520    | 25854         | NR            | 650    | 28202         | NR            | 780    | 1616          | NR            | 910    | 888           | NR            |
| 395    | 599           | NR            | 525    | 26952         | NR            | 655    | 26484         | NR            | 785    | 1573          | NR            | 915    | 1068          | NR            |
| 400    | 568           | NR            | 530    | 28081         | NR            | 660    | 24930         | NR            | 790    | 1452          | NR            | 920    | 1179          | NR            |
| 405    | 577           | NR            | 535    | 28884         | NR            | 665    | 23070         | NR            | 795    | 1263          | NR            | 925    | 1008          | NR            |
| 410    | 720           | NR            | 540    | 29271         | NR            | 670    | 20926         | NR            | 800    | 1203          | NR            | 930    | 927           | NR            |
| 415    | 1084          | NR            | 545    | 29657         | NR            | 675    | 19011         | NR            | 805    | 1175          | NR            | 935    | 1185          | NR            |
| 420    | 1884          | NR            | 550    | 30152         | NR            | 680    | 17237         | NR            | 810    | 1108          | NR            | 940    | 1166          | NR            |
| 425    | 3574          | NR            | 555    | 30445         | NR            | 685    | 15540         | NR            | 815    | 1125          | NR            | 945    | 779           | NR            |
| 430    | 6636          | NR            | 560    | 30559         | NR            | 690    | 13894         | NR            | 820    | 988           | NR            | 950    | 905           | NR            |
| 435    | 12267         | NR            | 565    | 30663         | NR            | 695    | 12196         | NR            | 825    | 1070          | NR            | 955    | 1369          | NR            |
| 440    | 21326         | NR            | 570    | 30877         | NR            | 700    | 10840         | NR            | 830    | 1219          | NR            | 960    | 1280          | NR            |
| 445    | 30150         | NR            | 575    | 30916         | NR            | 705    | 9613          | NR            | 835    | 944           | NR            | 965    | 1177          | NR            |
| 450    | 29740         | NR            | 580    | 31248         | NR            | 710    | 8583          | NR            | 840    | 983           | NR            | 970    | 868           | NR            |
| 455    | 22827         | NR            | 585    | 31581         | NR            | 715    | 7631          | NR            | 845    | 1097          | NR            | 975    | 843           | NR            |
| 460    | 19023         | NR            | 590    | 32218         | NR            | 720    | 6779          | NR            | 850    | 856           | NR            | 980    | 744           | NR            |
| 465    | 16163         | NR            | 595    | 32417         | NR            | 725    | 5950          | NR            | 855    | 949           | NR            | 985    | 1113          | NR            |
| 470    | 13739         | NR            | 600    | 32976         | NR            | 730    | 5282          | NR            | 860    | 954           | NR            | 990    | 1002          | NR            |
| 475    | 13571         | NR            | 605    | 33620         | NR            | 735    | 4673          | NR            | 865    | 1019          | NR            | 995    | 1732          | NR            |
| 480    | 14597         | NR            | 610    | 33704         | NR            | 740    | 4087          | NR            | 870    | 1089          | NR            | 1000   | 1390          | NR            |
| 485    | 15964         | NR            | 615    | 33846         | NR            | 745    | 3658          | NR            | 875    | 1089          | NR            |        |               |               |

REPORT NUMBER: SP1-2106-271-4

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 1498.3 S/P: 0.71**


| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 910           | NR            | 490    | 17463         | NR            | 620    | 33665         | NR            | 750    | 3275          | NR            | 880    | 1122          | NR            |
| 365    | 784           | NR            | 495    | 18986         | NR            | 625    | 33477         | NR            | 755    | 2901          | NR            | 885    | 1170          | NR            |
| 370    | 741           | NR            | 500    | 20627         | NR            | 630    | 32742         | NR            | 760    | 2665          | NR            | 890    | 751           | NR            |
| 375    | 805           | NR            | 505    | 21980         | NR            | 635    | 31767         | NR            | 765    | 2371          | NR            | 895    | 990           | NR            |
| 380    | 830           | NR            | 510    | 23346         | NR            | 640    | 30561         | NR            | 770    | 2039          | NR            | 900    | 982           | NR            |
| 385    | 690           | NR            | 515    | 24600         | NR            | 645    | 29699         | NR            | 775    | 1676          | NR            | 905    | 936           | NR            |
| 390    | 625           | NR            | 520    | 25854         | NR            | 650    | 28202         | NR            | 780    | 1616          | NR            | 910    | 888           | NR            |
| 395    | 599           | NR            | 525    | 26952         | NR            | 655    | 26484         | NR            | 785    | 1573          | NR            | 915    | 1068          | NR            |
| 400    | 568           | NR            | 530    | 28081         | NR            | 660    | 24930         | NR            | 790    | 1452          | NR            | 920    | 1179          | NR            |
| 405    | 577           | NR            | 535    | 28884         | NR            | 665    | 23070         | NR            | 795    | 1263          | NR            | 925    | 1008          | NR            |
| 410    | 720           | NR            | 540    | 29271         | NR            | 670    | 20926         | NR            | 800    | 1203          | NR            | 930    | 927           | NR            |
| 415    | 1084          | NR            | 545    | 29657         | NR            | 675    | 19011         | NR            | 805    | 1175          | NR            | 935    | 1185          | NR            |
| 420    | 1884          | NR            | 550    | 30152         | NR            | 680    | 17237         | NR            | 810    | 1108          | NR            | 940    | 1166          | NR            |
| 425    | 3574          | NR            | 555    | 30445         | NR            | 685    | 15540         | NR            | 815    | 1125          | NR            | 945    | 779           | NR            |
| 430    | 6636          | NR            | 560    | 30559         | NR            | 690    | 13894         | NR            | 820    | 988           | NR            | 950    | 905           | NR            |
| 435    | 12267         | NR            | 565    | 30663         | NR            | 695    | 12196         | NR            | 825    | 1070          | NR            | 955    | 1369          | NR            |
| 440    | 21326         | NR            | 570    | 30877         | NR            | 700    | 10840         | NR            | 830    | 1219          | NR            | 960    | 1280          | NR            |
| 445    | 30150         | NR            | 575    | 30916         | NR            | 705    | 9613          | NR            | 835    | 944           | NR            | 965    | 1177          | NR            |
| 450    | 29740         | NR            | 580    | 31248         | NR            | 710    | 8583          | NR            | 840    | 983           | NR            | 970    | 868           | NR            |
| 455    | 22827         | NR            | 585    | 31581         | NR            | 715    | 7631          | NR            | 845    | 1097          | NR            | 975    | 843           | NR            |
| 460    | 19023         | NR            | 590    | 32218         | NR            | 720    | 6779          | NR            | 850    | 856           | NR            | 980    | 744           | NR            |
| 465    | 16163         | NR            | 595    | 32417         | NR            | 725    | 5950          | NR            | 855    | 949           | NR            | 985    | 1113          | NR            |
| 470    | 13739         | NR            | 600    | 32976         | NR            | 730    | 5282          | NR            | 860    | 954           | NR            | 990    | 1002          | NR            |
| 475    | 13571         | NR            | 605    | 33620         | NR            | 735    | 4673          | NR            | 865    | 1019          | NR            | 995    | 1732          | NR            |
| 480    | 14597         | NR            | 610    | 33704         | NR            | 740    | 4087          | NR            | 870    | 1089          | NR            | 1000   | 1390          | NR            |
| 485    | 15964         | NR            | 615    | 33846         | NR            | 745    | 3658          | NR            | 875    | 1089          | NR            |        |               |               |

REPORT NUMBER: SP1-2106-271-4





TM-30-18

**Summary**

$R_f = 92.2$   
 $R_g = 98.9$   
 CIE  $R_a = 92.2$   
 $R_9 = 63.3$



**Color Vector Graphics**



REPORT NUMBER: SP1-2106-271-4

TM-30-18

**Individual Sample Fidelity Index ( $R_{f,i}$ )**


|            |             |            |            |
|------------|-------------|------------|------------|
| CES01 = 85 | CES26 = 93  | CES51 = 97 | CES76 = 86 |
| CES02 = 61 | CES27 = 92  | CES52 = 98 | CES77 = 90 |
| CES03 = 31 | CES28 = 96  | CES53 = 95 | CES78 = 84 |
| CES04 = 69 | CES29 = 95  | CES54 = 95 | CES79 = 97 |
| CES05 = 49 | CES30 = 97  | CES55 = 94 | CES80 = 94 |
| CES06 = 50 | CES31 = 96  | CES56 = 94 | CES81 = 91 |
| CES07 = 42 | CES32 = 91  | CES57 = 93 | CES82 = 97 |
| CES08 = 41 | CES33 = 98  | CES58 = 93 | CES83 = 98 |
| CES09 = 29 | CES34 = 93  | CES59 = 96 | CES84 = 94 |
| CES10 = 74 | CES35 = 96  | CES60 = 94 | CES85 = 86 |
| CES11 = 57 | CES36 = 85  | CES61 = 93 | CES86 = 90 |
| CES12 = 63 | CES37 = 94  | CES62 = 90 | CES87 = 92 |
| CES13 = 43 | CES38 = 91  | CES63 = 92 | CES88 = 96 |
| CES14 = 74 | CES39 = 99  | CES64 = 90 | CES89 = 88 |
| CES15 = 71 | CES40 = 98  | CES65 = 88 | CES90 = 96 |
| CES16 = 47 | CES41 = 98  | CES66 = 88 | CES91 = 76 |
| CES17 = 49 | CES42 = 95  | CES67 = 87 | CES92 = 82 |
| CES18 = 56 | CES43 = 95  | CES68 = 88 | CES93 = 89 |
| CES19 = 71 | CES44 = 100 | CES69 = 90 | CES94 = 83 |
| CES20 = 66 | CES45 = 97  | CES70 = 86 | CES95 = 84 |
| CES21 = 85 | CES46 = 97  | CES71 = 82 | CES96 = 92 |
| CES22 = 78 | CES47 = 98  | CES72 = 94 | CES97 = 95 |
| CES23 = 91 | CES48 = 93  | CES73 = 81 | CES98 = 93 |
| CES24 = 90 | CES49 = 96  | CES74 = 94 | CES99 = 92 |
| CES25 = 71 | CES50 = 98  | CES75 = 83 |            |



REPORT NUMBER: SP1-2106-271-4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-2106-271-4

TM-30-18

Measure Comparisons



(END OF REPORT)