

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P953009

Luminaire Tested: **GALN-SB6C-940-U-SLL**

Issue Date: 1/21/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P953009  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: GALN-SB6C-940-U-SLL  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(6) 90 CRI, 4000K, 615mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 32791 lumens  
Efficiency: N/A  
Efficacy: 109.0 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B3 - U0 - G5  
  
Input Watts (W): 300.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P953009  
 CATALOG NUMBER: GALN-SB6C-940-U-SLL

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 10 fc  
 Type IV - Short - N/A

REPORT NUMBER: P953009  
CATALOG NUMBER: GALN-SB6C-940-U-SLL

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral      - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P953009  
 CATALOG NUMBER: GALN-SB6C-940-U-SLL

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	8333.8	0.0	8333.8
	% Fixture	25.4	0.0	25.4
<b>Street Side</b>	Lumens	24457.2	0.0	24457.2
	% Fixture	74.6	0.0	74.6
<b>Total</b>	Lumens	32791.0	0.0	32791.0
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	447.3	1.4
10°-20°	1404.1	4.3
20°-30°	2168.9	6.6
30°-40°	2748.6	8.4
40°-50°	4145.5	12.6
50°-60°	6697.7	20.4
60°-70°	8349.8	25.5
70°-80°	5475.4	16.7
80°-90°	1353.6	4.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	32791.0	100.0
0°-180°	32791.0	100.0




REPORT NUMBER: P953009  
 CATALOG NUMBER: GALN-SB6C-940-U-SLL

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	2205.6	6.7			
FM (30°-60°)	9564.4	29.2			
FH (60°-80°)	11572.1	35.3			G4/12000
FVH (80°-90°)	1115.1	3.4			G5
BL (0°-30°)	1814.8	5.5	B3/2500		
BM (30°-60°)	4027.4	12.3	B3/5000		
BH (60°-80°)	2253.1	6.9	B3/2500		G3/2500
BVH (80°-90°)	238.5	0.7			G3/500
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G5**

Type IV Short



REPORT NUMBER: P953009

CATALOG NUMBER: GALN-SB6C-940-U-SLL

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°
0°	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0
2.5°	4849.0	4867.4	4885.9	4912.0	4938.1	4953.7	4969.3	4977.1	4984.9	4981.4
5°	5214.1	5278.3	5342.7	5406.4	5470.2	5504.8	5539.4	5560.3	5581.5	5597.4
7.5°	5580.9	5685.4	5789.8	5883.7	5977.7	6034.3	6090.8	6121.5	6151.9	6166.6
10°	5862.1	5985.6	6109.2	6219.4	6329.6	6396.4	6462.8	6492.6	6522.2	6533.4
12.5°	6034.3	6168.2	6301.9	6401.6	6500.9	6549.4	6597.8	6614.1	6630.3	6632.1
15°	6138.9	6254.5	6369.9	6432.4	6495.0	6496.8	6498.5	6481.2	6463.9	6443.5
17.5°	6197.8	6275.8	6353.8	6355.1	6356.1	6286.0	6215.9	6151.7	6087.4	6042.1
20°	6262.7	6289.8	6317.2	6235.0	6152.8	5998.1	5843.4	5730.8	5618.1	5548.9
22.5°	6337.9	6302.3	6266.6	6096.4	5926.1	5698.6	5471.1	5330.2	5189.4	5112.9
25°	6434.8	6322.4	6209.9	5951.4	5692.9	5416.6	5140.2	4992.1	4844.4	4772.0
27.5°	6566.3	6365.3	6164.0	5821.6	5479.4	5173.1	4866.9	4721.2	4575.7	4507.3
30°	6743.7	6443.8	6144.1	5722.6	5301.2	4982.1	4663.0	4527.9	4392.8	4329.1
32.5°	6953.0	6542.4	6132.0	5655.2	5178.3	4878.5	4578.6	4472.5	4366.3	4320.4
35°	7207.4	6704.9	6202.6	5705.7	5208.9	5000.6	4792.5	4767.7	4743.0	4739.2
37.5°	7635.6	7044.6	6453.5	6001.9	5550.3	5536.8	5523.3	5636.5	5749.6	5808.5
40°	8282.7	7639.9	6997.2	6661.3	6325.5	6562.5	6799.6	7074.7	7349.8	7486.8
42.5°	9140.9	8503.2	7865.4	7672.0	7478.5	7995.5	8512.5	9012.9	9513.3	9807.1
45°	10200.7	9627.8	9054.8	8969.5	8884.0	9712.3	10540.7	11362.9	12185.3	12684.5
47.5°	11526.1	10968.8	10411.3	10394.0	10376.7	11571.6	12766.2	13969.9	15173.5	15880.3
50°	13263.3	12574.8	11886.5	11889.4	11892.4	13432.3	14972.2	16561.1	18150.0	19110.7
52.5°	15257.4	14423.8	13590.3	13506.0	13421.6	15261.0	17100.5	19066.4	21032.1	22183.6
55°	17380.4	16556.8	15733.2	15404.6	15076.1	17123.3	19170.4	21514.0	23857.6	25227.1
57.5°	19311.4	18862.9	18414.2	17755.2	17096.3	19163.4	21230.6	23885.1	26539.5	28237.8
60°	20478.4	21175.0	21871.8	21053.4	20235.0	22191.2	24147.4	26989.6	29831.7	31667.1
62.5°	19885.8	21789.3	23692.7	23600.5	23508.1	25300.1	27092.3	29796.4	32500.2	34196.8
65°	18699.7	20486.2	22272.7	22626.2	22979.5	25256.9	27534.4	30156.4	32778.3	34222.7
67.5°	17110.5	18809.6	20508.7	20674.5	20840.1	23212.9	25585.6	28218.9	30852.2	31983.8
70°	15201.2	17049.2	18897.5	18971.6	19045.8	21167.8	23289.6	25555.7	27821.6	28450.6
72.5°	12925.9	15046.6	17167.6	17220.9	17274.0	18934.2	20594.4	22291.6	23988.6	24052.3
75°	10047.6	12242.6	14437.6	14634.7	14831.7	16123.4	17415.0	18609.8	19804.5	19484.4
77.5°	7178.8	9227.8	11276.9	11559.0	11841.0	12822.9	13804.8	14652.1	15499.6	14949.4
80°	4698.5	6422.4	8146.0	8496.6	8847.1	9588.7	10330.0	10775.0	11219.8	10334.8
82.5°	2731.2	3909.7	5088.3	5479.9	5871.6	6382.0	6892.5	7078.1	7263.6	6568.0
85°	1201.7	1827.1	2452.6	2785.7	3118.8	3538.2	3957.4	4062.8	4168.2	3611.0
87.5°	372.0	582.2	792.5	978.3	1164.1	1373.8	1583.5	1592.5	1601.4	1344.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P953009  
 CATALOG NUMBER: GALN-SB6C-940-U-SLL

**CANDELA DISTRIBUTION (continued):**

50°		55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
4509.0	0°	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0
4984.9	2.5°	4977.1	4969.3	4953.7	4938.1	4912.0	4885.9	4867.4	4849.0	4811.8	4774.6
5581.5	5°	5560.3	5539.4	5504.8	5470.2	5406.4	5342.7	5278.3	5214.1	5131.9	5049.7
6151.9	7.5°	6121.5	6090.8	6034.3	5977.7	5883.7	5789.8	5685.4	5580.9	5445.3	5309.8
6522.2	10°	6492.6	6462.8	6396.4	6329.6	6219.4	6109.2	5985.6	5862.1	5690.6	5519.2
6630.3	12.5°	6614.1	6597.8	6549.4	6500.9	6401.6	6301.9	6168.2	6034.3	5845.8	5657.6
6463.9	15°	6481.2	6498.5	6496.8	6495.0	6432.4	6369.9	6254.5	6138.9	5942.6	5746.2
6087.4	17.5°	6151.7	6215.9	6286.0	6356.1	6355.1	6353.8	6275.8	6197.8	5998.6	5799.5
5618.1	20°	5730.8	5843.4	5998.1	6152.8	6235.0	6317.2	6289.8	6262.7	6055.7	5848.6
5189.4	22.5°	5330.2	5471.1	5698.6	5926.1	6096.4	6266.6	6302.3	6337.9	6126.5	5914.9
4844.4	25°	4992.1	5140.2	5416.6	5692.9	5951.4	6209.9	6322.4	6434.8	6227.5	6020.4
4575.7	27.5°	4721.2	4866.9	5173.1	5479.4	5821.6	6164.0	6365.3	6566.3	6368.7	6171.0
4392.8	30°	4527.9	4663.0	4982.1	5301.2	5722.6	6144.1	6443.8	6743.7	6552.6	6361.8
4366.3	32.5°	4472.5	4578.6	4878.5	5178.3	5655.2	6132.0	6542.4	6953.0	6763.9	6575.0
4743.0	35°	4767.7	4792.5	5000.6	5208.9	5705.7	6202.6	6704.9	7207.4	7026.4	6845.2
5749.6	37.5°	5636.5	5523.3	5536.8	5550.3	6001.9	6453.5	7044.6	7635.6	7404.8	7174.0
7349.8	40°	7074.7	6799.6	6562.5	6325.5	6661.3	6997.2	7639.9	8282.7	7946.4	7610.0
9513.3	42.5°	9012.9	8512.5	7995.5	7478.5	7672.0	7865.4	8503.2	9140.9	8655.4	8169.9
12185.3	45°	11362.9	10540.7	9712.3	8884.0	8969.5	9054.8	9627.8	10200.7	9545.8	8890.9
15173.5	47.5°	13969.9	12766.2	11571.6	10376.7	10394.0	10411.3	10968.8	11526.1	10604.4	9682.5
18150.0	50°	16561.1	14972.2	13432.3	11892.4	11889.4	11886.5	12574.8	13263.3	11873.7	10484.0
21032.1	52.5°	19066.4	17100.5	15261.0	13421.6	13506.0	13590.3	14423.8	15257.4	13207.0	11156.7
23857.6	55°	21514.0	19170.4	17123.3	15076.1	15404.6	15733.2	16556.8	17380.4	14389.1	11398.1
26539.5	57.5°	23885.1	21230.6	19163.4	17096.3	17755.2	18414.2	18862.9	19311.4	15226.9	11142.5
29831.7	60°	26989.6	24147.4	22191.2	20235.0	21053.4	21871.8	21175.0	20478.4	15436.3	10394.0
32500.2	62.5°	29796.4	27092.3	25300.1	23508.1	23600.5	23692.7	21789.3	19885.8	14554.7	9223.6
32778.3	65°	30156.4	27534.4	25256.9	22979.5	22626.2	22272.7	20486.2	18699.7	13307.4	7915.1
30852.2	67.5°	28218.9	25585.6	23212.9	20840.1	20674.5	20508.7	18809.6	17110.5	11823.0	6535.5
27821.6	70°	25555.7	23289.6	21167.8	19045.8	18971.6	18897.5	17049.2	15201.2	10203.3	5205.5
23988.6	72.5°	22291.6	20594.4	18934.2	17274.0	17220.9	17167.6	15046.6	12925.9	8447.5	3969.2
19804.5	75°	18609.8	17415.0	16123.4	14831.7	14634.7	14437.6	12242.6	10047.6	6434.6	2821.7
15499.6	77.5°	14652.1	13804.8	12822.9	11841.0	11559.0	11276.9	9227.8	7178.8	4503.7	1828.5
11219.8	80°	10775.0	10330.0	9588.7	8847.1	8496.6	8146.0	6422.4	4698.5	2901.6	1104.8
7263.6	82.5°	7078.1	6892.5	6382.0	5871.6	5479.9	5088.3	3909.7	2731.2	1679.4	627.7
4168.2	85°	4062.8	3957.4	3538.2	3118.8	2785.7	2452.6	1827.1	1201.7	755.4	309.4
1601.4	87.5°	1592.5	1583.5	1373.8	1164.1	978.3	792.5	582.2	372.0	247.4	122.8
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P953009  
 CATALOG NUMBER: GALN-SB6C-940-U-SLL

**CANDELA DISTRIBUTION (continued):**

105°		110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
4509.0	0°	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0
4735.0	2.5°	4695.6	4655.8	4616.0	4577.9	4539.8	4503.0	4462.0	4428.8	4395.7	4365.8
4967.7	5°	4885.9	4803.4	4721.0	4644.0	4567.0	4494.3	4422.5	4359.9	4297.1	4244.5
5184.5	7.5°	5059.3	4937.3	4815.3	4707.9	4600.4	4501.3	4408.3	4324.9	4241.7	4172.5
5353.6	10°	5188.2	5040.1	4891.8	4764.8	4637.4	4515.1	4415.3	4327.4	4239.5	4170.3
5470.0	12.5°	5282.5	5107.7	4933.0	4789.2	4645.4	4516.8	4423.9	4351.9	4280.3	4234.3
5542.7	15°	5339.2	5138.0	4936.8	4770.3	4603.9	4461.5	4387.1	4352.6	4318.4	4324.6
5577.5	17.5°	5355.5	5121.9	4888.3	4688.1	4487.9	4320.4	4274.6	4287.2	4299.7	4375.1
5604.6	20°	5360.7	5077.6	4794.5	4546.4	4298.3	4103.3	4091.2	4150.0	4208.8	4339.8
5641.3	22.5°	5367.6	5023.3	4679.0	4380.1	4081.3	3859.3	3883.0	3970.1	4057.1	4206.6
5707.8	25°	5394.9	4969.6	4544.5	4194.5	3844.6	3617.1	3681.1	3781.5	3881.8	4016.3
5811.6	27.5°	5452.0	4933.8	4415.6	4024.7	3633.9	3426.8	3504.6	3601.5	3698.4	3809.0
5946.0	30°	5530.2	4917.0	4303.5	3882.9	3462.2	3288.3	3349.4	3426.3	3503.4	3595.1
6086.3	32.5°	5597.7	4896.3	4194.5	3760.5	3326.4	3186.3	3213.4	3258.9	3304.4	3377.6
6246.2	35°	5647.2	4857.2	4067.5	3640.3	3213.1	3096.3	3085.0	3097.5	3110.1	3166.0
6425.3	37.5°	5676.6	4790.2	3903.8	3498.7	3093.7	2991.6	2950.4	2936.6	2922.7	2962.9
6652.7	40°	5695.1	4698.0	3701.0	3329.9	2958.7	2866.2	2803.0	2771.7	2740.4	2769.3
6950.1	42.5°	5730.3	4602.8	3475.7	3143.5	2811.3	2726.0	2646.4	2604.9	2563.4	2586.9
7341.5	45°	5792.0	4514.4	3237.0	2945.6	2654.2	2567.7	2490.7	2450.2	2409.9	2429.6
7758.5	47.5°	5834.4	4441.4	3048.4	2789.0	2529.6	2418.0	2351.8	2317.8	2283.9	2302.6
8145.3	50°	5806.7	4361.8	2916.9	2685.0	2453.2	2306.4	2229.4	2199.3	2169.4	2198.5
8396.6	52.5°	5636.3	4227.4	2818.6	2616.5	2414.6	2245.9	2138.2	2108.5	2078.9	2122.7
8341.2	55°	5284.2	4004.5	2724.8	2566.8	2408.9	2251.9	2089.8	2042.7	1995.8	2058.0
7951.6	57.5°	4760.8	3690.3	2619.6	2508.0	2396.4	2258.0	2060.7	1992.2	1923.7	1990.5
7226.4	60°	4058.8	3282.3	2505.8	2418.0	2330.3	2239.0	2033.4	1944.6	1855.7	1914.4
6245.9	62.5°	3268.1	2794.0	2319.9	2261.6	2203.5	2192.2	2001.6	1890.5	1779.6	1816.8
5245.4	65°	2576.0	2354.7	2133.4	2105.9	2078.4	2079.8	1934.4	1816.4	1698.2	1712.6
4265.4	67.5°	1995.3	1932.5	1869.5	1884.9	1900.2	1896.4	1814.7	1716.4	1618.1	1613.6
3358.4	70°	1511.4	1529.4	1547.2	1618.5	1689.6	1689.6	1662.8	1592.9	1523.0	1507.4
2567.5	72.5°	1165.8	1220.0	1274.3	1375.4	1476.3	1493.2	1493.6	1445.6	1397.7	1374.9
1863.5	75°	905.3	954.4	1003.5	1116.7	1229.9	1308.1	1301.5	1264.6	1227.6	1205.8
1262.7	77.5°	696.9	730.3	763.9	873.8	983.7	1112.6	1109.1	1079.5	1049.9	1027.8
813.6	80°	522.5	536.4	550.2	643.3	736.2	890.2	889.7	865.0	840.0	821.5
500.4	82.5°	373.4	375.8	378.6	447.1	515.6	647.1	654.4	642.3	630.2	617.0
267.5	85°	225.8	224.6	223.2	273.4	323.6	421.3	430.8	417.9	404.9	390.2
110.9	87.5°	99.0	97.8	96.5	117.0	137.6	178.2	190.3	185.1	179.9	177.2
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P953009  
 CATALOG NUMBER: GALN-SB6C-940-U-SLL

**CANDELA DISTRIBUTION (continued):**

160°		165°	170°	175°	180°	185°	190°	195°	200°	205°	210°
4509.0	0°	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0
4336.0	2.5°	4309.9	4283.8	4257.5	4231.3	4211.1	4190.7	4174.2	4157.8	4145.0	4132.2
4192.1	5°	4145.7	4099.3	4057.3	4015.1	3982.7	3950.2	3927.5	3904.8	3888.7	3872.7
4103.3	7.5°	4045.0	3986.5	3934.9	3883.6	3845.0	3806.6	3779.6	3752.6	3734.1	3715.7
4101.1	10°	4038.2	3975.3	3917.3	3859.3	3813.3	3767.1	3737.0	3706.6	3689.1	3671.6
4188.6	12.5°	4139.1	4090.0	4029.9	3970.1	3911.2	3852.4	3813.5	3774.6	3755.0	3735.6
4330.8	15°	4318.0	4305.2	4253.1	4201.1	4117.3	4033.6	3974.4	3915.2	3888.1	3861.1
4450.6	17.5°	4490.7	4530.7	4488.6	4446.8	4335.8	4224.9	4137.7	4050.5	4010.4	3970.1
4471.0	20°	4554.9	4638.8	4619.4	4599.9	4473.1	4346.4	4239.5	4132.7	4081.3	4029.8
4356.4	22.5°	4465.6	4574.8	4586.6	4598.2	4477.0	4355.9	4245.9	4135.7	4081.5	4027.2
4150.9	25°	4258.3	4365.8	4405.9	4445.9	4346.6	4247.4	4149.5	4051.9	4004.8	3958.0
3919.4	27.5°	4005.5	4091.7	4136.3	4181.2	4110.4	4039.8	3963.8	3887.9	3856.4	3824.7
3686.8	30°	3758.3	3829.9	3866.3	3902.6	3848.8	3794.8	3740.5	3685.8	3669.7	3653.4
3451.0	32.5°	3519.5	3588.2	3628.5	3669.0	3619.5	3569.9	3526.4	3483.0	3472.4	3461.9
3221.7	35°	3289.6	3357.6	3406.0	3454.5	3419.2	3384.0	3343.9	3303.9	3287.8	3271.9
3002.9	37.5°	3070.5	3138.3	3198.2	3258.1	3241.8	3225.5	3188.7	3151.7	3122.4	3093.4
2798.2	40°	2863.6	2929.0	2997.8	3066.9	3070.9	3074.7	3043.3	3012.0	2969.5	2927.2
2610.6	42.5°	2672.6	2734.7	2809.1	2883.5	2903.4	2923.3	2896.8	2870.5	2817.7	2764.9
2449.7	45°	2508.5	2567.4	2644.5	2721.7	2750.2	2778.8	2754.9	2731.2	2670.8	2610.6
2321.1	47.5°	2378.8	2436.2	2512.3	2588.5	2621.3	2654.2	2637.6	2621.0	2567.4	2513.7
2227.7	50°	2282.0	2336.2	2404.4	2472.5	2514.8	2557.0	2555.9	2555.2	2512.3	2469.4
2166.3	52.5°	2216.1	2265.8	2329.3	2392.9	2442.9	2493.0	2501.9	2510.9	2476.0	2441.0
2119.9	55°	2173.5	2227.2	2282.9	2338.4	2391.4	2444.5	2457.0	2469.4	2439.0	2408.5
2057.3	57.5°	2120.3	2183.2	2238.3	2293.5	2346.9	2400.2	2412.8	2425.5	2394.7	2363.9
1972.8	60°	2045.2	2117.5	2173.4	2229.4	2283.1	2336.7	2350.6	2364.4	2334.3	2304.4
1854.0	62.5°	1938.2	2022.7	2082.4	2142.1	2191.2	2240.3	2253.7	2267.0	2239.8	2212.7
1726.8	65°	1817.1	1907.6	1964.7	2021.8	2065.1	2108.3	2122.0	2135.5	2109.4	2083.2
1609.1	67.5°	1692.5	1776.1	1830.3	1884.2	1921.6	1959.0	1972.3	1985.5	1961.4	1937.5
1491.8	70°	1565.2	1638.6	1685.3	1732.0	1765.7	1799.5	1812.3	1825.1	1805.5	1786.0
1352.2	72.5°	1410.0	1467.6	1509.8	1552.0	1585.1	1618.1	1633.4	1648.6	1632.3	1616.1
1183.8	75°	1226.8	1269.7	1307.9	1346.1	1376.2	1406.4	1422.3	1438.2	1430.2	1422.3
1005.6	77.5°	1040.6	1075.4	1108.2	1141.1	1172.8	1204.3	1219.1	1234.0	1222.9	1211.5
802.8	80°	831.9	860.8	888.5	916.2	940.2	964.1	983.8	1003.5	998.7	994.0
603.9	82.5°	601.4	599.0	589.3	579.6	630.9	682.1	715.6	749.2	747.1	744.9
375.5	85°	363.0	350.4	323.6	296.7	344.7	392.8	434.3	475.8	472.4	468.9
174.4	87.5°	173.9	173.4	153.0	132.4	152.4	172.7	189.5	206.2	202.1	197.6
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P953009  
 CATALOG NUMBER: GALN-SB6C-940-U-SLL

**CANDELA DISTRIBUTION (continued):**

215°		220°	225°	230°	235°	240°	245°	250°	255°	260°	265°
4509.0	0°	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0
4120.4	2.5°	4108.5	4093.8	4108.5	4120.4	4132.2	4145.0	4157.8	4174.2	4190.7	4211.1
3860.4	5°	3848.1	3836.0	3848.1	3860.4	3872.7	3888.7	3904.8	3927.5	3950.2	3982.7
3704.6	7.5°	3693.7	3685.4	3693.7	3704.6	3715.7	3734.1	3752.6	3779.6	3806.6	3845.0
3662.3	10°	3652.9	3649.1	3652.9	3662.3	3671.6	3689.1	3706.6	3737.0	3767.1	3813.3
3727.7	12.5°	3719.7	3718.3	3719.7	3727.7	3735.6	3755.0	3774.6	3813.5	3852.4	3911.2
3850.7	15°	3840.3	3839.4	3840.3	3850.7	3861.1	3888.1	3915.2	3974.4	4033.6	4117.3
3956.9	17.5°	3943.6	3941.5	3943.6	3956.9	3970.1	4010.4	4050.5	4137.7	4224.9	4335.8
4013.3	20°	3996.9	3991.7	3996.9	4013.3	4029.8	4081.3	4132.7	4239.5	4346.4	4473.1
4009.0	22.5°	3990.8	3983.0	3990.8	4009.0	4027.2	4081.5	4135.7	4245.9	4355.9	4477.0
3940.8	25°	3923.9	3913.8	3923.9	3940.8	3958.0	4004.8	4051.9	4149.5	4247.4	4346.6
3816.9	27.5°	3809.2	3806.6	3809.2	3816.9	3824.7	3856.4	3887.9	3963.8	4039.8	4110.4
3653.4	30°	3653.4	3656.0	3653.4	3653.4	3653.4	3669.7	3685.8	3740.5	3794.8	3848.8
3463.3	32.5°	3464.8	3467.4	3464.8	3463.3	3461.9	3472.4	3483.0	3526.4	3569.9	3619.5
3268.5	35°	3265.0	3263.3	3265.0	3268.5	3271.9	3287.8	3303.9	3343.9	3384.0	3419.2
3078.0	37.5°	3062.6	3053.9	3062.6	3078.0	3093.4	3122.4	3151.7	3188.7	3225.5	3241.8
2898.5	40°	2870.1	2853.2	2870.1	2898.5	2927.2	2969.5	3012.0	3043.3	3074.7	3070.9
2723.2	42.5°	2681.5	2654.2	2681.5	2723.2	2764.9	2817.7	2870.5	2896.8	2923.3	2903.4
2561.6	45°	2512.7	2481.2	2512.7	2561.6	2610.6	2670.8	2731.2	2754.9	2778.8	2750.2
2468.4	47.5°	2423.2	2392.9	2423.2	2468.4	2513.7	2567.4	2621.0	2637.6	2654.2	2621.3
2427.5	50°	2385.7	2356.6	2385.7	2427.5	2469.4	2512.3	2555.2	2555.9	2557.0	2514.8
2403.5	52.5°	2366.1	2339.3	2366.1	2403.5	2441.0	2476.0	2510.9	2501.9	2493.0	2442.9
2375.6	55°	2342.8	2318.5	2342.8	2375.6	2408.5	2439.0	2469.4	2457.0	2444.5	2391.4
2331.3	57.5°	2298.6	2273.6	2298.6	2331.3	2363.9	2394.7	2425.5	2412.8	2400.2	2346.9
2270.8	60°	2237.2	2211.3	2237.2	2270.8	2304.4	2334.3	2364.4	2350.6	2336.7	2283.1
2177.4	62.5°	2142.1	2110.9	2142.1	2177.4	2212.7	2239.8	2267.0	2253.7	2240.3	2191.2
2049.0	65°	2014.9	1988.1	2014.9	2049.0	2083.2	2109.4	2135.5	2122.0	2108.3	2065.1
1905.7	67.5°	1873.9	1849.6	1873.9	1905.7	1937.5	1961.4	1985.5	1972.3	1959.0	1921.6
1755.5	70°	1725.1	1697.4	1725.1	1755.5	1786.0	1805.5	1825.1	1812.3	1799.5	1765.7
1587.0	72.5°	1558.1	1531.3	1558.1	1587.0	1616.1	1632.3	1648.6	1633.4	1618.1	1585.1
1397.9	75°	1373.5	1347.9	1373.5	1397.9	1422.3	1430.2	1438.2	1422.3	1406.4	1376.2
1187.0	77.5°	1162.4	1142.0	1162.4	1187.0	1211.5	1222.9	1234.0	1219.1	1204.3	1172.8
961.0	80°	927.8	889.4	927.8	961.0	994.0	998.7	1003.5	983.8	964.1	940.2
717.0	82.5°	689.0	664.4	689.0	717.0	744.9	747.1	749.2	715.6	682.1	630.9
447.1	85°	425.3	403.1	425.3	447.1	468.9	472.4	475.8	434.3	392.8	344.7
186.5	87.5°	175.1	164.4	175.1	186.5	197.6	202.1	206.2	189.5	172.7	152.4
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P953009  
 CATALOG NUMBER: GALN-SB6C-940-U-SLL

**CANDELA DISTRIBUTION (continued):**

270°		275°	280°	285°	290°	295°	300°	305°	310°	315°	320°
4509.0	0°	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0
4231.3	2.5°	4257.5	4283.8	4309.9	4336.0	4365.8	4395.7	4428.8	4462.0	4503.0	4539.8
4015.1	5°	4057.3	4099.3	4145.7	4192.1	4244.5	4297.1	4359.9	4422.5	4494.3	4567.0
3883.6	7.5°	3934.9	3986.5	4045.0	4103.3	4172.5	4241.7	4324.9	4408.3	4501.3	4600.4
3859.3	10°	3917.3	3975.3	4038.2	4101.1	4170.3	4239.5	4327.4	4415.3	4515.1	4637.4
3970.1	12.5°	4029.9	4090.0	4139.1	4188.6	4234.3	4280.3	4351.9	4423.9	4516.8	4645.4
4201.1	15°	4253.1	4305.2	4318.0	4330.8	4324.6	4318.4	4352.6	4387.1	4461.5	4603.9
4446.8	17.5°	4488.6	4530.7	4490.7	4450.6	4375.1	4299.7	4287.2	4274.6	4320.4	4487.9
4599.9	20°	4619.4	4638.8	4554.9	4471.0	4339.8	4208.8	4150.0	4091.2	4103.3	4298.3
4598.2	22.5°	4586.6	4574.8	4465.6	4356.4	4206.6	4057.1	3970.1	3883.0	3859.3	4081.3
4445.9	25°	4405.9	4365.8	4258.3	4150.9	4016.3	3881.8	3781.5	3681.1	3617.1	3844.6
4181.2	27.5°	4136.3	4091.7	4005.5	3919.4	3809.0	3698.4	3601.5	3504.6	3426.8	3633.9
3902.6	30°	3866.3	3829.9	3758.3	3686.8	3595.1	3503.4	3426.3	3349.4	3288.3	3462.2
3669.0	32.5°	3628.5	3588.2	3519.5	3451.0	3377.6	3304.4	3258.9	3213.4	3186.3	3326.4
3454.5	35°	3406.0	3357.6	3289.6	3221.7	3166.0	3110.1	3097.5	3085.0	3096.3	3213.1
3258.1	37.5°	3198.2	3138.3	3070.5	3002.9	2962.9	2922.7	2936.6	2950.4	2991.6	3093.7
3066.9	40°	2997.8	2929.0	2863.6	2798.2	2769.3	2740.4	2771.7	2803.0	2866.2	2958.7
2883.5	42.5°	2809.1	2734.7	2672.6	2610.6	2586.9	2563.4	2604.9	2646.4	2726.0	2811.3
2721.7	45°	2644.5	2567.4	2508.5	2449.7	2429.6	2409.9	2450.2	2490.7	2567.7	2654.2
2588.5	47.5°	2512.3	2436.2	2378.8	2321.1	2302.6	2283.9	2317.8	2351.8	2418.0	2529.6
2472.5	50°	2404.4	2336.2	2282.0	2227.7	2198.5	2169.4	2199.3	2229.4	2306.4	2453.2
2392.9	52.5°	2329.3	2265.8	2216.1	2166.3	2122.7	2078.9	2108.5	2138.2	2245.9	2414.6
2338.4	55°	2282.9	2227.2	2173.5	2119.9	2058.0	1995.8	2042.7	2089.8	2251.9	2408.9
2293.5	57.5°	2238.3	2183.2	2120.3	2057.3	1990.5	1923.7	1992.2	2060.7	2258.0	2396.4
2229.4	60°	2173.4	2117.5	2045.2	1972.8	1914.4	1855.7	1944.6	2033.4	2239.0	2330.3
2142.1	62.5°	2082.4	2022.7	1938.2	1854.0	1816.8	1779.6	1890.5	2001.6	2192.2	2203.5
2021.8	65°	1964.7	1907.6	1817.1	1726.8	1712.6	1698.2	1816.4	1934.4	2079.8	2078.4
1884.2	67.5°	1830.3	1776.1	1692.5	1609.1	1613.6	1618.1	1716.4	1814.7	1896.4	1900.2
1732.0	70°	1685.3	1638.6	1565.2	1491.8	1507.4	1523.0	1592.9	1662.8	1689.6	1689.6
1552.0	72.5°	1509.8	1467.6	1410.0	1352.2	1374.9	1397.7	1445.6	1493.6	1493.2	1476.3
1346.1	75°	1307.9	1269.7	1226.8	1183.8	1205.8	1227.6	1264.6	1301.5	1308.1	1229.9
1141.1	77.5°	1108.2	1075.4	1040.6	1005.6	1027.8	1049.9	1079.5	1109.1	1112.6	983.7
916.2	80°	888.5	860.8	831.9	802.8	821.5	840.0	865.0	889.7	890.2	736.2
579.6	82.5°	589.3	599.0	601.4	603.9	617.0	630.2	642.3	654.4	647.1	515.6
296.7	85°	323.6	350.4	363.0	375.5	390.2	404.9	417.9	430.8	421.3	323.6
132.4	87.5°	153.0	173.4	173.9	174.4	177.2	179.9	185.1	190.3	178.2	137.6
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P953009  
 CATALOG NUMBER: GALN-SB6C-940-U-SLL

**CANDELA DISTRIBUTION (continued):**

325°		330°	335°	340°	345°	350°	355°	360°
4509.0	0°	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0	4509.0
4577.9	2.5°	4616.0	4655.8	4695.6	4735.0	4774.6	4811.8	4849.0
4644.0	5°	4721.0	4803.4	4885.9	4967.7	5049.7	5131.9	5214.1
4707.9	7.5°	4815.3	4937.3	5059.3	5184.5	5309.8	5445.3	5580.9
4764.8	10°	4891.8	5040.1	5188.2	5353.6	5519.2	5690.6	5862.1
4789.2	12.5°	4933.0	5107.7	5282.5	5470.0	5657.6	5845.8	6034.3
4770.3	15°	4936.8	5138.0	5339.2	5542.7	5746.2	5942.6	6138.9
4688.1	17.5°	4888.3	5121.9	5355.5	5577.5	5799.5	5998.6	6197.8
4546.4	20°	4794.5	5077.6	5360.7	5604.6	5848.6	6055.7	6262.7
4380.1	22.5°	4679.0	5023.3	5367.6	5641.3	5914.9	6126.5	6337.9
4194.5	25°	4544.5	4969.6	5394.9	5707.8	6020.4	6227.5	6434.8
4024.7	27.5°	4415.6	4933.8	5452.0	5811.6	6171.0	6368.7	6566.3
3882.9	30°	4303.5	4917.0	5530.2	5946.0	6361.8	6552.6	6743.7
3760.5	32.5°	4194.5	4896.3	5597.7	6086.3	6575.0	6763.9	6953.0
3640.3	35°	4067.5	4857.2	5647.2	6246.2	6845.2	7026.4	7207.4
3498.7	37.5°	3903.8	4790.2	5676.6	6425.3	7174.0	7404.8	7635.6
3329.9	40°	3701.0	4698.0	5695.1	6652.7	7610.0	7946.4	8282.7
3143.5	42.5°	3475.7	4602.8	5730.3	6950.1	8169.9	8655.4	9140.9
2945.6	45°	3237.0	4514.4	5792.0	7341.5	8890.9	9545.8	10200.7
2789.0	47.5°	3048.4	4441.4	5834.4	7758.5	9682.5	10604.4	11526.1
2685.0	50°	2916.9	4361.8	5806.7	8145.3	10484.0	11873.7	13263.3
2616.5	52.5°	2818.6	4227.4	5636.3	8396.6	11156.7	13207.0	15257.4
2566.8	55°	2724.8	4004.5	5284.2	8341.2	11398.1	14389.1	17380.4
2508.0	57.5°	2619.6	3690.3	4760.8	7951.6	11142.5	15226.9	19311.4
2418.0	60°	2505.8	3282.3	4058.8	7226.4	10394.0	15436.3	20478.4
2261.6	62.5°	2319.9	2794.0	3268.1	6245.9	9223.6	14554.7	19885.8
2105.9	65°	2133.4	2354.7	2576.0	5245.4	7915.1	13307.4	18699.7
1884.9	67.5°	1869.5	1932.5	1995.3	4265.4	6535.5	11823.0	17110.5
1618.5	70°	1547.2	1529.4	1511.4	3358.4	5205.5	10203.3	15201.2
1375.4	72.5°	1274.3	1220.0	1165.8	2567.5	3969.2	8447.5	12925.9
1116.7	75°	1003.5	954.4	905.3	1863.5	2821.7	6434.6	10047.6
873.8	77.5°	763.9	730.3	696.9	1262.7	1828.5	4503.7	7178.8
643.3	80°	550.2	536.4	522.5	813.6	1104.8	2901.6	4698.5
447.1	82.5°	378.6	375.8	373.4	500.4	627.7	1679.4	2731.2
273.4	85°	223.2	224.6	225.8	267.5	309.4	755.4	1201.7
117.0	87.5°	96.5	97.8	99.0	110.9	122.8	247.4	372.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)