

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P950888

Luminaire Tested: **GALN-SB5A-950-U-SLL**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P950888
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GALN-SB5A-950-U-SLL
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(5) 90 CRI, 5000K, 350mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR LEFT OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15707 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U0 - G4


Input Watts (W): 141.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P950888
 CATALOG NUMBER: GALN-SB5A-950-U-SLL

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 4.8 fc
 Type IV - Short - N/A

REPORT NUMBER: P950888
CATALOG NUMBER: GALN-SB5A-950-U-SLL

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P950888

CATALOG NUMBER: GALN-SB5A-950-U-SLL

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3991.9	0.0	3991.9
	% Fixture	25.4	0.0	25.4
Street Side	Lumens	11715.1	0.0	11715.1
	% Fixture	74.6	0.0	74.6
Total	Lumens	15707.0	0.0	15707.0
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.3	1.4
10°-20°	672.6	4.3
20°-30°	1038.9	6.6
30°-40°	1316.6	8.4
40°-50°	1985.7	12.6
50°-60°	3208.2	20.4
60°-70°	3999.6	25.5
70°-80°	2622.7	16.7
80°-90°	648.4	4.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	15707.0	100.0
0°-180°	15707.0	100.0



REPORT NUMBER: P950888


CATALOG NUMBER: GALN-SB5A-950-U-SLL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1056.5	6.7			
FM (30°-60°)	4581.4	29.2			
FH (60°-80°)	5543.1	35.3			G3/7500
FVH (80°-90°)	534.1	3.4			G4/750
BL (0°-30°)	869.3	5.5	B2/1000		
BM (30°-60°)	1929.1	12.3	B2/2500		
BH (60°-80°)	1079.2	6.9	B3/2500		G3/2500
BVH (80°-90°)	114.3	0.7			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G4

Type IV Short



REPORT NUMBER: P950888

CATALOG NUMBER: GALN-SB5A-950-U-SLL

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°
0°	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8
2.5°	2322.7	2331.5	2340.4	2352.9	2365.4	2372.8	2380.3	2384.0	2387.8	2386.1
5°	2497.6	2528.3	2559.2	2589.7	2620.2	2636.8	2653.4	2663.4	2673.5	2681.2
7.5°	2673.3	2723.3	2773.3	2818.3	2863.3	2890.4	2917.5	2932.2	2946.8	2953.8
10°	2808.0	2867.1	2926.3	2979.1	3031.9	3063.9	3095.7	3110.0	3124.2	3129.5
12.5°	2890.4	2954.6	3018.6	3066.4	3114.0	3137.2	3160.4	3168.2	3176.0	3176.8
15°	2940.6	2995.9	3051.2	3081.1	3111.1	3112.0	3112.8	3104.5	3096.2	3086.4
17.5°	2968.8	3006.1	3043.5	3044.1	3044.6	3011.0	2977.5	2946.7	2915.9	2894.2
20°	2999.8	3012.8	3025.9	2986.6	2947.2	2873.1	2799.0	2745.1	2691.1	2658.0
22.5°	3035.9	3018.8	3001.7	2920.2	2838.6	2729.6	2620.7	2553.2	2485.7	2449.1
25°	3082.3	3028.4	2974.6	2850.7	2726.9	2594.6	2462.2	2391.2	2320.5	2285.8
27.5°	3145.3	3049.0	2952.6	2788.6	2624.6	2477.9	2331.2	2261.5	2191.8	2159.0
30°	3230.2	3086.6	2943.1	2741.2	2539.3	2386.4	2233.6	2168.9	2104.2	2073.7
32.5°	3330.5	3133.9	2937.3	2708.8	2480.4	2336.8	2193.2	2142.4	2091.5	2069.5
35°	3452.4	3211.7	2971.1	2733.0	2495.1	2395.3	2295.6	2283.8	2271.9	2270.1
37.5°	3657.5	3374.4	3091.3	2874.9	2658.6	2652.2	2645.7	2699.9	2754.1	2782.3
40°	3967.5	3659.6	3351.7	3190.8	3029.9	3143.5	3257.0	3388.8	3520.6	3586.2
42.5°	4378.5	4073.0	3767.6	3674.9	3582.2	3829.9	4077.5	4317.2	4556.9	4697.6
45°	4886.2	4611.8	4337.3	4296.4	4255.5	4652.2	5049.0	5442.9	5836.8	6075.9
47.5°	5521.0	5254.1	4987.0	4978.8	4970.5	5542.8	6115.0	6691.6	7268.1	7606.7
50°	6353.2	6023.4	5693.7	5695.1	5696.5	6434.1	7171.8	7932.8	8693.9	9154.1
52.5°	7308.3	6909.0	6509.8	6469.4	6429.0	7310.1	8191.2	9132.9	10074.5	10626.0
55°	8325.3	7930.8	7536.3	7378.9	7221.5	8202.1	9182.7	10305.3	11427.9	12083.9
57.5°	9250.2	9035.4	8820.5	8504.8	8189.2	9179.4	10169.5	11441.1	12712.5	13526.0
60°	9809.2	10142.9	10476.7	10084.6	9692.6	10629.7	11566.7	12928.1	14289.5	15168.7
62.5°	9525.4	10437.1	11348.9	11304.7	11260.5	12118.9	12977.3	14272.6	15567.7	16380.4
65°	8957.2	9813.0	10668.7	10838.0	11007.3	12098.1	13189.1	14445.0	15700.9	16392.8
67.5°	8196.0	9009.9	9823.7	9903.1	9982.5	11119.1	12255.6	13517.0	14778.3	15320.3
70°	7281.4	8166.6	9052.0	9087.4	9123.0	10139.4	11155.8	12241.3	13326.7	13627.9
72.5°	6191.5	7207.4	8223.3	8248.9	8274.3	9069.5	9864.8	10677.7	11490.6	11521.1
75°	4812.8	5864.2	6915.7	7010.1	7104.5	7723.2	8341.9	8914.1	9486.4	9333.1
77.5°	3438.7	4420.1	5401.7	5536.8	5671.9	6142.2	6612.6	7018.4	7424.4	7160.8
80°	2250.6	3076.3	3902.0	4069.9	4237.8	4593.0	4948.1	5161.3	5374.3	4950.4
82.5°	1308.3	1872.8	2437.3	2624.9	2812.5	3057.0	3301.5	3390.4	3479.3	3146.1
85°	575.6	875.2	1174.8	1334.4	1493.9	1694.8	1895.6	1946.1	1996.6	1729.7
87.5°	178.2	278.9	379.6	468.6	557.6	658.1	758.5	762.8	767.1	644.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P950888
 CATALOG NUMBER: GALN-SB5A-950-U-SLL

CANDELA DISTRIBUTION (continued):

50°		55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
2159.8	0°	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8
2387.8	2.5°	2384.0	2380.3	2372.8	2365.4	2352.9	2340.4	2331.5	2322.7	2304.9	2287.1
2673.5	5°	2663.4	2653.4	2636.8	2620.2	2589.7	2559.2	2528.3	2497.6	2458.2	2418.8
2946.8	7.5°	2932.2	2917.5	2890.4	2863.3	2818.3	2773.3	2723.3	2673.3	2608.3	2543.4
3124.2	10°	3110.0	3095.7	3063.9	3031.9	2979.1	2926.3	2867.1	2808.0	2725.8	2643.7
3176.0	12.5°	3168.2	3160.4	3137.2	3114.0	3066.4	3018.6	2954.6	2890.4	2800.2	2710.0
3096.2	15°	3104.5	3112.8	3112.0	3111.1	3081.1	3051.2	2995.9	2940.6	2846.5	2752.4
2915.9	17.5°	2946.7	2977.5	3011.0	3044.6	3044.1	3043.5	3006.1	2968.8	2873.4	2778.0
2691.1	20°	2745.1	2799.0	2873.1	2947.2	2986.6	3025.9	3012.8	2999.8	2900.7	2801.5
2485.7	22.5°	2553.2	2620.7	2729.6	2838.6	2920.2	3001.7	3018.8	3035.9	2934.6	2833.2
2320.5	25°	2391.2	2462.2	2594.6	2726.9	2850.7	2974.6	3028.4	3082.3	2983.0	2883.8
2191.8	27.5°	2261.5	2331.2	2477.9	2624.6	2788.6	2952.6	3049.0	3145.3	3050.6	2955.9
2104.2	30°	2168.9	2233.6	2386.4	2539.3	2741.2	2943.1	3086.6	3230.2	3138.7	3047.3
2091.5	32.5°	2142.4	2193.2	2336.8	2480.4	2708.8	2937.3	3133.9	3330.5	3239.9	3149.4
2271.9	35°	2283.8	2295.6	2395.3	2495.1	2733.0	2971.1	3211.7	3452.4	3365.7	3278.9
2754.1	37.5°	2699.9	2645.7	2652.2	2658.6	2874.9	3091.3	3374.4	3657.5	3546.9	3436.4
3520.6	40°	3388.8	3257.0	3143.5	3029.9	3190.8	3351.7	3659.6	3967.5	3806.3	3645.2
4556.9	42.5°	4317.2	4077.5	3829.9	3582.2	3674.9	3767.6	4073.0	4378.5	4146.0	3913.4
5836.8	45°	5442.9	5049.0	4652.2	4255.5	4296.4	4337.3	4611.8	4886.2	4572.5	4258.8
7268.1	47.5°	6691.6	6115.0	5542.8	4970.5	4978.8	4987.0	5254.1	5521.0	5079.5	4638.0
8693.9	50°	7932.8	7171.8	6434.1	5696.5	5695.1	5693.7	6023.4	6353.2	5687.5	5021.9
10074.5	52.5°	9132.9	8191.2	7310.1	6429.0	6469.4	6509.8	6909.0	7308.3	6326.2	5344.1
11427.9	55°	10305.3	9182.7	8202.1	7221.5	7378.9	7536.3	7930.8	8325.3	6892.5	5459.7
12712.5	57.5°	11441.1	10169.5	9179.4	8189.2	8504.8	8820.5	9035.4	9250.2	7293.8	5337.3
14289.5	60°	12928.1	11566.7	10629.7	9692.6	10084.6	10476.7	10142.9	9809.2	7394.0	4978.8
15567.7	62.5°	14272.6	12977.3	12118.9	11260.5	11304.7	11348.9	10437.1	9525.4	6971.8	4418.2
15700.9	65°	14445.0	13189.1	12098.1	11007.3	10838.0	10668.7	9813.0	8957.2	6374.3	3791.3
14778.3	67.5°	13517.0	12255.6	11119.1	9982.5	9903.1	9823.7	9009.9	8196.0	5663.3	3130.5
13326.7	70°	12241.3	11155.8	10139.4	9123.0	9087.4	9052.0	8166.6	7281.4	4887.4	2493.4
11490.6	72.5°	10677.7	9864.8	9069.5	8274.3	8248.9	8223.3	7207.4	6191.5	4046.4	1901.3
9486.4	75°	8914.1	8341.9	7723.2	7104.5	7010.1	6915.7	5864.2	4812.8	3082.2	1351.6
7424.4	77.5°	7018.4	6612.6	6142.2	5671.9	5536.8	5401.7	4420.1	3438.7	2157.3	875.9
5374.3	80°	5161.3	4948.1	4593.0	4237.8	4069.9	3902.0	3076.3	2250.6	1389.9	529.2
3479.3	82.5°	3390.4	3301.5	3057.0	2812.5	2624.9	2437.3	1872.8	1308.3	804.4	300.7
1996.6	85°	1946.1	1895.6	1694.8	1493.9	1334.4	1174.8	875.2	575.6	361.9	148.2
767.1	87.5°	762.8	758.5	658.1	557.6	468.6	379.6	278.9	178.2	118.5	58.8
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P950888
 CATALOG NUMBER: GALN-SB5A-950-U-SLL

CANDELA DISTRIBUTION (continued):

105°		110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
2159.8	0°	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8
2268.1	2.5°	2249.2	2230.1	2211.1	2192.8	2174.6	2156.9	2137.3	2121.4	2105.6	2091.2
2379.6	5°	2340.4	2300.8	2261.4	2224.5	2187.6	2152.8	2118.4	2088.4	2058.3	2033.1
2483.4	7.5°	2423.4	2365.0	2306.5	2255.1	2203.6	2156.1	2111.6	2071.7	2031.8	1998.6
2564.4	10°	2485.2	2414.2	2343.2	2282.3	2221.3	2162.7	2114.9	2072.8	2030.7	1997.6
2620.2	12.5°	2530.3	2446.6	2362.9	2294.0	2225.2	2163.6	2119.1	2084.6	2050.3	2028.2
2655.0	15°	2557.5	2461.1	2364.7	2285.0	2205.3	2137.1	2101.4	2084.9	2068.5	2071.5
2671.6	17.5°	2565.3	2453.4	2341.5	2245.6	2149.7	2069.5	2047.5	2053.6	2059.6	2095.7
2684.6	20°	2567.8	2432.2	2296.6	2177.7	2058.9	1965.5	1959.7	1987.9	2016.1	2078.8
2702.2	22.5°	2571.1	2406.2	2241.2	2098.1	1955.0	1848.6	1860.0	1901.7	1943.4	2015.0
2734.0	25°	2584.2	2380.5	2176.8	2009.2	1841.6	1732.6	1763.3	1811.3	1859.4	1923.8
2783.8	27.5°	2611.5	2363.3	2115.1	1927.9	1740.6	1641.4	1678.7	1725.1	1771.6	1824.5
2848.2	30°	2649.0	2355.3	2061.4	1859.9	1658.4	1575.1	1604.4	1641.2	1678.2	1722.1
2915.4	32.5°	2681.3	2345.3	2009.2	1801.3	1593.4	1526.2	1539.2	1561.0	1582.8	1617.9
2992.0	35°	2705.0	2326.6	1948.3	1743.7	1539.1	1483.1	1477.7	1483.7	1489.8	1516.5
3077.7	37.5°	2719.1	2294.5	1869.9	1675.9	1481.9	1433.0	1413.3	1406.6	1400.0	1419.2
3186.6	40°	2728.0	2250.4	1772.8	1595.0	1417.2	1372.9	1342.7	1327.7	1312.7	1326.5
3329.1	42.5°	2744.8	2204.8	1664.9	1505.8	1346.6	1305.8	1267.6	1247.8	1227.9	1239.1
3516.6	45°	2774.4	2162.4	1550.5	1410.9	1271.4	1229.9	1193.1	1173.7	1154.3	1163.8
3716.3	47.5°	2794.7	2127.4	1460.2	1335.9	1211.7	1158.2	1126.5	1110.3	1094.0	1103.0
3901.6	50°	2781.4	2089.3	1397.2	1286.1	1175.1	1104.8	1067.9	1053.5	1039.1	1053.1
4022.0	52.5°	2699.8	2024.9	1350.1	1253.3	1156.6	1075.8	1024.2	1010.0	995.8	1016.8
3995.5	55°	2531.1	1918.2	1305.2	1229.5	1153.9	1078.7	1001.0	978.5	956.0	985.8
3808.8	57.5°	2280.4	1767.7	1254.8	1201.3	1147.9	1081.6	987.1	954.3	921.5	953.4
3461.5	60°	1944.2	1572.2	1200.3	1158.2	1116.2	1072.5	974.0	931.5	888.9	917.0
2991.8	62.5°	1565.4	1338.3	1111.3	1083.3	1055.5	1050.1	958.8	905.5	852.4	870.2
2512.6	65°	1233.9	1127.9	1021.9	1008.7	995.6	996.2	926.6	870.1	813.5	820.3
2043.2	67.5°	955.8	925.7	895.5	902.9	910.2	908.4	869.2	822.2	775.1	772.9
1608.7	70°	724.0	732.6	741.1	775.3	809.3	809.3	796.5	763.0	729.5	722.0
1229.9	72.5°	558.4	584.4	610.4	658.8	707.1	715.3	715.4	692.5	669.5	658.6
892.6	75°	433.6	457.2	480.7	534.9	589.1	626.6	623.4	605.8	588.0	577.6
604.9	77.5°	333.8	349.8	365.9	418.5	471.2	532.9	531.3	517.1	502.9	492.3
389.7	80°	250.3	256.9	263.6	308.1	352.7	426.4	426.2	414.3	402.4	393.5
239.7	82.5°	178.9	180.0	181.3	214.2	247.0	310.0	313.5	307.6	301.8	295.5
128.1	85°	108.2	107.6	106.9	131.0	155.0	201.8	206.4	200.2	193.9	186.9
53.1	87.5°	47.4	46.8	46.2	56.0	65.9	85.4	91.2	88.7	86.2	84.9
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P950888
 CATALOG NUMBER: GALN-SB5A-950-U-SLL

CANDELA DISTRIBUTION (continued):

160°		165°	170°	175°	180°	185°	190°	195°	200°	205°	210°
2159.8	0°	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8
2077.0	2.5°	2064.5	2051.9	2039.3	2026.8	2017.1	2007.3	1999.5	1991.6	1985.5	1979.3
2008.0	5°	1985.8	1963.6	1943.4	1923.2	1907.7	1892.1	1881.3	1870.4	1862.7	1855.0
1965.5	7.5°	1937.6	1909.6	1884.9	1860.2	1841.8	1823.4	1810.4	1797.5	1788.6	1779.8
1964.4	10°	1934.3	1904.2	1876.4	1848.6	1826.6	1804.5	1790.0	1775.5	1767.1	1758.7
2006.4	12.5°	1982.7	1959.1	1930.4	1901.7	1873.5	1845.3	1826.7	1808.0	1798.7	1789.4
2074.5	15°	2068.3	2062.2	2037.3	2012.3	1972.2	1932.1	1903.7	1875.4	1862.4	1849.5
2131.8	17.5°	2151.1	2170.2	2150.1	2130.0	2076.9	2023.8	1982.0	1940.2	1921.0	1901.7
2141.6	20°	2181.8	2222.0	2212.7	2203.4	2142.6	2081.9	2030.7	1979.6	1955.0	1930.3
2086.7	22.5°	2139.0	2191.3	2197.0	2202.5	2144.5	2086.5	2033.8	1981.0	1955.1	1929.0
1988.3	25°	2039.8	2091.2	2110.5	2129.6	2082.0	2034.5	1987.6	1940.9	1918.3	1895.9
1877.4	27.5°	1918.7	1959.9	1981.3	2002.8	1968.9	1935.1	1898.7	1862.3	1847.2	1832.1
1766.0	30°	1800.2	1834.5	1851.9	1869.4	1843.6	1817.7	1791.7	1765.5	1757.8	1750.0
1653.0	32.5°	1685.9	1718.8	1738.1	1757.5	1733.8	1710.0	1689.2	1668.4	1663.3	1658.3
1543.2	35°	1575.7	1608.3	1631.5	1654.7	1637.8	1621.0	1601.7	1582.6	1574.9	1567.3
1438.4	37.5°	1470.8	1503.3	1532.0	1560.6	1552.8	1545.0	1527.4	1509.7	1495.6	1481.7
1340.3	40°	1371.7	1403.0	1436.0	1469.0	1471.0	1472.8	1457.8	1442.8	1422.4	1402.2
1250.5	42.5°	1280.2	1309.9	1345.6	1381.2	1390.7	1400.3	1387.6	1375.0	1349.7	1324.4
1173.4	45°	1201.6	1229.8	1266.7	1303.7	1317.4	1331.0	1319.6	1308.3	1279.3	1250.5
1111.8	47.5°	1139.4	1166.9	1203.4	1239.9	1255.6	1271.4	1263.4	1255.5	1229.8	1204.1
1067.1	50°	1093.1	1119.0	1151.7	1184.4	1204.6	1224.8	1224.3	1224.0	1203.4	1182.9
1037.7	52.5°	1061.5	1085.3	1115.7	1146.2	1170.2	1194.1	1198.4	1202.8	1186.0	1169.3
1015.4	55°	1041.1	1066.8	1093.5	1120.1	1145.5	1170.9	1176.9	1182.9	1168.3	1153.7
985.4	57.5°	1015.6	1045.8	1072.1	1098.6	1124.2	1149.7	1155.8	1161.8	1147.1	1132.3
945.0	60°	979.6	1014.3	1041.1	1067.9	1093.6	1119.3	1125.9	1132.6	1118.1	1103.8
888.1	62.5°	928.4	968.9	997.5	1026.1	1049.6	1073.1	1079.5	1085.9	1072.9	1059.9
827.1	65°	870.4	913.7	941.1	968.5	989.2	1009.9	1016.4	1022.9	1010.4	997.9
770.8	67.5°	810.7	850.8	876.7	902.6	920.5	938.4	944.7	951.0	939.5	928.1
714.6	70°	749.7	784.9	807.2	829.6	845.8	861.9	868.1	874.2	864.9	855.5
647.7	72.5°	675.4	703.0	723.2	743.4	759.3	775.1	782.4	789.7	781.9	774.1
567.1	75°	587.6	608.2	626.5	644.8	659.2	673.6	681.3	688.9	685.1	681.3
481.7	77.5°	498.4	515.1	530.8	546.6	561.8	576.8	584.0	591.1	585.8	580.3
384.6	80°	398.5	412.3	425.6	438.8	450.4	461.8	471.3	480.7	478.4	476.1
289.3	82.5°	288.1	286.9	282.3	277.6	302.2	326.7	342.8	358.9	357.9	356.8
179.8	85°	173.9	167.8	155.0	142.1	165.1	188.1	208.0	227.9	226.3	224.6
83.5	87.5°	83.3	83.0	73.3	63.4	73.0	82.7	90.8	98.8	96.8	94.6
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P950888
 CATALOG NUMBER: GALN-SB5A-950-U-SLL

CANDELA DISTRIBUTION (continued):

215°		220°	225°	230°	235°	240°	245°	250°	255°	260°	265°
2159.8	0°	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8
1973.7	2.5°	1968.0	1960.9	1968.0	1973.7	1979.3	1985.5	1991.6	1999.5	2007.3	2017.1
1849.1	5°	1843.2	1837.4	1843.2	1849.1	1855.0	1862.7	1870.4	1881.3	1892.1	1907.7
1774.5	7.5°	1769.3	1765.3	1769.3	1774.5	1779.8	1788.6	1797.5	1810.4	1823.4	1841.8
1754.2	10°	1749.8	1747.9	1749.8	1754.2	1758.7	1767.1	1775.5	1790.0	1804.5	1826.6
1785.6	12.5°	1781.8	1781.1	1781.8	1785.6	1789.4	1798.7	1808.0	1826.7	1845.3	1873.5
1844.5	15°	1839.5	1839.1	1839.5	1844.5	1849.5	1862.4	1875.4	1903.7	1932.1	1972.2
1895.4	17.5°	1889.0	1888.0	1889.0	1895.4	1901.7	1921.0	1940.2	1982.0	2023.8	2076.9
1922.4	20°	1914.5	1912.0	1914.5	1922.4	1930.3	1955.0	1979.6	2030.7	2081.9	2142.6
1920.3	22.5°	1911.6	1907.9	1911.6	1920.3	1929.0	1955.1	1981.0	2033.8	2086.5	2144.5
1887.7	25°	1879.5	1874.7	1879.5	1887.7	1895.9	1918.3	1940.9	1987.6	2034.5	2082.0
1828.3	27.5°	1824.6	1823.4	1824.6	1828.3	1832.1	1847.2	1862.3	1898.7	1935.1	1968.9
1750.0	30°	1750.0	1751.3	1750.0	1750.0	1750.0	1757.8	1765.5	1791.7	1817.7	1843.6
1658.9	32.5°	1659.7	1660.9	1659.7	1658.9	1658.3	1663.3	1668.4	1689.2	1710.0	1733.8
1565.6	35°	1563.9	1563.1	1563.9	1565.6	1567.3	1574.9	1582.6	1601.7	1621.0	1637.8
1474.3	37.5°	1467.0	1462.8	1467.0	1474.3	1481.7	1495.6	1509.7	1527.4	1545.0	1552.8
1388.4	40°	1374.8	1366.7	1374.8	1388.4	1402.2	1422.4	1442.8	1457.8	1472.8	1471.0
1304.4	42.5°	1284.5	1271.4	1284.5	1304.4	1324.4	1349.7	1375.0	1387.6	1400.3	1390.7
1227.0	45°	1203.6	1188.5	1203.6	1227.0	1250.5	1279.3	1308.3	1319.6	1331.0	1317.4
1182.4	47.5°	1160.7	1146.2	1160.7	1182.4	1204.1	1229.8	1255.5	1263.4	1271.4	1255.6
1162.8	50°	1142.7	1128.8	1142.7	1162.8	1182.9	1203.4	1224.0	1224.3	1224.8	1204.6
1151.3	52.5°	1133.4	1120.5	1133.4	1151.3	1169.3	1186.0	1202.8	1198.4	1194.1	1170.2
1137.9	55°	1122.2	1110.6	1122.2	1137.9	1153.7	1168.3	1182.9	1176.9	1170.9	1145.5
1116.7	57.5°	1101.1	1089.0	1101.1	1116.7	1132.3	1147.1	1161.8	1155.8	1149.7	1124.2
1087.7	60°	1071.6	1059.2	1071.6	1087.7	1103.8	1118.1	1132.6	1125.9	1119.3	1093.6
1043.0	62.5°	1026.1	1011.1	1026.1	1043.0	1059.9	1072.9	1085.9	1079.5	1073.1	1049.6
981.5	65°	965.1	952.3	965.1	981.5	997.9	1010.4	1022.9	1016.4	1009.9	989.2
912.8	67.5°	897.6	886.0	897.6	912.8	928.1	939.5	951.0	944.7	938.4	920.5
840.9	70°	826.3	813.1	826.3	840.9	855.5	864.9	874.2	868.1	861.9	845.8
760.2	72.5°	746.3	733.5	746.3	760.2	774.1	781.9	789.7	782.4	775.1	759.3
669.6	75°	657.9	645.6	657.9	669.6	681.3	685.1	688.9	681.3	673.6	659.2
568.6	77.5°	556.8	547.0	556.8	568.6	580.3	585.8	591.1	584.0	576.8	561.8
460.3	80°	444.4	426.0	444.4	460.3	476.1	478.4	480.7	471.3	461.8	450.4
343.5	82.5°	330.0	318.3	330.0	343.5	356.8	357.9	358.9	342.8	326.7	302.2
214.2	85°	203.7	193.1	203.7	214.2	224.6	226.3	227.9	208.0	188.1	165.1
89.3	87.5°	83.9	78.7	83.9	89.3	94.6	96.8	98.8	90.8	82.7	73.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P950888
 CATALOG NUMBER: GALN-SB5A-950-U-SLL

CANDELA DISTRIBUTION (continued):

270°		275°	280°	285°	290°	295°	300°	305°	310°	315°	320°
2159.8	0°	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8
2026.8	2.5°	2039.3	2051.9	2064.5	2077.0	2091.2	2105.6	2121.4	2137.3	2156.9	2174.6
1923.2	5°	1943.4	1963.6	1985.8	2008.0	2033.1	2058.3	2088.4	2118.4	2152.8	2187.6
1860.2	7.5°	1884.9	1909.6	1937.6	1965.5	1998.6	2031.8	2071.7	2111.6	2156.1	2203.6
1848.6	10°	1876.4	1904.2	1934.3	1964.4	1997.6	2030.7	2072.8	2114.9	2162.7	2221.3
1901.7	12.5°	1930.4	1959.1	1982.7	2006.4	2028.2	2050.3	2084.6	2119.1	2163.6	2225.2
2012.3	15°	2037.3	2062.2	2068.3	2074.5	2071.5	2068.5	2084.9	2101.4	2137.1	2205.3
2130.0	17.5°	2150.1	2170.2	2151.1	2131.8	2095.7	2059.6	2053.6	2047.5	2069.5	2149.7
2203.4	20°	2212.7	2222.0	2181.8	2141.6	2078.8	2016.1	1987.9	1959.7	1965.5	2058.9
2202.5	22.5°	2197.0	2191.3	2139.0	2086.7	2015.0	1943.4	1901.7	1860.0	1848.6	1955.0
2129.6	25°	2110.5	2091.2	2039.8	1988.3	1923.8	1859.4	1811.3	1763.3	1732.6	1841.6
2002.8	27.5°	1981.3	1959.9	1918.7	1877.4	1824.5	1771.6	1725.1	1678.7	1641.4	1740.6
1869.4	30°	1851.9	1834.5	1800.2	1766.0	1722.1	1678.2	1641.2	1604.4	1575.1	1658.4
1757.5	32.5°	1738.1	1718.8	1685.9	1653.0	1617.9	1582.8	1561.0	1539.2	1526.2	1593.4
1654.7	35°	1631.5	1608.3	1575.7	1543.2	1516.5	1489.8	1483.7	1477.7	1483.1	1539.1
1560.6	37.5°	1532.0	1503.3	1470.8	1438.4	1419.2	1400.0	1406.6	1413.3	1433.0	1481.9
1469.0	40°	1436.0	1403.0	1371.7	1340.3	1326.5	1312.7	1327.7	1342.7	1372.9	1417.2
1381.2	42.5°	1345.6	1309.9	1280.2	1250.5	1239.1	1227.9	1247.8	1267.6	1305.8	1346.6
1303.7	45°	1266.7	1229.8	1201.6	1173.4	1163.8	1154.3	1173.7	1193.1	1229.9	1271.4
1239.9	47.5°	1203.4	1166.9	1139.4	1111.8	1103.0	1094.0	1110.3	1126.5	1158.2	1211.7
1184.4	50°	1151.7	1119.0	1093.1	1067.1	1053.1	1039.1	1053.5	1067.9	1104.8	1175.1
1146.2	52.5°	1115.7	1085.3	1061.5	1037.7	1016.8	995.8	1010.0	1024.2	1075.8	1156.6
1120.1	55°	1093.5	1066.8	1041.1	1015.4	985.8	956.0	978.5	1001.0	1078.7	1153.9
1098.6	57.5°	1072.1	1045.8	1015.6	985.4	953.4	921.5	954.3	987.1	1081.6	1147.9
1067.9	60°	1041.1	1014.3	979.6	945.0	917.0	888.9	931.5	974.0	1072.5	1116.2
1026.1	62.5°	997.5	968.9	928.4	888.1	870.2	852.4	905.5	958.8	1050.1	1055.5
968.5	65°	941.1	913.7	870.4	827.1	820.3	813.5	870.1	926.6	996.2	995.6
902.6	67.5°	876.7	850.8	810.7	770.8	772.9	775.1	822.2	869.2	908.4	910.2
829.6	70°	807.2	784.9	749.7	714.6	722.0	729.5	763.0	796.5	809.3	809.3
743.4	72.5°	723.2	703.0	675.4	647.7	658.6	669.5	692.5	715.4	715.3	707.1
644.8	75°	626.5	608.2	587.6	567.1	577.6	588.0	605.8	623.4	626.6	589.1
546.6	77.5°	530.8	515.1	498.4	481.7	492.3	502.9	517.1	531.3	532.9	471.2
438.8	80°	425.6	412.3	398.5	384.6	393.5	402.4	414.3	426.2	426.4	352.7
277.6	82.5°	282.3	286.9	288.1	289.3	295.5	301.8	307.6	313.5	310.0	247.0
142.1	85°	155.0	167.8	173.9	179.8	186.9	193.9	200.2	206.4	201.8	155.0
63.4	87.5°	73.3	83.0	83.3	83.5	84.9	86.2	88.7	91.2	85.4	65.9
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P950888
 CATALOG NUMBER: GALN-SB5A-950-U-SLL

CANDELA DISTRIBUTION (continued):

325°		330°	335°	340°	345°	350°	355°	360°
2159.8	0°	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8	2159.8
2192.8	2.5°	2211.1	2230.1	2249.2	2268.1	2287.1	2304.9	2322.7
2224.5	5°	2261.4	2300.8	2340.4	2379.6	2418.8	2458.2	2497.6
2255.1	7.5°	2306.5	2365.0	2423.4	2483.4	2543.4	2608.3	2673.3
2282.3	10°	2343.2	2414.2	2485.2	2564.4	2643.7	2725.8	2808.0
2294.0	12.5°	2362.9	2446.6	2530.3	2620.2	2710.0	2800.2	2890.4
2285.0	15°	2364.7	2461.1	2557.5	2655.0	2752.4	2846.5	2940.6
2245.6	17.5°	2341.5	2453.4	2565.3	2671.6	2778.0	2873.4	2968.8
2177.7	20°	2296.6	2432.2	2567.8	2684.6	2801.5	2900.7	2999.8
2098.1	22.5°	2241.2	2406.2	2571.1	2702.2	2833.2	2934.6	3035.9
2009.2	25°	2176.8	2380.5	2584.2	2734.0	2883.8	2983.0	3082.3
1927.9	27.5°	2115.1	2363.3	2611.5	2783.8	2955.9	3050.6	3145.3
1859.9	30°	2061.4	2355.3	2649.0	2848.2	3047.3	3138.7	3230.2
1801.3	32.5°	2009.2	2345.3	2681.3	2915.4	3149.4	3239.9	3330.5
1743.7	35°	1948.3	2326.6	2705.0	2992.0	3278.9	3365.7	3452.4
1675.9	37.5°	1869.9	2294.5	2719.1	3077.7	3436.4	3546.9	3657.5
1595.0	40°	1772.8	2250.4	2728.0	3186.6	3645.2	3806.3	3967.5
1505.8	42.5°	1664.9	2204.8	2744.8	3329.1	3913.4	4146.0	4378.5
1410.9	45°	1550.5	2162.4	2774.4	3516.6	4258.8	4572.5	4886.2
1335.9	47.5°	1460.2	2127.4	2794.7	3716.3	4638.0	5079.5	5521.0
1286.1	50°	1397.2	2089.3	2781.4	3901.6	5021.9	5687.5	6353.2
1253.3	52.5°	1350.1	2024.9	2699.8	4022.0	5344.1	6326.2	7308.3
1229.5	55°	1305.2	1918.2	2531.1	3995.5	5459.7	6892.5	8325.3
1201.3	57.5°	1254.8	1767.7	2280.4	3808.8	5337.3	7293.8	9250.2
1158.2	60°	1200.3	1572.2	1944.2	3461.5	4978.8	7394.0	9809.2
1083.3	62.5°	1111.3	1338.3	1565.4	2991.8	4418.2	6971.8	9525.4
1008.7	65°	1021.9	1127.9	1233.9	2512.6	3791.3	6374.3	8957.2
902.9	67.5°	895.5	925.7	955.8	2043.2	3130.5	5663.3	8196.0
775.3	70°	741.1	732.6	724.0	1608.7	2493.4	4887.4	7281.4
658.8	72.5°	610.4	584.4	558.4	1229.9	1901.3	4046.4	6191.5
534.9	75°	480.7	457.2	433.6	892.6	1351.6	3082.2	4812.8
418.5	77.5°	365.9	349.8	333.8	604.9	875.9	2157.3	3438.7
308.1	80°	263.6	256.9	250.3	389.7	529.2	1389.9	2250.6
214.2	82.5°	181.3	180.0	178.9	239.7	300.7	804.4	1308.3
131.0	85°	106.9	107.6	108.2	128.1	148.2	361.9	575.6
56.0	87.5°	46.2	46.8	47.4	53.1	58.8	118.5	178.2
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)