

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P946584

Luminaire Tested: **GALN-SB2A-940-U-SLR-HSS**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P946584
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GALN-SB2A-940-U-SLR-HSS
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(2) 90 CRI, 4000K, 350mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4961 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 57.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P946584
 CATALOG NUMBER: GALN-SB2A-940-U-SLR-HSS

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.5 fc
 Type IV - Short - N/A

REPORT NUMBER: P946584
CATALOG NUMBER: GALN-SB2A-940-U-SLR-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P946584
 CATALOG NUMBER: GALN-SB2A-940-U-SLR-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	694.8	0.0	694.8
	% Fixture	14.0	0.0	14.0
Street Side	Lumens	4266.2	0.0	4266.2
	% Fixture	86.0	0.0	86.0
Total	Lumens	4961.0	0.0	4961.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.6	1.4
10°-20°	202.7	4.1
20°-30°	298.7	6.0
30°-40°	383.7	7.7
40°-50°	620.6	12.5
50°-60°	1088.3	21.9
60°-70°	1361.7	27.4
70°-80°	795.7	16.0
80°-90°	142.0	2.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4961.0	100.0
0°-180°	4961.0	100.0

Coefficient of Utilization



REPORT NUMBER: P946584


CATALOG NUMBER: GALN-SB2A-940-U-SLR-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	386.9	7.8			
FM (30°-60°)	1738.8	35.0			
FH (60°-80°)	2004.0	40.4			G2/5000
FVH (80°-90°)	136.5	2.8			G2/225
BL (0°-30°)	182.1	3.7	B1/500		
BM (30°-60°)	353.8	7.1	B1/1000		
BH (60°-80°)	153.4	3.1	B1/500		G1/500
BVH (80°-90°)	5.5	0.1			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short



REPORT NUMBER: P946584
 CATALOG NUMBER: GALN-SB2A-940-U-SLR-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9
2.5°	776.1	762.8	755.0	735.5	716.0	700.3	679.1	665.1	648.3	632.3
5°	865.0	843.5	817.5	781.9	749.5	716.3	684.2	652.4	618.9	588.2
7.5°	940.2	909.1	863.3	816.1	774.8	734.8	697.2	655.2	614.5	566.3
10°	997.6	958.0	897.8	835.9	788.4	748.1	711.5	676.0	635.0	576.9
12.5°	1032.5	990.1	918.7	846.2	791.9	746.7	718.4	702.7	686.6	628.8
15°	1058.1	1012.3	933.3	853.4	784.0	728.6	707.8	723.5	742.0	705.1
17.5°	1084.7	1036.6	952.5	856.5	762.8	693.4	684.5	725.2	767.9	766.2
20°	1110.0	1062.2	969.2	854.4	728.6	650.7	658.6	710.5	760.1	780.9
22.5°	1139.1	1088.5	985.3	846.5	684.2	610.7	635.3	687.3	730.7	755.3
25°	1174.6	1121.7	1007.9	834.9	636.4	577.6	611.8	660.3	695.5	712.6
27.5°	1212.9	1161.3	1037.9	828.8	597.7	554.0	585.1	628.2	659.6	671.6
30°	1260.4	1207.4	1073.5	821.9	572.4	540.3	557.4	590.9	621.7	633.6
32.5°	1312.4	1258.7	1107.6	805.5	557.1	530.1	530.4	551.6	579.6	594.0
35°	1377.3	1320.2	1144.2	769.6	544.8	518.1	504.1	514.4	537.6	554.7
37.5°	1469.9	1400.9	1189.0	718.4	526.7	499.7	476.4	478.8	496.6	515.4
40°	1597.7	1509.2	1241.6	665.1	500.7	473.7	446.0	445.0	458.0	476.4
42.5°	1770.7	1652.4	1304.8	614.1	475.7	442.2	413.9	412.2	422.4	438.5
45°	1999.0	1835.6	1382.4	570.4	456.3	411.5	383.5	382.8	391.3	405.3
47.5°	2291.2	2090.2	1460.0	540.7	446.0	387.2	358.5	359.9	367.4	380.0
50°	2669.5	2422.1	1483.6	525.6	446.0	374.2	336.3	343.1	349.3	358.8
52.5°	3123.0	2740.6	1405.7	512.0	448.7	375.9	317.5	332.2	336.6	344.8
55°	3543.4	2896.8	1208.5	493.2	449.4	386.5	301.4	323.3	331.5	334.6
57.5°	3787.4	2843.1	977.1	461.4	446.7	393.7	291.2	312.4	328.1	330.1
60°	3740.9	2654.8	719.4	437.1	426.5	391.0	288.1	295.6	320.6	323.6
62.5°	3382.8	2339.0	499.3	418.3	382.1	379.0	287.1	269.3	304.2	311.7
65°	2719.1	1841.4	352.7	360.2	334.9	353.0	281.6	242.0	284.3	294.6
67.5°	1972.6	1246.1	254.6	291.9	303.5	311.0	269.3	222.1	261.8	275.5
70°	1265.9	672.9	178.7	192.8	255.6	264.2	248.1	204.4	238.9	254.6
72.5°	899.9	397.5	128.5	135.0	205.4	220.1	218.4	184.6	212.2	231.4
75°	621.0	219.1	86.8	96.4	149.0	178.7	168.5	158.6	179.8	199.2
77.5°	389.3	98.1	51.9	67.0	97.7	140.5	115.5	122.7	140.1	158.2
80°	216.7	37.9	29.0	44.4	53.3	102.2	63.9	78.9	103.2	116.2
82.5°	47.2	4.8	13.0	19.1	20.8	59.5	33.8	45.8	64.9	63.9
85°	0.0	0.0	2.4	2.7	1.4	25.6	12.3	15.0	21.2	19.8
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P946584
 CATALOG NUMBER: GALN-SB2A-940-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

90°		95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
686.9	0°	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9
617.9	2.5°	615.2	598.4	586.1	580.0	574.8	579.6	582.4	582.4	594.0	600.8
569.4	5°	557.4	527.3	504.4	489.1	479.8	482.9	486.3	490.1	504.8	514.7
540.7	7.5°	517.4	471.3	436.4	414.9	403.6	405.3	407.7	410.8	425.2	435.1
544.8	10°	509.9	443.6	394.4	366.0	352.4	350.0	348.6	347.6	356.1	363.6
591.2	12.5°	540.7	445.0	376.3	341.8	325.0	317.8	309.6	303.1	304.5	309.3
661.6	15°	595.7	462.4	370.5	329.1	308.3	296.3	286.7	278.9	277.2	278.9
723.2	17.5°	658.6	486.0	369.8	318.2	292.2	279.9	272.0	264.9	262.5	262.8
757.7	20°	700.3	504.8	367.7	305.9	276.8	265.9	259.1	251.9	249.5	250.2
748.1	22.5°	704.4	514.7	364.7	292.2	261.4	252.2	245.4	238.9	238.5	238.5
712.2	25°	682.2	514.7	358.2	279.9	246.8	238.5	232.4	224.5	225.9	226.6
671.6	27.5°	647.6	502.4	345.9	270.0	234.1	225.6	219.4	212.2	213.9	215.0
633.6	30°	613.5	486.7	331.2	258.7	222.1	212.2	207.8	201.6	202.3	203.7
596.0	32.5°	581.7	469.9	313.7	249.5	210.2	200.3	196.9	190.0	191.0	192.4
559.1	35°	550.2	451.5	293.2	238.5	199.2	189.3	186.6	178.7	179.4	181.5
522.2	37.5°	516.4	432.0	276.5	227.6	188.7	178.4	175.7	167.5	168.1	170.5
483.9	40°	480.9	412.8	260.1	216.0	177.4	167.1	164.7	155.8	156.5	159.3
446.3	42.5°	445.0	392.0	247.4	201.0	165.8	154.8	152.4	144.2	145.2	148.3
413.5	45°	411.8	367.1	239.2	184.2	154.8	142.5	140.1	132.6	134.7	138.1
385.8	47.5°	383.5	341.4	235.8	170.2	143.2	129.9	127.8	121.7	125.1	128.8
362.3	50°	359.2	316.8	231.4	155.8	132.3	118.9	116.9	112.8	117.2	121.0
346.2	52.5°	341.8	288.8	221.8	142.9	122.7	109.7	109.0	107.0	111.1	114.5
334.2	55°	326.7	259.7	206.4	131.6	114.1	101.8	102.5	101.5	104.9	107.7
327.1	57.5°	313.1	234.4	186.9	122.7	104.9	95.0	97.1	95.7	97.4	99.1
319.5	60°	296.6	208.8	163.7	112.8	94.0	88.2	90.6	86.8	86.5	87.1
305.9	62.5°	272.4	174.3	139.4	100.5	84.4	80.7	81.7	74.5	69.0	69.0
285.7	65°	238.5	140.1	116.9	86.8	73.5	70.4	69.7	59.5	51.9	51.3
263.8	67.5°	199.2	115.2	97.1	73.1	61.2	59.1	59.8	52.3	44.8	44.1
242.0	70°	162.3	95.4	78.3	58.4	47.2	49.2	52.3	44.8	37.6	36.6
216.3	72.5°	131.9	75.9	61.2	44.8	34.9	40.7	44.4	36.6	29.7	29.0
184.6	75°	101.8	55.7	43.7	30.4	25.3	31.4	34.9	26.7	21.2	20.2
142.9	77.5°	68.0	34.5	24.6	19.1	15.0	21.5	23.2	14.0	12.3	12.0
103.9	80°	41.4	16.1	10.6	9.2	5.1	7.9	9.2	5.8	6.5	6.8
55.4	82.5°	20.8	4.4	1.7	0.3	0.0	0.0	2.7	1.4	2.7	3.4
15.0	85°	1.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.7	1.7
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P946584
 CATALOG NUMBER: GALN-SB2A-940-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

185°		195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
686.9	0°	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9
603.6	2.5°	622.7	637.0	650.7	672.6	695.1	717.4	739.9	761.8	769.6	775.5
521.2	5°	550.9	577.9	609.4	652.8	699.2	747.1	795.6	840.0	860.2	873.9
443.6	7.5°	476.8	512.0	557.1	622.3	695.1	771.4	847.6	917.6	950.1	976.4
370.5	10°	403.3	441.6	498.6	573.1	671.6	780.9	886.2	982.6	1024.6	1057.8
317.8	12.5°	338.7	374.6	434.4	516.7	634.7	773.4	908.4	1024.3	1073.8	1111.1
280.2	15°	293.2	318.5	371.5	460.4	590.9	749.1	909.8	1044.1	1098.4	1137.4
264.5	17.5°	267.9	276.5	311.0	402.9	542.4	717.4	897.1	1050.9	1109.0	1145.2
250.5	20°	254.3	255.6	265.2	328.4	480.2	687.6	885.2	1057.8	1118.9	1149.3
240.6	22.5°	243.3	243.3	245.7	268.6	399.9	652.1	881.4	1069.7	1132.6	1151.4
229.3	25°	233.4	233.4	234.1	240.3	316.8	597.7	879.0	1088.2	1151.4	1156.5
218.0	27.5°	223.2	223.5	223.5	226.9	255.3	523.9	868.8	1112.1	1173.9	1163.4
207.1	30°	212.9	213.6	213.6	216.0	225.9	437.5	848.6	1140.8	1203.3	1172.2
196.2	32.5°	202.7	203.3	203.3	205.4	212.6	349.3	823.3	1167.1	1233.1	1176.0
185.6	35°	192.1	193.1	192.4	195.1	202.7	277.9	791.2	1193.4	1265.2	1188.0
175.3	37.5°	181.5	182.2	181.8	184.6	193.1	239.9	753.9	1213.3	1308.9	1214.6
164.4	40°	170.9	170.5	170.5	173.6	182.8	229.0	707.1	1244.7	1371.8	1261.4
153.5	42.5°	159.9	159.9	159.3	162.7	174.0	220.8	662.3	1301.1	1463.4	1335.9
143.2	45°	150.0	149.7	148.3	151.4	165.4	206.4	646.6	1406.3	1598.8	1456.6
132.9	47.5°	140.5	140.1	136.7	139.4	155.2	193.4	705.4	1578.6	1786.4	1634.0
124.7	50°	131.9	132.3	125.8	128.2	144.9	183.5	832.9	1802.1	2035.5	1872.9
117.9	52.5°	124.1	124.1	115.5	116.9	132.3	174.6	954.2	2044.4	2364.3	2206.1
110.7	55°	116.2	115.5	105.9	106.6	119.6	162.0	972.3	2280.9	2812.7	2707.4
102.9	57.5°	107.3	105.9	97.1	97.1	108.0	152.8	842.8	2462.7	3369.1	3444.3
88.2	60°	96.4	95.4	89.5	87.8	98.8	161.0	594.7	2483.9	3727.9	4424.1
70.1	62.5°	82.4	83.7	80.7	78.3	89.9	167.1	352.4	2313.4	3641.1	4735.8
54.3	65°	64.9	70.4	69.7	68.0	98.8	140.8	208.1	1986.0	3374.9	4484.2
47.5	67.5°	55.4	59.1	58.1	58.1	103.6	107.0	130.9	1551.6	3008.5	4185.9
39.6	70°	47.2	50.9	47.2	47.2	78.3	64.9	90.6	1083.4	2613.1	3855.7
31.8	72.5°	39.0	42.7	38.6	35.9	62.5	48.5	66.3	677.0	2237.9	3511.9
22.6	75°	29.7	34.2	31.1	27.7	41.4	36.2	50.2	393.4	1854.1	3004.8
13.7	77.5°	18.8	24.6	23.2	19.5	30.4	26.3	36.2	234.1	1430.6	2347.9
8.2	80°	11.6	12.6	13.0	12.3	17.4	17.8	24.6	133.3	979.1	1636.4
5.1	82.5°	7.5	7.5	5.8	6.5	8.5	10.3	14.0	50.2	575.5	996.2
3.1	85°	5.5	4.8	3.1	3.1	4.1	5.1	5.5	15.4	233.4	393.4
1.4	87.5°	2.7	2.4	1.0	1.4	2.1	1.7	1.4	0.7	58.8	125.8
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P946584
 CATALOG NUMBER: GALN-SB2A-940-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

285°		295°	305°	315°	325°	335°	345°	355°	360°
686.9	0°	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9
788.4	2.5°	795.3	805.9	806.6	806.6	797.3	797.0	778.2	776.1
904.6	5°	936.4	943.3	945.0	941.6	923.1	909.4	872.9	865.0
1023.2	7.5°	1065.6	1079.3	1079.3	1071.1	1041.0	1013.0	960.0	940.2
1121.3	10°	1168.8	1184.5	1181.1	1164.4	1126.4	1087.8	1023.6	997.6
1180.8	12.5°	1219.1	1235.1	1226.2	1207.1	1170.2	1129.5	1061.9	1032.5
1197.9	15°	1218.0	1213.6	1204.4	1202.0	1184.2	1153.4	1090.2	1058.1
1187.3	17.5°	1174.6	1137.0	1129.9	1153.8	1176.3	1168.8	1114.8	1084.7
1162.0	20°	1105.9	1040.3	1033.8	1079.6	1143.9	1176.7	1137.7	1110.0
1125.4	22.5°	1033.5	962.7	947.7	998.3	1095.0	1179.1	1166.8	1139.1
1085.1	25°	964.8	893.7	878.7	925.8	1040.7	1175.0	1198.2	1174.6
1046.5	27.5°	907.4	838.7	824.7	871.8	988.4	1163.4	1229.7	1212.9
1008.2	30°	862.9	799.4	789.1	834.6	943.3	1149.0	1269.6	1260.4
972.7	32.5°	837.0	790.5	794.3	831.5	919.0	1133.3	1307.9	1312.4
955.2	35°	862.6	864.7	897.5	912.8	941.6	1130.9	1359.9	1377.3
976.1	37.5°	990.1	1061.2	1129.2	1116.5	1051.9	1158.6	1437.4	1469.9
1067.0	40°	1207.1	1353.0	1463.4	1415.2	1252.6	1243.3	1549.2	1597.7
1228.3	42.5°	1472.3	1719.7	1901.6	1772.4	1511.3	1391.7	1708.8	1770.7
1423.4	45°	1752.2	2171.9	2458.3	2189.7	1787.1	1599.4	1950.4	1999.0
1606.3	47.5°	2047.1	2721.4	3091.9	2652.4	2042.7	1835.9	2279.9	2291.2
1779.5	50°	2369.8	3324.0	3737.8	3114.8	2289.5	2107.0	2682.5	2669.5
1981.5	52.5°	2677.0	3943.6	4370.1	3579.3	2506.1	2443.2	3149.7	3123.0
2257.7	55°	2970.2	4562.9	5006.1	4025.6	2710.5	2887.5	3704.7	3543.4
2655.8	57.5°	3310.3	5119.6	5661.6	4474.0	2996.2	3464.4	4325.3	3787.4
3418.3	60°	3813.0	5752.2	6402.9	5088.5	3539.6	4070.7	4547.8	3740.9
4331.5	62.5°	4454.9	6333.9	6941.9	5690.7	4085.4	4184.9	4220.1	3382.8
4145.2	65°	4579.6	6481.2	6972.3	5851.6	4015.0	3549.9	3445.3	2719.1
3702.6	67.5°	4248.8	6214.9	6547.1	5551.9	3551.6	2743.3	2585.4	1972.6
3412.1	70°	3877.6	5707.4	5806.2	5042.3	3123.7	2017.8	1746.1	1265.9
3213.2	72.5°	3497.2	5030.4	4826.0	4379.0	2745.4	1469.2	1259.4	899.9
2929.9	75°	3045.4	4140.1	3801.4	3638.4	2273.1	1153.1	911.1	621.0
2520.1	77.5°	2438.8	2914.2	2823.6	2820.2	1708.1	842.4	608.0	389.3
1968.9	80°	1720.4	1891.3	1845.2	2124.0	1145.9	611.1	366.0	216.7
1370.5	82.5°	832.9	1045.8	1073.5	1264.9	557.4	359.5	84.4	47.2
535.9	85°	326.0	504.4	425.5	480.2	156.5	100.1	2.1	0.0
88.2	87.5°	36.6	58.4	53.7	42.4	19.1	4.1	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)