

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P948726

Luminaire Tested: **GALN-SB3C-940-U-SLR-HSS**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P948726
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GALN-SB3C-940-U-SLR-HSS
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(3) 90 CRI, 4000K, 615mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12427 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G3


Input Watts (W): 149.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P948726
 CATALOG NUMBER: GALN-SB3C-940-U-SLR-HSS

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 3.8 fc
 Type IV - Short - N/A

REPORT NUMBER: P948726
CATALOG NUMBER: GALN-SB3C-940-U-SLR-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P948726

CATALOG NUMBER: GALN-SB3C-940-U-SLR-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1740.3	0.0	1740.3
	% Fixture	14.0	0.0	14.0
Street Side	Lumens	10686.7	0.0	10686.7
	% Fixture	86.0	0.0	86.0
Total	Lumens	12427.0	0.0	12427.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.4	1.4
10°-20°	507.8	4.1
20°-30°	748.2	6.0
30°-40°	961.2	7.7
40°-50°	1554.5	12.5
50°-60°	2726.0	21.9
60°-70°	3411.0	27.4
70°-80°	1993.2	16.0
80°-90°	355.6	2.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	12427.0	100.0
0°-180°	12427.0	100.0

Coefficient of Utilization



REPORT NUMBER: P948726


CATALOG NUMBER: GALN-SB3C-940-U-SLR-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	969.3	7.8			
FM (30°-60°)	4355.5	35.0			
FH (60°-80°)	5019.9	40.4			G3/7500
FVH (80°-90°)	342.0	2.8			G3/500
BL (0°-30°)	456.2	3.7	B1/500		
BM (30°-60°)	886.2	7.1	B1/1000		
BH (60°-80°)	384.3	3.1	B1/500		G1/500
BVH (80°-90°)	13.7	0.1			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G3

Type IV Short



REPORT NUMBER: P948726
 CATALOG NUMBER: GALN-SB3C-940-U-SLR-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	1720.7	1720.7	1720.7	1720.7	1720.7	1720.7	1720.7	1720.7	1720.7	1720.7
2.5°	1944.2	1910.8	1891.1	1842.3	1793.5	1754.1	1701.1	1666.0	1624.0	1583.8
5°	2166.8	2112.8	2047.8	1958.7	1877.4	1794.4	1713.9	1634.3	1550.4	1473.3
7.5°	2355.1	2277.2	2162.5	2044.3	1940.8	1840.6	1746.4	1641.1	1539.3	1418.5
10°	2498.9	2399.6	2248.9	2094.0	1975.0	1874.0	1782.4	1693.3	1590.6	1445.1
12.5°	2586.2	2480.1	2301.2	2119.7	1983.6	1870.6	1799.5	1760.1	1719.9	1575.2
15°	2650.5	2535.7	2338.0	2137.7	1963.9	1825.2	1773.0	1812.3	1858.6	1766.1
17.5°	2717.2	2596.5	2385.9	2145.4	1910.8	1737.0	1714.7	1816.6	1923.6	1919.4
20°	2780.6	2660.7	2427.9	2140.2	1825.2	1630.0	1649.7	1779.8	1903.9	1956.2
22.5°	2853.3	2726.6	2468.1	2120.5	1713.9	1529.8	1591.5	1721.6	1830.3	1892.0
25°	2942.4	2809.7	2524.6	2091.4	1594.0	1446.8	1532.4	1654.0	1742.1	1784.9
27.5°	3038.3	2909.0	2599.9	2076.0	1497.3	1387.7	1465.6	1573.5	1652.3	1682.2
30°	3157.3	3024.6	2689.0	2058.9	1434.0	1353.5	1396.3	1480.2	1557.2	1587.2
32.5°	3287.4	3153.0	2774.6	2017.8	1395.4	1327.8	1328.7	1381.7	1451.9	1487.9
35°	3450.0	3307.1	2866.2	1927.9	1364.6	1297.8	1262.7	1288.4	1346.6	1389.4
37.5°	3682.0	3509.1	2978.3	1799.5	1319.2	1251.6	1193.4	1199.4	1243.9	1291.0
40°	4002.2	3780.5	3110.2	1666.0	1254.2	1186.5	1117.2	1114.6	1147.2	1193.4
42.5°	4435.4	4139.2	3268.6	1538.4	1191.7	1107.8	1036.7	1032.4	1058.1	1098.4
45°	5007.3	4598.1	3462.9	1428.8	1142.9	1030.7	960.5	958.8	980.2	1015.3
47.5°	5739.2	5235.8	3657.2	1354.3	1117.2	970.0	898.0	901.5	920.3	952.0
50°	6686.9	6067.1	3716.3	1316.7	1117.2	937.4	842.4	859.5	874.9	898.9
52.5°	7823.0	6865.0	3521.1	1282.4	1124.0	941.7	795.3	832.1	843.2	863.8
55°	8875.9	7256.2	3027.1	1235.3	1125.8	968.2	755.1	809.9	830.4	838.1
57.5°	9487.2	7121.8	2447.6	1155.7	1118.9	986.2	729.4	782.5	821.8	827.0
60°	9370.8	6650.1	1802.1	1094.9	1068.4	979.4	721.7	740.5	803.0	810.7
62.5°	8473.6	5859.1	1250.7	1047.9	957.1	949.4	719.1	674.6	761.9	780.8
65°	6811.1	4612.6	883.5	902.3	839.0	884.3	705.4	606.1	712.3	737.9
67.5°	4941.4	3121.3	637.8	731.1	760.2	779.0	674.6	556.5	655.8	690.0
70°	3171.0	1685.6	447.7	482.8	640.4	661.8	621.5	511.9	598.4	637.8
72.5°	2254.1	995.6	321.9	338.2	514.5	551.3	547.0	462.3	531.6	579.6
75°	1555.5	548.8	217.4	241.4	373.3	447.7	422.1	397.2	450.3	499.1
77.5°	975.1	245.7	130.1	167.8	244.8	351.9	289.4	307.3	351.0	396.4
80°	542.8	95.0	72.8	111.3	133.6	256.0	160.1	197.8	258.5	291.1
82.5°	118.1	12.0	32.5	47.9	52.2	149.0	84.8	114.7	162.7	160.1
85°	0.0	0.0	6.0	6.8	3.4	64.2	30.8	37.7	53.1	49.7
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P948726
 CATALOG NUMBER: GALN-SB3C-940-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

90°		95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
1720.7	0°	1720.7	1720.7	1720.7	1720.7	1720.7	1720.7	1720.7	1720.7	1720.7	1720.7
1547.8	2.5°	1541.0	1499.0	1468.2	1452.8	1439.9	1451.9	1458.8	1458.8	1487.9	1505.0
1426.2	5°	1396.3	1320.9	1263.6	1225.1	1202.0	1209.7	1218.2	1227.6	1264.4	1289.3
1354.3	7.5°	1296.1	1180.5	1093.2	1039.3	1011.0	1015.3	1021.3	1029.0	1065.0	1089.8
1364.6	10°	1277.3	1111.2	987.9	916.9	882.6	876.6	873.2	870.6	892.0	910.9
1481.0	12.5°	1354.3	1114.6	942.6	856.1	814.1	796.2	775.6	759.4	762.8	774.8
1657.4	15°	1492.2	1158.3	928.0	824.4	772.2	742.2	718.3	698.6	694.3	698.6
1811.5	17.5°	1649.7	1217.4	926.3	797.0	732.0	701.1	681.4	663.5	657.5	658.3
1898.0	20°	1754.1	1264.4	921.2	766.2	693.4	666.0	648.9	630.9	624.9	626.7
1874.0	22.5°	1764.4	1289.3	913.4	732.0	654.9	631.8	614.7	598.4	597.6	597.6
1784.1	25°	1708.8	1289.3	897.2	701.1	618.1	597.6	582.1	562.5	565.9	567.6
1682.2	27.5°	1622.3	1258.5	866.4	676.3	586.4	565.0	549.6	531.6	535.9	538.5
1587.2	30°	1536.7	1219.1	829.6	648.1	556.5	531.6	520.5	505.1	506.8	510.2
1493.0	32.5°	1457.1	1177.1	785.9	624.9	526.5	501.7	493.1	476.0	478.6	482.0
1400.6	35°	1378.3	1130.9	734.5	597.6	499.1	474.3	467.4	447.7	449.4	454.6
1308.1	37.5°	1293.6	1082.1	692.6	570.2	472.6	446.9	440.0	419.5	421.2	427.2
1212.2	40°	1204.5	1034.2	651.5	541.0	444.3	418.6	412.6	390.4	392.1	398.9
1118.1	42.5°	1114.6	981.9	619.8	503.4	415.2	387.8	381.8	361.3	363.8	371.5
1035.9	45°	1031.6	919.4	599.3	461.4	387.8	357.0	351.0	332.2	337.3	345.9
966.5	47.5°	960.5	855.2	590.7	426.3	358.7	325.3	320.2	304.8	313.3	322.7
907.5	50°	899.8	793.6	579.6	390.4	331.3	297.9	292.8	282.5	293.6	303.1
867.2	52.5°	856.1	723.4	555.6	357.8	307.3	274.8	273.1	268.0	278.2	286.8
837.3	55°	818.4	650.6	517.1	329.6	285.9	255.1	256.8	254.3	262.8	269.7
819.3	57.5°	784.2	587.3	468.3	307.3	262.8	238.0	243.1	239.7	244.0	248.3
800.4	60°	743.1	523.1	410.1	282.5	235.4	220.9	226.9	217.4	216.6	218.3
766.2	62.5°	682.3	436.6	349.3	251.7	211.5	202.0	204.6	186.6	172.9	172.9
715.7	65°	597.6	351.0	292.8	217.4	184.1	176.4	174.6	149.0	130.1	128.4
660.9	67.5°	499.1	288.5	243.1	183.2	153.2	148.1	149.8	131.0	112.1	110.4
606.1	70°	406.6	238.8	196.0	146.4	118.1	123.3	131.0	112.1	94.2	91.6
541.9	72.5°	330.5	190.1	153.2	112.1	87.3	101.9	111.3	91.6	74.5	72.8
462.3	75°	255.1	139.5	109.6	76.2	63.4	78.8	87.3	66.8	53.1	50.5
357.8	77.5°	170.4	86.5	61.6	47.9	37.7	53.9	58.2	35.1	30.8	30.0
260.3	80°	103.6	40.2	26.5	23.1	12.8	19.7	23.1	14.6	16.3	17.1
138.7	82.5°	52.2	11.1	4.3	0.9	0.0	0.0	6.8	3.4	6.8	8.6
37.7	85°	4.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.7	4.3
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P948726
 CATALOG NUMBER: GALN-SB3C-940-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

185°		195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
1720.7	0°	1720.7	1720.7	1720.7	1720.7	1720.7	1720.7	1720.7	1720.7	1720.7	1720.7
1511.9	2.5°	1559.8	1595.8	1630.0	1684.8	1741.3	1796.9	1853.4	1908.2	1927.9	1942.5
1305.5	5°	1380.0	1447.6	1526.4	1635.1	1751.6	1871.4	1993.0	2104.3	2154.8	2189.0
1111.2	7.5°	1194.2	1282.4	1395.4	1558.9	1741.3	1932.2	2123.1	2298.6	2379.9	2445.9
928.0	10°	1010.2	1106.1	1249.0	1435.7	1682.2	1956.2	2219.8	2461.3	2566.6	2649.6
796.2	12.5°	848.4	938.3	1088.1	1294.4	1589.8	1937.3	2275.5	2565.7	2689.8	2783.2
702.0	15°	734.5	797.9	930.6	1153.2	1480.2	1876.6	2278.9	2615.4	2751.5	2849.1
662.6	17.5°	671.2	692.6	779.0	1009.3	1358.6	1796.9	2247.2	2632.5	2778.0	2868.8
627.5	20°	636.9	640.4	664.3	822.7	1202.8	1722.5	2217.3	2649.6	2802.8	2879.0
602.7	22.5°	609.5	609.5	615.5	672.9	1001.6	1633.4	2207.9	2679.6	2837.1	2884.2
574.4	25°	584.7	584.7	586.4	601.8	793.6	1497.3	2201.9	2725.8	2884.2	2897.0
546.2	27.5°	559.0	559.9	559.9	568.4	639.5	1312.4	2176.2	2785.7	2940.7	2914.1
518.8	30°	533.3	535.1	535.1	541.0	565.9	1095.8	2125.7	2857.6	3014.3	2936.4
491.4	32.5°	507.7	509.4	509.4	514.5	532.5	874.9	2062.3	2923.5	3088.8	2945.8
464.9	35°	481.1	483.7	482.0	488.8	507.7	696.0	1981.8	2989.5	3169.2	2975.8
439.2	37.5°	454.6	456.3	455.4	462.3	483.7	601.0	1888.5	3039.1	3278.8	3042.5
411.8	40°	428.0	427.2	427.2	434.9	458.0	573.6	1771.3	3117.9	3436.3	3159.8
384.4	42.5°	400.7	400.7	398.9	407.5	435.8	553.0	1659.1	3259.1	3665.8	3346.5
358.7	45°	375.8	375.0	371.5	379.2	414.3	517.1	1619.7	3522.8	4004.8	3648.7
333.0	47.5°	351.9	351.0	342.4	349.3	388.7	484.5	1767.0	3954.3	4474.8	4093.0
312.5	50°	330.5	331.3	315.0	321.0	363.0	459.7	2086.3	4514.2	5098.9	4691.4
295.4	52.5°	310.8	310.8	289.4	292.8	331.3	437.5	2390.2	5121.1	5922.4	5526.1
277.4	55°	291.1	289.4	265.4	267.1	299.6	405.8	2435.6	5713.5	7045.6	6781.9
257.7	57.5°	268.8	265.4	243.1	243.1	270.5	382.7	2111.1	6169.0	8439.3	8627.7
220.9	60°	241.4	238.8	224.3	220.0	247.4	403.2	1489.6	6222.1	9338.2	11082.1
175.5	62.5°	206.3	209.7	202.0	196.0	225.2	418.6	882.6	5794.9	9120.8	11862.8
136.1	65°	162.7	176.4	174.6	170.4	247.4	352.7	521.4	4974.7	8453.9	11232.8
119.0	67.5°	138.7	148.1	145.5	145.5	259.4	268.0	327.9	3886.7	7536.2	10485.4
99.3	70°	118.1	127.6	118.1	118.1	196.0	162.7	226.9	2713.8	6545.7	9658.4
79.6	72.5°	97.6	107.0	96.7	89.9	156.7	121.6	166.1	1695.9	5605.7	8797.2
56.5	75°	74.5	85.6	77.9	69.3	103.6	90.7	125.8	985.4	4644.3	7526.7
34.2	77.5°	47.1	61.6	58.2	48.8	76.2	65.9	90.7	586.4	3583.6	5881.3
20.5	80°	29.1	31.7	32.5	30.8	43.7	44.5	61.6	333.9	2452.7	4099.0
12.8	82.5°	18.8	18.8	14.6	16.3	21.4	25.7	35.1	125.8	1441.7	2495.5
7.7	85°	13.7	12.0	7.7	7.7	10.3	12.8	13.7	38.5	584.7	985.4
3.4	87.5°	6.8	6.0	2.6	3.4	5.1	4.3	3.4	1.7	147.2	315.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P948726
 CATALOG NUMBER: GALN-SB3C-940-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

285°		295°	305°	315°	325°	335°	345°	355°	360°
1720.7	0°	1720.7	1720.7	1720.7	1720.7	1720.7	1720.7	1720.7	1720.7
1975.0	2.5°	1992.1	2018.7	2020.4	2020.4	1997.3	1996.4	1949.3	1944.2
2266.1	5°	2345.7	2362.8	2367.1	2358.5	2312.3	2278.1	2186.5	2166.8
2563.1	7.5°	2669.3	2703.5	2703.5	2683.0	2607.7	2537.5	2404.8	2355.1
2808.8	10°	2927.8	2967.2	2958.6	2916.7	2821.7	2724.9	2564.0	2498.9
2957.8	12.5°	3053.7	3093.9	3071.7	3023.7	2931.3	2829.4	2659.9	2586.2
3000.6	15°	3051.1	3040.0	3016.9	3010.9	2966.4	2889.3	2730.9	2650.5
2974.1	17.5°	2942.4	2848.2	2830.2	2890.2	2946.7	2927.8	2792.6	2717.2
2910.7	20°	2770.3	2605.9	2589.7	2704.4	2865.3	2947.5	2849.9	2780.6
2819.1	22.5°	2588.8	2411.6	2373.9	2500.6	2742.9	2953.5	2922.7	2853.3
2718.1	25°	2416.7	2238.7	2201.0	2319.1	2606.8	2943.2	3001.5	2942.4
2621.3	27.5°	2272.9	2100.8	2065.7	2183.9	2475.8	2914.1	3080.2	3038.3
2525.5	30°	2161.6	2002.4	1976.7	2090.6	2362.8	2878.2	3180.4	3157.3
2436.4	32.5°	2096.6	1980.1	1989.6	2082.9	2302.0	2838.8	3276.3	3287.4
2392.8	35°	2160.8	2165.9	2248.1	2286.6	2358.5	2832.8	3406.4	3450.0
2445.0	37.5°	2480.1	2658.2	2828.5	2796.8	2635.0	2902.1	3600.7	3682.0
2672.7	40°	3023.7	3389.3	3665.8	3545.1	3137.6	3114.5	3880.7	4002.2
3076.8	42.5°	3688.0	4307.8	4763.3	4439.7	3785.6	3486.0	4280.5	4435.4
3565.6	45°	4389.2	5440.5	6157.9	5485.0	4476.5	4006.5	4885.7	5007.3
4023.6	47.5°	5128.0	6817.0	7745.1	6644.1	5116.9	4598.9	5711.0	5739.2
4457.7	50°	5936.1	8326.3	9363.1	7802.4	5735.0	5277.8	6719.5	6686.9
4963.6	52.5°	6705.8	9878.4	10946.8	8965.8	6277.7	6120.2	7889.7	7823.0
5655.3	55°	7440.3	11429.7	12540.0	10083.9	6789.7	7233.1	9280.0	8875.9
6652.7	57.5°	8292.1	12824.2	14182.0	11207.1	7505.3	8678.2	10834.7	9487.2
8562.6	60°	9551.4	14408.9	16038.9	12746.3	8866.5	10196.9	11392.0	9370.8
10850.1	62.5°	11159.1	15865.9	17388.9	14254.8	10233.7	10482.8	10571.0	8473.6
10383.5	65°	11471.6	16234.9	17465.1	14658.0	10057.4	8892.2	8630.2	6811.1
9274.9	67.5°	10642.9	15568.0	16400.1	13907.2	8896.5	6871.8	6476.3	4941.4
8547.2	70°	9713.2	14296.7	14544.1	12630.8	7824.7	5054.4	4373.8	3171.0
8049.0	72.5°	8760.4	12600.8	12088.9	10969.1	6877.0	3680.3	3154.7	2254.1
7339.3	75°	7628.6	10370.7	9522.3	9113.9	5693.9	2888.4	2282.3	1555.5
6312.8	77.5°	6109.1	7299.9	7073.0	7064.5	4278.7	2110.3	1523.0	975.1
4931.9	80°	4309.6	4737.6	4622.0	5320.6	2870.5	1530.7	916.9	542.8
3432.9	82.5°	2086.3	2619.6	2689.0	3168.4	1396.3	900.6	211.5	118.1
1342.3	85°	816.7	1263.6	1065.8	1202.8	392.1	250.8	5.1	0.0
220.9	87.5°	91.6	146.4	134.4	106.2	47.9	10.3	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)