

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P954814

Luminaire Tested: **GALN-SB7D-950-U-SLL-HSS**

Issue Date: 1/21/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P954814  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: GALN-SB7D-950-U-SLL-HSS  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(7) 90 CRI, 5000K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 38422 lumens  
Efficiency: N/A  
Efficacy: 74.9 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B3 - U0 - G5  
  
Input Watts (W): 512.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P954814  
 CATALOG NUMBER: GALN-SB7D-950-U-SLL-HSS

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 14 fc  
 Type IV - Short - N/A

REPORT NUMBER: P954814  
CATALOG NUMBER: GALN-SB7D-950-U-SLL-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral      - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P954814  
 CATALOG NUMBER: GALN-SB7D-950-U-SLL-HSS

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	7637.1	0.0	7637.1
	% Fixture	19.9	0.0	19.9
<b>Street Side</b>	Lumens	30784.9	0.0	30784.9
	% Fixture	80.1	0.0	80.1
<b>Total</b>	Lumens	38422.0	0.0	38422.0
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	523.8	1.4
10°-20°	1570.2	4.1
20°-30°	2313.2	6.0
30°-40°	2971.8	7.7
40°-50°	4806.3	12.5
50°-60°	8428.3	21.9
60°-70°	10546.2	27.4
70°-80°	6162.7	16.0
80°-90°	1099.5	2.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	38422.0	100.0
0°-180°	38422.0	100.0



REPORT NUMBER: P954814


CATALOG NUMBER: GALN-SB7D-950-U-SLL-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	2570.9	6.7			
FM (30°-60°)	12057.3	31.4			
FH (60°-80°)	15108.7	39.3			G5
FVH (80°-90°)	1048.0	2.7			G5
BL (0°-30°)	1836.3	4.8	B3/2500		
BM (30°-60°)	4149.2	10.8	B3/5000		
BH (60°-80°)	1600.1	4.2	B3/2500		G3/2500
BVH (80°-90°)	51.5	0.1			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G5**

Type IV Short



REPORT NUMBER: P954814

CATALOG NUMBER: GALN-SB7D-950-U-SLL-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	5320.2	5320.2	5320.2	5320.2	5320.2	5320.2	5320.2	5320.2	5320.2	5320.2
2.5°	5960.8	6005.8	6106.3	6159.3	6241.3	6246.6	6246.6	6175.2	6172.5	6026.9
5°	6662.2	6768.1	7006.3	7252.4	7305.4	7318.6	7292.1	7149.2	7043.3	6760.1
7.5°	7358.3	7562.1	7924.7	8253.0	8358.8	8358.8	8295.3	8062.4	7845.3	7435.1
10°	7935.3	8192.1	8684.4	9052.3	9174.1	9147.6	9017.9	8724.1	8425.0	7927.4
12.5°	8316.5	8605.0	9145.0	9441.4	9565.8	9497.0	9348.8	9062.9	8747.9	8223.8
15°	8507.1	8808.8	9277.3	9433.5	9399.1	9327.6	9309.1	9171.4	8933.2	8443.5
17.5°	8589.1	8869.7	9195.2	9097.3	8806.2	8750.6	8935.8	9110.5	9052.3	8634.1
20°	8665.9	8901.4	8999.4	8565.3	8057.1	8006.8	8361.5	8859.1	9113.2	8811.4
22.5°	8771.7	8917.3	8716.2	8004.1	7456.2	7339.8	7731.5	8480.6	9131.7	9036.4
25°	8917.3	8957.0	8403.8	7472.1	6921.6	6805.1	7170.4	8059.7	9100.0	9279.9
27.5°	9092.0	9010.0	8104.7	7027.5	6495.4	6386.9	6752.2	7654.8	9010.0	9523.5
30°	9319.6	9078.8	7808.3	6683.4	6191.0	6111.6	6463.7	7305.4	8898.8	9833.1
32.5°	9549.9	9107.9	7533.0	6482.2	6122.2	6151.3	6439.8	7117.4	8777.0	10129.6
35°	9798.7	9200.5	7398.0	6680.7	6696.6	6950.7	7069.8	7292.1	8758.5	10531.9
37.5°	10137.5	9407.0	7559.5	7668.0	8218.5	8745.3	8647.3	8147.1	8972.9	11132.8
40°	10624.6	9769.6	8263.5	9348.8	10479.0	11333.9	10960.7	9700.8	9629.3	11998.3
42.5°	11333.9	10346.6	9512.9	11402.7	13319.1	14727.2	13726.7	11704.5	10778.1	13234.4
45°	12382.1	11281.0	11024.2	13570.5	16820.9	19039.0	16958.5	13840.5	12387.4	15105.7
47.5°	13835.2	12654.7	12440.3	15854.8	21077.1	23946.3	20542.4	15820.4	14219.0	17657.3
50°	15764.8	14504.9	13782.3	18353.4	25743.5	28948.9	24123.6	17731.4	16318.0	20775.3
52.5°	18311.1	17085.6	15346.6	20733.0	30542.3	33845.6	27720.7	19409.5	18922.5	24393.6
55°	21783.8	20968.5	17485.3	23004.0	35338.4	38771.4	31177.5	20992.4	22363.4	28692.1
57.5°	26092.9	26675.2	20568.9	25637.6	39650.2	43848.1	34650.2	23205.1	26831.4	33498.8
60°	28872.1	34263.8	26474.0	29531.2	44549.5	49589.2	39409.3	27413.7	31526.9	35222.0
62.5°	28199.8	36677.7	33546.5	34502.0	49054.5	53763.3	44073.1	31640.7	32411.0	32683.6
65°	26137.9	34729.6	32103.9	35468.1	50195.3	53998.9	45319.8	31095.5	27493.1	26683.1
67.5°	23300.4	32418.9	28676.2	32905.9	48133.4	50706.2	42998.5	27506.3	21246.5	20023.6
70°	20238.0	29862.0	26426.4	30031.4	44202.8	44967.7	39052.0	24192.4	15627.1	13522.9
72.5°	17331.7	27199.3	24885.9	27085.5	38959.3	37376.5	33914.4	21262.3	11378.9	9753.7
75°	14359.3	23271.3	22691.7	23586.3	32064.2	29441.2	28178.6	17604.4	8930.6	7056.6
77.5°	11079.8	18184.0	19518.1	18888.1	22569.9	21868.5	21842.0	13229.1	6524.5	4708.8
80°	7583.3	12673.2	15248.6	13324.4	14647.8	14290.5	16450.3	8875.0	4732.6	2834.8
82.5°	4457.3	7715.6	10614.0	6450.4	8099.4	8313.8	9796.1	4317.1	2784.5	653.8
85°	1807.8	3046.6	4150.3	2525.1	3906.8	3295.4	3718.9	1212.3	775.5	15.9
87.5°	455.3	974.0	682.9	283.2	452.6	415.6	328.2	148.2	31.8	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P954814  
 CATALOG NUMBER: GALN-SB7D-950-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

90°		95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
5320.2	0°	5320.2	5320.2	5320.2	5320.2	5320.2	5320.2	5320.2	5320.2	5320.2	5320.2
6011.1	2.5°	5907.8	5846.9	5696.1	5545.2	5423.4	5259.3	5150.8	5021.1	4896.7	4785.5
6699.2	5°	6532.5	6331.3	6056.0	5804.6	5547.8	5299.0	5052.9	4793.5	4555.3	4409.7
7281.6	7.5°	7040.7	6686.0	6320.7	6000.5	5690.8	5399.6	5074.1	4759.1	4385.9	4187.4
7726.2	10°	7419.2	6953.3	6474.3	6106.3	5794.0	5510.8	5235.5	4917.9	4467.9	4219.1
7996.2	12.5°	7668.0	7114.8	6553.7	6132.8	5783.4	5563.7	5442.0	5317.6	4870.2	4579.1
8194.7	15°	7840.0	7228.6	6609.2	6071.9	5643.1	5481.7	5603.4	5746.4	5460.5	5124.3
8401.2	17.5°	8028.0	7376.8	6633.1	5907.8	5370.5	5301.7	5616.7	5947.5	5934.3	5600.8
8597.0	20°	8226.5	7506.5	6617.2	5643.1	5039.6	5100.5	5502.9	5886.6	6048.1	5868.1
8822.0	22.5°	8430.3	7630.9	6556.3	5299.0	4730.0	4920.5	5322.9	5659.0	5849.6	5794.0
9097.3	25°	8687.0	7805.6	6466.3	4928.5	4473.2	4737.9	5113.8	5386.4	5518.7	5516.1
9393.8	27.5°	8994.1	8038.6	6418.7	4629.4	4290.6	4531.4	4865.0	5108.5	5201.1	5201.1
9761.7	30°	9351.4	8313.8	6365.7	4433.5	4184.7	4317.1	4576.4	4814.7	4907.3	4907.3
10164.0	32.5°	9748.4	8578.5	6238.7	4314.4	4105.3	4107.9	4272.1	4489.1	4600.3	4616.1
10666.9	35°	10224.9	8861.7	5960.8	4219.1	4012.7	3904.1	3983.5	4163.5	4295.9	4330.3
11384.2	37.5°	10849.5	9208.5	5563.7	4078.8	3869.7	3689.7	3708.3	3845.9	3991.5	4044.4
12374.1	40°	11688.6	9616.1	5150.8	3877.7	3668.6	3454.2	3446.2	3546.8	3689.7	3748.0
13713.5	42.5°	12797.6	10105.8	4756.4	3684.4	3425.1	3205.4	3192.1	3271.5	3395.9	3456.8
15481.6	45°	14216.4	10706.6	4417.6	3533.6	3186.8	2969.8	2964.5	3030.7	3139.2	3202.7
17744.6	47.5°	16188.3	11307.4	4187.4	3454.2	2998.9	2776.6	2787.2	2845.4	2943.3	2988.3
20674.7	50°	18758.4	11490.1	4070.9	3454.2	2898.3	2604.5	2657.5	2705.1	2779.2	2805.7
24187.1	52.5°	21225.3	10886.6	3965.0	3475.3	2911.6	2458.9	2572.8	2607.2	2670.7	2681.3
27442.8	55°	22434.9	9359.3	3819.4	3480.6	2993.6	2334.5	2503.9	2567.5	2591.3	2588.6
29332.7	57.5°	22019.3	7567.4	3573.3	3459.5	3049.2	2255.1	2419.2	2541.0	2556.9	2533.1
28972.7	60°	20560.9	5571.7	3385.4	3303.3	3028.0	2231.3	2289.5	2482.8	2506.6	2474.8
26198.8	62.5°	18115.2	3867.1	3239.8	2959.2	2935.4	2223.4	2085.7	2355.7	2413.9	2369.0
21058.5	65°	14261.4	2731.6	2789.8	2593.9	2734.2	2181.0	1874.0	2202.2	2281.6	2212.8
15277.8	67.5°	9650.5	1971.9	2260.4	2350.4	2408.7	2085.7	1720.5	2027.5	2133.4	2043.4
9804.0	70°	5211.7	1384.3	1492.8	1979.9	2046.0	1921.6	1582.8	1850.2	1971.9	1874.0
6969.2	72.5°	3078.3	995.2	1045.5	1590.8	1704.6	1691.4	1429.3	1643.7	1791.9	1675.5
4809.4	75°	1696.6	672.3	746.4	1154.0	1384.3	1304.9	1228.1	1392.3	1543.1	1429.3
3014.8	77.5°	759.7	402.3	518.8	757.0	1087.9	894.6	950.2	1085.2	1225.5	1106.4
1678.1	80°	293.8	225.0	344.1	412.9	791.4	495.0	611.4	799.4	899.9	804.6
365.3	82.5°	37.1	100.6	148.2	161.5	460.6	262.0	354.7	502.9	495.0	428.8
0.0	85°	0.0	18.5	21.2	10.6	198.5	95.3	116.5	164.1	153.5	116.5
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	5.3	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P954814  
 CATALOG NUMBER: GALN-SB7D-950-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

185°		195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
5320.2	0°	5320.2	5320.2	5320.2	5320.2	5320.2	5320.2	5320.2	5320.2	5320.2	5320.2
4764.4	2.5°	4634.7	4539.4	4491.7	4452.0	4489.1	4510.3	4510.3	4600.3	4653.2	4674.4
4317.1	5°	4084.1	3906.8	3787.7	3716.2	3740.0	3766.5	3795.6	3909.4	3986.2	4036.5
4007.4	7.5°	3650.0	3380.1	3213.3	3126.0	3139.2	3157.7	3181.5	3292.7	3369.5	3435.6
3949.1	10°	3435.6	3054.5	2834.8	2728.9	2710.4	2699.8	2691.9	2758.0	2816.3	2869.2
4187.4	12.5°	3446.2	2914.2	2646.9	2517.2	2461.6	2398.1	2347.8	2358.4	2395.4	2461.6
4613.5	15°	3581.2	2869.2	2548.9	2387.5	2294.8	2220.7	2159.8	2146.6	2159.8	2170.4
5100.5	17.5°	3763.9	2863.9	2464.2	2263.1	2167.8	2106.9	2051.3	2032.8	2035.4	2048.7
5423.4	20°	3909.4	2848.0	2369.0	2144.0	2059.3	2006.3	1950.7	1932.2	1937.5	1940.2
5455.2	22.5°	3986.2	2824.2	2263.1	2024.9	1953.4	1900.5	1850.2	1847.5	1847.5	1863.4
5283.2	25°	3986.2	2773.9	2167.8	1911.0	1847.5	1799.9	1739.0	1749.6	1754.9	1776.1
5015.8	27.5°	3890.9	2678.6	2091.0	1813.1	1746.9	1699.3	1643.7	1656.9	1664.9	1688.7
4751.1	30°	3769.1	2564.8	2003.7	1720.5	1643.7	1609.3	1561.7	1566.9	1577.5	1604.0
4505.0	32.5°	3639.5	2429.8	1932.2	1627.8	1551.1	1524.6	1471.7	1479.6	1490.2	1519.3
4261.5	35°	3496.5	2271.0	1847.5	1543.1	1466.4	1445.2	1384.3	1389.6	1405.5	1437.3
3999.4	37.5°	3345.6	2141.3	1762.8	1461.1	1381.7	1360.5	1297.0	1302.3	1320.8	1357.8
3724.2	40°	3197.4	2014.3	1672.8	1373.7	1294.3	1275.8	1207.0	1212.3	1233.4	1273.1
3446.2	42.5°	3036.0	1916.3	1556.4	1283.7	1199.0	1180.5	1117.0	1124.9	1148.7	1188.4
3189.5	45°	2842.7	1852.8	1426.7	1199.0	1103.7	1085.2	1027.0	1042.9	1069.3	1109.0
2969.8	47.5°	2644.2	1826.3	1318.1	1109.0	1005.8	989.9	942.3	968.8	997.9	1029.6
2781.9	50°	2453.7	1791.9	1207.0	1024.3	921.1	905.2	873.5	907.9	937.0	966.1
2646.9	52.5°	2236.6	1717.8	1106.4	950.2	849.6	844.4	828.5	860.2	886.7	913.2
2530.4	55°	2011.6	1598.7	1019.0	884.1	788.8	794.1	786.1	812.6	833.8	857.6
2424.5	57.5°	1815.8	1447.8	950.2	812.6	735.8	751.7	741.1	754.4	767.6	796.7
2297.5	60°	1617.2	1267.9	873.5	727.9	682.9	701.4	672.3	669.7	675.0	682.9
2109.6	62.5°	1349.9	1079.9	778.2	653.8	624.7	632.6	577.0	534.7	534.7	542.6
1847.5	65°	1085.2	905.2	672.3	569.1	545.3	540.0	460.6	402.3	397.0	420.9
1543.1	67.5°	892.0	751.7	566.4	473.8	457.9	463.2	405.0	346.7	341.4	367.9
1257.3	70°	738.5	606.1	452.6	365.3	381.1	405.0	346.7	291.2	283.2	307.0
1021.7	72.5°	587.6	473.8	346.7	270.0	315.0	344.1	283.2	230.3	225.0	246.2
788.8	75°	431.4	338.8	235.6	195.9	243.5	270.0	206.5	164.1	156.2	174.7
526.7	77.5°	267.3	190.6	148.2	116.5	166.8	180.0	108.5	95.3	92.6	105.9
320.3	80°	124.4	82.1	71.5	39.7	60.9	71.5	45.0	50.3	52.9	63.5
161.5	82.5°	34.4	13.2	2.6	0.0	0.0	21.2	10.6	21.2	26.5	39.7
13.2	85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	5.3	13.2	23.8
0.0	87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	10.6
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P954814  
 CATALOG NUMBER: GALN-SB7D-950-U-SLL-HSS

**CANDELA DISTRIBUTION (continued):**

285°		295°	305°	315°	325°	335°	345°	355°	360°
5320.2	0°	5320.2	5320.2	5320.2	5320.2	5320.2	5320.2	5320.2	5320.2
4822.6	2.5°	4933.8	5039.6	5209.0	5383.7	5555.8	5730.5	5899.9	5960.8
4266.8	5°	4475.9	4719.4	5055.5	5415.5	5786.1	6161.9	6506.0	6662.2
3692.4	7.5°	3965.0	4314.4	4820.0	5383.7	5974.0	6564.2	7106.9	7358.3
3123.3	10°	3419.8	3861.8	4438.8	5201.1	6048.1	6863.3	7609.8	7935.3
2623.1	12.5°	2901.0	3364.2	4002.1	4915.2	5989.9	7035.4	7932.7	8316.5
2271.0	15°	2466.9	2877.2	3565.3	4576.4	5801.9	7046.0	8086.2	8507.1
2075.1	17.5°	2141.3	2408.7	3120.7	4200.6	5555.8	6948.0	8139.1	8589.1
1969.3	20°	1979.9	2054.0	2543.6	3718.9	5325.5	6855.4	8192.1	8665.9
1884.6	22.5°	1884.6	1903.1	2080.4	3096.8	5050.2	6826.3	8284.7	8771.7
1807.8	25°	1807.8	1813.1	1860.8	2453.7	4629.4	6807.8	8427.6	8917.3
1728.4	27.5°	1731.1	1731.1	1757.5	1977.2	4057.7	6728.4	8612.9	9092.0
1649.0	30°	1654.3	1654.3	1672.8	1749.6	3388.0	6572.2	8835.3	9319.6
1569.6	32.5°	1574.9	1574.9	1590.8	1646.4	2705.1	6376.3	9039.1	9549.9
1487.5	35°	1495.5	1490.2	1511.4	1569.6	2151.9	6127.5	9242.9	9798.7
1405.5	37.5°	1410.8	1408.1	1429.3	1495.5	1858.1	5839.0	9396.4	10137.5
1323.4	40°	1320.8	1320.8	1344.6	1416.1	1773.4	5476.4	9639.9	10624.6
1238.7	42.5°	1238.7	1233.4	1259.9	1347.3	1709.9	5129.6	10076.7	11333.9
1162.0	45°	1159.3	1148.7	1172.6	1281.1	1598.7	5007.9	10891.9	12382.1
1087.9	47.5°	1085.2	1058.7	1079.9	1201.7	1498.1	5463.1	12225.9	13835.2
1021.7	50°	1024.3	974.0	992.6	1122.3	1421.4	6450.4	13957.0	15764.8
960.8	52.5°	960.8	894.6	905.2	1024.3	1352.6	7390.1	15833.6	18311.1
899.9	55°	894.6	820.5	825.8	926.4	1254.6	7530.4	17665.2	21783.8
831.1	57.5°	820.5	751.7	751.7	836.4	1183.2	6527.2	19073.4	26092.9
746.4	60°	738.5	693.5	680.2	764.9	1246.7	4605.6	19237.5	28872.1
637.9	62.5°	648.5	624.7	606.1	696.1	1294.3	2728.9	17916.7	28199.8
502.9	65°	545.3	540.0	526.7	764.9	1090.5	1611.9	15381.0	26137.9
428.8	67.5°	457.9	450.0	450.0	802.0	828.5	1013.8	12016.8	23300.4
365.3	70°	394.4	365.3	365.3	606.1	502.9	701.4	8390.6	20238.0
301.7	72.5°	330.9	299.1	277.9	484.4	375.9	513.5	5243.5	17331.7
230.3	75°	264.7	240.9	214.4	320.3	280.6	389.1	3046.6	14359.3
145.6	77.5°	190.6	180.0	150.9	235.6	203.8	280.6	1813.1	11079.8
90.0	80°	97.9	100.6	95.3	135.0	137.6	190.6	1032.3	7583.3
58.2	82.5°	58.2	45.0	50.3	66.2	79.4	108.5	389.1	4457.3
42.3	85°	37.1	23.8	23.8	31.8	39.7	42.3	119.1	1807.8
21.2	87.5°	18.5	7.9	10.6	15.9	13.2	10.6	5.3	455.3
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)