

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P951247

Luminaire Tested: **GALN-SB5B-950-U-SLR**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P951247
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GALN-SB5B-950-U-SLR
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(5) 90 CRI, 5000K, 450mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 19717 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U0 - G4


Input Watts (W): 182.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P951247
 CATALOG NUMBER: GALN-SB5B-950-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 5.4 fc
 Type IV - Short - N/A

REPORT NUMBER: P951247
CATALOG NUMBER: GALN-SB5B-950-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P951247

CATALOG NUMBER: GALN-SB5B-950-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	5011.1	0.0	5011.1
	% Fixture	25.4	0.0	25.4
Street Side	Lumens	14705.9	0.0	14705.9
	% Fixture	74.6	0.0	74.6
Total	Lumens	19717.0	0.0	19717.0
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	269.0	1.4
10°-20°	844.3	4.3
20°-30°	1304.2	6.6
30°-40°	1652.7	8.4
40°-50°	2492.7	12.6
50°-60°	4027.3	20.4
60°-70°	5020.7	25.5
70°-80°	3292.3	16.7
80°-90°	813.9	4.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	19717.0	100.0
0°-180°	19717.0	100.0



REPORT NUMBER: P951247


CATALOG NUMBER: GALN-SB5B-950-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1326.2	6.7			
FM (30°-60°)	5751.0	29.2			
FH (60°-80°)	6958.2	35.3			G3/7500
FVH (80°-90°)	670.5	3.4			G4/750
BL (0°-30°)	1091.2	5.5	B3/2500		
BM (30°-60°)	2421.7	12.3	B2/2500		
BH (60°-80°)	1354.8	6.9	B3/2500		G3/2500
BVH (80°-90°)	143.4	0.7			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G4

Type IV Short



REPORT NUMBER: P951247

CATALOG NUMBER: GALN-SB5B-950-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°
0°	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3
2.5°	2915.7	2893.3	2871.0	2847.1	2823.4	2799.5	2775.6	2752.7	2729.8	2707.6
5°	3135.2	3085.8	3036.4	2987.1	2937.9	2888.2	2838.7	2792.4	2746.1	2702.4
7.5°	3355.8	3274.2	3192.7	3117.4	3042.1	2968.8	2895.4	2830.8	2766.2	2706.6
10°	3524.8	3421.7	3318.6	3219.1	3119.6	3030.6	2941.4	2865.0	2788.5	2714.9
12.5°	3628.4	3515.1	3401.9	3289.1	3176.3	3071.2	2966.2	2879.7	2793.2	2715.9
15°	3691.3	3573.2	3455.1	3332.8	3210.4	3089.4	2968.4	2868.4	2768.3	2682.6
17.5°	3726.7	3606.9	3487.2	3353.7	3220.2	3079.8	2939.3	2818.9	2698.6	2597.9
20°	3765.7	3641.3	3516.7	3370.0	3223.3	3053.1	2882.9	2733.7	2584.5	2467.3
22.5°	3810.9	3683.8	3556.6	3392.1	3227.5	3020.5	2813.4	2633.7	2454.1	2320.6
25°	3869.2	3744.6	3620.0	3432.0	3243.9	2988.2	2732.6	2522.1	2311.7	2174.9
27.5°	3948.3	3829.5	3710.6	3494.5	3278.3	2966.7	2655.1	2420.1	2185.0	2060.5
30°	4054.9	3940.1	3825.3	3575.3	3325.3	2956.6	2587.7	2334.7	2081.8	1977.3
32.5°	4180.8	4067.1	3953.5	3659.7	3365.9	2944.1	2522.1	2261.2	2000.2	1915.9
35°	4333.7	4224.9	4116.0	3755.8	3395.6	2920.6	2445.7	2188.9	1932.0	1861.8
37.5°	4591.2	4452.5	4313.7	3863.5	3413.3	2880.3	2347.3	2103.8	1860.2	1798.8
40°	4980.3	4778.1	4575.8	4000.2	3424.4	2824.9	2225.4	2002.2	1779.1	1723.4
42.5°	5496.4	5204.4	4912.5	4179.0	3445.6	2767.6	2089.9	1890.2	1690.4	1639.1
45°	6133.6	5739.8	5346.0	4414.4	3482.7	2714.5	1946.4	1771.2	1596.0	1543.9
47.5°	6930.6	6376.3	5822.0	4665.1	3508.2	2670.6	1833.0	1677.0	1521.1	1453.9
50°	7975.1	7139.6	6303.9	4897.7	3491.6	2622.7	1753.9	1614.5	1475.1	1386.8
52.5°	9174.2	7941.3	6708.4	5048.8	3389.1	2541.9	1694.8	1573.3	1451.9	1350.4
55°	10450.7	8652.1	6853.6	5015.5	3177.4	2407.9	1638.4	1543.4	1448.4	1354.1
57.5°	11611.8	9155.9	6699.9	4781.2	2862.6	2218.9	1575.2	1508.0	1440.9	1357.7
60°	12313.5	9281.7	6249.8	4345.2	2440.5	1973.6	1506.7	1453.9	1401.2	1346.3
62.5°	11957.2	8751.7	5546.1	3755.6	1965.1	1680.0	1395.0	1359.9	1324.9	1318.2
65°	11244.0	8001.6	4759.3	3154.0	1548.9	1415.9	1282.8	1266.3	1249.7	1250.5
67.5°	10288.4	7109.1	3929.8	2564.8	1199.8	1162.0	1124.1	1133.4	1142.6	1140.3
70°	9140.3	6135.2	3130.0	2019.4	908.8	919.6	930.3	973.2	1015.9	1015.9
72.5°	7772.2	5079.4	2386.7	1543.8	701.0	733.6	766.2	827.0	887.7	897.9
75°	6041.5	3869.1	1696.7	1120.5	544.3	573.9	603.4	671.5	739.5	786.5
77.5°	4316.6	2708.0	1099.5	759.3	419.1	439.1	459.3	525.4	591.5	669.0
80°	2825.2	1744.7	664.3	489.2	314.2	322.5	330.8	386.8	442.7	535.3
82.5°	1642.3	1009.8	377.5	300.9	224.5	226.0	227.6	268.8	310.0	389.1
85°	722.6	454.2	186.0	160.8	135.8	135.0	134.2	164.4	194.6	253.3
87.5°	223.7	148.8	73.9	66.7	59.5	58.8	58.1	70.3	82.7	107.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P951247
 CATALOG NUMBER: GALN-SB5B-950-U-SLR

CANDELA DISTRIBUTION (continued):

50°		55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
2711.3	0°	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3
2683.0	2.5°	2663.0	2643.1	2625.1	2607.2	2591.5	2575.8	2560.0	2544.3	2532.1	2519.8
2659.2	5°	2621.6	2583.8	2552.2	2520.7	2492.8	2464.9	2439.6	2414.2	2394.8	2375.2
2650.7	7.5°	2600.6	2550.5	2508.9	2467.3	2432.2	2397.1	2366.1	2335.2	2312.0	2288.9
2654.9	10°	2602.0	2549.2	2507.5	2465.9	2428.2	2390.3	2355.4	2320.6	2292.9	2265.1
2660.1	12.5°	2616.8	2573.7	2546.0	2518.6	2488.8	2459.3	2423.2	2387.2	2351.8	2316.4
2637.9	15°	2617.2	2596.6	2600.4	2604.1	2596.4	2588.7	2557.4	2526.1	2475.7	2425.4
2570.3	17.5°	2577.9	2585.4	2630.7	2676.1	2700.2	2724.3	2699.0	2673.8	2607.1	2540.4
2460.0	20°	2495.4	2530.7	2609.5	2688.4	2738.8	2789.3	2777.6	2765.9	2689.6	2613.5
2334.8	22.5°	2387.2	2439.5	2529.4	2619.5	2685.1	2750.8	2757.9	2764.8	2692.0	2619.2
2213.4	25°	2273.8	2334.1	2415.0	2495.9	2560.5	2625.1	2649.3	2673.3	2613.6	2554.0
2107.3	27.5°	2165.6	2223.8	2290.3	2356.7	2408.5	2460.3	2487.2	2514.1	2471.6	2429.1
2014.0	30°	2060.2	2106.6	2161.7	2216.9	2259.8	2302.9	2324.8	2346.6	2314.2	2281.8
1932.2	32.5°	1959.6	1986.9	2030.9	2075.1	2116.3	2157.6	2181.8	2206.1	2176.4	2146.5
1855.0	35°	1862.5	1870.1	1903.7	1937.2	1978.0	2018.9	2048.0	2077.1	2055.9	2034.8
1774.1	37.5°	1765.8	1757.4	1781.6	1805.6	1846.3	1887.1	1923.1	1959.1	1949.3	1939.5
1685.4	40°	1666.6	1647.8	1665.1	1682.5	1721.8	1761.2	1802.6	1844.1	1846.5	1848.8
1591.3	42.5°	1566.3	1541.3	1555.5	1569.7	1607.0	1644.3	1689.1	1733.8	1745.8	1757.7
1497.6	45°	1473.3	1449.1	1460.9	1473.0	1508.4	1543.7	1590.1	1636.5	1653.7	1670.9
1414.1	47.5°	1393.7	1373.3	1384.6	1395.7	1430.3	1464.9	1510.6	1556.4	1576.2	1596.0
1340.5	50°	1322.4	1304.4	1321.9	1339.5	1372.2	1404.7	1445.7	1486.7	1512.1	1537.5
1285.7	52.5°	1267.8	1250.0	1276.4	1302.6	1332.5	1362.4	1400.6	1438.9	1468.9	1499.0
1256.6	55°	1228.3	1200.1	1237.4	1274.7	1306.9	1339.2	1372.7	1406.1	1437.9	1469.9
1239.1	57.5°	1197.9	1156.7	1196.9	1237.0	1274.9	1312.8	1345.8	1379.0	1411.2	1443.2
1222.7	60°	1169.3	1115.8	1151.1	1186.3	1229.7	1273.2	1306.8	1340.5	1372.8	1405.0
1203.5	62.5°	1136.7	1070.0	1092.4	1114.8	1165.4	1216.2	1252.1	1288.0	1317.6	1347.1
1163.2	65°	1092.2	1021.1	1029.8	1038.3	1092.6	1147.0	1181.4	1215.7	1241.7	1267.7
1091.2	67.5°	1032.1	973.0	970.3	967.6	1017.7	1068.0	1100.5	1133.0	1155.5	1177.9
999.8	70°	957.8	915.8	906.4	897.0	941.1	985.2	1013.3	1041.4	1061.7	1082.0
898.1	72.5°	869.2	840.4	826.7	813.1	847.8	882.5	907.8	933.2	953.1	973.0
782.6	75°	760.4	738.2	725.0	711.8	737.6	763.4	786.4	809.4	827.5	845.6
666.9	77.5°	649.1	631.3	618.0	604.7	625.7	646.6	666.4	686.1	705.2	724.1
535.0	80°	520.1	505.1	494.0	482.7	500.2	517.6	534.2	550.9	565.3	579.7
393.5	82.5°	386.2	378.9	371.0	363.1	361.6	360.2	354.4	348.5	379.3	410.1
259.1	85°	251.3	243.5	234.6	225.8	218.3	210.7	194.6	178.4	207.2	236.2
114.4	87.5°	111.3	108.2	106.5	104.9	104.6	104.2	92.0	79.6	91.7	103.8
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P951247
 CATALOG NUMBER: GALN-SB5B-950-U-SLR

CANDELA DISTRIBUTION (continued):

105°		110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
2711.3	0°	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3
2509.9	2.5°	2500.1	2492.4	2484.7	2477.6	2470.4	2461.6	2470.4	2477.6	2484.7	2492.4
2361.6	5°	2348.0	2338.3	2328.6	2321.2	2313.8	2306.5	2313.8	2321.2	2328.6	2338.3
2272.6	7.5°	2256.4	2245.3	2234.2	2227.6	2221.0	2216.0	2221.0	2227.6	2234.2	2245.3
2247.0	10°	2228.7	2218.2	2207.7	2202.1	2196.5	2194.2	2196.5	2202.1	2207.7	2218.2
2293.0	12.5°	2269.6	2257.9	2246.2	2241.4	2236.6	2235.8	2236.6	2241.4	2246.2	2257.9
2389.8	15°	2354.2	2337.9	2321.6	2315.4	2309.1	2308.6	2309.1	2315.4	2321.6	2337.9
2488.0	17.5°	2435.6	2411.4	2387.2	2379.3	2371.3	2370.0	2371.3	2379.3	2387.2	2411.4
2549.2	20°	2485.0	2454.1	2423.1	2413.2	2403.3	2400.2	2403.3	2413.2	2423.1	2454.1
2553.0	22.5°	2486.7	2454.2	2421.5	2410.6	2399.7	2395.0	2399.7	2410.6	2421.5	2454.2
2495.1	25°	2436.4	2408.1	2379.9	2369.6	2359.4	2353.4	2359.4	2369.6	2379.9	2408.1
2383.4	27.5°	2337.8	2318.8	2299.8	2295.1	2290.4	2288.9	2290.4	2295.1	2299.8	2318.8
2249.1	30°	2216.2	2206.6	2196.8	2196.8	2196.8	2198.3	2196.8	2196.8	2196.8	2206.6
2120.4	32.5°	2094.3	2088.0	2081.6	2082.4	2083.4	2084.9	2083.4	2082.4	2081.6	2088.0
2010.7	35°	1986.6	1976.9	1967.4	1965.3	1963.2	1962.2	1963.2	1965.3	1967.4	1976.9
1917.3	37.5°	1895.1	1877.5	1860.0	1850.8	1841.5	1836.3	1841.5	1850.8	1860.0	1877.5
1829.9	40°	1811.1	1785.5	1760.1	1742.9	1725.8	1715.6	1725.8	1742.9	1760.1	1785.5
1741.8	42.5°	1726.0	1694.3	1662.5	1637.5	1612.4	1596.0	1612.4	1637.5	1662.5	1694.3
1656.5	45°	1642.3	1605.9	1569.7	1540.3	1510.9	1491.9	1510.9	1540.3	1569.7	1605.9
1586.0	47.5°	1576.0	1543.7	1511.5	1484.2	1457.1	1438.9	1457.1	1484.2	1511.5	1543.7
1536.9	50°	1536.4	1510.6	1484.8	1459.7	1434.5	1417.0	1434.5	1459.7	1484.8	1510.6
1504.4	52.5°	1509.8	1488.8	1467.8	1445.2	1422.7	1406.6	1422.7	1445.2	1467.8	1488.8
1477.4	55°	1484.8	1466.5	1448.2	1428.5	1408.7	1394.1	1408.7	1428.5	1448.2	1466.5
1450.8	57.5°	1458.4	1439.9	1421.4	1401.8	1382.2	1367.1	1382.2	1401.8	1421.4	1439.9
1413.4	60°	1421.7	1403.6	1385.6	1365.4	1345.2	1329.6	1345.2	1365.4	1385.6	1403.6
1355.1	62.5°	1363.1	1346.8	1330.5	1309.2	1288.0	1269.3	1288.0	1309.2	1330.5	1346.8
1275.9	65°	1284.0	1268.3	1252.6	1232.0	1211.5	1195.4	1211.5	1232.0	1252.6	1268.3
1185.9	67.5°	1193.8	1179.4	1165.0	1145.9	1126.7	1112.2	1126.7	1145.9	1165.0	1179.4
1089.7	70°	1097.4	1085.6	1073.9	1055.6	1037.3	1020.6	1037.3	1055.6	1073.9	1085.6
982.1	72.5°	991.3	981.5	971.7	954.2	936.9	920.7	936.9	954.2	971.7	981.5
855.2	75°	864.8	860.0	855.2	840.5	825.9	810.5	825.9	840.5	855.2	860.0
733.1	77.5°	742.0	735.3	728.5	713.7	698.9	686.7	698.9	713.7	728.5	735.3
591.6	80°	603.4	600.5	597.7	577.8	557.9	534.8	557.9	577.8	597.7	600.5
430.3	82.5°	450.5	449.2	447.9	431.1	414.3	399.5	414.3	431.1	447.9	449.2
261.1	85°	286.1	284.0	281.9	268.8	255.7	242.4	255.7	268.8	281.9	284.0
113.9	87.5°	124.0	121.5	118.8	112.2	105.3	98.8	105.3	112.2	118.8	121.5
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P951247
 CATALOG NUMBER: GALN-SB5B-950-U-SLR

CANDELA DISTRIBUTION (continued):

160°		165°	170°	175°	180°	185°	190°	195°	200°	205°	210°
2711.3	0°	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3
2500.1	2.5°	2509.9	2519.8	2532.1	2544.3	2560.0	2575.8	2591.5	2607.2	2625.1	2643.1
2348.0	5°	2361.6	2375.2	2394.8	2414.2	2439.6	2464.9	2492.8	2520.7	2552.2	2583.8
2256.4	7.5°	2272.6	2288.9	2312.0	2335.2	2366.1	2397.1	2432.2	2467.3	2508.9	2550.5
2228.7	10°	2247.0	2265.1	2292.9	2320.6	2355.4	2390.3	2428.2	2465.9	2507.5	2549.2
2269.6	12.5°	2293.0	2316.4	2351.8	2387.2	2423.2	2459.3	2488.8	2518.6	2546.0	2573.7
2354.2	15°	2389.8	2425.4	2475.7	2526.1	2557.4	2588.7	2596.4	2604.1	2600.4	2596.6
2435.6	17.5°	2488.0	2540.4	2607.1	2673.8	2699.0	2724.3	2700.2	2676.1	2630.7	2585.4
2485.0	20°	2549.2	2613.5	2689.6	2765.9	2777.6	2789.3	2738.8	2688.4	2609.5	2530.7
2486.7	22.5°	2553.0	2619.2	2692.0	2764.8	2757.9	2750.8	2685.1	2619.5	2529.4	2439.5
2436.4	25°	2495.1	2554.0	2613.6	2673.3	2649.3	2625.1	2560.5	2495.9	2415.0	2334.1
2337.8	27.5°	2383.4	2429.1	2471.6	2514.1	2487.2	2460.3	2408.5	2356.7	2290.3	2223.8
2216.2	30°	2249.1	2281.8	2314.2	2346.6	2324.8	2302.9	2259.8	2216.9	2161.7	2106.6
2094.3	32.5°	2120.4	2146.5	2176.4	2206.1	2181.8	2157.6	2116.3	2075.1	2030.9	1986.9
1986.6	35°	2010.7	2034.8	2055.9	2077.1	2048.0	2018.9	1978.0	1937.2	1903.7	1870.1
1895.1	37.5°	1917.3	1939.5	1949.3	1959.1	1923.1	1887.1	1846.3	1805.6	1781.6	1757.4
1811.1	40°	1829.9	1848.8	1846.5	1844.1	1802.6	1761.2	1721.8	1682.5	1665.1	1647.8
1726.0	42.5°	1741.8	1757.7	1745.8	1733.8	1689.1	1644.3	1607.0	1569.7	1555.5	1541.3
1642.3	45°	1656.5	1670.9	1653.7	1636.5	1590.1	1543.7	1508.4	1473.0	1460.9	1449.1
1576.0	47.5°	1586.0	1596.0	1576.2	1556.4	1510.6	1464.9	1430.3	1395.7	1384.6	1373.3
1536.4	50°	1536.9	1537.5	1512.1	1486.7	1445.7	1404.7	1372.2	1339.5	1321.9	1304.4
1509.8	52.5°	1504.4	1499.0	1468.9	1438.9	1400.6	1362.4	1332.5	1302.6	1276.4	1250.0
1484.8	55°	1477.4	1469.9	1437.9	1406.1	1372.7	1339.2	1306.9	1274.7	1237.4	1200.1
1458.4	57.5°	1450.8	1443.2	1411.2	1379.0	1345.8	1312.8	1274.9	1237.0	1196.9	1156.7
1421.7	60°	1413.4	1405.0	1372.8	1340.5	1306.8	1273.2	1229.7	1186.3	1151.1	1115.8
1363.1	62.5°	1355.1	1347.1	1317.6	1288.0	1252.1	1216.2	1165.4	1114.8	1092.4	1070.0
1284.0	65°	1275.9	1267.7	1241.7	1215.7	1181.4	1147.0	1092.6	1038.3	1029.8	1021.1
1193.8	67.5°	1185.9	1177.9	1155.5	1133.0	1100.5	1068.0	1017.7	967.6	970.3	973.0
1097.4	70°	1089.7	1082.0	1061.7	1041.4	1013.3	985.2	941.1	897.0	906.4	915.8
991.3	72.5°	982.1	973.0	953.1	933.2	907.8	882.5	847.8	813.1	826.7	840.4
864.8	75°	855.2	845.6	827.5	809.4	786.4	763.4	737.6	711.8	725.0	738.2
742.0	77.5°	733.1	724.1	705.2	686.1	666.4	646.6	625.7	604.7	618.0	631.3
603.4	80°	591.6	579.7	565.3	550.9	534.2	517.6	500.2	482.7	494.0	505.1
450.5	82.5°	430.3	410.1	379.3	348.5	354.4	360.2	361.6	363.1	371.0	378.9
286.1	85°	261.1	236.2	207.2	178.4	194.6	210.7	218.3	225.8	234.6	243.5
124.0	87.5°	113.9	103.8	91.7	79.6	92.0	104.2	104.6	104.9	106.5	108.2
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P951247
 CATALOG NUMBER: GALN-SB5B-950-U-SLR

CANDELA DISTRIBUTION (continued):

215°		220°	225°	230°	235°	240°	245°	250°	255°	260°	265°
2711.3	0°	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3
2663.0	2.5°	2683.0	2707.6	2729.8	2752.7	2775.6	2799.5	2823.4	2847.1	2871.0	2893.3
2621.6	5°	2659.2	2702.4	2746.1	2792.4	2838.7	2888.2	2937.9	2987.1	3036.4	3085.8
2600.6	7.5°	2650.7	2706.6	2766.2	2830.8	2895.4	2968.8	3042.1	3117.4	3192.7	3274.2
2602.0	10°	2654.9	2714.9	2788.5	2865.0	2941.4	3030.6	3119.6	3219.1	3318.6	3421.7
2616.8	12.5°	2660.1	2715.9	2793.2	2879.7	2966.2	3071.2	3176.3	3289.1	3401.9	3515.1
2617.2	15°	2637.9	2682.6	2768.3	2868.4	2968.4	3089.4	3210.4	3332.8	3455.1	3573.2
2577.9	17.5°	2570.3	2597.9	2698.6	2818.9	2939.3	3079.8	3220.2	3353.7	3487.2	3606.9
2495.4	20°	2460.0	2467.3	2584.5	2733.7	2882.9	3053.1	3223.3	3370.0	3516.7	3641.3
2387.2	22.5°	2334.8	2320.6	2454.1	2633.7	2813.4	3020.5	3227.5	3392.1	3556.6	3683.8
2273.8	25°	2213.4	2174.9	2311.7	2522.1	2732.6	2988.2	3243.9	3432.0	3620.0	3744.6
2165.6	27.5°	2107.3	2060.5	2185.0	2420.1	2655.1	2966.7	3278.3	3494.5	3710.6	3829.5
2060.2	30°	2014.0	1977.3	2081.8	2334.7	2587.7	2956.6	3325.3	3575.3	3825.3	3940.1
1959.6	32.5°	1932.2	1915.9	2000.2	2261.2	2522.1	2944.1	3365.9	3659.7	3953.5	4067.1
1862.5	35°	1855.0	1861.8	1932.0	2188.9	2445.7	2920.6	3395.6	3755.8	4116.0	4224.9
1765.8	37.5°	1774.1	1798.8	1860.2	2103.8	2347.3	2880.3	3413.3	3863.5	4313.7	4452.5
1666.6	40°	1685.4	1723.4	1779.1	2002.2	2225.4	2824.9	3424.4	4000.2	4575.8	4778.1
1566.3	42.5°	1591.3	1639.1	1690.4	1890.2	2089.9	2767.6	3445.6	4179.0	4912.5	5204.4
1473.3	45°	1497.6	1543.9	1596.0	1771.2	1946.4	2714.5	3482.7	4414.4	5346.0	5739.8
1393.7	47.5°	1414.1	1453.9	1521.1	1677.0	1833.0	2670.6	3508.2	4665.1	5822.0	6376.3
1322.4	50°	1340.5	1386.8	1475.1	1614.5	1753.9	2622.7	3491.6	4897.7	6303.9	7139.6
1267.8	52.5°	1285.7	1350.4	1451.9	1573.3	1694.8	2541.9	3389.1	5048.8	6708.4	7941.3
1228.3	55°	1256.6	1354.1	1448.4	1543.4	1638.4	2407.9	3177.4	5015.5	6853.6	8652.1
1197.9	57.5°	1239.1	1357.7	1440.9	1508.0	1575.2	2218.9	2862.6	4781.2	6699.9	9155.9
1169.3	60°	1222.7	1346.3	1401.2	1453.9	1506.7	1973.6	2440.5	4345.2	6249.8	9281.7
1136.7	62.5°	1203.5	1318.2	1324.9	1359.9	1395.0	1680.0	1965.1	3755.6	5546.1	8751.7
1092.2	65°	1163.2	1250.5	1249.7	1266.3	1282.8	1415.9	1548.9	3154.0	4759.3	8001.6
1032.1	67.5°	1091.2	1140.3	1142.6	1133.4	1124.1	1162.0	1199.8	2564.8	3929.8	7109.1
957.8	70°	999.8	1015.9	1015.9	973.2	930.3	919.6	908.8	2019.4	3130.0	6135.2
869.2	72.5°	898.1	897.9	887.7	827.0	766.2	733.6	701.0	1543.8	2386.7	5079.4
760.4	75°	782.6	786.5	739.5	671.5	603.4	573.9	544.3	1120.5	1696.7	3869.1
649.1	77.5°	666.9	669.0	591.5	525.4	459.3	439.1	419.1	759.3	1099.5	2708.0
520.1	80°	535.0	535.3	442.7	386.8	330.8	322.5	314.2	489.2	664.3	1744.7
386.2	82.5°	393.5	389.1	310.0	268.8	227.6	226.0	224.5	300.9	377.5	1009.8
251.3	85°	259.1	253.3	194.6	164.4	134.2	135.0	135.8	160.8	186.0	454.2
111.3	87.5°	114.4	107.2	82.7	70.3	58.1	58.8	59.5	66.7	73.9	148.8
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P951247
 CATALOG NUMBER: GALN-SB5B-950-U-SLR

CANDELA DISTRIBUTION (continued):

270°		275°	280°	285°	290°	295°	300°	305°	310°	315°	320°
2711.3	0°	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3
2915.7	2.5°	2926.7	2937.9	2953.6	2969.3	2978.6	2988.0	2992.7	2997.4	2995.3	2997.4
3135.2	5°	3173.8	3212.5	3250.8	3289.2	3310.0	3330.8	3343.4	3356.1	3365.7	3356.1
3355.8	7.5°	3418.6	3481.4	3537.8	3594.3	3628.4	3662.4	3680.8	3699.1	3708.0	3699.1
3524.8	10°	3599.1	3673.4	3739.7	3806.0	3846.1	3886.1	3904.0	3921.8	3928.5	3921.8
3628.4	12.5°	3708.9	3789.3	3849.2	3909.0	3938.1	3967.2	3977.0	3986.8	3987.8	3986.8
3691.3	15°	3760.8	3830.2	3867.8	3905.4	3906.5	3907.5	3897.1	3886.7	3874.4	3886.7
3726.7	17.5°	3773.6	3820.5	3821.2	3821.9	3779.7	3737.6	3699.0	3660.3	3633.0	3660.3
3765.7	20°	3782.0	3798.5	3749.0	3699.6	3606.6	3513.6	3445.9	3378.1	3336.5	3378.1
3810.9	22.5°	3789.5	3768.1	3665.7	3563.3	3426.5	3289.7	3205.0	3120.3	3074.4	3120.3
3869.2	25°	3801.6	3734.0	3578.5	3423.1	3256.9	3090.8	3001.7	2912.9	2869.4	2912.9
3948.3	27.5°	3827.4	3706.4	3500.5	3294.7	3110.6	2926.4	2838.8	2751.3	2710.2	2751.3
4054.9	30°	3874.6	3694.4	3441.0	3187.5	2995.7	2803.9	2722.6	2641.3	2603.1	2641.3
4180.8	32.5°	3933.9	3687.1	3400.4	3113.7	2933.4	2753.1	2689.3	2625.4	2597.9	2625.4
4333.7	35°	4031.6	3729.6	3430.8	3132.1	3006.8	2881.7	2866.8	2851.9	2849.6	2851.9
4591.2	37.5°	4235.8	3880.4	3608.9	3337.4	3329.2	3321.1	3389.2	3457.2	3492.6	3457.2
4980.3	40°	4593.8	4207.3	4005.4	3803.5	3946.0	4088.5	4253.9	4419.4	4501.8	4419.4
5496.4	42.5°	5112.9	4729.4	4613.1	4496.8	4807.6	5118.5	5419.4	5720.3	5896.9	5720.3
6133.6	45°	5789.1	5444.6	5393.3	5341.9	5839.9	6338.1	6832.5	7326.9	7627.1	7326.9
6930.6	47.5°	6595.5	6260.2	6249.8	6239.4	6957.9	7676.2	8400.0	9123.7	9548.7	9123.7
7975.1	50°	7561.1	7147.3	7149.0	7150.8	8076.8	9002.7	9958.1	10913.5	11491.1	10913.5
9174.2	52.5°	8672.9	8171.7	8121.1	8070.3	9176.3	10282.4	11464.5	12646.5	13338.8	12646.5
10450.7	55°	9955.5	9460.3	9262.7	9065.1	10296.1	11527.0	12936.2	14345.4	15168.9	14345.4
11611.8	57.5°	11342.1	11072.4	10676.1	10279.9	11522.8	12765.8	14362.0	15958.0	16979.2	15958.0
12313.5	60°	12732.4	13151.4	12659.3	12167.2	13343.4	14519.7	16228.6	17937.6	19041.2	17937.6
11957.2	62.5°	13101.7	14246.3	14190.8	14135.3	15212.8	16290.4	17916.4	19542.2	20562.3	19542.2
11244.0	65°	12318.2	13392.4	13605.0	13817.4	15186.8	16556.3	18132.9	19709.4	20577.9	19709.4
10288.4	67.5°	11310.1	12331.7	12431.4	12531.0	13957.8	15384.5	16967.8	18551.2	19231.6	18551.2
9140.3	70°	10251.6	11362.9	11407.5	11452.1	12728.0	14003.9	15366.5	16729.0	17107.1	16729.0
7772.2	72.5°	9047.4	10322.8	10354.8	10386.7	11385.0	12383.2	13403.8	14424.2	14462.5	14424.2
6041.5	75°	7361.4	8681.2	8799.7	8918.2	9694.9	10471.5	11189.9	11908.3	11715.8	11908.3
4316.6	77.5°	5548.6	6780.7	6950.3	7119.9	7710.3	8300.8	8810.2	9319.8	8989.0	9319.8
2825.2	80°	3861.7	4898.2	5108.9	5319.7	5765.6	6211.3	6478.9	6746.4	6214.3	6746.4
1642.3	82.5°	2350.9	3059.6	3295.0	3530.6	3837.5	4144.4	4256.0	4367.6	3949.3	4367.6
722.6	85°	1098.7	1474.8	1675.0	1875.3	2127.5	2379.6	2442.9	2506.3	2171.3	2506.3
223.7	87.5°	350.1	476.5	588.2	700.0	826.1	952.2	957.6	962.9	808.4	962.9
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P951247
 CATALOG NUMBER: GALN-SB5B-950-U-SLR

CANDELA DISTRIBUTION (continued):

325°		330°	335°	340°	345°	350°	355°	360°
2711.3	0°	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3	2711.3
2992.7	2.5°	2988.0	2978.6	2969.3	2953.6	2937.9	2926.7	2915.7
3343.4	5°	3330.8	3310.0	3289.2	3250.8	3212.5	3173.8	3135.2
3680.8	7.5°	3662.4	3628.4	3594.3	3537.8	3481.4	3418.6	3355.8
3904.0	10°	3886.1	3846.1	3806.0	3739.7	3673.4	3599.1	3524.8
3977.0	12.5°	3967.2	3938.1	3909.0	3849.2	3789.3	3708.9	3628.4
3897.1	15°	3907.5	3906.5	3905.4	3867.8	3830.2	3760.8	3691.3
3699.0	17.5°	3737.6	3779.7	3821.9	3821.2	3820.5	3773.6	3726.7
3445.9	20°	3513.6	3606.6	3699.6	3749.0	3798.5	3782.0	3765.7
3205.0	22.5°	3289.7	3426.5	3563.3	3665.7	3768.1	3789.5	3810.9
3001.7	25°	3090.8	3256.9	3423.1	3578.5	3734.0	3801.6	3869.2
2838.8	27.5°	2926.4	3110.6	3294.7	3500.5	3706.4	3827.4	3948.3
2722.6	30°	2803.9	2995.7	3187.5	3441.0	3694.4	3874.6	4054.9
2689.3	32.5°	2753.1	2933.4	3113.7	3400.4	3687.1	3933.9	4180.8
2866.8	35°	2881.7	3006.8	3132.1	3430.8	3729.6	4031.6	4333.7
3389.2	37.5°	3321.1	3329.2	3337.4	3608.9	3880.4	4235.8	4591.2
4253.9	40°	4088.5	3946.0	3803.5	4005.4	4207.3	4593.8	4980.3
5419.4	42.5°	5118.5	4807.6	4496.8	4613.1	4729.4	5112.9	5496.4
6832.5	45°	6338.1	5839.9	5341.9	5393.3	5444.6	5789.1	6133.6
8400.0	47.5°	7676.2	6957.9	6239.4	6249.8	6260.2	6595.5	6930.6
9958.1	50°	9002.7	8076.8	7150.8	7149.0	7147.3	7561.1	7975.1
11464.5	52.5°	10282.4	9176.3	8070.3	8121.1	8171.7	8672.9	9174.2
12936.2	55°	11527.0	10296.1	9065.1	9262.7	9460.3	9955.5	10450.7
14362.0	57.5°	12765.8	11522.8	10279.9	10676.1	11072.4	11342.1	11611.8
16228.6	60°	14519.7	13343.4	12167.2	12659.3	13151.4	12732.4	12313.5
17916.4	62.5°	16290.4	15212.8	14135.3	14190.8	14246.3	13101.7	11957.2
18132.9	65°	16556.3	15186.8	13817.4	13605.0	13392.4	12318.2	11244.0
16967.8	67.5°	15384.5	13957.8	12531.0	12431.4	12331.7	11310.1	10288.4
15366.5	70°	14003.9	12728.0	11452.1	11407.5	11362.9	10251.6	9140.3
13403.8	72.5°	12383.2	11385.0	10386.7	10354.8	10322.8	9047.4	7772.2
11189.9	75°	10471.5	9694.9	8918.2	8799.7	8681.2	7361.4	6041.5
8810.2	77.5°	8300.8	7710.3	7119.9	6950.3	6780.7	5548.6	4316.6
6478.9	80°	6211.3	5765.6	5319.7	5108.9	4898.2	3861.7	2825.2
4256.0	82.5°	4144.4	3837.5	3530.6	3295.0	3059.6	2350.9	1642.3
2442.9	85°	2379.6	2127.5	1875.3	1675.0	1474.8	1098.7	722.6
957.6	87.5°	952.2	826.1	700.0	588.2	476.5	350.1	223.7
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)