

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P991037

Luminaire Tested: **GPC-SA2C-735-U-T3BC**

Issue Date: 07/03/2025

Test Information

Test Method: LM-79-08
Report Number: P991037
Test Lab: INNOVATION CENTER(G1)
Issue Date: 07/03/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GPC-SA2C-735-U-T3BC
Description: GALLEON PEDESTRAIAN COMPANION 1050mA 2xLight Square PACKAGE 70CRI
3500K FIXTURE w/ TYPE III ANGLED BACKLIGHT CONTROL
Light Source: (28) 3500K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10642.5 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Luminous Opening: Rectangular (W 1.33' x L: 0.67' x H: 0')
IES Classification: Type III - Short
BUG Rating: B0 - U0 - G2

Input Watts (W): 94.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P991037

CATALOG NUMBER: GPC-SA2C-735-U-T3BC

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 6.7 fc
 Type III - Short - N/A

REPORT NUMBER: P991037
CATALOG NUMBER: GPC-SA2C-735-U-T3BC

Luminous Intensity Polar Plot



REPORT NUMBER: P991037

CATALOG NUMBER: GPC-SA2C-735-U-T3BC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	28.8	0.0	28.8
	% Fixture	0.3	0.0	0.3
Street Side	Lumens	10613.6	0.0	10613.6
	% Fixture	99.7	0.0	99.7
Total	Lumens	10642.5	0.0	10642.5
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	10.4	0.1
10°-20°	123.2	1.2
20°-30°	435.6	4.1
30°-40°	1004.1	9.4
40°-50°	1693.8	15.9
50°-60°	2792.5	26.2
60°-70°	3172.3	29.8
70°-80°	1304.3	12.3
80°-90°	106.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10642.5	100.0
0°-180°	10642.5	100.0



REPORT NUMBER: P991037


CATALOG NUMBER: GPC-SA2C-735-U-T3BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	563.2	5.3			
FM	(30°-60°)	5484.9	51.5			
FH	(60°-80°)	4460.2	41.9			G2/5000
FVH	(80°-90°)	105.4	1.0			G2/225
BL	(0°-30°)	6.1	0.1	B0/110		
BM	(30°-60°)	5.5	0.1	B0/220		
BH	(60°-80°)	16.5	0.2	B0/110		G0/110
BVH	(80°-90°)	0.8	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type III Short





REPORT NUMBER: P991037

CATALOG NUMBER: GPC-SA2C-735-U-T3BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	44°	45°	55°	65°	75°	85°
0°	59.6	59.6	59.6	59.6	59.6	59.6	59.6	59.6	59.6	59.6	59.6
2.5°	79.4	80.3	79.4	78.6	75.1	71.7	71.7	69.1	66.5	63.9	61.3
5°	139.9	136.4	133.0	125.2	110.5	97.6	95.8	84.6	75.1	68.2	62.2
7.5°	354.9	345.4	312.6	273.7	208.1	159.7	158.0	120.0	90.7	74.3	63.0
10°	740.9	715.0	664.9	582.0	449.9	329.0	303.1	184.8	119.2	82.0	63.9
12.5°	1126.0	1126.9	1079.4	966.3	804.8	610.5	576.8	334.2	170.1	95.8	64.8
15°	1464.5	1455.9	1414.4	1334.1	1159.7	935.2	904.9	574.2	257.3	114.8	66.5
17.5°	1723.5	1711.5	1686.4	1632.0	1504.2	1283.2	1251.2	866.1	398.9	139.9	67.4
20°	2027.5	2018.9	1986.9	1911.8	1795.2	1619.1	1573.3	1185.6	607.9	181.3	69.1
22.5°	2404.0	2378.9	2340.1	2244.2	2100.0	1910.9	1895.4	1510.3	864.4	246.1	72.5
25°	2839.2	2803.8	2758.0	2637.1	2459.2	2229.6	2210.6	1828.9	1140.7	343.7	77.7
27.5°	3366.8	3334.0	3251.9	3095.6	2882.4	2607.8	2586.2	2154.4	1447.2	476.7	84.6
30°	3938.4	3896.1	3760.5	3557.6	3354.7	3030.0	2978.2	2487.7	1753.8	642.4	94.1
32.5°	4471.2	4416.8	4249.3	4009.2	3796.8	3454.0	3408.2	2864.2	2075.9	840.2	108.8
35°	4943.5	4879.6	4647.4	4385.7	4172.4	3870.2	3828.8	3230.4	2388.4	1064.7	126.9
37.5°	5319.2	5276.8	4955.6	4660.3	4486.7	4219.1	4191.4	3623.2	2736.4	1323.7	152.0
40°	5706.9	5650.7	5273.4	4901.2	4704.3	4481.6	4448.7	3939.3	3070.6	1603.5	183.1
42.5°	6035.0	5982.3	5627.4	5232.8	4925.4	4660.3	4639.6	4204.4	3394.4	1894.5	223.6
45°	6382.1	6334.6	6016.9	5707.7	5246.6	4838.2	4802.8	4423.7	3710.5	2234.7	277.2
47.5°	6858.8	6795.7	6492.6	6255.2	5727.6	5111.9	5072.2	4638.7	4030.8	2590.5	351.4
50°	7455.5	7409.7	7190.4	7001.3	6441.7	5611.0	5526.4	4917.6	4334.8	2998.1	448.2
52.5°	8034.9	8019.3	8034.9	7967.5	7541.8	6477.1	6312.2	5386.5	4721.6	3423.8	574.2
55°	8107.4	8154.9	8342.3	8558.1	8487.3	7718.0	7578.9	6100.6	5200.0	3960.9	766.8
57.5°	7844.9	7871.7	8110.8	8491.6	8720.5	8603.0	8585.8	7282.8	5875.2	4599.0	1056.1
59°	7576.3	7629.0	7819.8	8208.4	8536.6	8730.0	8743.8	8033.1	6389.0	4996.2	1294.4
60°	7427.0	7443.4	7591.0	7973.6	8325.9	8631.5	8671.3	8417.4	6794.0	5295.8	1507.7
62.5°	6955.5	6964.1	7043.6	7344.9	7656.6	7938.1	8021.9	8651.4	7918.3	6047.1	2261.5
65°	6338.9	6350.2	6470.2	6759.5	7056.5	7245.6	7281.0	7995.1	8510.6	6829.4	3314.1
67.5°	5227.6	5290.7	5443.5	5899.4	6317.4	6543.6	6569.5	6838.0	8186.8	7358.7	3871.1
70°	3539.5	3479.9	3859.0	4493.6	5249.2	5589.4	5591.2	5708.6	6969.3	7228.4	3227.8
72.5°	1545.7	1640.6	1917.0	2475.7	3391.0	4211.3	4194.0	4593.0	5558.3	6141.2	2399.7
75°	678.7	700.3	816.9	1113.1	1542.2	2287.4	2550.8	3687.1	4183.7	4016.1	1745.1
77.5°	365.3	370.4	401.5	465.4	589.8	1080.2	1140.7	2335.8	2966.1	2315.0	1127.7
80°	139.0	139.0	145.1	166.7	246.1	422.3	453.3	1055.2	2046.5	1183.0	569.9
82.5°	87.2	85.5	86.3	87.2	100.2	144.2	153.7	419.7	966.3	583.7	150.2
85°	44.0	45.8	50.9	61.3	72.5	88.9	91.5	131.3	293.6	136.4	38.9
87.5°	28.5	29.4	31.9	41.4	50.9	64.8	66.5	91.5	116.6	95.8	7.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P991037

CATALOG NUMBER: GPC-SA2C-735-U-T3BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	59.6	59.6	59.6	59.6	59.6	59.6	59.6	59.6	59.6	59.6	59.6
2.5°	60.4	58.7	56.1	53.5	50.9	46.6	43.2	41.4	40.6	39.7	39.7
5°	59.6	57.0	51.8	47.5	43.2	38.0	33.7	31.1	30.2	29.4	29.4
7.5°	58.7	54.4	48.4	42.3	36.3	30.2	25.0	22.5	21.6	20.7	19.9
10°	57.9	52.7	44.0	37.1	30.2	23.3	18.1	14.7	13.8	13.0	13.0
12.5°	57.0	50.1	40.6	32.8	24.2	16.4	12.1	8.6	6.9	6.0	6.0
15°	56.1	47.5	38.0	27.6	18.1	10.4	5.2	2.6	0.9	0.9	0.9
17.5°	53.5	44.9	33.7	21.6	12.1	5.2	1.7	0.0	0.0	0.0	0.0
20°	51.8	42.3	29.4	16.4	6.9	2.6	0.0	0.0	0.0	0.0	0.0
22.5°	50.9	40.6	25.0	11.2	5.2	0.0	0.0	0.0	0.0	0.0	0.0
25°	50.9	38.9	20.7	8.6	2.6	0.0	0.0	0.0	0.0	0.0	0.0
27.5°	51.8	37.1	16.4	6.0	0.9	0.0	0.0	0.0	0.0	0.0	0.0
30°	50.1	35.4	12.1	4.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
32.5°	50.1	31.9	8.6	2.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
35°	50.9	27.6	6.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	53.5	24.2	5.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40°	57.9	22.5	4.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	63.9	21.6	3.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	70.8	21.6	1.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	81.2	22.5	0.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	93.3	23.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	107.1	24.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	121.8	23.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	141.6	22.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
59°	162.3	20.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	183.9	19.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	297.0	17.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	582.9	15.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	996.5	16.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	1058.6	15.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	695.1	13.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	354.0	13.8	0.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	158.9	13.8	1.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	63.9	7.8	1.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	25.9	5.2	2.6	0.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	10.4	5.2	3.5	1.7	0.9	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	6.9	5.2	4.3	3.5	1.7	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-5

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-735-U-5WQ

Data in this report applies to families of products including GSS-SB1A-735-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-5
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-735-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3500K CCT 26 LEDS

Spectral Parameters

CCT (K):	3369	CRI (Ra):	70.1		
CIE u':	0.2386	R1:	66.6	R9:	-40.2
CIE v':	0.5156	R2:	77.6	R10:	49.1
Duv:	0.0013	R3:	88.5	R11:	66.3
CIE x:	0.4143	R4:	69.5	R12:	45.7
CIE y:	0.3980	R5:	66.4	R13:	68.0
CIE z:	0.1877	R6:	69.6	R14:	93.4
Peak Wavelength (nm):	590	R7:	77.5	R15:	57.6
Dominant Wavelength (nm):	580	R8:	44.9		
Purity:	43.80166				
Rf:	71.4				
Rg:	96				



Test Conditions

Stabilization Time: 21M
 Operation Time: 1H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-5

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-5

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.29

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.36

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

TM-30-18

Summary

$R_f = 71.4$
 $R_g = 96$
 CIE $R_a = 70.1$
 $R_g = -40.2$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 57	CES51 = 84	CES76 = 50
CES02 = 62	CES27 = 80	CES52 = 86	CES77 = 74
CES03 = 31	CES28 = 81	CES53 = 72	CES78 = 54
CES04 = 70	CES29 = 50	CES54 = 79	CES79 = 81
CES05 = 48	CES30 = 55	CES55 = 78	CES80 = 79
CES06 = 51	CES31 = 56	CES56 = 67	CES81 = 74
CES07 = 40	CES32 = 54	CES57 = 65	CES82 = 91
CES08 = 39	CES33 = 60	CES58 = 68	CES83 = 86
CES09 = 29	CES34 = 69	CES59 = 85	CES84 = 89
CES10 = 75	CES35 = 83	CES60 = 91	CES85 = 83
CES11 = 58	CES36 = 88	CES61 = 85	CES86 = 66
CES12 = 64	CES37 = 78	CES62 = 78	CES87 = 77
CES13 = 43	CES38 = 64	CES63 = 71	CES88 = 75
CES14 = 74	CES39 = 92	CES64 = 70	CES89 = 68
CES15 = 71	CES40 = 86	CES65 = 64	CES90 = 72
CES16 = 47	CES41 = 81	CES66 = 65	CES91 = 95
CES17 = 50	CES42 = 79	CES67 = 63	CES92 = 62
CES18 = 56	CES43 = 71	CES68 = 69	CES93 = 78
CES19 = 72	CES44 = 98	CES69 = 80	CES94 = 51
CES20 = 65	CES45 = 80	CES70 = 60	CES95 = 70
CES21 = 87	CES46 = 75	CES71 = 58	CES96 = 76
CES22 = 79	CES47 = 71	CES72 = 85	CES97 = 82
CES23 = 92	CES48 = 61	CES73 = 51	CES98 = 72
CES24 = 91	CES49 = 74	CES74 = 94	CES99 = 60
CES25 = 72	CES50 = 83	CES75 = 57	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)