Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1390535

Luminaire Tested: **GSS-SA5A-927-U-LBC**

Issue Date: 02/18/2026

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1390535
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SA5A-927-U-LBC
Description:	GALLEON SLIM SITE LUMINAIRE 615mA 5xLight Square PACKAGE 90CRI 2700K FIXTURE w/ LEFT CORNER BACKLIGHT CONTROL
Light Source:	(70) 2700K CCT, 90 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Luminaire Equipment:

Sample No.	Condition	Description
a	good	reflector
b	good	lens
c	good	housing
d	good	cord

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	8767.2 lumens
Efficiency:	N/A
Efficacy:	63.6 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type III - Short
BUG Rating:	B0 - U0 - G2


Input Watts (W):	137.9
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.97
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1390535
CATALOG NUMBER: GSS-SA5A-927-U-LBC

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 17.2 fc
Type III - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1390535
CATALOG NUMBER: GSS-SA5A-927-U-LBC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1390535
CATALOG NUMBER: GSS-SA5A-927-U-LBC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	45.9	0.0	45.9
	% Fixture	0.5	0.0	0.5
Street Side	Lumens	8721.3	0.0	8721.3
	% Fixture	99.5	0.0	99.5
Total	Lumens	8767.2	0.0	8767.2
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	3.0	0.0
10°-20°	14.7	0.2
20°-30°	189.7	2.2
30°-40°	591.5	6.7
40°-50°	1932.4	22.0
50°-60°	3102.7	35.4
60°-70°	2381.5	27.2
70°-80°	542.2	6.2
80°-90°	9.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8767.2	100.0
0°-180°	8767.2	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1390535
CATALOG NUMBER: GSS-SA5A-927-U-LBC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	201.4	2.3			
FM	(30°-60°)	5607.6	64.0			
FH	(60°-80°)	2904.1	33.1			G2/5000
FVH	(80°-90°)	8.3	0.1			G0/10
BL	(0°-30°)	5.9	0.1	B0/110		
BM	(30°-60°)	19.1	0.2	B0/220		
BH	(60°-80°)	19.6	0.2	B0/110		G0/110
BVH	(80°-90°)	1.3	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2
Type III Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1390535
CATALOG NUMBER: GSS-SA5A-927-U-LBC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	32.4	32.4	32.4	32.4	32.4	*32.4*	32.4	32.4	32.4	32.4	32.4
2.5°	43.1	43.1	43.1	40.5	37.8	*35.1*	32.4	32.4	32.4	29.7	29.7
5°	45.8	45.8	45.8	43.1	43.1	*40.5*	37.8	37.8	37.8	35.1	32.4
7.5°	48.5	51.2	51.2	51.2	51.2	*48.5*	45.8	45.8	43.1	40.5	37.8
10°	51.2	53.9	59.3	62.0	62.0	*62.0*	59.3	56.6	51.2	45.8	43.1
12.5°	56.6	62.0	67.4	72.8	75.5	*75.5*	72.8	70.1	62.0	51.2	48.5
15°	62.0	67.4	78.2	94.4	102.5	*110.6*	99.8	89.0	72.8	62.0	53.9
17.5°	67.4	78.2	102.5	142.9	199.6	*215.7*	199.6	145.6	94.4	67.4	59.3
20°	72.8	86.3	156.4	350.6	606.8	*790.2*	682.3	404.5	153.7	78.2	64.7
22.5°	80.9	102.5	342.5	973.6	1577.7	*1998.4*	1704.4	995.1	380.3	99.8	72.8
25°	91.7	140.2	649.9	1712.5	2740.0	*3282.1*	2783.2	1788.0	712.0	145.6	83.6
27.5°	107.9	213.1	1032.9	2429.9	3665.0	*4123.5*	3683.9	2529.7	1103.0	234.6	102.5
30°	137.5	320.9	1378.1	3190.4	4398.6	*4851.6*	4350.0	3209.3	1456.3	331.7	137.5
32.5°	169.9	383.0	1761.0	3737.8	5115.9	*5741.6*	4997.3	3692.0	1774.5	385.7	169.9
35°	172.6	428.8	2138.6	4341.9	5992.4	*6728.7*	5838.7	4182.8	2135.9	436.9	169.9
37.5°	169.9	490.8	2545.8	4921.8	6963.3	*7944.9*	6844.6	4741.1	2521.6	517.8	167.2
40°	172.6	590.6	3036.7	6014.0	8721.6	*10172.5*	8516.7	5628.3	2958.5	636.5	175.3
42.5°	191.5	806.4	4034.5	8484.3	12311.2	*14382.3*	11971.4	7980.0	3983.3	825.2	191.5
45°	264.3	1321.5	6337.6	11663.9	17327.3	*19608.9*	16887.7	11526.4	6175.8	1264.8	240.0
47.5°	434.2	2187.2	9099.2	14584.6	19870.4	*22111.5*	19554.9	14323.0	9201.7	2295.0	434.2
50°	590.6	3190.4	10633.7	15536.6	20720.0	*23193.0*	20264.2	15239.9	10668.8	3368.4	679.6
52.5°	685.0	3419.6	10860.2	15814.4	20887.2	*23797.1*	20417.9	15431.4	10849.5	3576.0	738.9
55°	695.8	3071.7	10444.9	15881.8	21564.1	*24913.6*	20970.8	15501.5	10353.2	3093.3	666.1
57°	*663.4*	*2578.2*	*10026.9*	*16227.0*	*22289.5*	*25461.0*	*21531.7*	*15760.4*	*9897.5*	*2535.0*	*582.5*
57.5°	649.9	2440.7	9889.4	16337.6	22335.4	*25396.3*	21591.0	15881.8	9754.5	2429.9	563.6
60°	472.0	1960.6	9565.8	16442.7	21542.5	*24093.7*	20655.2	15895.3	9288.0	1839.3	423.4
62.5°	383.0	1429.3	8959.0	15132.1	18753.9	*20725.4*	17899.0	14441.7	8584.1	1334.9	345.2
65°	329.0	1014.0	7667.2	11949.8	15086.2	*16504.8*	14538.8	11631.5	6990.3	887.3	304.7
67.5°	299.4	698.5	5385.6	9029.1	11674.7	*13869.9*	11483.2	8700.1	5043.1	596.0	283.2
70°	269.7	496.2	3050.1	6275.6	9503.7	*11316.0*	9242.1	6329.5	3039.4	453.1	272.4
72.5°	240.0	353.3	1469.8	4277.2	6232.4	*6882.4*	6130.0	4285.3	1556.1	366.8	253.5
75°	202.3	267.0	563.6	1243.3	1931.0	*2699.6*	2009.2	1378.1	631.1	291.3	226.5
77.5°	129.4	126.8	175.3	347.9	636.5	*860.3*	868.4	528.6	210.4	156.4	164.5
80°	59.3	67.4	89.0	99.8	134.8	*132.1*	180.7	132.1	99.8	72.8	64.7
82.5°	24.3	24.3	29.7	21.6	27.0	*27.0*	24.3	18.9	29.7	21.6	18.9
85°	2.7	2.7	2.7	2.7	2.7	*0.0*	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1390535
CATALOG NUMBER: GSS-SA5A-927-U-LBC

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°	185°
0°	32.4	32.4	32.4	32.4	32.4	32.4	32.4	32.4	32.4	32.4	32.4
2.5°	29.7	27.0	27.0	24.3	24.3	24.3	21.6	21.6	21.6	18.9	18.9
5°	32.4	29.7	27.0	24.3	21.6	21.6	18.9	18.9	16.2	16.2	16.2
7.5°	35.1	32.4	29.7	24.3	21.6	21.6	18.9	16.2	13.5	13.5	13.5
10°	40.5	35.1	29.7	24.3	21.6	18.9	16.2	13.5	10.8	10.8	10.8
12.5°	45.8	37.8	29.7	27.0	21.6	18.9	16.2	13.5	10.8	10.8	8.1
15°	48.5	40.5	32.4	24.3	21.6	18.9	16.2	10.8	8.1	8.1	5.4
17.5°	53.9	40.5	32.4	24.3	18.9	16.2	13.5	10.8	5.4	5.4	2.7
20°	53.9	40.5	32.4	24.3	18.9	16.2	13.5	5.4	2.7	0.0	0.0
22.5°	59.3	43.1	32.4	24.3	18.9	13.5	8.1	2.7	0.0	0.0	0.0
25°	64.7	43.1	32.4	24.3	16.2	10.8	5.4	0.0	0.0	0.0	0.0
27.5°	72.8	45.8	35.1	24.3	16.2	8.1	0.0	0.0	0.0	0.0	0.0
30°	78.2	48.5	32.4	24.3	13.5	5.4	0.0	0.0	0.0	0.0	0.0
32.5°	94.4	48.5	32.4	24.3	13.5	5.4	0.0	0.0	0.0	0.0	0.0
35°	99.8	48.5	32.4	21.6	10.8	2.7	0.0	0.0	0.0	0.0	0.0
37.5°	97.1	51.2	32.4	21.6	10.8	0.0	0.0	0.0	0.0	0.0	0.0
40°	86.3	51.2	32.4	21.6	8.1	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	83.6	53.9	32.4	21.6	10.8	0.0	0.0	0.0	0.0	0.0	0.0
45°	86.3	51.2	35.1	21.6	13.5	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	89.0	48.5	35.1	18.9	16.2	0.0	0.0	0.0	0.0	0.0	0.0
50°	91.7	48.5	37.8	21.6	13.5	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	102.5	48.5	37.8	24.3	8.1	0.0	0.0	0.0	0.0	0.0	0.0
55°	118.7	48.5	37.8	29.7	5.4	0.0	0.0	0.0	0.0	0.0	0.0
57°	*132.1*	*48.5*	*40.5*	*32.4*	*2.7*	*0.0*	*0.0*	*0.0*	*0.0*	*0.0*	*0.0*
57.5°	132.1	51.2	40.5	32.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	153.7	59.3	45.8	35.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	169.9	67.4	53.9	32.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	180.7	70.1	59.3	27.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	188.8	72.8	62.0	24.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	186.1	78.2	62.0	18.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	183.4	91.7	56.6	16.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	161.8	105.2	48.5	13.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	137.5	102.5	45.8	8.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	78.2	80.9	37.8	2.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	18.9	29.7	21.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1390535
CATALOG NUMBER: GSS-SA5A-927-U-LBC

CANDELA DISTRIBUTION (continued):

	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°	285°
0°	32.4	32.4	32.4	32.4	32.4	32.4	32.4	32.4	32.4	32.4	32.4
2.5°	18.9	18.9	18.9	18.9	21.6	24.3	29.7	35.1	37.8	40.5	43.1
5°	16.2	13.5	13.5	13.5	16.2	18.9	24.3	32.4	35.1	37.8	40.5
7.5°	10.8	10.8	10.8	10.8	13.5	16.2	21.6	29.7	32.4	35.1	37.8
10°	8.1	8.1	8.1	8.1	8.1	13.5	18.9	27.0	29.7	32.4	37.8
12.5°	5.4	5.4	5.4	2.7	5.4	8.1	16.2	24.3	27.0	32.4	35.1
15°	2.7	0.0	0.0	0.0	2.7	5.4	13.5	21.6	27.0	29.7	35.1
17.5°	0.0	0.0	0.0	0.0	0.0	2.7	8.1	18.9	24.3	27.0	35.1
20°	0.0	0.0	0.0	0.0	0.0	0.0	5.4	16.2	18.9	24.3	29.7
22.5°	0.0	0.0	0.0	0.0	0.0	0.0	2.7	10.8	16.2	18.9	27.0
25°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	8.1	10.8	16.2	21.6
27.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	5.4	10.8	13.5	18.9
30°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	5.4	8.1	10.8	18.9
32.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.7	8.1	10.8	16.2
35°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.7	5.4	8.1	13.5
37.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.7	5.4	8.1	13.5
40°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	5.4	8.1	10.8
42.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.7	5.4	10.8
45°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.7	5.4	10.8
47.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.7	5.4	10.8
50°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.7	5.4	10.8
52.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.7	5.4	8.1
55°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.7	5.4	8.1
57°	*0.0*	*0.0*	*0.0*	*0.0*	*0.0*	*0.0*	*0.0*	*0.0*	*0.0*	*2.7*	*8.1*
57.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.7	5.4
60°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.7	5.4
62.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.7	5.4
65°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.7	5.4
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.7	5.4
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.7	5.4
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.7	5.4
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.7	8.1
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.7	2.7	8.1
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.7	5.4	8.1
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.7	5.4	8.1
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.7	8.1
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	2.7	8.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1390535
CATALOG NUMBER: GSS-SA5A-927-U-LBC

CANDELA DISTRIBUTION (continued):

	295°	305°	315°	325°	335°	345°	355°	360°
0°	32.4	32.4	32.4	32.4	32.4	32.4	32.4	32.4
2.5°	43.1	40.5	40.5	37.8	40.5	40.5	43.1	43.1
5°	40.5	37.8	37.8	37.8	37.8	43.1	45.8	45.8
7.5°	40.5	37.8	37.8	35.1	37.8	43.1	45.8	48.5
10°	40.5	37.8	35.1	35.1	37.8	43.1	48.5	51.2
12.5°	37.8	37.8	35.1	35.1	37.8	45.8	53.9	56.6
15°	37.8	37.8	35.1	35.1	40.5	45.8	56.6	62.0
17.5°	37.8	37.8	32.4	35.1	37.8	48.5	59.3	67.4
20°	35.1	37.8	32.4	32.4	37.8	48.5	62.0	72.8
22.5°	32.4	32.4	32.4	32.4	37.8	48.5	67.4	80.9
25°	29.7	29.7	29.7	32.4	40.5	51.2	72.8	91.7
27.5°	24.3	27.0	29.7	32.4	40.5	53.9	78.2	107.9
30°	21.6	27.0	29.7	32.4	40.5	53.9	86.3	137.5
32.5°	21.6	24.3	27.0	32.4	40.5	53.9	99.8	169.9
35°	18.9	24.3	27.0	32.4	40.5	56.6	107.9	172.6
37.5°	18.9	21.6	27.0	35.1	43.1	59.3	102.5	169.9
40°	16.2	21.6	27.0	35.1	43.1	62.0	97.1	172.6
42.5°	16.2	21.6	27.0	35.1	45.8	64.7	94.4	191.5
45°	16.2	21.6	29.7	35.1	45.8	62.0	94.4	264.3
47.5°	16.2	18.9	32.4	35.1	48.5	59.3	99.8	434.2
50°	13.5	18.9	29.7	35.1	48.5	56.6	102.5	590.6
52.5°	10.8	16.2	24.3	37.8	51.2	59.3	113.3	685.0
55°	10.8	13.5	21.6	43.1	51.2	59.3	142.9	695.8
57°	*8.1*	*10.8*	*18.9*	*48.5*	*53.9*	*62.0*	*151.0*	*663.4*
57.5°	8.1	10.8	18.9	51.2	53.9	64.7	153.7	649.9
60°	8.1	8.1	16.2	51.2	59.3	75.5	169.9	472.0
62.5°	8.1	8.1	16.2	45.8	67.4	83.6	180.7	383.0
65°	8.1	8.1	13.5	40.5	72.8	86.3	186.1	329.0
67.5°	8.1	8.1	13.5	37.8	72.8	91.7	188.8	299.4
70°	8.1	8.1	16.2	32.4	70.1	97.1	180.7	269.7
72.5°	8.1	8.1	13.5	29.7	67.4	110.6	172.6	240.0
75°	8.1	8.1	10.8	27.0	62.0	124.1	156.4	202.3
77.5°	8.1	8.1	8.1	24.3	59.3	118.7	129.4	129.4
80°	8.1	8.1	8.1	16.2	51.2	97.1	70.1	59.3
82.5°	8.1	8.1	5.4	10.8	32.4	35.1	27.0	24.3
85°	8.1	8.1	5.4	5.4	5.4	5.4	2.7	2.7
87.5°	8.1	8.1	5.4	2.7	2.7	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-13

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-927-U-5WQ

Data in this report applies to families of products including GSS-SB1A-927-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-13
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-927-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 90 CRI 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2731
CIE u':	0.2605
CIE v':	0.5298
Duv:	0.0021
CIE x:	0.4610
CIE y:	0.4166
CIE z:	0.1224
Peak Wavelength (nm):	622
Dominant Wavelength (nm):	583
Purity:	63.43685
Rf:	92.6
Rg:	98

CRI (Ra):	91.8				
R1:	91.4	R9:	54.7		
R2:	95.1	R10:	87.7		
R3:	97.6	R11:	92.9		
R4:	92.3	R12:	84.0		
R5:	91.1	R13:	92.2		
R6:	94.7	R14:	97.8		
R7:	92.3	R15:	86.8		
R8:	80.0				



Test Conditions


Stabilization Time:	M
Operation Time:	1H 0M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-13


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-13

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2731K
CIE x = 0.4610
CIE y = 0.4166
Duv = 0.0021

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-13

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	253	NR	620	997	NR	750	78	NR	880	2	NR
365	0	NR	495	285	NR	625	996	NR	755	67	NR	885	1	NR
370	0	NR	500	314	NR	630	989	NR	760	58	NR	890	1	NR
375	0	NR	505	343	NR	635	969	NR	765	50	NR	895	1	NR
380	0	NR	510	372	NR	640	939	NR	770	42	NR	900	1	NR
385	0	NR	515	401	NR	645	901	NR	775	36	NR	905	1	NR
390	0	NR	520	431	NR	650	858	NR	780	31	NR	910	1	NR
395	0	NR	525	459	NR	655	806	NR	785	26	NR	915	1	NR
400	0	NR	530	488	NR	660	752	NR	790	23	NR	920	1	NR
405	2	NR	535	516	NR	665	696	NR	795	19	NR	925	1	NR
410	5	NR	540	540	NR	670	636	NR	800	17	NR	930	0	NR
415	10	NR	545	566	NR	675	579	NR	805	14	NR	935	0	NR
420	19	NR	550	589	NR	680	524	NR	810	12	NR	940	0	NR
425	34	NR	555	612	NR	685	470	NR	815	11	NR	945	0	NR
430	61	NR	560	634	NR	690	421	NR	820	9	NR	950	0	NR
435	113	NR	565	660	NR	695	371	NR	825	8	NR	955	0	NR
440	198	NR	570	688	NR	700	327	NR	830	7	NR	960	0	NR
445	288	NR	575	719	NR	705	288	NR	835	6	NR	965	0	NR
450	286	NR	580	754	NR	710	251	NR	840	5	NR	970	0	NR
455	228	NR	585	791	NR	715	220	NR	845	4	NR	975	0	NR
460	207	NR	590	831	NR	720	192	NR	850	4	NR	980	0	NR
465	186	NR	595	870	NR	725	166	NR	855	3	NR	985	0	NR
470	168	NR	600	907	NR	730	144	NR	860	3	NR	990	1	NR
475	177	NR	605	940	NR	735	124	NR	865	2	NR	995	1	NR
480	198	NR	610	967	NR	740	106	NR	870	2	NR	1000	0	NR
485	223	NR	615	988	NR	745	91	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-13

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.27**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	253	NR	620	997	NR	750	78	NR	880	2	NR
365	0	NR	495	285	NR	625	996	NR	755	67	NR	885	1	NR
370	0	NR	500	314	NR	630	989	NR	760	58	NR	890	1	NR
375	0	NR	505	343	NR	635	969	NR	765	50	NR	895	1	NR
380	0	NR	510	372	NR	640	939	NR	770	42	NR	900	1	NR
385	0	NR	515	401	NR	645	901	NR	775	36	NR	905	1	NR
390	0	NR	520	431	NR	650	858	NR	780	31	NR	910	1	NR
395	0	NR	525	459	NR	655	806	NR	785	26	NR	915	1	NR
400	0	NR	530	488	NR	660	752	NR	790	23	NR	920	1	NR
405	2	NR	535	516	NR	665	696	NR	795	19	NR	925	1	NR
410	5	NR	540	540	NR	670	636	NR	800	17	NR	930	0	NR
415	10	NR	545	566	NR	675	579	NR	805	14	NR	935	0	NR
420	19	NR	550	589	NR	680	524	NR	810	12	NR	940	0	NR
425	34	NR	555	612	NR	685	470	NR	815	11	NR	945	0	NR
430	61	NR	560	634	NR	690	421	NR	820	9	NR	950	0	NR
435	113	NR	565	660	NR	695	371	NR	825	8	NR	955	0	NR
440	198	NR	570	688	NR	700	327	NR	830	7	NR	960	0	NR
445	288	NR	575	719	NR	705	288	NR	835	6	NR	965	0	NR
450	286	NR	580	754	NR	710	251	NR	840	5	NR	970	0	NR
455	228	NR	585	791	NR	715	220	NR	845	4	NR	975	0	NR
460	207	NR	590	831	NR	720	192	NR	850	4	NR	980	0	NR
465	186	NR	595	870	NR	725	166	NR	855	3	NR	985	0	NR
470	168	NR	600	907	NR	730	144	NR	860	3	NR	990	1	NR
475	177	NR	605	940	NR	735	124	NR	865	2	NR	995	1	NR
480	198	NR	610	967	NR	740	106	NR	870	2	NR	1000	0	NR
485	223	NR	615	988	NR	745	91	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-13

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.38**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	253	NR	620	997	NR	750	78	NR	880	2	NR
365	0	NR	495	285	NR	625	996	NR	755	67	NR	885	1	NR
370	0	NR	500	314	NR	630	989	NR	760	58	NR	890	1	NR
375	0	NR	505	343	NR	635	969	NR	765	50	NR	895	1	NR
380	0	NR	510	372	NR	640	939	NR	770	42	NR	900	1	NR
385	0	NR	515	401	NR	645	901	NR	775	36	NR	905	1	NR
390	0	NR	520	431	NR	650	858	NR	780	31	NR	910	1	NR
395	0	NR	525	459	NR	655	806	NR	785	26	NR	915	1	NR
400	0	NR	530	488	NR	660	752	NR	790	23	NR	920	1	NR
405	2	NR	535	516	NR	665	696	NR	795	19	NR	925	1	NR
410	5	NR	540	540	NR	670	636	NR	800	17	NR	930	0	NR
415	10	NR	545	566	NR	675	579	NR	805	14	NR	935	0	NR
420	19	NR	550	589	NR	680	524	NR	810	12	NR	940	0	NR
425	34	NR	555	612	NR	685	470	NR	815	11	NR	945	0	NR
430	61	NR	560	634	NR	690	421	NR	820	9	NR	950	0	NR
435	113	NR	565	660	NR	695	371	NR	825	8	NR	955	0	NR
440	198	NR	570	688	NR	700	327	NR	830	7	NR	960	0	NR
445	288	NR	575	719	NR	705	288	NR	835	6	NR	965	0	NR
450	286	NR	580	754	NR	710	251	NR	840	5	NR	970	0	NR
455	228	NR	585	791	NR	715	220	NR	845	4	NR	975	0	NR
460	207	NR	590	831	NR	720	192	NR	850	4	NR	980	0	NR
465	186	NR	595	870	NR	725	166	NR	855	3	NR	985	0	NR
470	168	NR	600	907	NR	730	144	NR	860	3	NR	990	1	NR
475	177	NR	605	940	NR	735	124	NR	865	2	NR	995	1	NR
480	198	NR	610	967	NR	740	106	NR	870	2	NR	1000	0	NR
485	223	NR	615	988	NR	745	91	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-13

TM-30-18


Summary


R_f = 92.6
R_g = 98
CIE R_a = 91.8
R_9 = 54.7


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-13

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 94	CES51 = 98	CES76 = 90
CES02 = 64	CES27 = 95	CES52 = 98	CES77 = 90
CES03 = 32	CES28 = 97	CES53 = 96	CES78 = 89
CES04 = 71	CES29 = 95	CES54 = 96	CES79 = 93
CES05 = 51	CES30 = 98	CES55 = 95	CES80 = 94
CES06 = 52	CES31 = 96	CES56 = 94	CES81 = 82
CES07 = 44	CES32 = 91	CES57 = 94	CES82 = 97
CES08 = 43	CES33 = 97	CES58 = 94	CES83 = 96
CES09 = 29	CES34 = 96	CES59 = 96	CES84 = 96
CES10 = 77	CES35 = 98	CES60 = 96	CES85 = 85
CES11 = 59	CES36 = 90	CES61 = 94	CES86 = 82
CES12 = 66	CES37 = 95	CES62 = 95	CES87 = 93
CES13 = 44	CES38 = 96	CES63 = 94	CES88 = 95
CES14 = 74	CES39 = 99	CES64 = 92	CES89 = 85
CES15 = 72	CES40 = 98	CES65 = 89	CES90 = 96
CES16 = 48	CES41 = 98	CES66 = 91	CES91 = 85
CES17 = 50	CES42 = 97	CES67 = 90	CES92 = 82
CES18 = 57	CES43 = 97	CES68 = 91	CES93 = 89
CES19 = 72	CES44 = 99	CES69 = 93	CES94 = 79
CES20 = 68	CES45 = 99	CES70 = 90	CES95 = 87
CES21 = 87	CES46 = 96	CES71 = 89	CES96 = 92
CES22 = 79	CES47 = 94	CES72 = 96	CES97 = 96
CES23 = 92	CES48 = 93	CES73 = 87	CES98 = 93
CES24 = 91	CES49 = 96	CES74 = 92	CES99 = 90
CES25 = 72	CES50 = 98	CES75 = 90	





REPORT NUMBER: SP1-2407-184-13

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-13

TM-30-18

Measure Comparisons





(END OF REPORT)