Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360691

Luminaire Tested: **GSS-SB2A-722-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360691
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB2A-722-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 2SQUARE 58W 70CRI 2200K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(52) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	6788.2 lumens
Efficiency:	N/A
Efficacy:	117.0 lumens/watt
Luminous Opening:	Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B3 - U0 - G3


Input Watts (W):	58
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	9.0%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360691
CATALOG NUMBER: GSS-SB2A-722-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 3.3 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360691
CATALOG NUMBER: GSS-SB2A-722-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360691
CATALOG NUMBER: GSS-SB2A-722-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3394.1	0.0	3394.1
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	3394.1	0.0	3394.1
	% Fixture	50.0	0.0	50.0
Total	Lumens	6788.2	0.0	6788.2
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.5	1.9
10°-20°	394.6	5.8
20°-30°	659.5	9.7
30°-40°	909.4	13.4
40°-50°	1114.9	16.4
50°-60°	1306.5	19.2
60°-70°	1450.8	21.4
70°-80°	788.9	11.6
80°-90°	34.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6788.2	100.0
0°-180°	6788.2	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360691
CATALOG NUMBER: GSS-SB2A-722-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	591.7	8.7			
FM	(30°-60°)	1665.4	24.5			
FH	(60°-80°)	1119.9	16.5			G1/1800
FVH	(80°-90°)	17.1	0.3			G1/100
BL	(0°-30°)	591.7	8.7	B2/1000		
BM	(30°-60°)	1665.4	24.5	B2/2500		
BH	(60°-80°)	1119.9	16.5	B3/2500		G3/2500
BVH	(80°-90°)	17.1	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360691
CATALOG NUMBER: GSS-SB2A-722-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	1337.4	1337.4	1337.4	1337.4	1337.4	1337.4	1337.4	1337.4	1337.4	1337.4	1337.4
2.5°	1338.9	1338.9	1334.5	1340.4	1337.4	1338.9	1340.4	1338.9	1337.4	1338.9	1340.4
5°	1346.4	1343.4	1346.4	1349.3	1344.9	1347.8	1346.4	1338.9	1343.4	1343.4	1343.4
7.5°	1359.7	1362.7	1359.7	1367.2	1362.7	1371.6	1362.7	1356.8	1355.3	1353.8	1353.8
10°	1365.7	1365.7	1364.2	1377.6	1380.5	1389.4	1383.5	1374.6	1370.1	1364.2	1358.2
12.5°	1349.3	1352.3	1359.7	1385.0	1396.9	1414.7	1410.3	1392.4	1379.0	1374.6	1365.7
15°	1331.5	1334.5	1349.3	1380.5	1408.8	1435.5	1434.0	1411.7	1395.4	1383.5	1370.1
17.5°	1303.3	1307.7	1328.5	1376.1	1426.6	1456.3	1465.2	1442.9	1425.1	1405.8	1388.0
20°	1255.7	1255.7	1292.9	1353.8	1423.6	1490.5	1514.3	1496.4	1475.6	1444.4	1420.7
22.5°	1202.2	1205.2	1242.3	1322.6	1422.1	1520.2	1566.3	1547.0	1526.2	1492.0	1456.3
25°	1148.7	1148.7	1190.3	1281.0	1402.8	1541.0	1627.2	1616.8	1575.2	1544.0	1497.9
27.5°	1099.7	1099.7	1144.3	1239.4	1370.1	1547.0	1688.1	1688.1	1642.1	1596.0	1545.5
30°	1041.7	1056.6	1107.1	1206.7	1340.4	1536.6	1732.7	1761.0	1719.3	1659.9	1585.6
32.5°	992.7	1003.1	1055.1	1160.6	1297.3	1524.7	1783.2	1853.1	1810.0	1728.3	1645.0
35°	934.7	933.2	992.7	1096.7	1236.4	1497.9	1823.4	1963.1	1921.5	1833.8	1720.8
37.5°	858.9	858.9	919.9	1020.9	1178.4	1451.9	1856.1	2084.9	2053.7	1954.1	1833.8
40°	777.2	786.1	839.6	942.1	1108.6	1396.9	1856.1	2184.5	2200.8	2098.3	1973.5
42.5°	717.8	720.7	769.8	866.4	1031.3	1325.5	1832.3	2270.7	2319.7	2233.5	2071.5
45°	655.3	662.8	704.4	793.5	951.1	1240.8	1790.7	2367.3	2446.0	2386.6	2174.1
47.5°	579.6	587.0	634.5	725.2	875.3	1148.7	1720.8	2468.3	2633.3	2590.2	2356.9
50°	491.9	497.8	542.4	639.0	790.6	1043.2	1633.2	2544.1	2820.5	2863.6	2633.3
52.5°	384.9	389.3	436.9	530.5	689.5	942.1	1509.8	2590.2	3009.2	3160.8	3003.3
55°	276.4	283.8	325.4	402.7	555.8	806.9	1362.7	2613.9	3215.8	3513.0	3462.5
57.5°	199.1	202.1	230.3	289.8	413.1	647.9	1174.0	2573.8	3401.5	3933.5	4039.1
60°	165.0	165.0	169.4	197.6	282.3	457.7	948.1	2425.2	3560.6	4358.6	4684.0
62.5°	151.6	151.6	154.5	159.0	185.8	297.2	677.6	2123.6	3578.4	4767.2	5391.4
65°	138.2	138.2	141.2	144.1	150.1	193.2	408.7	1554.4	3229.2	4771.7	5771.8
67.5°	126.3	126.3	127.8	129.3	132.3	141.2	224.4	942.1	2584.2	4645.4	5917.4
70°	114.4	114.4	114.4	112.9	117.4	118.9	148.6	478.5	1728.3	4195.1	5847.6
72.5°	*101.1*	*101.1*	*99.6*	*96.6*	*98.1*	*98.1*	*110.0*	*234.8*	*897.6*	*3334.7*	*5279.9*
75°	86.2	87.7	81.7	78.8	77.3	78.8	87.7	133.7	401.2	2022.5	3945.4
77.5°	72.8	75.8	66.9	60.9	59.4	59.4	68.4	83.2	172.4	734.1	1768.4
80°	55.0	56.5	49.0	43.1	43.1	41.6	50.5	60.9	81.7	218.4	396.8
82.5°	31.2	31.2	28.2	25.3	23.8	25.3	34.2	41.6	50.5	77.3	108.5
85°	7.4	7.4	8.9	10.4	10.4	13.4	19.3	22.3	26.7	31.2	41.6
87.5°	1.5	1.5	1.5	3.0	4.5	4.5	7.4	10.4	13.4	16.3	17.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360691
CATALOG NUMBER: GSS-SB2A-722-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	1337.4	1337.4	*1337.4*
2.5°	1340.4	1341.9	*1340.4*
5°	1349.3	1346.4	*1341.9*
7.5°	1350.8	1352.3	*1353.8*
10°	1356.8	1362.7	*1353.8*
12.5°	1362.7	1358.2	*1355.3*
15°	1367.2	1365.7	*1356.8*
17.5°	1383.5	1377.6	*1376.1*
20°	1408.8	1407.3	*1402.8*
22.5°	1438.5	1435.5	*1434.0*
25°	1481.6	1471.2	*1465.2*
27.5°	1517.2	1508.3	*1505.4*
30°	1552.9	1535.1	*1535.1*
32.5°	1584.1	1579.7	*1576.7*
35°	1658.4	1636.1	*1639.1*
37.5°	1749.1	1726.8	*1707.5*
40°	1876.9	1847.1	*1835.3*
42.5°	1958.6	1928.9	*1931.9*
45°	2004.7	1952.7	*1939.3*
47.5°	2129.5	2064.1	*2046.3*
50°	2331.6	2251.4	*2229.1*
52.5°	2658.5	2529.2	*2499.5*
55°	3068.7	2909.7	*2879.9*
57.5°	3630.4	3419.4	*3355.5*
60°	4314.0	4052.4	*3955.8*
62.5°	5135.8	4813.3	*4721.2*
65°	5753.9	5485.0	*5342.3*
67.5°	6248.8	6027.4	*5959.0*
70°	6543.0	6553.4	*6571.3*
72.5°	*6202.7*	*6488.1*	*6624.8*
75°	4545.8	4767.2	*4979.7*
77.5°	1756.5	1584.1	*1533.6*
80°	283.8	266.0	*274.9*
82.5°	127.8	135.2	*142.7*
85°	83.2	96.6	*102.5*
87.5°	19.3	19.3	*19.3*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)