

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P991110

Luminaire Tested: **GPC-SA2B-735-U-T2BC**

Issue Date: 07/03/2025

Test Information

Test Method: LM-79-08
Report Number: P991110
Test Lab: INNOVATION CENTER(G1)
Issue Date: 07/03/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GPC-SA2B-735-U-T2BC
Description: GALLEON PEDESTRAIAN COMPANION 800mA 2xLight Square PACKAGE 70CRI
3500K FIXTURE w/ TYPE II ANGLED BACKLIGHT CONTROL
Light Source: (28) 3500K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8017.3 lumens
Efficiency: N/A
Efficacy: 111.0 lumens/watt
Luminous Opening: Rectangular (W 1.33' x L: 0.67' x H: 0')
IES Classification: Type II - Short
BUG Rating: B0 - U0 - G2

Input Watts (W): 72.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P991110

CATALOG NUMBER: GPC-SA2B-735-U-T2BC

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 6.5 fc
 Type II - Short - N/A

REPORT NUMBER: P991110
CATALOG NUMBER: GPC-SA2B-735-U-T2BC

Luminous Intensity Polar Plot



REPORT NUMBER: P991110

CATALOG NUMBER: GPC-SA2B-735-U-T2BC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	35.7	0.0	35.7
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	7981.6	0.0	7981.6
	% Fixture	99.6	0.0	99.6
Total	Lumens	8017.3	0.0	8017.3
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	10.6	0.1
10°-20°	88.5	1.1
20°-30°	271.4	3.4
30°-40°	705.2	8.8
40°-50°	1775.4	22.1
50°-60°	2573.7	32.1
60°-70°	1985.0	24.8
70°-80°	547.6	6.8
80°-90°	59.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8017.3	100.0
0°-180°	8017.3	100.0



REPORT NUMBER: P991110


CATALOG NUMBER: GPC-SA2B-735-U-T2BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	363.9	4.5			
FM	(30°-60°)	5042.6	62.9			
FH	(60°-80°)	2516.7	31.4			G2/5000
FVH	(80°-90°)	58.3	0.7			G1/100
BL	(0°-30°)	6.6	0.1	B0/110		
BM	(30°-60°)	11.7	0.1	B0/220		
BH	(60°-80°)	16.0	0.2	B0/110		G0/110
BVH	(80°-90°)	1.4	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type II Short



REPORT NUMBER: P991110

CATALOG NUMBER: GPC-SA2B-735-U-T2BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	66°	75°	85°
0°	57.6	57.6	57.6	57.6	57.6	57.6	57.6	57.6	57.6	57.6	57.6
2.5°	92.4	92.4	90.9	87.9	80.3	75.8	71.2	66.7	65.1	62.1	59.1
5°	168.2	165.1	163.6	148.5	133.3	115.1	97.0	81.8	80.3	69.7	60.6
7.5°	353.0	353.0	322.7	286.3	245.4	189.4	139.4	107.6	103.0	80.3	62.1
10°	577.2	578.7	559.0	501.5	427.2	333.3	225.7	139.4	136.4	93.9	63.6
12.5°	778.7	777.2	757.5	716.6	634.8	516.6	354.5	201.5	189.4	109.1	63.6
15°	907.5	907.5	904.5	883.3	825.7	704.5	525.7	295.4	281.8	131.8	65.1
17.5°	1033.2	1040.8	1030.2	1021.1	978.7	887.8	704.5	425.7	398.4	168.2	68.2
20°	1184.7	1192.3	1187.8	1174.1	1121.1	1040.8	883.3	575.7	548.4	228.8	74.2
22.5°	1360.5	1366.5	1357.5	1352.9	1286.2	1184.7	1048.4	756.0	715.1	306.0	81.8
25°	1577.1	1572.6	1569.6	1543.8	1478.7	1368.1	1204.4	922.6	890.8	409.1	92.4
27.5°	1831.7	1825.6	1805.9	1772.6	1677.1	1555.9	1371.1	1099.9	1069.6	533.3	107.6
30°	2175.6	2139.2	2110.4	2036.2	1908.9	1748.3	1557.4	1274.1	1240.8	681.8	124.2
32.5°	2660.4	2649.8	2537.7	2343.7	2160.4	1968.0	1765.0	1459.0	1424.1	834.8	147.0
35°	3530.0	3480.0	3284.6	2796.7	2452.8	2243.7	1975.6	1643.8	1607.4	1012.0	177.3
37.5°	4507.2	4463.2	4273.9	3686.0	2896.7	2528.6	2210.4	1852.9	1813.5	1206.0	215.1
40°	5487.4	5473.8	5402.5	4932.9	3796.6	2908.8	2521.0	2119.5	2074.1	1401.4	268.2
42.5°	6590.3	6550.9	6505.5	6346.4	5351.0	3670.9	2952.8	2424.0	2384.6	1642.3	343.9
45°	6940.3	6925.1	6979.7	7132.7	6979.7	5267.7	3622.4	2839.1	2799.7	1951.3	453.0
47.5°	6822.1	6807.0	6957.0	7208.4	7558.4	7184.2	4660.2	3434.5	3361.8	2321.0	615.1
50°	6225.2	6231.3	6496.4	6999.4	7500.8	7947.8	6393.4	4226.9	4176.9	2846.7	833.3
52.5°	5660.1	5670.7	6002.5	6646.4	7197.8	7976.6	8046.2	5379.8	5164.7	3490.6	1102.9
55°	5110.1	5095.0	5346.5	6316.1	7143.3	7582.7	8565.9	6732.7	6591.8	4325.4	1368.1
57.5°	4528.4	4510.2	4642.0	5363.2	7029.7	7637.2	8429.5	8325.0	8156.8	5284.4	1581.7
60°	3473.9	3433.0	3693.6	4245.1	6152.5	7703.9	8159.9	8909.8	8899.2	6569.1	1689.2
62.5°	1665.0	1731.7	2084.7	2683.1	4113.3	7113.0	8264.4	8693.2	8714.4	7702.3	1937.7
65°	849.9	865.1	1046.9	1465.0	2177.1	5113.2	7962.9	8393.2	8361.4	7481.1	2581.6
67.5°	572.7	580.3	665.1	886.3	1263.5	2142.2	6187.3	7853.8	7831.1	6376.7	2964.9
70°	507.5	510.6	531.8	603.0	757.5	943.9	2833.1	6590.3	6760.0	4870.8	2707.3
72.5°	496.9	496.9	493.9	498.4	489.4	512.1	993.9	3967.8	4214.8	3402.7	2193.7
75°	486.3	487.8	483.3	468.1	380.3	319.7	363.6	1671.1	1852.9	2239.2	1643.8
77.5°	454.5	457.5	471.2	433.3	345.4	225.7	207.6	530.3	619.6	1430.2	1204.4
80°	171.2	171.2	171.2	157.6	230.3	171.2	150.0	216.6	230.3	806.0	740.8
82.5°	125.7	124.2	118.2	109.1	92.4	86.4	122.7	163.6	163.6	377.2	281.8
85°	36.4	36.4	40.9	54.5	68.2	75.8	93.9	125.7	130.3	143.9	42.4
87.5°	16.7	16.7	21.2	27.3	36.4	54.5	78.8	107.6	109.1	119.7	7.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P991110

CATALOG NUMBER: GPC-SA2B-735-U-T2BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	57.6	57.6	57.6	57.6	57.6	57.6	57.6	57.6	57.6	57.6	57.6
2.5°	57.6	56.1	54.5	53.0	50.0	47.0	42.4	40.9	39.4	39.4	39.4
5°	57.6	54.5	50.0	45.5	42.4	37.9	34.8	33.3	31.8	30.3	30.3
7.5°	56.1	51.5	45.5	40.9	37.9	33.3	28.8	27.3	25.8	25.8	25.8
10°	56.1	50.0	42.4	37.9	33.3	27.3	22.7	21.2	19.7	18.2	18.2
12.5°	53.0	47.0	39.4	33.3	27.3	21.2	16.7	13.6	12.1	12.1	12.1
15°	51.5	45.5	36.4	28.8	21.2	15.2	10.6	7.6	6.1	7.6	7.6
17.5°	50.0	40.9	33.3	22.7	15.2	9.1	4.5	1.5	1.5	1.5	1.5
20°	50.0	39.4	28.8	18.2	10.6	4.5	1.5	0.0	0.0	0.0	0.0
22.5°	51.5	39.4	25.8	15.2	6.1	3.0	0.0	0.0	0.0	0.0	0.0
25°	53.0	37.9	22.7	10.6	4.5	1.5	0.0	0.0	0.0	0.0	0.0
27.5°	54.5	36.4	19.7	7.6	3.0	0.0	0.0	0.0	0.0	0.0	0.0
30°	57.6	34.8	16.7	6.1	1.5	0.0	0.0	0.0	0.0	0.0	0.0
32.5°	62.1	33.3	13.6	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
35°	66.7	30.3	9.1	1.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	72.7	30.3	6.1	1.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40°	81.8	30.3	6.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	97.0	31.8	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	125.7	40.9	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	178.8	62.1	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	253.0	89.4	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	316.6	93.9	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	328.8	66.7	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	283.3	54.5	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	243.9	36.4	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	293.9	30.3	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	468.1	28.8	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	728.7	28.8	4.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	816.6	28.8	4.5	1.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	631.8	22.7	4.5	1.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	396.9	18.2	4.5	3.0	1.5	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	216.6	12.1	4.5	3.0	1.5	0.0	0.0	0.0	0.0	0.0	0.0
80°	81.8	9.1	4.5	3.0	3.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	28.8	7.6	6.1	4.5	3.0	1.5	0.0	0.0	0.0	0.0	0.0
85°	10.6	6.1	6.1	4.5	4.5	1.5	0.0	0.0	0.0	0.0	0.0
87.5°	6.1	6.1	6.1	6.1	4.5	1.5	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-5

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-735-U-5WQ

Data in this report applies to families of products including GSS-SB1A-735-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-5
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-735-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3500K CCT 26 LEDS

Spectral Parameters

CCT (K):	3369	CRI (Ra):	70.1		
CIE u':	0.2386	R1:	66.6	R9:	-40.2
CIE v':	0.5156	R2:	77.6	R10:	49.1
Duv:	0.0013	R3:	88.5	R11:	66.3
CIE x:	0.4143	R4:	69.5	R12:	45.7
CIE y:	0.3980	R5:	66.4	R13:	68.0
CIE z:	0.1877	R6:	69.6	R14:	93.4
Peak Wavelength (nm):	590	R7:	77.5	R15:	57.6
Dominant Wavelength (nm):	580	R8:	44.9		
Purity:	43.80166				
Rf:	71.4				
Rg:	96				



Test Conditions

Stabilization Time: 21M
 Operation Time: 1H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-5

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-5

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Scotopic Flux vs. Wavelength


Scotopic Lumens: NR
S/P: 1.29

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.36

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

TM-30-18

Summary

$R_f = 71.4$
 $R_g = 96$
 CIE $R_a = 70.1$
 $R_g = -40.2$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 57	CES51 = 84	CES76 = 50
CES02 = 62	CES27 = 80	CES52 = 86	CES77 = 74
CES03 = 31	CES28 = 81	CES53 = 72	CES78 = 54
CES04 = 70	CES29 = 50	CES54 = 79	CES79 = 81
CES05 = 48	CES30 = 55	CES55 = 78	CES80 = 79
CES06 = 51	CES31 = 56	CES56 = 67	CES81 = 74
CES07 = 40	CES32 = 54	CES57 = 65	CES82 = 91
CES08 = 39	CES33 = 60	CES58 = 68	CES83 = 86
CES09 = 29	CES34 = 69	CES59 = 85	CES84 = 89
CES10 = 75	CES35 = 83	CES60 = 91	CES85 = 83
CES11 = 58	CES36 = 88	CES61 = 85	CES86 = 66
CES12 = 64	CES37 = 78	CES62 = 78	CES87 = 77
CES13 = 43	CES38 = 64	CES63 = 71	CES88 = 75
CES14 = 74	CES39 = 92	CES64 = 70	CES89 = 68
CES15 = 71	CES40 = 86	CES65 = 64	CES90 = 72
CES16 = 47	CES41 = 81	CES66 = 65	CES91 = 95
CES17 = 50	CES42 = 79	CES67 = 63	CES92 = 62
CES18 = 56	CES43 = 71	CES68 = 69	CES93 = 78
CES19 = 72	CES44 = 98	CES69 = 80	CES94 = 51
CES20 = 65	CES45 = 80	CES70 = 60	CES95 = 70
CES21 = 87	CES46 = 75	CES71 = 58	CES96 = 76
CES22 = 79	CES47 = 71	CES72 = 85	CES97 = 82
CES23 = 92	CES48 = 61	CES73 = 51	CES98 = 72
CES24 = 91	CES49 = 74	CES74 = 94	CES99 = 60
CES25 = 72	CES50 = 83	CES75 = 57	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)