

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P991264

Luminaire Tested: **GPC-SA1D-750-U-RBC**

Issue Date: 07/03/2025

Test Information

Test Method: LM-79-08
Report Number: P991264
Test Lab: INNOVATION CENTER(G1)
Issue Date: 07/03/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GPC-SA1D-750-U-RBC
Description: GALLEON PEDESTRAIAN COMPANION 1200mA 1xLight Square PACKAGE 70CRI
5000K FIXTURE w/ RIGHT CORNER BACKLIGHT CONTROL
Light Source: (14) 5000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5474.6 lumens
Efficiency: N/A
Efficacy: 97.6 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 0.67' x H: 0')
IES Classification: Type III - Short
BUG Rating: B0 - U0 - G2

Input Watts (W): 56.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P991264

CATALOG NUMBER: GPC-SA1D-750-U-RBC

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 0.4 fc
 Type III - Short - N/A

REPORT NUMBER: P991264

CATALOG NUMBER: GPC-SA1D-750-U-RBC

Luminous Intensity Polar Plot



REPORT NUMBER: P991264

CATALOG NUMBER: GPC-SA1D-750-U-RBC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	24.5	0.0	24.5
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	5450.1	0.0	5450.1
	% Fixture	99.6	0.0	99.6
Total	Lumens	5474.6	0.0	5474.6
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.8	0.0
10°-20°	9.5	0.2
20°-30°	138.3	2.5
30°-40°	397.5	7.3
40°-50°	1132.2	20.7
50°-60°	1780.9	32.5
60°-70°	1518.7	27.7
70°-80°	484.4	8.8
80°-90°	12.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5474.6	100.0
0°-180°	5474.6	100.0



REPORT NUMBER: P991264


CATALOG NUMBER: GPC-SA1D-750-U-RBC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	147.6	2.7			
FM	(30°-60°)	3297.5	60.2			
FH	(60°-80°)	1993.4	36.4			G2/5000
FVH	(80°-90°)	11.7	0.2			G1/100
BL	(0°-30°)	1.0	0.0	B0/110		
BM	(30°-60°)	13.1	0.2	B0/220		
BH	(60°-80°)	9.7	0.2	B0/110		G0/110
BVH	(80°-90°)	0.7	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type III Short





REPORT NUMBER: P991264

CATALOG NUMBER: GPC-SA1D-750-U-RBC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	47°	55°	65°	75°	85°
0°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
2.5°	19.7	20.8	21.9	20.8	18.6	14.2	14.2	11.0	7.7	4.4	3.3
5°	21.9	21.9	21.9	20.8	18.6	14.2	13.1	9.9	6.6	4.4	2.2
7.5°	24.1	24.1	23.0	20.8	17.5	14.2	13.1	9.9	6.6	3.3	0.0
10°	26.3	26.3	24.1	21.9	17.5	13.1	12.1	8.8	5.5	2.2	0.0
12.5°	29.6	28.5	25.2	21.9	17.5	12.1	12.1	8.8	4.4	1.1	0.0
15°	34.0	30.7	26.3	21.9	16.4	12.1	11.0	7.7	3.3	0.0	0.0
17.5°	37.3	34.0	27.4	20.8	15.3	11.0	9.9	6.6	3.3	0.0	0.0
20°	40.5	35.1	27.4	20.8	15.3	9.9	8.8	5.5	1.1	0.0	0.0
22.5°	46.0	37.3	27.4	20.8	14.2	8.8	7.7	4.4	0.0	0.0	0.0
25°	57.0	39.4	27.4	19.7	13.1	7.7	6.6	2.2	0.0	0.0	0.0
27.5°	70.1	42.7	27.4	18.6	12.1	6.6	5.5	1.1	0.0	0.0	0.0
30°	84.4	46.0	27.4	18.6	11.0	5.5	4.4	0.0	0.0	0.0	0.0
32.5°	99.7	50.4	27.4	17.5	9.9	4.4	3.3	0.0	0.0	0.0	0.0
35°	128.2	57.0	27.4	17.5	8.8	3.3	2.2	0.0	0.0	0.0	0.0
37.5°	141.3	65.7	27.4	16.4	8.8	2.2	1.1	0.0	0.0	0.0	0.0
40°	146.8	63.5	26.3	16.4	7.7	1.1	0.0	0.0	0.0	0.0	0.0
42.5°	158.9	59.2	27.4	15.3	7.7	1.1	0.0	0.0	0.0	0.0	0.0
45°	193.9	59.2	29.6	15.3	6.6	2.2	0.0	0.0	0.0	0.0	0.0
47.5°	336.4	61.4	28.5	15.3	6.6	2.2	0.0	0.0	0.0	0.0	0.0
50°	553.3	72.3	27.4	16.4	7.7	1.1	0.0	0.0	0.0	0.0	0.0
52.5°	642.0	87.7	27.4	17.5	9.9	0.0	0.0	0.0	0.0	0.0	0.0
55°	615.7	107.4	27.4	18.6	12.1	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	559.9	101.9	29.6	21.9	15.3	0.0	0.0	0.0	0.0	0.0	0.0
58°	539.1	101.9	29.6	21.9	15.3	0.0	0.0	0.0	0.0	0.0	0.0
60°	422.9	104.1	34.0	24.1	16.4	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	314.4	106.3	38.3	27.4	16.4	1.1	0.0	0.0	0.0	0.0	0.0
65°	233.4	110.7	40.5	31.8	15.3	2.2	0.0	0.0	0.0	0.0	0.0
67.5°	186.3	113.9	43.8	35.1	17.5	4.4	1.1	0.0	0.0	0.0	0.0
70°	160.0	109.6	47.1	36.2	16.4	6.6	3.3	0.0	0.0	0.0	0.0
72.5°	142.4	103.0	53.7	35.1	17.5	6.6	3.3	0.0	0.0	0.0	0.0
75°	128.2	94.2	61.4	34.0	17.5	6.6	4.4	0.0	0.0	0.0	0.0
77.5°	96.4	82.2	60.3	32.9	16.4	6.6	4.4	0.0	0.0	0.0	0.0
80°	48.2	54.8	52.6	29.6	13.1	5.5	4.4	1.1	0.0	0.0	0.0
82.5°	19.7	20.8	26.3	21.9	11.0	4.4	4.4	1.1	0.0	0.0	0.0
85°	2.2	4.4	7.7	8.8	7.7	4.4	4.4	1.1	0.0	0.0	0.0
87.5°	0.0	1.1	4.4	6.6	5.5	3.3	2.2	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P991264

CATALOG NUMBER: GPC-SA1D-750-U-RBC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
2.5°	2.2	2.2	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
5°	1.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
58°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P991264

CATALOG NUMBER: GPC-SA1D-750-U-RBC

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
2.5°	1.1	2.2	2.2	2.2	3.3	3.3	4.4	5.5	5.5	5.5	6.6
5°	0.0	0.0	1.1	1.1	2.2	3.3	4.4	6.6	7.7	7.7	8.8
7.5°	0.0	0.0	0.0	1.1	2.2	3.3	4.4	6.6	8.8	9.9	11.0
10°	0.0	0.0	0.0	0.0	1.1	2.2	4.4	7.7	11.0	13.1	15.3
12.5°	0.0	0.0	0.0	0.0	0.0	1.1	4.4	8.8	13.1	16.4	18.6
15°	0.0	0.0	0.0	0.0	0.0	1.1	4.4	8.8	16.4	19.7	24.1
17.5°	0.0	0.0	0.0	0.0	0.0	0.0	4.4	9.9	18.6	24.1	32.9
20°	0.0	0.0	0.0	0.0	0.0	0.0	3.3	9.9	20.8	29.6	49.3
22.5°	0.0	0.0	0.0	0.0	0.0	0.0	3.3	9.9	23.0	38.3	90.9
25°	0.0	0.0	0.0	0.0	0.0	0.0	2.2	9.9	26.3	57.0	151.2
27.5°	0.0	0.0	0.0	0.0	0.0	0.0	2.2	11.0	31.8	80.0	221.3
30°	0.0	0.0	0.0	0.0	0.0	0.0	2.2	11.0	39.4	108.5	309.0
32.5°	0.0	0.0	0.0	0.0	0.0	0.0	1.1	11.0	46.0	137.0	420.7
35°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	9.9	54.8	181.9	528.1
37.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	9.9	67.9	200.5	619.0
40°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	8.8	64.6	218.0	723.1
42.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	9.9	59.2	243.2	886.4
45°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	9.9	59.2	322.1	1247.9
47.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	8.8	72.3	501.8	1907.5
50°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	6.6	93.1	770.2	2716.1
52.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	5.5	112.9	947.7	3185.0
55°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	5.5	135.9	948.8	3169.7
57.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	6.6	151.2	849.1	2860.7
58°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	7.7	150.1	821.7	2775.3
60°	0.0	0.0	0.0	0.0	0.0	0.0	1.1	11.0	131.5	713.3	2422.5
62.5°	0.0	0.0	0.0	0.0	0.0	0.0	4.4	17.5	115.0	511.7	2008.3
65°	0.0	0.0	0.0	0.0	0.0	0.0	8.8	19.7	105.2	371.4	1507.6
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	11.0	23.0	100.8	263.0	1048.5
70°	0.0	0.0	0.0	0.0	0.0	0.0	13.1	26.3	93.1	188.4	690.3
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	13.1	32.9	87.7	147.9	416.3
75°	0.0	0.0	0.0	0.0	0.0	0.0	13.1	41.6	76.7	120.5	223.5
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	13.1	44.9	63.5	87.7	135.9
80°	0.0	0.0	0.0	0.0	0.0	0.0	12.1	40.5	46.0	38.3	46.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	6.6	24.1	9.9	9.9	15.3
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P991264

CATALOG NUMBER: GPC-SA1D-750-U-RBC

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	313°	315°	325°	335°	345°	355°	360°
0°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
2.5°	7.7	7.7	7.7	7.7	8.8	8.8	12.1	15.3	18.6	19.7
5°	9.9	11.0	12.1	12.1	12.1	13.1	15.3	17.5	20.8	21.9
7.5°	14.2	15.3	17.5	17.5	17.5	18.6	19.7	21.9	24.1	24.1
10°	18.6	21.9	23.0	24.1	25.2	25.2	25.2	26.3	27.4	26.3
12.5°	25.2	29.6	35.1	36.2	36.2	36.2	35.1	32.9	30.7	29.6
15°	35.1	48.2	65.7	72.3	69.0	61.4	53.7	41.6	36.2	34.0
17.5°	64.6	131.5	238.8	264.0	258.6	222.4	130.4	63.5	42.7	37.3
20°	174.2	425.1	701.2	768.0	803.1	665.1	384.6	147.9	52.6	40.5
22.5°	375.8	883.1	1368.5	1541.6	1552.5	1249.0	748.3	300.2	75.6	46.0
25°	604.8	1412.3	2074.0	2241.7	2245.0	1925.0	1196.4	486.5	115.0	57.0
27.5°	926.9	1979.8	2720.5	2859.6	2857.4	2533.1	1728.9	742.8	161.1	70.1
30°	1256.7	2422.5	3146.7	3319.8	3336.2	2948.4	2173.7	1046.3	210.4	84.4
32.5°	1583.2	2750.1	3535.6	3765.7	3751.5	3315.4	2483.8	1295.0	294.7	99.7
35°	1840.7	3029.4	3966.2	4248.9	4259.8	3718.6	2758.8	1536.1	367.0	128.2
37.5°	2060.9	3389.9	4539.2	4865.7	4880.0	4220.4	3047.0	1772.7	429.5	141.3
40°	2332.6	3981.6	5488.1	6042.5	6044.6	5156.1	3565.2	2037.9	513.9	146.8
42.5°	2942.9	5249.2	7341.9	8138.4	8207.4	7097.6	4743.0	2613.1	646.4	158.9
45°	4163.4	6920.1	9706.3	10623.3	10711.0	9513.4	6762.3	3941.0	937.9	193.9
47.5°	5615.2	8372.9	11080.2	11963.3	12021.4	10656.2	8114.3	5477.1	1596.3	336.4
50°	6508.1	8910.8	11585.3	12427.8	12437.7	11032.0	8538.3	6274.7	2274.5	553.3
52.5°	6785.3	8979.9	11605.0	12624.0	12652.4	10988.2	8596.4	6435.8	2557.2	642.0
55°	6672.4	8939.3	11813.2	12998.7	13029.3	11166.8	8556.9	6259.4	2424.6	615.7
57.5°	6415.0	9097.1	12155.0	13443.5	13443.5	11496.5	8702.7	5963.6	2100.3	559.9
58°	6376.6	9136.5	12173.6	13467.6	13457.7	11517.4	8762.9	5920.8	2029.1	539.1
60°	6324.0	9258.2	12035.6	13111.5	13083.0	11370.5	8872.5	5882.5	1684.0	422.9
62.5°	6247.3	8984.2	11029.8	12064.1	11990.7	10341.7	8558.0	5657.9	1256.7	314.4
65°	5854.0	7973.0	9194.6	9911.2	9888.1	8507.6	7366.0	5068.4	905.0	233.4
67.5°	4934.8	6241.9	7427.3	8290.7	8296.2	6945.3	5760.9	4050.6	615.7	186.3
70°	3471.0	4603.9	6314.2	7275.0	7318.9	5825.5	4267.5	2699.7	406.5	160.0
72.5°	2072.9	3477.6	5250.3	5980.0	5957.0	4834.0	3166.4	1609.5	247.6	142.4
75°	1004.7	2078.4	2653.6	3077.7	3060.1	2418.1	1687.3	788.9	180.8	128.2
77.5°	272.8	638.8	1027.7	1336.7	1372.8	968.5	553.3	211.5	112.9	96.4
80°	92.0	197.2	335.3	455.8	467.8	418.5	208.2	74.5	49.3	48.2
82.5°	35.1	48.2	61.4	54.8	54.8	57.0	44.9	31.8	23.0	19.7
85°	0.0	0.0	1.1	2.2	2.2	3.3	3.3	3.3	2.2	2.2
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-6

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-750-U-5WQ


Data in this report applies to families of products including GSS-SB1A-750-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-6
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-750-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI
 5000K CCT 26 LEDS

Spectral Parameters

CCT (K):	4896	CRI (Ra):	70.2		
CIE u':	0.2101	R1:	68.1	R9:	-35.1
CIE v':	0.4901	R2:	73.9	R10:	39.3
Duv:	0.0035	R3:	79.4	R11:	71.1
CIE x:	0.3489	R4:	72.1	R12:	43.8
CIE y:	0.3618	R5:	69.2	R13:	68.1
CIE z:	0.2893	R6:	65.7	R14:	88.4
Peak Wavelength (nm):	443	R7:	78.1	R15:	59.7
Dominant Wavelength (nm):	570	R8:	55.3		
Purity:	13.25435				
Rf:	70.7				
Rg:	96.8				



Test Conditions


Stabilization Time: 21M
 Operation Time: 1H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-6

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-6

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-6

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-6

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.7

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-6

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.37


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-6




TM-30-18

Summary

$R_f = 70.7$
 $R_g = 96.8$
 $CIE R_a = 70.2$
 $R_g = -35.1$



Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 85	CES26 = 53	CES51 = 87	CES76 = 42
CES02 = 59	CES27 = 78	CES52 = 88	CES77 = 64
CES03 = 30	CES28 = 76	CES53 = 74	CES78 = 45
CES04 = 69	CES29 = 48	CES54 = 80	CES79 = 74
CES05 = 46	CES30 = 56	CES55 = 79	CES80 = 71
CES06 = 50	CES31 = 54	CES56 = 68	CES81 = 72
CES07 = 39	CES32 = 50	CES57 = 65	CES82 = 88
CES08 = 38	CES33 = 60	CES58 = 67	CES83 = 82
CES09 = 29	CES34 = 62	CES59 = 87	CES84 = 87
CES10 = 72	CES35 = 79	CES60 = 91	CES85 = 84
CES11 = 56	CES36 = 90	CES61 = 87	CES86 = 74
CES12 = 61	CES37 = 72	CES62 = 79	CES87 = 75
CES13 = 41	CES38 = 66	CES63 = 72	CES88 = 76
CES14 = 74	CES39 = 91	CES64 = 70	CES89 = 74
CES15 = 70	CES40 = 83	CES65 = 63	CES90 = 73
CES16 = 46	CES41 = 83	CES66 = 64	CES91 = 92
CES17 = 49	CES42 = 70	CES67 = 62	CES92 = 67
CES18 = 55	CES43 = 68	CES68 = 69	CES93 = 81
CES19 = 71	CES44 = 98	CES69 = 80	CES94 = 56
CES20 = 64	CES45 = 78	CES70 = 56	CES95 = 71
CES21 = 85	CES46 = 77	CES71 = 53	CES96 = 77
CES22 = 77	CES47 = 73	CES72 = 84	CES97 = 82
CES23 = 91	CES48 = 65	CES73 = 46	CES98 = 71
CES24 = 90	CES49 = 76	CES74 = 94	CES99 = 59
CES25 = 71	CES50 = 85	CES75 = 49	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)