Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P1199365

Luminaire Tested: GPC-SB2A-827-U-SLR

Issue Date: 10/30/2025

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2024
Report Number:	P1199365
	TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)
Test Lab:	INNOVATION CENTER
Issue Date:	3/15/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGRAW-EDISON
Catalog Number:	GPC-SB2A-827-U-SLR
Description:	GALLEON PEDESTRIAN LUMINAIRE
	(2) 80 CRI, 2700K, 350mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT ELIMINATOF RIGHT OPTICS
Light Source:	-
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	7771 lumens
Efficiency:	N/A
Efficacy:	135.6 lumens/watt
Luminous Opening:	Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification:	Type IV - Short
BUG Rating:	B2 - U0 - G3

Input Watts (W):	57.3
Input Voltage (V):	120.0
Input Current (Ain):	0.484
Voltage Rise (V):	NR
Power Factor:	0.994
Total Harmonic Distortion (THDi):	9.038
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1199365
CATALOG NUMBER: GPC-SB2A-827-U-SLR

Iso-Footcandle Lines of Horizontal Illumination




Based on 10 foot mounting height. Maximum calculated value = 13.2 fc
Type IV - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1199365
CATALOG NUMBER: GPC-SB2A-827-U-SLR

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1199365
CATALOG NUMBER: GPC-SB2A-827-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1975.0	0.0	1975.0
	% Fixture	25.4	0.0	25.4
Street Side	Lumens	5796.0	0.0	5796.0
	% Fixture	74.6	0.0	74.6
Total	Lumens	7771.0	0.0	7771.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.0	1.4
10°-20°	332.8	4.3
20°-30°	514.0	6.6
30°-40°	651.4	8.4
40°-50°	982.4	12.6
50°-60°	1587.3	20.4
60°-70°	1978.8	25.5
70°-80°	1297.6	16.7
80°-90°	320.8	4.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7771.0	100.0
0°-180°	7771.0	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1199365
CATALOG NUMBER: GPC-SB2A-827-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	522.7	6.7			
FM	(30°-60°)	2266.6	29.2			
FH	(60°-80°)	2742.4	35.3			G2/5000
FVH	(80°-90°)	264.3	3.4			G3/500
BL	(0°-30°)	430.1	5.5	B1/500		
BM	(30°-60°)	954.4	12.3	B1/1000		
BH	(60°-80°)	533.9	6.9	B2/1000		G2/1000
BVH	(80°-90°)	56.5	0.7			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3
Type IV Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1199365
CATALOG NUMBER: GPC-SB2A-827-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6
2.5°	1149.2	1140.3	1131.5	1122.1	1112.8	1103.4	1093.9	1084.9	1075.9	1067.1	1057.4
5°	1235.7	1216.2	1196.7	1177.3	1157.9	1138.3	1118.8	1100.6	1082.3	1065.1	1048.1
7.5°	1322.6	1290.5	1258.3	1228.7	1199.0	1170.1	1141.2	1115.7	1090.2	1066.7	1044.7
10°	1389.2	1348.6	1308.0	1268.7	1229.5	1194.4	1159.3	1129.2	1099.0	1070.0	1046.4
12.5°	1430.0	1385.4	1340.8	1296.3	1251.9	1210.5	1169.0	1135.0	1100.9	1070.4	1048.4
15°	1454.8	1408.3	1361.8	1313.5	1265.3	1217.6	1169.9	1130.5	1091.0	1057.3	1039.7
17.5°	1468.8	1421.6	1374.4	1321.8	1269.2	1213.8	1158.5	1111.0	1063.6	1023.9	1013.0
20°	1484.2	1435.1	1386.0	1328.2	1270.4	1203.3	1136.2	1077.4	1018.6	972.4	969.6
22.5°	1502.0	1451.9	1401.7	1336.9	1272.0	1190.4	1108.8	1038.0	967.2	914.6	920.2
25°	1525.0	1475.8	1426.8	1352.7	1278.5	1177.7	1077.0	994.0	911.1	857.2	872.4
27.5°	1556.1	1509.3	1462.4	1377.3	1292.1	1169.2	1046.4	953.8	861.2	812.1	830.5
30°	1598.2	1552.9	1507.7	1409.1	1310.6	1165.3	1019.9	920.2	820.5	779.3	793.8
32.5°	1647.8	1603.0	1558.2	1442.4	1326.6	1160.3	994.0	891.2	788.3	755.1	761.5
35°	1708.0	1665.2	1622.2	1480.3	1338.3	1151.1	963.9	862.7	761.5	733.8	731.1
37.5°	1809.5	1754.8	1700.1	1522.7	1345.3	1135.2	925.1	829.2	733.2	709.0	699.2
40°	1962.9	1883.2	1803.5	1576.6	1349.7	1113.4	877.1	789.1	701.2	679.2	664.3
42.5°	2166.3	2051.2	1936.2	1647.1	1358.0	1090.8	823.7	745.0	666.2	646.0	627.2
45°	2417.4	2262.2	2107.0	1739.8	1372.6	1069.9	767.1	698.1	629.0	608.5	590.3
47.5°	2731.5	2513.1	2294.6	1838.6	1382.7	1052.5	722.4	661.0	599.5	573.0	557.3
50°	3143.2	2813.9	2484.5	1930.3	1376.1	1033.7	691.3	636.3	581.4	546.6	528.3
52.5°	3615.8	3129.9	2644.0	1989.9	1335.7	1001.8	668.0	620.1	572.2	532.2	506.7
55°	4118.9	3410.0	2701.2	1976.7	1252.3	949.0	645.7	608.3	570.9	533.7	495.3
57.5°	4576.5	3608.6	2640.6	1884.4	1128.2	874.5	620.8	594.4	567.9	535.1	488.4
60°	4853.1	3658.2	2463.2	1712.6	961.9	777.9	593.8	573.0	552.2	530.6	481.9
62.5°	4712.7	3449.3	2185.9	1480.2	774.5	662.1	549.8	536.0	522.2	519.5	474.3
65°	*4431.6*	*3153.7*	*1875.8*	*1243.1*	*610.5*	*558.0*	*505.6*	*499.1*	*492.5*	*492.9*	*458.4*
67.5°	4054.9	2801.9	1548.8	1010.8	472.9	458.0	443.1	446.7	450.3	449.4	430.1
70°	3602.5	2418.0	1233.6	795.9	358.2	362.4	366.7	383.6	400.4	400.4	394.1
72.5°	3063.2	2001.9	940.6	608.5	276.3	289.1	302.0	325.9	349.9	353.9	354.0
75°	2381.1	1524.9	668.7	441.6	214.5	226.2	237.8	264.6	291.5	310.0	308.4
77.5°	1701.3	1067.3	433.3	299.3	165.2	173.1	181.0	207.1	233.1	263.7	262.8
80°	1113.5	687.6	261.8	192.8	123.8	127.1	130.4	152.5	174.5	211.0	210.8
82.5°	647.3	398.0	148.8	118.6	88.5	89.1	89.7	106.0	122.2	153.4	155.1
85°	284.8	179.0	73.3	63.4	53.5	53.2	52.9	64.8	76.7	99.8	102.1
87.5°	88.2	58.6	29.1	26.3	23.5	23.2	22.9	27.7	32.6	42.2	45.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1199365
CATALOG NUMBER: GPC-SB2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6
2.5°	1049.6	1041.7	1034.6	1027.6	1021.4	1015.2	1009.0	1002.8	998.0	993.1	989.2
5°	1033.2	1018.3	1005.9	993.5	982.5	971.5	961.5	951.5	943.8	936.1	930.8
7.5°	1025.0	1005.2	988.8	972.4	958.6	944.7	932.5	920.3	911.2	902.1	895.7
10°	1025.5	1004.7	988.3	971.9	957.0	942.1	928.3	914.6	903.7	892.8	885.6
12.5°	1031.3	1014.4	1003.5	992.6	980.9	969.3	955.0	940.9	926.9	913.0	903.7
15°	1031.5	1023.4	1024.9	1026.3	1023.3	1020.3	1007.9	995.6	975.7	955.9	941.9
17.5°	1016.0	1019.0	1036.8	1054.7	1064.2	1073.7	1063.7	1053.8	1027.5	1001.2	980.6
20°	983.5	997.4	1028.5	1059.6	1079.4	1099.3	1094.7	1090.1	1060.1	1030.0	1004.7
22.5°	940.9	961.5	996.9	1032.4	1058.3	1084.2	1086.9	1089.7	1061.0	1032.3	1006.2
25°	896.2	919.9	951.8	983.7	1009.2	1034.6	1044.1	1053.6	1030.1	1006.6	983.4
27.5°	853.5	876.5	902.7	928.8	949.3	969.7	980.3	990.9	974.1	957.4	939.4
30°	812.0	830.3	852.0	873.7	890.7	907.6	916.2	924.9	912.1	899.3	886.4
32.5°	772.3	783.1	800.5	817.8	834.1	850.4	859.9	869.5	857.8	846.0	835.7
35°	734.1	737.1	750.3	763.5	779.6	795.7	807.2	818.7	810.3	802.0	792.5
37.5°	695.9	692.6	702.2	711.6	727.7	743.7	757.9	772.1	768.3	764.4	755.7
40°	656.9	649.4	656.3	663.1	678.6	694.1	710.4	726.8	727.7	728.7	721.2
42.5°	617.3	607.5	613.1	618.7	633.4	648.1	665.7	683.3	688.1	692.8	686.5
45°	580.7	571.1	575.8	580.5	594.5	608.4	626.7	645.0	651.8	658.5	652.9
47.5°	549.3	541.3	545.7	550.1	563.7	577.3	595.4	613.4	621.2	629.0	625.1
50°	521.2	514.1	521.0	527.9	540.8	553.6	569.8	586.0	596.0	606.0	605.7
52.5°	499.7	492.7	503.0	513.4	525.2	537.0	552.0	567.1	578.9	590.8	592.9
55°	484.1	473.0	487.7	502.4	515.1	527.8	541.0	554.2	566.7	579.3	582.3
57.5°	472.1	455.9	471.7	487.5	502.5	517.4	530.4	543.5	556.2	568.8	571.8
60°	460.9	439.8	453.7	467.5	484.7	501.8	515.1	528.3	541.1	553.8	557.0
62.5°	448.0	421.7	430.5	439.4	459.3	479.3	493.5	507.6	519.3	530.9	534.1
65°	*430.5*	*402.5*	*405.9*	*409.2*	*430.6*	*452.1*	*465.6*	*479.1*	*489.4*	*499.6*	*502.9*
67.5°	406.8	383.5	382.4	381.3	401.1	420.9	433.7	446.5	455.4	464.3	467.4
70°	377.5	360.9	357.2	353.5	370.9	388.3	399.4	410.5	418.5	426.4	429.5
72.5°	342.6	331.2	325.8	320.5	334.1	347.8	357.8	367.8	375.6	383.5	387.1
75°	299.7	290.9	285.8	280.6	290.7	300.9	310.0	319.0	326.2	333.3	337.1
77.5°	255.8	248.8	243.6	238.3	246.6	254.8	262.6	270.4	277.9	285.4	288.9
80°	205.0	199.1	194.7	190.3	197.2	204.0	210.6	217.1	222.8	228.5	233.2
82.5°	152.2	149.3	146.2	143.1	142.5	142.0	139.7	137.4	149.5	161.6	169.6
85°	99.0	96.0	92.5	89.0	86.0	83.0	76.7	70.3	81.7	93.1	102.9
87.5°	43.9	42.6	42.0	41.3	41.2	41.1	36.2	31.4	36.1	40.9	44.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1199365
CATALOG NUMBER: GPC-SB2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6
2.5°	985.3	982.3	979.3	976.5	973.7	970.2	973.7	976.5	979.3	982.3	985.3
5°	925.4	921.6	917.8	914.9	911.9	909.1	911.9	914.9	917.8	921.6	925.4
7.5°	889.3	884.9	880.6	877.9	875.4	873.4	875.4	877.9	880.6	884.9	889.3
10°	878.4	874.3	870.1	867.9	865.7	864.8	865.7	867.9	870.1	874.3	878.4
12.5°	894.5	889.9	885.3	883.4	881.5	881.2	881.5	883.4	885.3	889.9	894.5
15°	927.9	921.4	915.0	912.6	910.1	909.9	910.1	912.6	915.0	921.4	927.9
17.5°	959.9	950.4	940.9	937.7	934.6	934.1	934.6	937.7	940.9	950.4	959.9
20°	979.4	967.2	955.0	951.1	947.2	946.0	947.2	951.1	955.0	967.2	979.4
22.5°	980.1	967.3	954.4	950.1	945.8	943.9	945.8	950.1	954.4	967.3	980.1
25°	960.2	949.1	938.0	933.9	929.9	927.5	929.9	933.9	938.0	949.1	960.2
27.5°	921.4	913.9	906.4	904.6	902.7	902.1	902.7	904.6	906.4	913.9	921.4
30°	873.5	869.7	865.8	865.8	865.8	866.4	865.8	865.8	865.8	869.7	873.5
32.5°	825.4	822.9	820.4	820.7	821.1	821.7	821.1	820.7	820.4	822.9	825.4
35°	783.0	779.2	775.4	774.6	773.8	773.3	773.8	774.6	775.4	779.2	783.0
37.5°	746.9	740.0	733.1	729.4	725.8	723.7	725.8	729.4	733.1	740.0	746.9
40°	713.8	703.7	693.7	686.9	680.2	676.2	680.2	686.9	693.7	703.7	713.8
42.5°	680.3	667.8	655.3	645.4	635.5	629.0	635.5	645.4	655.3	667.8	680.3
45°	647.3	632.9	618.7	607.1	595.5	588.0	595.5	607.1	618.7	632.9	647.3
47.5°	621.1	608.4	595.7	585.0	574.3	567.1	574.3	585.0	595.7	608.4	621.1
50°	605.6	595.4	585.2	575.3	565.4	558.5	565.4	575.3	585.2	595.4	605.6
52.5°	595.1	586.8	578.5	569.6	560.7	554.4	560.7	569.6	578.5	586.8	595.1
55°	585.2	578.0	570.8	563.0	555.2	549.5	555.2	563.0	570.8	578.0	585.2
57.5°	574.8	567.5	560.2	552.5	544.7	538.8	544.7	552.5	560.2	567.5	574.8
60°	560.3	553.2	546.1	538.1	530.2	524.0	530.2	538.1	546.1	553.2	560.3
62.5°	537.2	530.8	524.4	516.0	507.6	500.3	507.6	516.0	524.4	530.8	537.2
65°	*506.1*	*499.9*	*493.7*	*485.6*	*477.5*	*471.1*	*477.5*	*485.6*	*493.7*	*499.9*	*506.1*
67.5°	470.5	464.8	459.2	451.6	444.1	438.3	444.1	451.6	459.2	464.8	470.5
70°	432.5	427.9	423.2	416.0	408.8	402.3	408.8	416.0	423.2	427.9	432.5
72.5°	390.7	386.8	383.0	376.1	369.2	362.9	369.2	376.1	383.0	386.8	390.7
75°	340.8	338.9	337.1	331.3	325.5	319.4	325.5	331.3	337.1	338.9	340.8
77.5°	292.4	289.8	287.1	281.3	275.5	270.6	275.5	281.3	287.1	289.8	292.4
80°	237.8	236.7	235.6	227.7	219.9	210.8	219.9	227.7	235.6	236.7	237.8
82.5°	177.5	177.1	176.5	169.9	163.3	157.5	163.3	169.9	176.5	177.1	177.5
85°	112.8	111.9	111.1	106.0	100.8	95.5	100.8	106.0	111.1	111.9	112.8
87.5°	48.9	47.9	46.8	44.2	41.5	39.0	41.5	44.2	46.8	47.9	48.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1199365
CATALOG NUMBER: GPC-SB2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6
2.5°	989.2	993.1	998.0	1002.8	1009.0	1015.2	1021.4	1027.6	1034.6	1041.7	1049.6
5°	930.8	936.1	943.8	951.5	961.5	971.5	982.5	993.5	1005.9	1018.3	1033.2
7.5°	895.7	902.1	911.2	920.3	932.5	944.7	958.6	972.4	988.8	1005.2	1025.0
10°	885.6	892.8	903.7	914.6	928.3	942.1	957.0	971.9	988.3	1004.7	1025.5
12.5°	903.7	913.0	926.9	940.9	955.0	969.3	980.9	992.6	1003.5	1014.4	1031.3
15°	941.9	955.9	975.7	995.6	1007.9	1020.3	1023.3	1026.3	1024.9	1023.4	1031.5
17.5°	980.6	1001.2	1027.5	1053.8	1063.7	1073.7	1064.2	1054.7	1036.8	1019.0	1016.0
20°	1004.7	1030.0	1060.1	1090.1	1094.7	1099.3	1079.4	1059.6	1028.5	997.4	983.5
22.5°	1006.2	1032.3	1061.0	1089.7	1086.9	1084.2	1058.3	1032.4	996.9	961.5	940.9
25°	983.4	1006.6	1030.1	1053.6	1044.1	1034.6	1009.2	983.7	951.8	919.9	896.2
27.5°	939.4	957.4	974.1	990.9	980.3	969.7	949.3	928.8	902.7	876.5	853.5
30°	886.4	899.3	912.1	924.9	916.2	907.6	890.7	873.7	852.0	830.3	812.0
32.5°	835.7	846.0	857.8	869.5	859.9	850.4	834.1	817.8	800.5	783.1	772.3
35°	792.5	802.0	810.3	818.7	807.2	795.7	779.6	763.5	750.3	737.1	734.1
37.5°	755.7	764.4	768.3	772.1	757.9	743.7	727.7	711.6	702.2	692.6	695.9
40°	721.2	728.7	727.7	726.8	710.4	694.1	678.6	663.1	656.3	649.4	656.9
42.5°	686.5	692.8	688.1	683.3	665.7	648.1	633.4	618.7	613.1	607.5	617.3
45°	652.9	658.5	651.8	645.0	626.7	608.4	594.5	580.5	575.8	571.1	580.7
47.5°	625.1	629.0	621.2	613.4	595.4	577.3	563.7	550.1	545.7	541.3	549.3
50°	605.7	606.0	596.0	586.0	569.8	553.6	540.8	527.9	521.0	514.1	521.2
52.5°	592.9	590.8	578.9	567.1	552.0	537.0	525.2	513.4	503.0	492.7	499.7
55°	582.3	579.3	566.7	554.2	541.0	527.8	515.1	502.4	487.7	473.0	484.1
57.5°	571.8	568.8	556.2	543.5	530.4	517.4	502.5	487.5	471.7	455.9	472.1
60°	557.0	553.8	541.1	528.3	515.1	501.8	484.7	467.5	453.7	439.8	460.9
62.5°	534.1	530.9	519.3	507.6	493.5	479.3	459.3	439.4	430.5	421.7	448.0
65°	*502.9*	*499.6*	*489.4*	*479.1*	*465.6*	*452.1*	*430.6*	*409.2*	*405.9*	*402.5*	*430.5*
67.5°	467.4	464.3	455.4	446.5	433.7	420.9	401.1	381.3	382.4	383.5	406.8
70°	429.5	426.4	418.5	410.5	399.4	388.3	370.9	353.5	357.2	360.9	377.5
72.5°	387.1	383.5	375.6	367.8	357.8	347.8	334.1	320.5	325.8	331.2	342.6
75°	337.1	333.3	326.2	319.0	310.0	300.9	290.7	280.6	285.8	290.9	299.7
77.5°	288.9	285.4	277.9	270.4	262.6	254.8	246.6	238.3	243.6	248.8	255.8
80°	233.2	228.5	222.8	217.1	210.6	204.0	197.2	190.3	194.7	199.1	205.0
82.5°	169.6	161.6	149.5	137.4	139.7	142.0	142.5	143.1	146.2	149.3	152.2
85°	102.9	93.1	81.7	70.3	76.7	83.0	86.0	89.0	92.5	96.0	99.0
87.5°	44.9	40.9	36.1	31.4	36.2	41.1	41.2	41.3	42.0	42.6	43.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1199365
CATALOG NUMBER: GPC-SB2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6
2.5°	1057.4	1067.1	1075.9	1084.9	1093.9	1103.4	1112.8	1122.1	1131.5	1140.3	1149.2
5°	1048.1	1065.1	1082.3	1100.6	1118.8	1138.3	1157.9	1177.3	1196.7	1216.2	1235.7
7.5°	1044.7	1066.7	1090.2	1115.7	1141.2	1170.1	1199.0	1228.7	1258.3	1290.5	1322.6
10°	1046.4	1070.0	1099.0	1129.2	1159.3	1194.4	1229.5	1268.7	1308.0	1348.6	1389.2
12.5°	1048.4	1070.4	1100.9	1135.0	1169.0	1210.5	1251.9	1296.3	1340.8	1385.4	1430.0
15°	1039.7	1057.3	1091.0	1130.5	1169.9	1217.6	1265.3	1313.5	1361.8	1408.3	1454.8
17.5°	1013.0	1023.9	1063.6	1111.0	1158.5	1213.8	1269.2	1321.8	1374.4	1421.6	1468.8
20°	969.6	972.4	1018.6	1077.4	1136.2	1203.3	1270.4	1328.2	1386.0	1435.1	1484.2
22.5°	920.2	914.6	967.2	1038.0	1108.8	1190.4	1272.0	1336.9	1401.7	1451.9	1502.0
25°	872.4	857.2	911.1	994.0	1077.0	1177.7	1278.5	1352.7	1426.8	1475.8	1525.0
27.5°	830.5	812.1	861.2	953.8	1046.4	1169.2	1292.1	1377.3	1462.4	1509.3	1556.1
30°	793.8	779.3	820.5	920.2	1019.9	1165.3	1310.6	1409.1	1507.7	1552.9	1598.2
32.5°	761.5	755.1	788.3	891.2	994.0	1160.3	1326.6	1442.4	1558.2	1603.0	1647.8
35°	731.1	733.8	761.5	862.7	963.9	1151.1	1338.3	1480.3	1622.2	1665.2	1708.0
37.5°	699.2	709.0	733.2	829.2	925.1	1135.2	1345.3	1522.7	1700.1	1754.8	1809.5
40°	664.3	679.2	701.2	789.1	877.1	1113.4	1349.7	1576.6	1803.5	1883.2	1962.9
42.5°	627.2	646.0	666.2	745.0	823.7	1090.8	1358.0	1647.1	1936.2	2051.2	2166.3
45°	590.3	608.5	629.0	698.1	767.1	1069.9	1372.6	1739.8	2107.0	2262.2	2417.4
47.5°	557.3	573.0	599.5	661.0	722.4	1052.5	1382.7	1838.6	2294.6	2513.1	2731.5
50°	528.3	546.6	581.4	636.3	691.3	1033.7	1376.1	1930.3	2484.5	2813.9	3143.2
52.5°	506.7	532.2	572.2	620.1	668.0	1001.8	1335.7	1989.9	2644.0	3129.9	3615.8
55°	495.3	533.7	570.9	608.3	645.7	949.0	1252.3	1976.7	2701.2	3410.0	4118.9
57.5°	488.4	535.1	567.9	594.4	620.8	874.5	1128.2	1884.4	2640.6	3608.6	4576.5
60°	481.9	530.6	552.2	573.0	593.8	777.9	961.9	1712.6	2463.2	3658.2	4853.1
62.5°	474.3	519.5	522.2	536.0	549.8	662.1	774.5	1480.2	2185.9	3449.3	4712.7
65°	*458.4*	*492.9*	*492.5*	*499.1*	*505.6*	*558.0*	*610.5*	*1243.1*	*1875.8*	*3153.7*	*4431.6*
67.5°	430.1	449.4	450.3	446.7	443.1	458.0	472.9	1010.8	1548.8	2801.9	4054.9
70°	394.1	400.4	400.4	383.6	366.7	362.4	358.2	795.9	1233.6	2418.0	3602.5
72.5°	354.0	353.9	349.9	325.9	302.0	289.1	276.3	608.5	940.6	2001.9	3063.2
75°	308.4	310.0	291.5	264.6	237.8	226.2	214.5	441.6	668.7	1524.9	2381.1
77.5°	262.8	263.7	233.1	207.1	181.0	173.1	165.2	299.3	433.3	1067.3	1701.3
80°	210.8	211.0	174.5	152.5	130.4	127.1	123.8	192.8	261.8	687.6	1113.5
82.5°	155.1	153.4	122.2	106.0	89.7	89.1	88.5	118.6	148.8	398.0	647.3
85°	102.1	99.8	76.7	64.8	52.9	53.2	53.5	63.4	73.3	179.0	284.8
87.5°	45.1	42.2	32.6	27.7	22.9	23.2	23.5	26.3	29.1	58.6	88.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1199365
CATALOG NUMBER: GPC-SB2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	*1068.6*	1068.6	1068.6
2.5°	1153.5	1157.9	1164.1	1170.3	1174.0	1177.7	1179.5	1181.3	*1180.5*	1181.3	1179.5
5°	1250.9	1266.1	1281.2	1296.4	1304.6	1312.8	1317.7	1322.7	*1326.5*	1322.7	1317.7
7.5°	1347.4	1372.1	1394.4	1416.6	1430.0	1443.4	1450.7	1457.9	*1461.4*	1457.9	1450.7
10°	1418.5	1447.8	1473.9	1500.0	1515.9	1531.6	1538.7	1545.7	*1548.3*	1545.7	1538.7
12.5°	1461.8	1493.5	1517.1	1540.6	1552.1	1563.6	1567.4	1571.3	*1571.7*	1571.3	1567.4
15°	1482.2	1509.6	1524.4	1539.2	1539.6	1540.1	1535.9	1531.8	*1527.0*	1531.8	1535.9
17.5°	1487.3	1505.8	1506.1	1506.3	1489.7	1473.1	1457.9	1442.6	*1431.9*	1442.6	1457.9
20°	1490.6	1497.1	1477.6	1458.1	1421.5	1384.8	1358.1	1331.4	*1315.0*	1331.4	1358.1
22.5°	1493.6	1485.1	1444.8	1404.4	1350.5	1296.6	1263.2	1229.8	*1211.7*	1229.8	1263.2
25°	1498.3	1471.7	1410.4	1349.1	1283.6	1218.2	1183.1	1148.0	*1130.9*	1148.0	1183.1
27.5°	1508.5	1460.8	1379.6	1298.5	1226.0	1153.4	1118.9	1084.4	*1068.2*	1084.4	1118.9
30°	1527.1	1456.1	1356.2	1256.3	1180.7	1105.1	1073.0	1041.0	*1025.9*	1041.0	1073.0
32.5°	1550.5	1453.2	1340.2	1227.2	1156.1	1085.1	1059.9	1034.8	*1023.9*	1034.8	1059.9
35°	1589.0	1469.9	1352.2	1234.4	1185.1	1135.7	1129.9	1124.0	*1123.1*	1124.0	1129.9
37.5°	1669.5	1529.4	1422.4	1315.3	1312.1	1308.9	1335.8	1362.6	*1376.5*	1362.6	1335.8
40°	1810.6	1658.2	1578.6	1499.0	1555.2	1611.4	1676.6	1741.8	*1774.3*	1741.8	1676.6
42.5°	2015.1	1864.0	1818.1	1772.3	1894.8	2017.3	2135.9	2254.5	*2324.1*	2254.5	2135.9
45°	2281.7	2145.9	2125.6	2105.4	2301.7	2498.0	2692.9	2887.7	*3006.0*	2887.7	2692.9
47.5°	2599.4	2467.3	2463.2	2459.1	2742.3	3025.4	3310.7	3595.9	*3763.4*	3595.9	3310.7
50°	2980.0	2816.9	2817.6	2818.3	3183.3	3548.2	3924.8	4301.3	*4529.0*	4301.3	3924.8
52.5°	3418.2	3220.7	3200.7	3180.7	3616.6	4052.6	4518.5	4984.3	*5257.2*	4984.3	4518.5
55°	3923.7	3728.5	3650.7	3572.8	4058.0	4543.1	5098.5	5653.9	*5978.5*	5653.9	5098.5
57.5°	4470.2	4363.9	4207.7	4051.6	4541.5	5031.3	5660.4	6289.5	*6691.9*	6289.5	5660.4
60°	5018.2	5183.3	4989.4	4795.4	5259.0	5722.6	6396.1	7069.7	*7504.7*	7069.7	6396.1
62.5°	5163.7	5614.8	5593.0	5571.1	5995.8	6420.5	7061.3	7702.1	*8104.1*	7702.1	7061.3
65°	*4854.9*	*5278.3*	*5362.1*	*5445.8*	*5985.5*	*6525.3*	*7146.6*	*7768.0*	*8110.3*	*7768.0*	*7146.6*
67.5°	4457.6	4860.3	4899.6	4938.8	5501.1	6063.4	6687.5	7311.5	*7579.7*	7311.5	6687.5
70°	4040.4	4478.4	4496.0	4513.6	5016.5	5519.3	6056.3	6593.3	*6742.4*	6593.3	6056.3
72.5°	3565.8	4068.5	4081.1	4093.7	4487.1	4880.6	5282.8	5685.0	*5700.0*	5685.0	5282.8
75°	2901.3	3421.5	3468.2	3514.9	3821.0	4127.1	4410.2	4693.4	*4617.5*	4693.4	4410.2
77.5°	2186.9	2672.5	2739.3	2806.1	3038.8	3271.6	3472.4	3673.2	*3542.8*	3673.2	3472.4
80°	1522.0	1930.5	2013.6	2096.6	2272.4	2448.1	2553.5	2658.9	*2449.2*	2658.9	2553.5
82.5°	926.5	1205.9	1298.7	1391.5	1512.5	1633.4	1677.4	1721.4	*1556.5*	1721.4	1677.4
85°	433.0	581.2	660.2	739.1	838.5	937.9	962.8	987.8	*855.8*	987.8	962.8
87.5°	138.0	187.8	231.8	275.9	325.6	375.3	377.4	379.5	*318.6*	379.5	377.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1199365
CATALOG NUMBER: GPC-SB2A-827-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6	1068.6
2.5°	1177.7	1174.0	1170.3	1164.1	1157.9	1153.5	1149.2
5°	1312.8	1304.6	1296.4	1281.2	1266.1	1250.9	1235.7
7.5°	1443.4	1430.0	1416.6	1394.4	1372.1	1347.4	1322.6
10°	1531.6	1515.9	1500.0	1473.9	1447.8	1418.5	1389.2
12.5°	1563.6	1552.1	1540.6	1517.1	1493.5	1461.8	1430.0
15°	1540.1	1539.6	1539.2	1524.4	1509.6	1482.2	1454.8
17.5°	1473.1	1489.7	1506.3	1506.1	1505.8	1487.3	1468.8
20°	1384.8	1421.5	1458.1	1477.6	1497.1	1490.6	1484.2
22.5°	1296.6	1350.5	1404.4	1444.8	1485.1	1493.6	1502.0
25°	1218.2	1283.6	1349.1	1410.4	1471.7	1498.3	1525.0
27.5°	1153.4	1226.0	1298.5	1379.6	1460.8	1508.5	1556.1
30°	1105.1	1180.7	1256.3	1356.2	1456.1	1527.1	1598.2
32.5°	1085.1	1156.1	1227.2	1340.2	1453.2	1550.5	1647.8
35°	1135.7	1185.1	1234.4	1352.2	1469.9	1589.0	1708.0
37.5°	1308.9	1312.1	1315.3	1422.4	1529.4	1669.5	1809.5
40°	1611.4	1555.2	1499.0	1578.6	1658.2	1810.6	1962.9
42.5°	2017.3	1894.8	1772.3	1818.1	1864.0	2015.1	2166.3
45°	2498.0	2301.7	2105.4	2125.6	2145.9	2281.7	2417.4
47.5°	3025.4	2742.3	2459.1	2463.2	2467.3	2599.4	2731.5
50°	3548.2	3183.3	2818.3	2817.6	2816.9	2980.0	3143.2
52.5°	4052.6	3616.6	3180.7	3200.7	3220.7	3418.2	3615.8
55°	4543.1	4058.0	3572.8	3650.7	3728.5	3923.7	4118.9
57.5°	5031.3	4541.5	4051.6	4207.7	4363.9	4470.2	4576.5
60°	5722.6	5259.0	4795.4	4989.4	5183.3	5018.2	4853.1
62.5°	6420.5	5995.8	5571.1	5593.0	5614.8	5163.7	4712.7
65°	*6525.3*	*5985.5*	*5445.8*	*5362.1*	*5278.3*	*4854.9*	*4431.6*
67.5°	6063.4	5501.1	4938.8	4899.6	4860.3	4457.6	4054.9
70°	5519.3	5016.5	4513.6	4496.0	4478.4	4040.4	3602.5
72.5°	4880.6	4487.1	4093.7	4081.1	4068.5	3565.8	3063.2
75°	4127.1	3821.0	3514.9	3468.2	3421.5	2901.3	2381.1
77.5°	3271.6	3038.8	2806.1	2739.3	2672.5	2186.9	1701.3
80°	2448.1	2272.4	2096.6	2013.6	1930.5	1522.0	1113.5
82.5°	1633.4	1512.5	1391.5	1298.7	1205.9	926.5	647.3
85°	937.9	838.5	739.1	660.2	581.2	433.0	284.8
87.5°	375.3	325.6	275.9	231.8	187.8	138.0	88.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0


HS
SS

0

(END OF REPORT)