

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: 765826

Luminaire Tested: **GSL-XX-1000-HPS-XX-AR-SG-XX-X**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: 765826
Test Lab:
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GSL-XX-1000-HPS-XX-AR-SG-XX-X
Description: LARGE ARCHITECTURAL AREA FIXTURE-VERTICAL LAMP-ROUND DISTRIBUTION
Light Source: 1000 WATT HPS CLEAR E-25
Ballast/Driver: -

Summary

Lumens per Lamp: 140000 (1 lamp)
Luminaire Lumens: 112554.9 lumens
Efficiency: 80.4%
Efficacy: 112.6 lumens/watt
Luminous Opening: Point Source (0' x 0' x 0')
IES Classification: Type V - Short - Cutoff
BUG Rating: B5 - U5 - G5

Input Watts (W): 1000
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: 765826

CATALOG NUMBER: GSL-XX-1000-HPS-XX-AR-SG-XX-X

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 30 foot mounting height. Maximum calculated value = 7 fc
 Type V - Short - Cutoff

REPORT NUMBER: 765826

CATALOG NUMBER: GSL-XX-1000-HPS-XX-AR-SG-XX-X

Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: 765826

CATALOG NUMBER: GSL-XX-1000-HPS-XX-AR-SG-XX-X


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	55633.5	644.0	56277.4
	% Lamp	39.7	0.5	40.2
Street Side	Lumens	55633.5	644.0	56277.4
	% Lamp	39.7	0.5	40.2
Total	Lumens	111266.9	1288.0	112554.9
	% Lamp	79.5	0.9	80.4

ZONAL LUMENS:

Zone	Lumens	% Fixture	% Lamp
0°-10°	449.7	0.4	0.3
10°-20°	1769.8	1.6	1.3
20°-30°	3916.2	3.5	2.8
30°-40°	7301.1	6.5	5.2
40°-50°	14053.9	12.5	10.0
50°-60°	25881.9	23.0	18.5
60°-70°	30579.3	27.2	21.8
70°-80°	20401.6	18.1	14.6
80°-90°	7898.2	7.0	5.6
90°-100°	1162.4	1.0	0.8
100°-110°	189.1	0.2	0.1
110°-120°	11.9	0.0	0.0
120°-130°	0.0	0.0	0.0
130°-140°	0.0	0.0	0.0
140°-150°	0.0	0.0	0.0
150°-160°	0.0	0.0	0.0
160°-170°	0.0	0.0	0.0
170°-180°	0.0	0.0	0.0
0°-90°	111266.9	98.9	79.5
0°-180°	112554.9	100.0	80.4

Coefficient of Utilization



REPORT NUMBER: 765826


CATALOG NUMBER: GSL-XX-1000-HPS-XX-AR-SG-XX-X

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Lamp	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	3047.3	2.2			
FM	(30°-60°)	23160.6	16.5			
FH	(60°-80°)	25490.5	18.2			G5
FVH	(80°-90°)	3949.1	2.8			G5
BL	(0°-30°)	3047.3	2.2	B4/5000		
BM	(30°-60°)	23160.6	16.5	B5		
BH	(60°-80°)	25490.5	18.2	B5		G5
BVH	(80°-90°)	3949.1	2.8			G5
UL	(90°-100°)	1162.4	0.8		U5	
UH	(100°-180°)	644.0	0.5		U4/1000	
Trapped Light		27445.1	19.6			

BUG Rating: B5-U5-G5

Type V Short



REPORT NUMBER: 765826

CATALOG NUMBER: GSL-XX-1000-HPS-XX-AR-SG-XX-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	4481
5°	4363
15°	6140
25°	8330
35°	11043
45°	16073
50°	22736
55°	29099
60°	34113
62.5°	33034
65°	31400
67.5°	28940
70°	26005
72.5°	23371
75°	19071
77.5°	15660
80°	12487
82.5°	9790
85°	6949
87.5°	4681
90°	2681
95°	619
105°	48
115°	0
125°	0
135°	0
145°	0
155°	0
165°	0
175°	0
180°	0

(END OF REPORT)