Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360695

Luminaire Tested: **GSS-SB3A-722-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360695
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB3A-722-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 3SQUARE 85W 70CRI 2200K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(78) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	10225.8 lumens
Efficiency:	N/A
Efficacy:	120.3 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B3 - U0 - G3


Input Watts (W):	85
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	11.0%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360695
CATALOG NUMBER: GSS-SB3A-722-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 5 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360695
CATALOG NUMBER: GSS-SB3A-722-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360695
CATALOG NUMBER: GSS-SB3A-722-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	5112.9	0.0	5112.9
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	5112.9	0.0	5112.9
	% Fixture	50.0	0.0	50.0
Total	Lumens	10225.8	0.0	10225.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.0	1.9
10°-20°	594.4	5.8
20°-30°	993.4	9.7
30°-40°	1370.0	13.4
40°-50°	1679.4	16.4
50°-60°	1968.1	19.2
60°-70°	2185.5	21.4
70°-80°	1188.5	11.6
80°-90°	51.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10225.8	100.0
0°-180°	10225.8	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360695
CATALOG NUMBER: GSS-SB3A-722-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	891.4	8.7			
FM	(30°-60°)	2508.8	24.5			
FH	(60°-80°)	1687.0	16.5			G1/1800
FVH	(80°-90°)	25.8	0.3			G1/100
BL	(0°-30°)	891.4	8.7	B2/1000		
BM	(30°-60°)	2508.8	24.5	B3/5000		
BH	(60°-80°)	1687.0	16.5	B3/2500		G3/2500
BVH	(80°-90°)	25.8	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360695
CATALOG NUMBER: GSS-SB3A-722-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	2014.7	2014.7	2014.7	2014.7	2014.7	2014.7	2014.7	2014.7	2014.7	2014.7	2014.7
2.5°	2017.0	2017.0	2010.3	2019.2	2014.7	2017.0	2019.2	2017.0	2014.7	2017.0	2019.2
5°	2028.2	2023.7	2028.2	2032.6	2025.9	2030.4	2028.2	2017.0	2023.7	2023.7	2023.7
7.5°	2048.3	2052.8	2048.3	2059.5	2052.8	2066.2	2052.8	2043.8	2041.6	2039.4	2039.4
10°	2057.3	2057.3	2055.0	2075.2	2079.7	2093.1	2084.1	2070.7	2064.0	2055.0	2046.1
12.5°	2032.6	2037.1	2048.3	2086.4	2104.3	2131.1	2124.4	2097.6	2077.4	2070.7	2057.3
15°	2005.8	2010.3	2032.6	2079.7	2122.2	2162.5	2160.2	2126.7	2102.0	2084.1	2064.0
17.5°	1963.3	1970.0	2001.3	2072.9	2149.1	2193.8	2207.3	2173.7	2146.8	2117.7	2090.9
20°	1891.6	1891.6	1947.6	2039.4	2144.6	2245.3	2281.1	2254.3	2222.9	2175.9	2140.1
22.5°	1811.0	1815.5	1871.5	1992.4	2142.3	2290.1	2359.5	2330.4	2299.0	2247.6	2193.8
25°	1730.4	1730.4	1793.1	1929.7	2113.2	2321.4	2451.3	2435.6	2372.9	2325.9	2256.5
27.5°	1656.6	1656.6	1723.7	1867.0	2064.0	2330.4	2543.0	2543.0	2473.7	2404.3	2328.1
30°	1569.3	1591.6	1667.8	1817.7	2019.2	2314.7	2610.2	2652.7	2590.1	2500.5	2388.6
32.5°	1495.4	1511.1	1589.4	1748.3	1954.3	2296.8	2686.3	2791.5	2726.6	2603.5	2478.1
35°	1408.1	1405.8	1495.4	1652.1	1862.5	2256.5	2746.8	2957.2	2894.5	2762.4	2592.3
37.5°	1293.9	1293.9	1385.7	1537.9	1775.2	2187.1	2796.0	3140.8	3093.7	2943.8	2762.4
40°	1170.8	1184.2	1264.8	1419.3	1670.0	2104.3	2796.0	3290.7	3315.4	3160.9	2972.9
42.5°	1081.2	1085.7	1159.6	1305.1	1553.6	1996.8	2760.2	3420.6	3494.5	3364.6	3120.6
45°	987.2	998.4	1061.1	1195.4	1432.7	1869.2	2697.5	3566.1	3684.7	3595.2	3275.1
47.5°	873.1	884.2	955.9	1092.4	1318.5	1730.4	2592.3	3718.3	3966.8	3901.9	3550.4
50°	741.0	749.9	817.1	962.6	1190.9	1571.5	2460.2	3832.5	4248.9	4313.8	3966.8
52.5°	579.8	586.5	658.1	799.2	1038.7	1419.3	2274.4	3901.9	4533.2	4761.5	4524.2
55°	416.4	427.6	490.3	606.7	837.2	1215.6	2052.8	3937.7	4844.3	5292.1	5215.9
57.5°	300.0	304.4	347.0	436.5	622.3	976.0	1768.5	3877.3	5124.2	5925.6	6084.5
60°	248.5	248.5	255.2	297.7	425.3	689.5	1428.2	3653.4	5363.7	6565.8	7056.1
62.5°	228.3	228.3	232.8	239.5	279.8	447.7	1020.8	3199.0	5390.5	7181.4	8121.6
65°	208.2	208.2	212.7	217.1	226.1	291.0	615.6	2341.6	4864.5	7188.1	8694.7
67.5°	190.3	190.3	192.5	194.8	199.2	212.7	338.0	1419.3	3892.9	6997.9	8914.1
70°	172.4	172.4	172.4	170.1	176.8	179.1	223.9	720.8	2603.5	6319.6	8808.9
72.5°	*152.2*	*152.2*	*150.0*	*145.5*	*147.7*	*147.7*	*165.7*	*353.7*	*1352.1*	*5023.4*	*7953.7*
75°	129.8	132.1	123.1	118.6	116.4	118.6	132.1	201.5	604.4	3046.7	5943.5
77.5°	109.7	114.2	100.7	91.8	89.5	89.5	103.0	125.4	259.7	1105.9	2663.9
80°	82.8	85.1	73.9	64.9	64.9	62.7	76.1	91.8	123.1	329.1	597.7
82.5°	47.0	47.0	42.5	38.1	35.8	38.1	51.5	62.7	76.1	116.4	163.4
85°	11.2	11.2	13.4	15.7	15.7	20.1	29.1	33.6	40.3	47.0	62.7
87.5°	2.2	2.2	2.2	4.5	6.7	6.7	11.2	15.7	20.1	24.6	26.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360695
CATALOG NUMBER: GSS-SB3A-722-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	2014.7	2014.7	*2014.7*
2.5°	2019.2	2021.5	*2019.2*
5°	2032.6	2028.2	*2021.5*
7.5°	2034.9	2037.1	*2039.4*
10°	2043.8	2052.8	*2039.4*
12.5°	2052.8	2046.1	*2041.6*
15°	2059.5	2057.3	*2043.8*
17.5°	2084.1	2075.2	*2072.9*
20°	2122.2	2120.0	*2113.2*
22.5°	2167.0	2162.5	*2160.2*
25°	2231.9	2216.2	*2207.3*
27.5°	2285.6	2272.2	*2267.7*
30°	2339.3	2312.5	*2312.5*
32.5°	2386.3	2379.6	*2375.2*
35°	2498.3	2464.7	*2469.2*
37.5°	2634.8	2601.3	*2572.2*
40°	2827.4	2782.6	*2764.7*
42.5°	2950.5	2905.7	*2910.2*
45°	3019.9	2941.5	*2921.4*
47.5°	3207.9	3109.4	*3082.6*
50°	3512.4	3391.5	*3357.9*
52.5°	4004.9	3810.1	*3765.3*
55°	4622.7	4383.2	*4338.4*
57.5°	5468.9	5151.0	*5054.8*
60°	6498.7	6104.7	*5959.2*
62.5°	7736.6	7250.8	*7112.0*
65°	8667.9	8262.7	*8047.8*
67.5°	9413.3	9079.8	*8976.8*
70°	9856.6	9872.2	*9899.1*
72.5°	*9343.9*	*9773.7*	*9979.7*
75°	6847.9	7181.4	*7501.5*
77.5°	2646.0	2386.3	*2310.2*
80°	427.6	400.7	*414.1*
82.5°	192.5	203.7	*214.9*
85°	125.4	145.5	*154.5*
87.5°	29.1	29.1	*29.1*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)