Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360703

Luminaire Tested: **GSS-SB5A-722-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360703
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB5A-722-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 5SQUARE 143W 70CRI 2200K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(130) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	17760.2 lumens
Efficiency:	N/A
Efficacy:	124.2 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	143
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	10.5%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360703
CATALOG NUMBER: GSS-SB5A-722-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 8.7 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360703
CATALOG NUMBER: GSS-SB5A-722-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360703
CATALOG NUMBER: GSS-SB5A-722-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	8880.1	0.0	8880.1
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	8880.1	0.0	8880.1
	% Fixture	50.0	0.0	50.0
Total	Lumens	17760.2	0.0	17760.2
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	338.7	1.9
10°-20°	1032.3	5.8
20°-30°	1725.4	9.7
30°-40°	2379.4	13.4
40°-50°	2916.9	16.4
50°-60°	3418.1	19.2
60°-70°	3795.8	21.4
70°-80°	2064.2	11.6
80°-90°	89.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	17760.2	100.0
0°-180°	17760.2	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360703
CATALOG NUMBER: GSS-SB5A-722-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1548.2	8.7			
FM	(30°-60°)	4357.2	24.5			
FH	(60°-80°)	2930.0	16.5			G2/5000
FVH	(80°-90°)	44.7	0.3			G1/100
BL	(0°-30°)	1548.2	8.7	B3/2500		
BM	(30°-60°)	4357.2	24.5	B3/5000		
BH	(60°-80°)	2930.0	16.5	B4/5000		G4/5000
BVH	(80°-90°)	44.7	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360703
CATALOG NUMBER: GSS-SB5A-722-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	3499.2	3499.2	3499.2	3499.2	3499.2	3499.2	3499.2	3499.2	3499.2	3499.2	3499.2
2.5°	3503.1	3503.1	3491.4	3507.0	3499.2	3503.1	3507.0	3503.1	3499.2	3503.1	3507.0
5°	3522.5	3514.7	3522.5	3530.3	3518.6	3526.4	3522.5	3503.1	3514.7	3514.7	3514.7
7.5°	3557.5	3565.3	3557.5	3577.0	3565.3	3588.6	3565.3	3549.7	3545.9	3542.0	3542.0
10°	3573.1	3573.1	3569.2	3604.2	3611.9	3635.3	3619.7	3596.4	3584.7	3569.2	3553.6
12.5°	3530.3	3538.1	3557.5	3623.6	3654.7	3701.4	3689.7	3643.1	3608.1	3596.4	3573.1
15°	3483.6	3491.4	3530.3	3611.9	3685.8	3755.8	3751.9	3693.6	3650.8	3619.7	3584.7
17.5°	3409.8	3421.4	3475.9	3600.3	3732.5	3810.2	3833.6	3775.2	3728.6	3678.0	3631.4
20°	3285.4	3285.4	3382.6	3542.0	3724.7	3899.7	3961.9	3915.2	3860.8	3779.1	3716.9
22.5°	3145.4	3153.2	3250.4	3460.3	3720.8	3977.4	4097.9	4047.4	3993.0	3903.5	3810.2
25°	3005.4	3005.4	3114.3	3351.5	3670.3	4031.9	4257.4	4230.1	4121.3	4039.6	3919.1
27.5°	2877.1	2877.1	2993.8	3242.6	3584.7	4047.4	4416.8	4416.8	4296.2	4175.7	4043.5
30°	2725.5	2764.4	2896.6	3157.1	3507.0	4020.2	4533.4	4607.3	4498.4	4342.9	4148.5
32.5°	2597.2	2624.4	2760.5	3036.5	3394.2	3989.1	4665.6	4848.3	4735.6	4521.7	4304.0
35°	2445.5	2441.7	2597.2	2869.3	3234.8	3919.1	4770.6	5136.0	5027.2	4797.8	4502.3
37.5°	2247.3	2247.3	2406.7	2671.1	3083.2	3798.6	4856.1	5454.9	5373.2	5112.7	4797.8
40°	2033.4	2056.8	2196.7	2465.0	2900.4	3654.7	4856.1	5715.4	5758.1	5489.9	5163.3
42.5°	1877.9	1885.7	2014.0	2266.7	2698.3	3468.1	4793.9	5940.9	6069.2	5843.7	5419.9
45°	1714.6	1734.0	1842.9	2076.2	2488.3	3246.5	4685.0	6193.6	6399.6	6244.1	5688.1
47.5°	1516.3	1535.8	1660.2	1897.3	2290.0	3005.4	4502.3	6458.0	6889.5	6776.8	6166.4
50°	1286.9	1302.5	1419.1	1671.8	2068.4	2729.4	4272.9	6656.2	7379.4	7492.2	6889.5
52.5°	1007.0	1018.7	1143.1	1388.0	1804.0	2465.0	3950.2	6776.8	7873.2	8269.8	7857.6
55°	723.2	742.6	851.5	1053.6	1454.1	2111.2	3565.3	6839.0	8413.6	9191.2	9059.0
57.5°	521.0	528.8	602.6	758.2	1080.9	1695.2	3071.5	6734.0	8899.6	10291.5	10567.6
60°	431.6	431.6	443.2	517.1	738.7	1197.5	2480.5	6345.2	9315.6	11403.5	12255.0
62.5°	396.6	396.6	404.4	416.0	486.0	777.6	1772.9	5555.9	9362.3	12472.7	14105.7
65°	361.6	361.6	369.4	377.1	392.7	505.4	1069.2	4066.8	8448.6	12484.4	15101.0
67.5°	330.5	330.5	334.4	338.3	346.0	369.4	587.1	2465.0	6761.2	12153.9	15482.0
70°	299.4	299.4	299.4	295.5	307.2	311.0	388.8	1251.9	4521.7	10975.8	15299.3
72.5°	*264.4*	*264.4*	*260.5*	*252.7*	*256.6*	*256.6*	*287.7*	*614.3*	*2348.3*	*8724.7*	*13814.1*
75°	225.5	229.4	213.8	206.1	202.2	206.1	229.4	349.9	1049.8	5291.6	10322.6
77.5°	190.5	198.3	175.0	159.4	155.5	155.5	178.8	217.7	451.0	1920.7	4626.7
80°	143.9	147.7	128.3	112.8	112.8	108.9	132.2	159.4	213.8	571.5	1038.1
82.5°	81.6	81.6	73.9	66.1	62.2	66.1	89.4	108.9	132.2	202.2	283.8
85°	19.4	19.4	23.3	27.2	27.2	35.0	50.5	58.3	70.0	81.6	108.9
87.5°	3.9	3.9	3.9	7.8	11.7	11.7	19.4	27.2	35.0	42.8	46.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360703
CATALOG NUMBER: GSS-SB5A-722-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	3499.2	3499.2	*3499.2*
2.5°	3507.0	3510.9	*3507.0*
5°	3530.3	3522.5	*3510.9*
7.5°	3534.2	3538.1	*3542.0*
10°	3549.7	3565.3	*3542.0*
12.5°	3565.3	3553.6	*3545.9*
15°	3577.0	3573.1	*3549.7*
17.5°	3619.7	3604.2	*3600.3*
20°	3685.8	3681.9	*3670.3*
22.5°	3763.6	3755.8	*3751.9*
25°	3876.3	3849.1	*3833.6*
27.5°	3969.6	3946.3	*3938.5*
30°	4063.0	4016.3	*4016.3*
32.5°	4144.6	4132.9	*4125.2*
35°	4339.0	4280.7	*4288.5*
37.5°	4576.2	4517.9	*4467.3*
40°	4910.5	4832.8	*4801.7*
42.5°	5124.4	5046.6	*5054.4*
45°	5244.9	5108.8	*5073.8*
47.5°	5571.5	5400.4	*5353.8*
50°	6100.3	5890.3	*5832.0*
52.5°	6955.6	6617.4	*6539.6*
55°	8028.7	7612.7	*7534.9*
57.5°	9498.4	8946.3	*8779.1*
60°	11286.9	10602.6	*10349.8*
62.5°	13436.9	12593.2	*12352.2*
65°	15054.3	14350.6	*13977.3*
67.5°	16349.0	15769.7	*15590.9*
70°	17118.8	17146.1	*17192.7*
72.5°	*16228.5*	*16975.0*	*17332.7*
75°	11893.4	12472.7	*13028.7*
77.5°	4595.6	4144.6	*4012.4*
80°	742.6	696.0	*719.3*
82.5°	334.4	353.8	*373.2*
85°	217.7	252.7	*268.3*
87.5°	50.5	50.5	*50.5*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)