Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360707

Luminaire Tested: **GSS-SB6A-722-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360707
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6A-722-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 170W 70CRI 2200K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(156) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	21323.1 lumens
Efficiency:	N/A
Efficacy:	125.4 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	170
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	12.0%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360707
CATALOG NUMBER: GSS-SB6A-722-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 10.5 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360707
CATALOG NUMBER: GSS-SB6A-722-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360707
CATALOG NUMBER: GSS-SB6A-722-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	10661.6	0.0	10661.6
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	10661.6	0.0	10661.6
	% Fixture	50.0	0.0	50.0
Total	Lumens	21323.1	0.0	21323.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	406.6	1.9
10°-20°	1239.4	5.8
20°-30°	2071.5	9.7
30°-40°	2856.8	13.4
40°-50°	3502.0	16.4
50°-60°	4103.9	19.2
60°-70°	4557.3	21.4
70°-80°	2478.3	11.6
80°-90°	107.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	21323.1	100.0
0°-180°	21323.1	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360707
CATALOG NUMBER: GSS-SB6A-722-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1858.8	8.7			
FM	(30°-60°)	5231.3	24.5			
FH	(60°-80°)	3517.8	16.5			G2/5000
FVH	(80°-90°)	53.7	0.3			G1/100
BL	(0°-30°)	1858.8	8.7	B3/2500		
BM	(30°-60°)	5231.3	24.5	B4/8500		
BH	(60°-80°)	3517.8	16.5	B4/5000		G4/5000
BVH	(80°-90°)	53.7	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360707
CATALOG NUMBER: GSS-SB6A-722-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	4201.2	4201.2	4201.2	4201.2	4201.2	4201.2	4201.2	4201.2	4201.2	4201.2	4201.2
2.5°	4205.9	4205.9	4191.8	4210.5	4201.2	4205.9	4210.5	4205.9	4201.2	4205.9	4210.5
5°	4229.2	4219.9	4229.2	4238.5	4224.5	4233.9	4229.2	4205.9	4219.9	4219.9	4219.9
7.5°	4271.2	4280.5	4271.2	4294.5	4280.5	4308.5	4280.5	4261.9	4257.2	4252.5	4252.5
10°	4289.9	4289.9	4285.2	4327.2	4336.6	4364.6	4345.9	4317.9	4303.9	4285.2	4266.5
12.5°	4238.5	4247.9	4271.2	4350.6	4387.9	4443.9	4429.9	4373.9	4331.9	4317.9	4289.9
15°	4182.5	4191.8	4238.5	4336.6	4425.2	4509.3	4504.6	4434.6	4383.2	4345.9	4303.9
17.5°	4093.8	4107.8	4173.2	4322.5	4481.3	4574.6	4602.6	4532.6	4476.6	4415.9	4359.9
20°	3944.4	3944.4	4061.1	4252.5	4471.9	4682.0	4756.7	4700.7	4635.3	4537.3	4462.6
22.5°	3776.4	3785.7	3902.4	4154.5	4467.3	4775.3	4920.1	4859.4	4794.0	4686.7	4574.6
25°	3608.3	3608.3	3739.1	4023.8	4406.6	4840.7	5111.4	5078.8	4948.1	4850.0	4705.3
27.5°	3454.3	3454.3	3594.3	3893.1	4303.9	4859.4	5302.8	5302.8	5158.1	5013.4	4854.7
30°	3272.3	3318.9	3477.6	3790.4	4210.5	4826.7	5442.9	5531.6	5400.9	5214.1	4980.7
32.5°	3118.2	3150.9	3314.3	3645.7	4075.1	4789.3	5601.6	5821.0	5685.6	5428.9	5167.5
35°	2936.2	2931.5	3118.2	3445.0	3883.8	4705.3	5727.6	6166.4	6035.7	5760.3	5405.5
37.5°	2698.1	2698.1	2889.5	3206.9	3701.7	4560.6	5830.3	6549.2	6451.1	6138.4	5760.3
40°	2441.4	2469.4	2637.4	2959.5	3482.3	4387.9	5830.3	6861.9	6913.3	6591.2	6199.1
42.5°	2254.6	2264.0	2418.0	2721.4	3239.6	4163.8	5755.6	7132.7	7286.7	7016.0	6507.2
45°	2058.6	2081.9	2212.6	2492.7	2987.5	3897.8	5624.9	7436.1	7683.5	7496.8	6829.3
47.5°	1820.5	1843.9	1993.2	2278.0	2749.4	3608.3	5405.5	7753.5	8271.7	8136.3	7403.4
50°	1545.1	1563.8	1703.8	2007.2	2483.4	3276.9	5130.1	7991.6	8859.8	8995.2	8271.7
52.5°	1209.0	1223.0	1372.4	1666.5	2165.9	2959.5	4742.7	8136.3	9452.7	9928.8	9434.0
55°	868.2	891.6	1022.3	1265.0	1745.8	2534.7	4280.5	8211.0	10101.5	11035.1	10876.4
57.5°	625.5	634.8	723.5	910.3	1297.7	2035.2	3687.7	8084.9	10685.0	12356.1	12687.6
60°	518.1	518.1	532.1	620.8	886.9	1437.7	2978.2	7618.1	11184.5	13691.2	14713.5
62.5°	476.1	476.1	485.5	499.5	583.5	933.6	2128.6	6670.5	11240.5	14974.9	16935.4
65°	434.1	434.1	443.5	452.8	471.5	606.8	1283.7	4882.7	10143.5	14988.9	18130.4
67.5°	396.8	396.8	401.4	406.1	415.5	443.5	704.9	2959.5	8117.6	14592.1	18587.9
70°	359.4	359.4	359.4	354.8	368.8	373.4	466.8	1503.1	5428.9	13177.7	18368.5
72.5°	*317.4*	*317.4*	*312.8*	*303.4*	*308.1*	*308.1*	*345.4*	*737.5*	*2819.5*	*10474.9*	*16585.3*
75°	270.7	275.4	256.7	247.4	242.7	247.4	275.4	420.1	1260.4	6353.1	12393.5
77.5°	228.7	238.1	210.1	191.4	186.7	186.7	214.7	261.4	541.5	2306.0	5554.9
80°	172.7	177.4	154.0	135.4	135.4	130.7	158.7	191.4	256.7	686.2	1246.4
82.5°	98.0	98.0	88.7	79.4	74.7	79.4	107.4	130.7	158.7	242.7	340.8
85°	23.3	23.3	28.0	32.7	32.7	42.0	60.7	70.0	84.0	98.0	130.7
87.5°	4.7	4.7	4.7	9.3	14.0	14.0	23.3	32.7	42.0	51.3	56.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360707
CATALOG NUMBER: GSS-SB6A-722-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	4201.2	4201.2	*4201.2*
2.5°	4210.5	4215.2	*4210.5*
5°	4238.5	4229.2	*4215.2*
7.5°	4243.2	4247.9	*4252.5*
10°	4261.9	4280.5	*4252.5*
12.5°	4280.5	4266.5	*4257.2*
15°	4294.5	4289.9	*4261.9*
17.5°	4345.9	4327.2	*4322.5*
20°	4425.2	4420.6	*4406.6*
22.5°	4518.6	4509.3	*4504.6*
25°	4654.0	4621.3	*4602.6*
27.5°	4766.0	4738.0	*4728.7*
30°	4878.0	4822.0	*4822.0*
32.5°	4976.1	4962.1	*4952.7*
35°	5209.5	5139.4	*5148.8*
37.5°	5494.2	5424.2	*5363.5*
40°	5895.7	5802.3	*5765.0*
42.5°	6152.4	6059.0	*6068.4*
45°	6297.1	6133.7	*6091.7*
47.5°	6689.2	6483.8	*6427.8*
50°	7324.1	7072.0	*7002.0*
52.5°	8351.0	7944.9	*7851.5*
55°	9639.4	9139.9	*9046.5*
57.5°	11403.9	10741.0	*10540.3*
60°	13551.1	12729.6	*12426.2*
62.5°	16132.5	15119.6	*14830.2*
65°	18074.4	17229.5	*16781.4*
67.5°	19628.9	18933.3	*18718.6*
70°	20553.1	20585.8	*20641.8*
72.5°	*19484.2*	*20380.4*	*20809.9*
75°	14279.4	14974.9	*15642.4*
77.5°	5517.6	4976.1	*4817.4*
80°	891.6	835.6	*863.6*
82.5°	401.4	424.8	*448.1*
85°	261.4	303.4	*322.1*
87.5°	60.7	60.7	*60.7*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)