Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360324

Luminaire Tested: **GSS-SB6B-722-U-T3-HSS**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360324
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6B-722-U-T3-HSS
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 219W 70CRI 2200K FIXTURE w/ TYPE III DISTRIBUTION OPTIC AND HOUSE SIDE SHIELD
Light Source:	(156) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	19738.1 lumens
Efficiency:	N/A
Efficacy:	90.1 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type III - Short
BUG Rating:	B2 - U0 - G3


Input Watts (W):	219
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	8.7%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360324
CATALOG NUMBER: GSS-SB6B-722-U-T3-HSS

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 9 fc
Type III - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360324
CATALOG NUMBER: GSS-SB6B-722-U-T3-HSS

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360324
CATALOG NUMBER: GSS-SB6B-722-U-T3-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2360.1	0.0	2360.1
	% Fixture	12.0	0.0	12.0
Street Side	Lumens	17378.0	0.0	17378.0
	% Fixture	88.0	0.0	88.0
Total	Lumens	19738.1	0.0	19738.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.9	1.3
10°-20°	658.0	3.3
20°-30°	1172.9	5.9
30°-40°	2099.2	10.6
40°-50°	3306.8	16.8
50°-60°	4809.5	24.4
60°-70°	5233.0	26.5
70°-80°	2114.0	10.7
80°-90°	88.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	19738.1	100.0
0°-180°	19738.1	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360324
CATALOG NUMBER: GSS-SB6B-722-U-T3-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1391.8	7.1			
FM	(30°-60°)	8910.3	45.1			
FH	(60°-80°)	7003.8	35.5			G3/7500
FVH	(80°-90°)	72.1	0.4			G1/100
BL	(0°-30°)	695.0	3.5	B2/1000		
BM	(30°-60°)	1305.2	6.6	B2/2500		
BH	(60°-80°)	343.1	1.7	B1/500		G1/500
BVH	(80°-90°)	16.7	0.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3
Type III Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360324
CATALOG NUMBER: GSS-SB6B-722-U-T3-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	51°	55°	65°	75°	85°
0°	2802.8	2802.8	2802.8	2802.8	2802.8	2802.8	*2802.8*	2802.8	2802.8	2802.8	2802.8
2.5°	2826.4	2820.5	2826.4	2802.8	2814.6	2820.5	*2832.3*	2814.6	2808.7	2814.6	2808.7
5°	2814.6	2808.7	2814.6	2820.5	2832.3	2850.1	*2844.2*	2844.2	2856.0	2832.3	2832.3
7.5°	2714.1	2708.2	2743.6	2755.5	2802.8	2844.2	*2891.5*	2873.7	2897.4	2891.5	2873.7
10°	2589.9	2572.2	2607.6	2672.7	2743.6	2850.1	*2897.4*	2909.2	2962.4	2986.1	2974.2
12.5°	2518.9	2501.2	2548.5	2595.8	2708.2	2838.3	*2921.0*	2950.6	3009.7	3057.0	3068.9
15°	2465.7	2483.5	2530.8	2619.5	2725.9	2861.9	*2932.9*	2992.0	3116.2	3163.5	3163.5
17.5°	2501.2	2495.3	2536.7	2625.4	2755.5	2891.5	*2997.9*	3057.0	3204.9	3269.9	3264.0
20°	2850.1	2814.6	2808.7	2761.4	2802.8	2962.4	*3092.5*	3151.6	3293.6	3382.2	3376.3
22.5°	3299.5	3334.9	3240.3	3133.9	3003.8	3057.0	*3193.0*	3275.8	3417.7	3512.3	3476.9
25°	3908.5	3890.8	3825.7	3612.9	3376.3	3264.0	*3334.9*	3417.7	3595.1	3672.0	3612.9
27.5°	4553.0	4476.2	4393.4	4097.7	3784.3	3577.4	*3589.2*	3642.4	3849.4	3896.7	3760.7
30°	5244.9	5256.7	5120.7	4718.6	4286.9	3973.6	*3949.9*	3973.6	4139.1	4133.2	3944.0
32.5°	6037.2	6007.6	5877.5	5445.9	4966.9	4452.5	*4393.4*	4352.0	4422.9	4357.9	4139.1
35°	6593.0	6622.6	6480.7	6196.8	5717.9	5079.3	*4937.4*	4836.9	4765.9	4694.9	4458.4
37.5°	7089.7	7054.2	6971.5	6811.8	6344.7	5759.3	*5487.3*	5398.6	5244.9	5049.7	4830.9
40°	7202.1	7184.3	7142.9	7148.8	6847.3	6392.0	*6196.8*	6037.2	5771.1	5611.5	5327.6
42.5°	7184.3	7243.5	7255.3	7302.6	7131.1	7018.8	*6817.7*	6664.0	6415.6	6220.5	5924.8
45°	7278.9	7379.5	7462.2	7503.6	7391.3	7379.5	*7403.1*	7332.1	7160.7	6959.6	6622.6
47.5°	7468.1	7639.6	7769.7	7858.4	7834.8	8029.9	*7905.7*	7888.0	7958.9	7763.8	7426.8
50°	7822.9	7870.2	8177.7	8307.8	8526.6	8810.4	*8568.0*	8627.1	8769.0	8786.8	8165.9
52.5°	8089.0	8130.4	8437.9	8822.2	9307.1	9620.5	*9401.7*	9395.8	9650.1	9721.0	8881.4
55°	8160.0	8254.6	8650.8	9318.9	10229.5	10548.8	*10395.1*	10341.9	10678.9	10803.1	9514.1
57.5°	8059.4	8094.9	8662.6	9626.4	10897.7	11589.5	*11636.8*	11471.3	11778.7	11808.3	9981.2
60°	6971.5	7125.2	8118.6	9821.5	11465.3	12718.9	*12967.3*	12872.6	12896.3	12843.1	10330.0
62.5°	4819.1	4848.7	6309.2	9614.6	11932.5	13860.1	*14274.0*	14203.1	14002.0	13499.4	10152.7
65°	2294.3	2453.9	3388.2	8136.3	11997.5	14729.3	*15533.5*	15580.8	14646.6	13505.3	9466.7
67.5°	*1578.8*	*1584.7*	*1803.5*	*5741.5*	*10176.3*	*14977.7*	*16207.6*	*15988.8*	*14587.4*	*13381.2*	*8627.1*
70°	999.3	928.3	1040.7	3275.8	6876.8	11761.0	*14457.3*	15226.0	14339.1	12571.1	7290.8
72.5°	396.2	425.7	490.8	1076.2	3370.4	6699.5	*9443.1*	11589.5	12931.8	10874.0	5694.2
75°	177.4	189.2	248.3	449.4	869.2	2731.8	*3654.2*	5120.7	10347.8	8585.7	4032.7
77.5°	118.3	124.2	159.7	260.2	396.2	762.8	*1336.3*	1567.0	6202.8	4694.9	1892.2
80°	71.0	76.9	106.4	159.7	218.8	272.0	*408.0*	473.0	1637.9	1555.1	520.3
82.5°	47.3	41.4	71.0	88.7	130.1	112.3	*130.1*	153.7	449.4	396.2	141.9
85°	17.7	17.7	29.6	35.5	47.3	59.1	*53.2*	65.0	106.4	106.4	65.0
87.5°	0.0	0.0	5.9	5.9	17.7	23.7	*29.6*	29.6	41.4	41.4	35.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360324
CATALOG NUMBER: GSS-SB6B-722-U-T3-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2802.8	2802.8	2802.8	2802.8	2802.8	2802.8	2802.8	2802.8	2802.8	2802.8	2802.8
2.5°	2814.6	2796.9	2802.8	2790.9	2796.9	2785.0	2761.4	2785.0	2767.3	2767.3	2785.0
5°	2832.3	2826.4	2808.7	2779.1	2761.4	2720.0	2654.9	2625.4	2595.8	2578.1	2589.9
7.5°	2891.5	2867.8	2838.3	2767.3	2672.7	2548.5	2418.4	2270.6	2158.3	2146.4	2105.0
10°	2968.3	2944.7	2879.6	2720.0	2524.9	2170.1	1886.3	1691.1	1572.9	1496.0	1466.4
12.5°	3068.9	3039.3	2921.0	2649.0	2170.1	1673.4	1336.3	1194.4	1153.0	1135.3	1129.4
15°	3163.5	3128.0	2921.0	2418.4	1756.2	1259.5	1088.0	1052.5	1046.6	1052.5	1046.6
17.5°	3252.2	3204.9	2891.5	2105.0	1348.2	1064.3	1023.0	1005.2	999.3	993.4	993.4
20°	3358.6	3281.7	2808.7	1762.1	1111.6	1011.1	993.4	969.7	969.7	946.1	952.0
22.5°	3459.1	3352.7	2649.0	1419.1	1023.0	981.6	963.8	940.2	928.3	910.6	910.6
25°	3559.6	3423.6	2459.8	1176.7	969.7	952.0	934.3	910.6	881.0	857.4	857.4
27.5°	3707.5	3518.2	2235.1	1076.2	940.2	910.6	892.9	863.3	827.8	798.3	798.3
30°	3873.0	3648.3	2051.8	1058.4	928.3	857.4	827.8	780.5	756.9	733.2	733.2
32.5°	4074.1	3825.7	1915.8	1088.0	898.8	786.4	739.1	691.8	674.1	674.1	674.1
35°	4369.7	4085.9	1768.0	1093.9	863.3	715.5	638.6	591.3	591.3	615.0	615.0
37.5°	4765.9	4369.7	1691.1	1082.1	833.7	644.5	555.8	520.3	514.4	538.1	538.1
40°	5221.2	4683.1	1720.7	1040.7	792.3	573.6	490.8	461.2	455.3	461.2	467.1
42.5°	5717.9	5020.2	1791.6	981.6	721.4	514.4	443.5	425.7	419.8	419.8	419.8
45°	6244.2	5250.8	1862.6	922.4	650.4	467.1	413.9	402.1	396.2	396.2	396.2
47.5°	6746.8	5434.1	1815.3	869.2	591.3	437.6	390.3	390.3	384.3	384.3	384.3
50°	7178.4	5416.3	1614.3	816.0	526.3	413.9	378.4	372.5	372.5	366.6	366.6
52.5°	7420.8	5055.6	1300.9	756.9	467.1	390.3	366.6	360.7	354.8	348.9	348.9
55°	7515.5	4576.7	1011.1	668.2	425.7	372.5	354.8	348.9	337.0	331.1	325.2
57.5°	7349.9	3873.0	780.5	532.2	390.3	348.9	337.0	331.1	319.3	301.6	295.7
60°	7012.8	3104.3	585.4	408.0	348.9	319.3	319.3	313.4	289.7	260.2	254.3
62.5°	6421.5	2229.2	443.5	331.1	301.6	289.7	301.6	289.7	254.3	212.9	207.0
65°	5587.8	1377.7	343.0	283.8	266.1	254.3	272.0	260.2	218.8	171.5	159.7
67.5°	*4671.3*	*703.6*	*266.1*	*242.4*	*224.7*	*212.9*	*230.6*	*230.6*	*189.2*	*141.9*	*136.0*
70°	3606.9	390.3	212.9	201.0	183.3	165.6	195.1	201.0	165.6	124.2	118.3
72.5°	2678.6	248.3	171.5	165.6	141.9	118.3	159.7	171.5	141.9	94.6	88.7
75°	1750.3	195.1	130.1	130.1	100.5	94.6	136.0	147.8	124.2	71.0	71.0
77.5°	839.6	147.8	100.5	88.7	71.0	71.0	118.3	124.2	88.7	53.2	53.2
80°	277.9	100.5	71.0	59.1	47.3	47.3	94.6	71.0	47.3	41.4	41.4
82.5°	94.6	65.0	47.3	41.4	35.5	29.6	29.6	35.5	35.5	29.6	29.6
85°	47.3	41.4	35.5	29.6	23.7	23.7	23.7	23.7	29.6	29.6	29.6
87.5°	29.6	29.6	23.7	17.7	17.7	17.7	17.7	17.7	23.7	11.8	11.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)