Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360689

Luminaire Tested: **GSS-SB1C-722-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360689
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB1C-722-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 1SQUARE 52W 70CRI 2200K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(26) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	5523.8 lumens
Efficiency:	N/A
Efficacy:	106.2 lumens/watt
Luminous Opening:	Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B2 - U0 - G2


Input Watts (W):	52
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	10.1%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360689
CATALOG NUMBER: GSS-SB1C-722-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 2.7 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360689
CATALOG NUMBER: GSS-SB1C-722-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360689
CATALOG NUMBER: GSS-SB1C-722-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2761.9	0.0	2761.9
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	2761.9	0.0	2761.9
	% Fixture	50.0	0.0	50.0
Total	Lumens	5523.8	0.0	5523.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.3	1.9
10°-20°	321.1	5.8
20°-30°	536.6	9.7
30°-40°	740.0	13.4
40°-50°	907.2	16.4
50°-60°	1063.1	19.2
60°-70°	1180.6	21.4
70°-80°	642.0	11.6
80°-90°	27.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5523.8	100.0
0°-180°	5523.8	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360689
CATALOG NUMBER: GSS-SB1C-722-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	481.5	8.7			
FM	(30°-60°)	1355.2	24.5			
FH	(60°-80°)	911.3	16.5			G1/1800
FVH	(80°-90°)	13.9	0.3			G1/100
BL	(0°-30°)	481.5	8.7	B1/500		
BM	(30°-60°)	1355.2	24.5	B2/2500		
BH	(60°-80°)	911.3	16.5	B2/1000		G2/1000
BVH	(80°-90°)	13.9	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360689
CATALOG NUMBER: GSS-SB1C-722-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	1088.3	1088.3	1088.3	1088.3	1088.3	1088.3	1088.3	1088.3	1088.3	1088.3	1088.3
2.5°	1089.5	1089.5	1085.9	1090.7	1088.3	1089.5	1090.7	1089.5	1088.3	1089.5	1090.7
5°	1095.6	1093.2	1095.6	1098.0	1094.4	1096.8	1095.6	1089.5	1093.2	1093.2	1093.2
7.5°	1106.5	1108.9	1106.5	1112.5	1108.9	1116.1	1108.9	1104.0	1102.8	1101.6	1101.6
10°	1111.3	1111.3	1110.1	1121.0	1123.4	1130.6	1125.8	1118.5	1114.9	1110.1	1105.2
12.5°	1098.0	1100.4	1106.5	1127.0	1136.7	1151.2	1147.6	1133.1	1122.2	1118.5	1111.3
15°	1083.5	1085.9	1098.0	1123.4	1146.4	1168.1	1166.9	1148.8	1135.5	1125.8	1114.9
17.5°	1060.5	1064.1	1081.1	1119.8	1160.9	1185.1	1192.3	1174.2	1159.7	1143.9	1129.4
20°	1021.8	1021.8	1052.0	1101.6	1158.5	1212.9	1232.2	1217.7	1200.8	1175.4	1156.0
22.5°	978.3	980.7	1010.9	1076.2	1157.2	1237.1	1274.5	1258.8	1241.9	1214.1	1185.1
25°	934.7	934.7	968.6	1042.4	1141.5	1254.0	1324.1	1315.7	1281.8	1256.4	1218.9
27.5°	894.8	894.8	931.1	1008.5	1114.9	1258.8	1373.7	1373.7	1336.2	1298.7	1257.6
30°	847.7	859.8	900.9	981.9	1090.7	1250.4	1410.0	1432.9	1399.1	1350.7	1290.3
32.5°	807.8	816.2	858.6	944.4	1055.7	1240.7	1451.1	1507.9	1472.9	1406.3	1338.6
35°	760.6	759.4	807.8	892.4	1006.1	1218.9	1483.7	1597.4	1563.5	1492.2	1400.3
37.5°	698.9	698.9	748.5	830.7	958.9	1181.4	1510.3	1696.6	1671.2	1590.1	1492.2
40°	632.4	639.7	683.2	766.7	902.1	1136.7	1510.3	1777.6	1790.9	1707.4	1605.9
42.5°	584.1	586.5	626.4	705.0	839.2	1078.6	1491.0	1847.7	1887.6	1817.5	1685.7
45°	533.3	539.3	573.2	645.7	773.9	1009.7	1457.1	1926.3	1990.4	1942.0	1769.1
47.5°	471.6	477.6	516.3	590.1	712.2	934.7	1400.3	2008.5	2142.8	2107.7	1917.9
50°	400.3	405.1	441.4	520.0	643.3	848.9	1329.0	2070.2	2295.1	2330.2	2142.8
52.5°	313.2	316.8	355.5	431.7	561.1	766.7	1228.6	2107.7	2448.7	2572.1	2443.9
55°	224.9	231.0	264.8	327.7	452.3	656.6	1108.9	2127.1	2616.8	2858.6	2817.5
57.5°	162.0	164.5	187.4	235.8	336.2	527.2	955.3	2094.4	2767.9	3200.9	3286.7
60°	134.2	134.2	137.9	160.8	229.8	372.4	771.5	1973.5	2897.3	3546.7	3811.5
62.5°	123.3	123.3	125.8	129.4	151.2	241.8	551.4	1728.0	2911.8	3879.2	4387.1
65°	112.5	112.5	114.9	117.3	122.1	157.2	332.5	1264.9	2627.7	3882.9	4696.7
67.5°	102.8	102.8	104.0	105.2	107.6	114.9	182.6	766.7	2102.9	3780.1	4815.2
70°	93.1	93.1	93.1	91.9	95.5	96.7	120.9	389.4	1406.3	3413.7	4758.4
72.5°	*82.2*	*82.2*	*81.0*	*78.6*	*79.8*	*79.8*	*89.5*	*191.1*	*730.4*	*2713.5*	*4296.4*
75°	70.1	71.3	66.5	64.1	62.9	64.1	71.3	108.8	326.5	1645.8	3210.5
77.5°	59.3	61.7	54.4	49.6	48.4	48.4	55.6	67.7	140.3	597.4	1439.0
80°	44.7	46.0	39.9	35.1	35.1	33.9	41.1	49.6	66.5	177.8	322.9
82.5°	25.4	25.4	23.0	20.6	19.3	20.6	27.8	33.9	41.1	62.9	88.3
85°	6.0	6.0	7.3	8.5	8.5	10.9	15.7	18.1	21.8	25.4	33.9
87.5°	1.2	1.2	1.2	2.4	3.6	3.6	6.0	8.5	10.9	13.3	14.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360689
CATALOG NUMBER: GSS-SB1C-722-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	1088.3	1088.3	*1088.3*
2.5°	1090.7	1091.9	*1090.7*
5°	1098.0	1095.6	*1091.9*
7.5°	1099.2	1100.4	*1101.6*
10°	1104.0	1108.9	*1101.6*
12.5°	1108.9	1105.2	*1102.8*
15°	1112.5	1111.3	*1104.0*
17.5°	1125.8	1121.0	*1119.8*
20°	1146.4	1145.1	*1141.5*
22.5°	1170.5	1168.1	*1166.9*
25°	1205.6	1197.1	*1192.3*
27.5°	1234.6	1227.4	*1225.0*
30°	1263.7	1249.1	*1249.1*
32.5°	1289.0	1285.4	*1283.0*
35°	1349.5	1331.4	*1333.8*
37.5°	1423.3	1405.1	*1389.4*
40°	1527.3	1503.1	*1493.4*
42.5°	1593.8	1569.6	*1572.0*
45°	1631.3	1588.9	*1578.1*
47.5°	1732.8	1679.6	*1665.1*
50°	1897.3	1832.0	*1813.9*
52.5°	2163.3	2058.1	*2033.9*
55°	2497.1	2367.7	*2343.5*
57.5°	2954.2	2782.5	*2730.5*
60°	3510.4	3297.6	*3219.0*
62.5°	4179.1	3916.7	*3841.8*
65°	4682.2	4463.3	*4347.2*
67.5°	5084.9	4904.7	*4849.0*
70°	5324.3	5332.7	*5347.3*
72.5°	*5047.4*	*5279.5*	*5390.8*
75°	3699.1	3879.2	*4052.2*
77.5°	1429.3	1289.0	*1247.9*
80°	231.0	216.5	*223.7*
82.5°	104.0	110.0	*116.1*
85°	67.7	78.6	*83.4*
87.5°	15.7	15.7	*15.7*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)