Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360696

Luminaire Tested: **GSS-SB3B-722-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360696
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB3B-722-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 3SQUARE 109W 70CRI 2200K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(78) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	12883 lumens
Efficiency:	N/A
Efficacy:	118.2 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B3 - U0 - G3


Input Watts (W):	109
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	8.7%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360696
CATALOG NUMBER: GSS-SB3B-722-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 6.3 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360696
CATALOG NUMBER: GSS-SB3B-722-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360696
CATALOG NUMBER: GSS-SB3B-722-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	6441.5	0.0	6441.5
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	6441.5	0.0	6441.5
	% Fixture	50.0	0.0	50.0
Total	Lumens	12883.0	0.0	12883.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.7	1.9
10°-20°	748.8	5.8
20°-30°	1251.6	9.7
30°-40°	1726.0	13.4
40°-50°	2115.9	16.4
50°-60°	2479.5	19.2
60°-70°	2753.4	21.4
70°-80°	1497.3	11.6
80°-90°	64.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	12883.0	100.0
0°-180°	12883.0	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360696
CATALOG NUMBER: GSS-SB3B-722-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1123.0	8.7			
FM	(30°-60°)	3160.7	24.5			
FH	(60°-80°)	2125.4	16.5			G2/5000
FVH	(80°-90°)	32.4	0.3			G1/100
BL	(0°-30°)	1123.0	8.7	B3/2500		
BM	(30°-60°)	3160.7	24.5	B3/5000		
BH	(60°-80°)	2125.4	16.5	B3/2500		G3/2500
BVH	(80°-90°)	32.4	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360696
CATALOG NUMBER: GSS-SB3B-722-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	2538.3	2538.3	2538.3	2538.3	2538.3	2538.3	2538.3	2538.3	2538.3	2538.3	2538.3
2.5°	2541.1	2541.1	2532.6	2543.9	2538.3	2541.1	2543.9	2541.1	2538.3	2541.1	2543.9
5°	2555.2	2549.6	2555.2	2560.8	2552.4	2558.0	2555.2	2541.1	2549.6	2549.6	2549.6
7.5°	2580.6	2586.2	2580.6	2594.7	2586.2	2603.1	2586.2	2574.9	2572.1	2569.3	2569.3
10°	2591.9	2591.9	2589.0	2614.4	2620.1	2637.0	2625.7	2608.8	2600.3	2589.0	2577.8
12.5°	2560.8	2566.5	2580.6	2628.5	2651.1	2684.9	2676.5	2642.6	2617.2	2608.8	2591.9
15°	2527.0	2532.6	2560.8	2620.1	2673.7	2724.4	2721.6	2679.3	2648.3	2625.7	2600.3
17.5°	2473.4	2481.9	2521.4	2611.6	2707.5	2763.9	2780.8	2738.5	2704.7	2668.0	2634.2
20°	2383.2	2383.2	2453.7	2569.3	2701.9	2828.8	2873.9	2840.1	2800.6	2741.3	2696.2
22.5°	2281.6	2287.3	2357.8	2510.1	2699.0	2885.2	2972.6	2935.9	2896.5	2831.6	2763.9
25°	2180.1	2180.1	2259.1	2431.1	2662.4	2924.7	3088.2	3068.5	2989.5	2930.3	2842.9
27.5°	2087.0	2087.0	2171.6	2352.1	2600.3	2935.9	3203.9	3203.9	3116.4	3029.0	2933.1
30°	1977.0	2005.2	2101.1	2290.1	2543.9	2916.2	3288.5	3342.1	3263.1	3150.3	3009.3
32.5°	1884.0	1903.7	2002.4	2202.7	2462.1	2893.6	3384.4	3516.9	3435.1	3280.0	3122.1
35°	1774.0	1771.2	1884.0	2081.4	2346.5	2842.9	3460.5	3725.6	3646.7	3480.3	3265.9
37.5°	1630.1	1630.1	1745.8	1937.6	2236.5	2755.4	3522.6	3956.9	3897.7	3708.7	3480.3
40°	1475.0	1491.9	1593.5	1788.1	2104.0	2651.1	3522.6	4145.9	4176.9	3982.3	3745.4
42.5°	1362.2	1367.8	1460.9	1644.2	1957.3	2515.7	3477.4	4309.4	4402.5	4238.9	3931.5
45°	1243.8	1257.9	1336.8	1506.0	1805.0	2355.0	3398.5	4492.8	4642.2	4529.4	4126.1
47.5°	1099.9	1114.0	1204.3	1376.3	1661.2	2180.1	3265.9	4684.5	4997.6	4915.8	4473.0
50°	933.5	944.8	1029.4	1212.7	1500.4	1979.9	3099.5	4828.4	5352.9	5434.7	4997.6
52.5°	730.5	738.9	829.2	1006.9	1308.6	1788.1	2865.4	4915.8	5711.1	5998.8	5699.8
55°	524.6	538.7	617.6	764.3	1054.8	1531.4	2586.2	4960.9	6103.1	6667.2	6571.3
57.5°	377.9	383.6	437.1	550.0	784.0	1229.7	2228.0	4884.8	6455.7	7465.4	7665.6
60°	313.1	313.1	321.5	375.1	535.9	868.7	1799.4	4602.7	6757.5	8272.0	8889.6
62.5°	287.7	287.7	293.3	301.8	352.5	564.1	1286.1	4030.2	6791.3	9047.6	10232.1
65°	262.3	262.3	267.9	273.6	284.9	366.6	775.6	2950.0	6128.5	9056.0	10954.1
67.5°	239.7	239.7	242.5	245.4	251.0	267.9	425.9	1788.1	4904.5	8816.3	11230.5
70°	217.2	217.2	217.2	214.3	222.8	225.6	282.0	908.1	3280.0	7961.7	11097.9
72.5°	*191.8*	*191.8*	*189.0*	*183.3*	*186.1*	*186.1*	*208.7*	*445.6*	*1703.5*	*6328.8*	*10020.6*
75°	163.6	166.4	155.1	149.5	146.7	149.5	166.4	253.8	761.5	3838.4	7487.9
77.5°	138.2	143.8	126.9	115.6	112.8	112.8	129.7	157.9	327.2	1393.2	3356.2
80°	104.4	107.2	93.1	81.8	81.8	79.0	95.9	115.6	155.1	414.6	753.0
82.5°	59.2	59.2	53.6	47.9	45.1	47.9	64.9	79.0	95.9	146.7	205.9
85°	14.1	14.1	16.9	19.7	19.7	25.4	36.7	42.3	50.8	59.2	79.0
87.5°	2.8	2.8	2.8	5.6	8.5	8.5	14.1	19.7	25.4	31.0	33.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360696
CATALOG NUMBER: GSS-SB3B-722-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	2538.3	2538.3	*2538.3*
2.5°	2543.9	2546.7	*2543.9*
5°	2560.8	2555.2	*2546.7*
7.5°	2563.7	2566.5	*2569.3*
10°	2574.9	2586.2	*2569.3*
12.5°	2586.2	2577.8	*2572.1*
15°	2594.7	2591.9	*2574.9*
17.5°	2625.7	2614.4	*2611.6*
20°	2673.7	2670.8	*2662.4*
22.5°	2730.1	2724.4	*2721.6*
25°	2811.8	2792.1	*2780.8*
27.5°	2879.5	2862.6	*2857.0*
30°	2947.2	2913.4	*2913.4*
32.5°	3006.4	2998.0	*2992.3*
35°	3147.5	3105.2	*3110.8*
37.5°	3319.5	3277.2	*3240.5*
40°	3562.1	3505.6	*3483.1*
42.5°	3717.2	3660.8	*3666.4*
45°	3804.6	3705.9	*3680.5*
47.5°	4041.5	3917.4	*3883.6*
50°	4425.1	4272.8	*4230.5*
52.5°	5045.5	4800.2	*4743.8*
55°	5823.9	5522.2	*5465.8*
57.5°	6890.0	6489.5	*6368.3*
60°	8187.4	7691.0	*7507.7*
62.5°	9747.0	9135.0	*8960.1*
65°	10920.2	10409.8	*10139.0*
67.5°	11859.4	11439.2	*11309.4*
70°	12417.8	12437.6	*12471.4*
72.5°	*11772.0*	*12313.5*	*12572.9*
75°	8627.3	9047.6	*9450.9*
77.5°	3333.6	3006.4	*2910.6*
80°	538.7	504.8	*521.8*
82.5°	242.5	256.6	*270.7*
85°	157.9	183.3	*194.6*
87.5°	36.7	36.7	*36.7*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)