Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360700

Luminaire Tested: **GSS-SB4B-722-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360700
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB4B-722-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 4SQUARE 148W 70CRI 2200K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(104) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	17910.3 lumens
Efficiency:	N/A
Efficacy:	121.0 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	148
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	13.6%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360700
CATALOG NUMBER: GSS-SB4B-722-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 8.8 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360700
CATALOG NUMBER: GSS-SB4B-722-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360700
CATALOG NUMBER: GSS-SB4B-722-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	8955.2	0.0	8955.2
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	8955.2	0.0	8955.2
	% Fixture	50.0	0.0	50.0
Total	Lumens	17910.3	0.0	17910.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	341.6	1.9
10°-20°	1041.0	5.8
20°-30°	1740.0	9.7
30°-40°	2399.5	13.4
40°-50°	2941.5	16.4
50°-60°	3447.0	19.2
60°-70°	3827.9	21.4
70°-80°	2081.6	11.6
80°-90°	90.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	17910.3	100.0
0°-180°	17910.3	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360700
CATALOG NUMBER: GSS-SB4B-722-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1561.3	8.7			
FM	(30°-60°)	4394.0	24.5			
FH	(60°-80°)	2954.7	16.5			G2/5000
FVH	(80°-90°)	45.1	0.3			G1/100
BL	(0°-30°)	1561.3	8.7	B3/2500		
BM	(30°-60°)	4394.0	24.5	B3/5000		
BH	(60°-80°)	2954.7	16.5	B4/5000		G4/5000
BVH	(80°-90°)	45.1	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360700
CATALOG NUMBER: GSS-SB4B-722-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	3528.8	3528.8	3528.8	3528.8	3528.8	3528.8	3528.8	3528.8	3528.8	3528.8	3528.8
2.5°	3532.7	3532.7	3520.9	3536.6	3528.8	3532.7	3536.6	3532.7	3528.8	3532.7	3536.6
5°	3552.3	3544.5	3552.3	3560.2	3548.4	3556.2	3552.3	3532.7	3544.5	3544.5	3544.5
7.5°	3587.6	3595.4	3587.6	3607.2	3595.4	3619.0	3595.4	3579.8	3575.8	3571.9	3571.9
10°	3603.3	3603.3	3599.4	3634.6	3642.5	3666.0	3650.3	3626.8	3615.0	3599.4	3583.7
12.5°	3560.2	3568.0	3587.6	3654.3	3685.6	3732.7	3720.9	3673.9	3638.6	3626.8	3603.3
15°	3513.1	3520.9	3560.2	3642.5	3717.0	3787.6	3783.6	3724.8	3681.7	3650.3	3615.0
17.5°	3438.6	3450.4	3505.3	3630.7	3764.0	3842.5	3866.0	3807.2	3760.1	3709.1	3662.1
20°	3313.1	3313.1	3411.2	3571.9	3756.2	3932.6	3995.4	3948.3	3893.4	3811.1	3748.4
22.5°	3172.0	3179.8	3277.8	3489.6	3752.3	4011.1	4132.6	4081.6	4026.7	3936.6	3842.5
25°	3030.8	3030.8	3140.6	3379.8	3701.3	4065.9	4293.4	4265.9	4156.1	4073.8	3952.2
27.5°	2901.4	2901.4	3019.1	3270.0	3615.0	4081.6	4454.1	4454.1	4332.6	4211.0	4077.7
30°	2748.5	2787.7	2921.0	3183.7	3536.6	4054.2	4571.7	4646.2	4536.4	4379.6	4183.6
32.5°	2619.1	2646.6	2783.8	3062.2	3422.9	4022.8	4705.0	4889.3	4775.6	4560.0	4340.4
35°	2466.2	2462.3	2619.1	2893.6	3262.2	3952.2	4810.9	5179.5	5069.7	4838.4	4540.4
37.5°	2266.3	2266.3	2427.0	2693.6	3109.3	3830.7	4897.2	5501.0	5418.6	5155.9	4838.4
40°	2050.6	2074.1	2215.3	2485.8	2925.0	3685.6	4897.2	5763.7	5806.8	5536.3	5206.9
42.5°	1893.8	1901.6	2031.0	2285.9	2721.1	3497.4	4834.4	5991.1	6120.5	5893.1	5465.7
45°	1729.1	1748.7	1858.5	2093.7	2509.4	3273.9	4724.7	6245.9	6453.8	6296.9	5736.2
47.5°	1529.1	1548.7	1674.2	1913.4	2309.4	3030.8	4540.4	6512.6	6947.8	6834.1	6218.5
50°	1297.8	1313.5	1431.1	1686.0	2085.9	2752.5	4309.0	6712.5	7441.8	7555.5	6947.8
52.5°	1015.5	1027.3	1152.7	1399.8	1819.3	2485.8	3983.6	6834.1	7939.8	8339.7	7924.1
55°	729.3	748.9	858.7	1062.6	1466.4	2129.0	3595.4	6896.8	8484.8	9268.9	9135.6
57.5°	525.4	533.2	607.7	764.6	1090.0	1709.5	3097.5	6791.0	8974.9	10378.5	10656.9
60°	435.2	435.2	447.0	521.5	745.0	1207.6	2501.5	6398.9	9394.4	11499.9	12358.6
62.5°	399.9	399.9	407.8	419.5	490.1	784.2	1787.9	5602.9	9441.5	12578.2	14224.9
65°	364.6	364.6	372.5	380.3	396.0	509.7	1078.2	4101.2	8520.1	12589.9	15228.7
67.5°	333.3	333.3	337.2	341.1	349.0	372.5	592.1	2485.8	6818.4	12256.6	15612.9
70°	301.9	301.9	301.9	298.0	309.7	313.7	392.1	1262.5	4560.0	11068.6	15428.6
72.5°	*266.6*	*266.6*	*262.7*	*254.9*	*258.8*	*258.8*	*290.1*	*619.5*	*2368.2*	*8798.4*	*13930.9*
75°	227.4	231.3	215.6	207.8	203.9	207.8	231.3	352.9	1058.6	5336.3	10409.9
77.5°	192.1	200.0	176.4	160.8	156.8	156.8	180.4	219.6	454.8	1936.9	4665.8
80°	145.1	149.0	129.4	113.7	113.7	109.8	133.3	160.8	215.6	576.4	1046.9
82.5°	82.3	82.3	74.5	66.7	62.7	66.7	90.2	109.8	133.3	203.9	286.2
85°	19.6	19.6	23.5	27.4	27.4	35.3	51.0	58.8	70.6	82.3	109.8
87.5°	3.9	3.9	3.9	7.8	11.8	11.8	19.6	27.4	35.3	43.1	47.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360700
CATALOG NUMBER: GSS-SB4B-722-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	3528.8	3528.8	*3528.8*
2.5°	3536.6	3540.5	*3536.6*
5°	3560.2	3552.3	*3540.5*
7.5°	3564.1	3568.0	*3571.9*
10°	3579.8	3595.4	*3571.9*
12.5°	3595.4	3583.7	*3575.8*
15°	3607.2	3603.3	*3579.8*
17.5°	3650.3	3634.6	*3630.7*
20°	3717.0	3713.1	*3701.3*
22.5°	3795.4	3787.6	*3783.6*
25°	3909.1	3881.7	*3866.0*
27.5°	4003.2	3979.7	*3971.8*
30°	4097.3	4050.3	*4050.3*
32.5°	4179.6	4167.9	*4160.0*
35°	4375.7	4316.9	*4324.7*
37.5°	4614.9	4556.1	*4505.1*
40°	4952.1	4873.6	*4842.3*
42.5°	5167.7	5089.3	*5097.1*
45°	5289.3	5152.0	*5116.7*
47.5°	5618.6	5446.1	*5399.0*
50°	6151.8	5940.1	*5881.3*
52.5°	7014.4	6673.3	*6594.9*
55°	8096.6	7677.1	*7598.6*
57.5°	9578.7	9021.9	*8853.3*
60°	11382.3	10692.2	*10437.4*
62.5°	13550.5	12699.7	*12456.6*
65°	15181.6	14471.9	*14095.5*
67.5°	16487.3	15903.1	*15722.7*
70°	17263.6	17291.0	*17338.1*
72.5°	*16365.7*	*17118.5*	*17479.2*
75°	11993.9	12578.2	*13138.8*
77.5°	4634.5	4179.6	*4046.3*
80°	748.9	701.8	*725.4*
82.5°	337.2	356.8	*376.4*
85°	219.6	254.9	*270.5*
87.5°	51.0	51.0	*51.0*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)