Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1363396

Luminaire Tested: **GSS-SB6B-722-U-SL3**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1363396
Test Lab:	INNOVATION CENTER(G1)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6B-722-U-SL3
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 219W 70CRI 2200K FIXTURE w/ TYPE III SPILL CONTROL DISTRIBUTION OPTIC
Light Source:	(156) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	25350.6 lumens
Efficiency:	N/A
Efficacy:	115.8 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type III - Medium
BUG Rating:	B3 - U0 - G4


Input Watts (W):	219
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	8.7%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363396
CATALOG NUMBER: GSS-SB6B-722-U-SL3

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 13.4 fc
Type III - Medium - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363396
CATALOG NUMBER: GSS-SB6B-722-U-SL3

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1363396
CATALOG NUMBER: GSS-SB6B-722-U-SL3

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4948.4	0.0	4948.4
	% Fixture	19.5	0.0	19.5
Street Side	Lumens	20402.3	0.0	20402.3
	% Fixture	80.5	0.0	80.5
Total	Lumens	25350.6	0.0	25350.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	494.8	2.0
10°-20°	1214.1	4.8
20°-30°	1815.1	7.2
30°-40°	2587.5	10.2
40°-50°	3720.6	14.7
50°-60°	4981.6	19.7
60°-70°	5849.8	23.1
70°-80°	4172.4	16.5
80°-90°	514.9	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	25350.6	100.0
0°-180°	25350.6	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1363396
CATALOG NUMBER: GSS-SB6B-722-U-SL3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2119.6	8.4			
FM	(30°-60°)	9034.4	35.6			
FH	(60°-80°)	8820.3	34.8			G4/12000
FVH	(80°-90°)	427.9	1.7			G3/500
BL	(0°-30°)	1404.3	5.5	B3/2500		
BM	(30°-60°)	2255.3	8.9	B2/2500		
BH	(60°-80°)	1201.8	4.7	B3/2500		G3/2500
BVH	(80°-90°)	87.0	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G4
Type III Medium



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363396
CATALOG NUMBER: GSS-SB6B-722-U-SL3

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	60°	65°	75°	85°
0°	5377.0	5377.0	5377.0	5377.0	5377.0	5377.0	5377.0	5377.0	5377.0	5377.0	5377.0
2.5°	5547.4	5553.7	5528.5	5509.6	5509.6	5478.0	5478.0	5478.0	5446.5	5440.1	5396.0
5°	5610.5	5604.2	5591.6	5597.9	5604.2	5591.6	5597.9	5579.0	5534.8	5522.2	5452.8
7.5°	5433.8	5433.8	5465.4	5528.5	5616.9	5661.0	5686.3	5673.7	5654.7	5616.9	5515.9
10°	4796.4	4840.6	4935.3	5143.5	5402.3	5616.9	5755.7	5749.4	5755.7	5705.2	5591.6
12.5°	4234.7	4253.7	4342.0	4525.0	4897.4	5358.1	5743.1	5818.8	5837.7	5806.2	5667.3
15°	3931.8	3925.5	3994.9	4140.1	4424.1	4928.9	5604.2	5812.5	5926.1	5919.8	5774.6
17.5°	3799.3	3805.6	3843.4	3938.1	4146.4	4562.9	5358.1	5736.8	5970.3	6046.0	5875.6
20°	3862.4	3843.4	3862.4	3881.3	3994.9	4323.1	5093.0	5604.2	6008.1	6165.9	5989.2
22.5°	3994.9	3976.0	3969.7	3957.0	3982.3	4184.2	4853.2	5440.1	6039.7	6323.7	6121.7
25°	4228.4	4209.5	4152.7	4083.3	4051.7	4140.1	4695.4	5301.3	6071.3	6544.6	6292.1
27.5°	4562.9	4537.7	4455.6	4291.5	4190.6	4203.2	4644.9	5225.6	6128.1	6759.2	6456.2
30°	5061.5	5048.9	4865.8	4600.8	4392.5	4316.8	4670.2	5206.6	6191.2	7005.3	6620.3
32.5°	5509.6	5496.9	5358.1	5061.5	4714.4	4499.8	4733.3	5231.9	6273.2	7320.8	6860.1
35°	5875.6	5850.4	5736.8	5509.6	5156.1	4777.5	4872.1	5320.2	6449.9	7737.4	7150.4
37.5°	6248.0	6229.0	6071.3	5831.4	5610.5	5162.5	5105.7	5522.2	6689.7	8305.4	7573.3
40°	6696.0	6670.8	6481.5	6197.5	6001.8	5686.3	5440.1	5844.1	7055.8	8955.4	8052.9
42.5°	7125.2	7100.0	6879.1	6632.9	6386.8	6191.2	5913.5	6273.2	7510.2	9782.2	8620.9
45°	7623.8	7623.8	7314.5	7043.2	6784.4	6544.6	6361.6	6765.5	8040.3	10716.2	9252.0
47.5°	8090.8	8046.6	7743.7	7447.1	7194.6	6740.2	6790.7	7283.0	8633.5	11662.9	9933.6
50°	8242.3	8229.6	8027.7	7762.6	7548.0	6980.0	7232.5	7901.5	9302.5	12565.3	10577.4
52.5°	8419.0	8362.2	8071.9	8034.0	7787.9	7283.0	7775.2	8538.9	9914.7	13385.8	11094.9
55°	8639.9	8576.7	8179.1	8103.4	7970.9	7623.8	8393.7	9195.2	10495.3	14023.2	11580.8
57.5°	9043.8	8968.0	8406.3	8242.3	8135.0	8052.9	9094.3	9921.0	11082.2	14521.8	11997.3
60°	9277.3	9214.2	8734.5	8614.6	8456.8	8646.2	9845.3	10590.0	11637.6	14906.8	12319.2
62.5°	9157.4	9113.2	8778.7	9005.9	9132.1	9428.7	10703.6	11284.2	12079.4	15197.1	12331.8
65°	8538.9	8450.5	8223.3	8911.2	9908.4	10747.8	11795.4	12098.3	12369.7	14414.5	11587.1
67.5°	7055.8	6967.4	7100.0	7806.8	9466.6	12779.9	13297.4	12426.5	11845.9	13701.3	11479.8
70°	3206.0	3060.9	3862.4	5522.2	7832.0	12338.1	15386.4	13789.7	12376.0	13638.2	11265.3
72.5°	1571.5	1634.6	1887.0	2480.3	4790.1	9472.9	16964.2	17052.5	14174.7	13802.3	11416.7
74°	1230.7	1249.6	1457.9	1704.0	2675.9	7907.8	16118.5	17803.5	15708.3	14193.6	11183.2
75°	1060.3	1085.5	1293.8	1420.0	1722.9	6658.2	15045.6	17576.3	16408.8	14117.9	10665.7
77.5°	776.3	770.0	921.4	1129.7	807.8	2966.2	12186.7	13619.3	13991.6	11498.8	7112.6
80°	479.6	498.6	637.4	788.9	536.4	1129.7	7163.1	7440.8	6620.3	6658.2	3452.2
82.5°	290.3	302.9	340.8	410.2	296.6	397.6	3243.9	4045.4	3351.2	2177.3	580.6
85°	88.4	94.7	113.6	145.2	107.3	145.2	1091.8	984.5	700.5	290.3	170.4
87.5°	6.3	6.3	12.6	12.6	18.9	31.6	44.2	50.5	56.8	63.1	63.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1363396
CATALOG NUMBER: GSS-SB6B-722-U-SL3

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	5377.0	5377.0	5377.0	5377.0	5377.0	5377.0	5377.0	5377.0	5377.0	5377.0	5377.0
2.5°	5396.0	5377.0	5351.8	5307.6	5276.1	5244.5	5206.6	5149.8	5130.9	5137.2	5149.8
5°	5440.1	5389.7	5313.9	5212.9	5137.2	5074.1	4973.1	4891.1	4840.6	4840.6	4815.3
7.5°	5484.3	5414.9	5295.0	5124.6	4992.1	4815.3	4626.0	4436.7	4304.2	4247.4	4196.9
10°	5560.1	5452.8	5257.1	5029.9	4745.9	4392.5	4007.5	3616.2	3370.1	3243.9	3237.6
12.5°	5610.5	5503.3	5238.2	4872.1	4335.7	3666.7	3079.8	2757.9	2657.0	2612.8	2600.2
15°	5692.6	5547.4	5194.0	4581.8	3704.6	2903.1	2581.2	2486.6	2480.3	2486.6	2492.9
17.5°	5762.0	5585.3	5080.4	4121.1	2972.5	2524.4	2442.4	2436.1	2480.3	2499.2	2518.1
20°	5837.7	5616.9	4878.5	3477.4	2562.3	2410.8	2398.2	2436.1	2499.2	2549.7	2556.0
22.5°	5945.0	5642.1	4525.0	2840.0	2366.7	2347.7	2379.3	2417.1	2455.0	2499.2	2511.8
25°	6058.6	5642.1	4039.1	2404.5	2265.7	2316.2	2347.7	2316.2	2303.5	2341.4	2341.4
27.5°	6147.0	5597.9	3351.2	2171.0	2196.3	2278.3	2259.4	2189.9	2177.3	2202.6	2196.3
30°	6210.1	5433.8	2657.0	2044.8	2126.8	2196.3	2145.8	2107.9	2082.7	2089.0	2095.3
32.5°	6304.8	5181.4	2177.3	1956.4	2070.0	2063.7	2057.4	2019.5	1988.0	1994.3	2000.6
35°	6418.4	4764.9	1905.9	1893.3	2019.5	1969.1	1975.4	1931.2	1893.3	1893.3	1899.6
37.5°	6563.5	4266.3	1792.3	1868.1	1937.5	1931.2	1912.3	1855.5	1798.7	1786.0	1786.0
40°	6721.3	3654.1	1735.5	1855.5	1899.6	1918.6	1880.7	1811.3	1659.8	1565.1	1558.8
42.5°	6822.3	3149.2	1716.6	1836.5	1893.3	1912.3	1861.8	1647.2	1502.0	1438.9	1432.6
45°	6967.4	2871.5	1716.6	1786.0	1868.1	1887.0	1710.3	1565.1	1483.1	1451.5	1457.9
47.5°	7112.6	2871.5	1716.6	1748.2	1798.7	1823.9	1590.4	1527.3	1451.5	1451.5	1476.8
50°	7314.5	3029.3	1704.0	1691.4	1710.3	1615.6	1514.7	1464.2	1363.2	1325.3	1331.6
52.5°	7617.5	3269.1	1653.5	1609.3	1615.6	1495.7	1464.2	1388.4	1287.5	1211.7	1192.8
55°	7945.6	3527.9	1552.5	1514.7	1508.3	1420.0	1407.4	1325.3	1230.7	1129.7	1110.7
57.5°	8305.4	3736.2	1426.3	1420.0	1401.1	1344.3	1363.2	1306.4	1173.9	1041.3	1022.4
60°	8646.2	3969.7	1306.4	1319.0	1287.5	1274.8	1300.1	1262.2	1098.1	953.0	940.3
62.5°	8646.2	3963.4	1199.1	1211.7	1205.4	1173.9	1218.0	1192.8	997.1	877.2	864.6
65°	8172.8	3786.6	1072.9	1104.4	1129.7	1066.6	1123.4	1079.2	908.8	814.1	795.2
67.5°	8109.7	3717.2	946.7	978.2	1022.4	953.0	990.8	946.7	826.8	744.7	732.1
70°	7983.5	3559.4	833.1	870.9	889.9	814.1	864.6	833.1	744.7	681.6	669.0
72.5°	8046.6	3420.6	713.2	757.3	763.6	694.2	744.7	732.1	656.4	612.2	586.9
74°	*7693.2*	*2959.9*	*643.7*	*681.6*	*669.0*	*618.5*	*662.7*	*662.7*	*593.2*	*561.7*	*530.1*
75°	7226.2	2625.4	593.2	631.1	599.6	568.0	612.2	618.5	549.1	549.1	498.6
77.5°	4745.9	1760.8	467.0	492.3	479.6	460.7	486.0	479.6	429.2	416.5	385.0
80°	2322.5	965.6	353.4	340.8	347.1	340.8	359.7	353.4	328.2	315.6	309.2
82.5°	435.5	321.9	233.5	227.2	214.6	202.0	227.2	227.2	302.9	340.8	340.8
85°	132.5	126.2	113.6	113.6	107.3	94.7	101.0	145.2	176.7	119.9	113.6
87.5°	56.8	56.8	50.5	44.2	31.6	31.6	25.2	25.2	25.2	25.2	25.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)