Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360708

Luminaire Tested: **GSS-SB6B-722-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360708
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6B-722-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 219W 70CRI 2200K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(156) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	26864 lumens
Efficiency:	N/A
Efficacy:	122.7 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	219
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	8.7%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360708
CATALOG NUMBER: GSS-SB6B-722-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 13.2 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360708
CATALOG NUMBER: GSS-SB6B-722-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360708
CATALOG NUMBER: GSS-SB6B-722-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	13432.0	0.0	13432.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	13432.0	0.0	13432.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	26864.0	0.0	26864.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	512.3	1.9
10°-20°	1561.4	5.8
20°-30°	2609.8	9.7
30°-40°	3599.1	13.4
40°-50°	4412.0	16.4
50°-60°	5170.3	19.2
60°-70°	5741.5	21.4
70°-80°	3122.2	11.6
80°-90°	135.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	26864.0	100.0
0°-180°	26864.0	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360708
CATALOG NUMBER: GSS-SB6B-722-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2341.8	8.7			
FM	(30°-60°)	6590.7	24.5			
FH	(60°-80°)	4431.9	16.5			G2/5000
FVH	(80°-90°)	67.7	0.3			G1/100
BL	(0°-30°)	2341.8	8.7	B3/2500		
BM	(30°-60°)	6590.7	24.5	B4/8500		
BH	(60°-80°)	4431.9	16.5	B4/5000		G4/5000
BVH	(80°-90°)	67.7	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360708
CATALOG NUMBER: GSS-SB6B-722-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	5292.9	5292.9	5292.9	5292.9	5292.9	5292.9	5292.9	5292.9	5292.9	5292.9	5292.9
2.5°	5298.8	5298.8	5281.1	5304.6	5292.9	5298.8	5304.6	5298.8	5292.9	5298.8	5304.6
5°	5328.2	5316.4	5328.2	5339.9	5322.3	5334.0	5328.2	5298.8	5316.4	5316.4	5316.4
7.5°	5381.1	5392.8	5381.1	5410.5	5392.8	5428.1	5392.8	5369.3	5363.4	5357.6	5357.6
10°	5404.6	5404.6	5398.7	5451.7	5463.4	5498.7	5475.2	5439.9	5422.3	5398.7	5375.2
12.5°	5339.9	5351.7	5381.1	5481.1	5528.1	5598.7	5581.0	5510.5	5457.5	5439.9	5404.6
15°	5269.3	5281.1	5339.9	5463.4	5575.2	5681.0	5675.1	5586.9	5522.2	5475.2	5422.3
17.5°	5157.6	5175.3	5257.6	5445.8	5645.7	5763.3	5798.6	5710.4	5639.8	5563.4	5492.8
20°	4969.4	4969.4	5116.4	5357.6	5634.0	5898.6	5992.7	5922.1	5839.8	5716.3	5622.2
22.5°	4757.7	4769.5	4916.5	5234.1	5628.1	6016.2	6198.5	6122.1	6039.8	5904.5	5763.3
25°	4546.0	4546.0	4710.7	5069.4	5551.6	6098.6	6439.7	6398.5	6233.8	6110.3	5928.0
27.5°	4351.9	4351.9	4528.3	4904.7	5422.3	6122.1	6680.8	6680.8	6498.5	6316.2	6116.2
30°	4122.6	4181.4	4381.3	4775.3	5304.6	6080.9	6857.2	6968.9	6804.3	6569.0	6275.0
32.5°	3928.5	3969.7	4175.5	4593.0	5134.1	6033.9	7057.2	7333.6	7163.0	6839.6	6510.2
35°	3699.1	3693.2	3928.5	4340.2	4893.0	5928.0	7215.9	7768.8	7604.1	7257.1	6810.2
37.5°	3399.2	3399.2	3640.3	4040.2	4663.6	5745.7	7345.3	8251.0	8127.5	7733.5	7257.1
40°	3075.7	3111.0	3322.7	3728.5	4387.2	5528.1	7345.3	8645.0	8709.7	8303.9	7809.9
42.5°	2840.5	2852.3	3046.3	3428.6	4081.4	5245.8	7251.2	8986.1	9180.2	8839.1	8198.1
45°	2593.5	2622.9	2787.6	3140.4	3763.8	4910.6	7086.6	9368.4	9680.1	9444.8	8603.9
47.5°	2293.6	2323.0	2511.2	2869.9	3463.9	4546.0	6810.2	9768.3	10421.1	10250.5	9327.2
50°	1946.6	1970.1	2146.6	2528.8	3128.7	4128.4	6463.2	10068.2	11162.1	11332.6	10421.1
52.5°	1523.2	1540.8	1729.0	2099.5	2728.8	3728.5	5975.1	10250.5	11909.0	12508.8	11885.4
55°	1093.9	1123.3	1287.9	1593.7	2199.5	3193.4	5392.8	10344.6	12726.4	13902.6	13702.7
57.5°	788.0	799.8	911.5	1146.8	1634.9	2564.1	4646.0	10185.8	13461.5	15566.9	15984.5
60°	652.8	652.8	670.4	782.2	1117.4	1811.3	3752.1	9597.7	14090.8	17248.9	18536.8
62.5°	599.9	599.9	611.6	629.3	735.1	1176.2	2681.7	8403.9	14161.4	18866.1	21336.1
65°	546.9	546.9	558.7	570.5	594.0	764.5	1617.3	6151.5	12779.3	18883.8	22841.7
67.5°	499.9	499.9	505.8	511.6	523.4	558.7	888.0	3728.5	10227.0	18383.9	23418.0
70°	452.8	452.8	452.8	447.0	464.6	470.5	588.1	1893.7	6839.6	16602.0	23141.6
72.5°	*399.9*	*399.9*	*394.0*	*382.3*	*388.1*	*388.1*	*435.2*	*929.2*	*3552.1*	*13196.9*	*20895.1*
75°	341.1	347.0	323.5	311.7	305.8	311.7	347.0	529.3	1587.9	8004.0	15614.0
77.5°	288.2	299.9	264.6	241.1	235.2	235.2	270.5	329.3	682.2	2905.2	6998.4
80°	217.6	223.5	194.1	170.5	170.5	164.7	200.0	241.1	323.5	864.5	1570.2
82.5°	123.5	123.5	111.7	100.0	94.1	100.0	135.3	164.7	200.0	305.8	429.3
85°	29.4	29.4	35.3	41.2	41.2	52.9	76.5	88.2	105.9	123.5	164.7
87.5°	5.9	5.9	5.9	11.8	17.6	17.6	29.4	41.2	52.9	64.7	70.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360708
CATALOG NUMBER: GSS-SB6B-722-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	5292.9	5292.9	*5292.9*
2.5°	5304.6	5310.5	*5304.6*
5°	5339.9	5328.2	*5310.5*
7.5°	5345.8	5351.7	*5357.6*
10°	5369.3	5392.8	*5357.6*
12.5°	5392.8	5375.2	*5363.4*
15°	5410.5	5404.6	*5369.3*
17.5°	5475.2	5451.7	*5445.8*
20°	5575.2	5569.3	*5551.6*
22.5°	5692.8	5681.0	*5675.1*
25°	5863.3	5822.2	*5798.6*
27.5°	6004.5	5969.2	*5957.4*
30°	6145.6	6075.0	*6075.0*
32.5°	6269.1	6251.5	*6239.7*
35°	6563.2	6474.9	*6486.7*
37.5°	6921.9	6833.7	*6757.2*
40°	7427.7	7310.0	*7263.0*
42.5°	7751.1	7633.5	*7645.3*
45°	7933.4	7727.6	*7674.7*
47.5°	8427.4	8168.7	*8098.1*
50°	9227.2	8909.7	*8821.5*
52.5°	10521.1	10009.4	*9891.8*
55°	12144.2	11514.9	*11397.3*
57.5°	14367.2	13532.1	*13279.2*
60°	17072.4	16037.4	*15655.1*
62.5°	20324.6	19048.5	*18683.8*
65°	22771.1	21706.6	*21142.1*
67.5°	24729.5	23853.2	*23582.7*
70°	25893.9	25935.1	*26005.6*
72.5°	*24547.2*	*25676.3*	*26217.4*
75°	17989.9	18866.1	*19707.1*
77.5°	6951.3	6269.1	*6069.2*
80°	1123.3	1052.7	*1088.0*
82.5°	505.8	535.2	*564.6*
85°	329.3	382.3	*405.8*
87.5°	76.5	76.5	*76.5*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)