Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1359173

Luminaire Tested: **GSS-SB6C-722-U-T2**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1359173
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6C-722-U-T2
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 300W 70CRI 2200K FIXTURE w/ TYPE II DISTRIBUTION OPTIC
Light Source:	(156) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	34922.4 lumens
Efficiency:	N/A
Efficacy:	116.4 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type II - Medium
BUG Rating:	B3 - U0 - G4


Input Watts (W):	300
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	6.3%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359173
CATALOG NUMBER: GSS-SB6C-722-U-T2

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 15.5 fc
Type II - Medium - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359173
CATALOG NUMBER: GSS-SB6C-722-U-T2

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1359173
CATALOG NUMBER: GSS-SB6C-722-U-T2

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	8001.6	0.0	8001.6
	% Fixture	22.9	0.0	22.9
Street Side	Lumens	26920.8	0.0	26920.8
	% Fixture	77.1	0.0	77.1
Total	Lumens	34922.4	0.0	34922.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	497.7	1.4
10°-20°	1498.4	4.3
20°-30°	2531.7	7.2
30°-40°	3905.7	11.2
40°-50°	5964.7	17.1
50°-60°	8247.0	23.6
60°-70°	8334.2	23.9
70°-80°	3666.7	10.5
80°-90°	276.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	34922.4	100.0
0°-180°	34922.4	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1359173
CATALOG NUMBER: GSS-SB6C-722-U-T2

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2724.6	7.8			
FM	(30°-60°)	14277.9	40.9			
FH	(60°-80°)	9778.4	28.0			G4/12000
FVH	(80°-90°)	139.9	0.4			G2/225
BL	(0°-30°)	1803.3	5.2	B3/2500		
BM	(30°-60°)	3839.4	11.0	B3/5000		
BH	(60°-80°)	2222.6	6.4	B3/2500		G3/2500
BVH	(80°-90°)	136.3	0.4			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G4
Type II Medium



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359173
CATALOG NUMBER: GSS-SB6C-722-U-T2

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	79°	85°
0°	5208.8	5208.8	5208.8	5208.8	5208.8	5208.8	5208.8	5208.8	5208.8	*5208.8*	5208.8
2.5°	5450.5	5536.3	5536.3	5497.3	5481.7	5473.9	5419.3	5356.9	5333.5	*5294.5*	5271.1
5°	5785.8	5785.8	5801.4	5762.4	5785.8	5754.6	5676.6	5598.6	5505.1	*5434.9*	5403.7
7.5°	5817.0	5879.4	5918.3	5918.3	5965.1	5972.9	5933.9	5848.2	5731.2	*5622.0*	5567.4
10°	5848.2	5902.7	5902.7	5965.1	6066.5	6144.5	6167.9	6136.7	5949.5	*5871.6*	5762.4
12.5°	5778.0	5840.4	5863.8	5988.5	6128.9	6277.0	6386.2	6401.8	6284.8	*6144.5*	5980.7
15°	5536.3	5590.8	5684.4	5871.6	6121.1	6347.2	6557.7	6674.7	6542.1	*6440.8*	6214.6
17.5°	5208.8	5240.0	5395.9	5637.6	5980.7	6362.8	6729.3	6955.4	6924.2	*6791.7*	6526.5
20°	5177.6	5208.8	5255.5	5434.9	5832.6	6308.2	6838.4	7275.1	7360.9	*7158.1*	6830.7
22.5°	5442.7	5473.9	5473.9	5497.3	5746.8	6261.4	6947.6	7618.2	7813.1	*7641.6*	7220.5
25°	5809.2	5871.6	5801.4	5746.8	5832.6	6292.6	7010.0	8008.1	8390.2	*8179.6*	7657.2
27.5°	6331.6	6323.8	6261.4	6097.7	6074.3	6386.2	7181.5	8312.2	8943.8	*8725.5*	8109.4
30°	7056.8	7095.8	6955.4	6612.3	6456.4	6596.7	7415.5	8561.7	9528.6	*9349.3*	8538.3
32.5°	7875.5	7859.9	7688.4	7360.9	6978.8	6939.8	7633.8	8826.8	10199.2	*9973.1*	9076.3
35°	8756.6	8741.1	8686.5	8125.0	7626.0	7415.5	7984.7	9130.9	10978.9	*10791.8*	9707.9
37.5°	9552.0	9622.2	9785.9	8881.4	8351.2	8039.3	8436.9	9637.8	11977.0	*11704.1*	10472.1
40°	10230.4	10355.1	10511.1	9692.4	9029.6	8764.4	9037.4	10464.3	13045.3	*12881.5*	11392.2
42.5°	10854.2	10940.0	10924.4	10425.3	9856.1	9559.8	9793.7	11322.0	14425.5	*14308.5*	12522.9
45°	11618.3	11711.9	11672.9	11197.3	10628.1	10362.9	10784.0	12327.9	15735.5	*15751.0*	13591.1
47.5°	12366.9	12460.5	12437.1	12000.4	11454.6	11236.3	11813.3	13513.1	16998.7	*17209.2*	14753.0
50°	13068.7	13154.5	13201.2	12928.3	12452.7	12218.8	12819.2	14628.2	18222.9	*18698.5*	15860.2
52.5°	13263.6	13372.8	13692.5	13793.9	13583.3	13302.6	13739.3	15696.5	19275.5	*19985.1*	16928.5
55°	12624.2	12811.4	13497.6	14012.2	14636.0	14667.2	14698.4	16733.5	20195.6	*21146.9*	17903.2
57.5°	11509.2	11540.4	12343.5	13388.4	14869.9	16195.5	16351.5	17942.2	21092.4	*22277.6*	18870.1
60°	9037.4	8873.6	10175.8	11945.8	14027.8	16803.7	18987.0	19813.6	22207.4	*23642.2*	20031.9
62.5°	4842.3	4857.9	5933.9	8132.8	11618.3	16211.1	21248.3	22605.1	23837.1	*25412.2*	21755.2
65°	3041.0	3158.0	3766.2	4740.9	7033.4	12881.5	21388.7	26316.7	26418.1	*27985.4*	23915.1
67.5°	*2222.3*	*2253.5*	*2768.1*	*3477.7*	*4031.3*	*7555.8*	*17217.0*	*26363.5*	*28281.7*	*29794.4*	*24835.2*
70°	1653.1	1668.7	2035.2	2620.0	2939.7	3540.1	10971.1	22815.6	27314.8	*28063.4*	22534.9
72.5°	1208.6	1216.4	1411.4	1926.0	2315.9	2105.3	5154.2	16437.2	23720.1	*25053.5*	20273.6
75°	849.9	865.5	1005.9	1333.4	1559.5	1465.9	1965.0	10277.2	17029.8	*16881.7*	14160.3
77.5°	639.4	647.2	740.8	943.5	1060.5	959.1	1107.3	4803.3	6082.1	*5489.5*	4468.0
80°	467.9	491.2	538.0	592.6	709.6	616.0	623.8	1349.0	1465.9	*1286.6*	1154.0
82.5°	249.5	280.7	358.7	358.7	413.3	366.5	327.5	600.4	631.6	*592.6*	514.6
85°	78.0	78.0	85.8	109.2	163.7	163.7	163.7	202.7	210.5	*210.5*	179.3
87.5°	15.6	15.6	15.6	15.6	23.4	31.2	46.8	62.4	70.2	*78.0*	78.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359173
CATALOG NUMBER: GSS-SB6C-722-U-T2

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	5208.8	5208.8	5208.8	5208.8	5208.8	5208.8	5208.8	5208.8	5208.8	5208.8	5208.8
2.5°	5255.5	5201.0	5146.4	5052.8	5006.0	4935.8	4873.5	4842.3	4818.9	4811.1	4811.1
5°	5356.9	5271.1	5099.6	4935.8	4787.7	4655.1	4553.8	4475.8	4429.0	4390.0	4390.0
7.5°	5458.3	5341.3	5084.0	4795.5	4585.0	4421.2	4280.9	4234.1	4218.5	4179.5	4156.1
10°	5629.8	5442.7	5060.6	4647.3	4351.0	4210.7	4148.3	4132.7	4140.5	4148.3	4148.3
12.5°	5762.4	5559.7	4998.2	4460.2	4171.7	4093.7	4101.5	4140.5	4202.9	4195.1	4179.5
15°	5949.5	5645.4	4873.5	4241.9	4031.3	4031.3	4109.3	4195.1	4257.5	4296.4	4273.1
17.5°	6167.9	5746.8	4686.3	4039.1	3914.4	3984.5	4148.3	4234.1	4343.2	4366.6	4351.0
20°	6440.8	5832.6	4475.8	3844.2	3836.4	3984.5	4124.9	4249.7	4335.4	4358.8	4374.4
22.5°	6705.9	5910.5	4202.9	3703.8	3750.6	3937.8	4070.3	4202.9	4241.9	4265.3	4273.1
25°	6978.8	5988.5	3953.4	3594.7	3688.2	3875.4	3984.5	4039.1	4046.9	4031.3	4031.3
27.5°	7275.1	5996.3	3703.8	3508.9	3618.1	3781.8	3844.2	3859.8	3828.6	3719.4	3688.2
30°	7587.0	5918.3	3501.1	3430.9	3540.1	3672.6	3719.4	3672.6	3563.5	3407.5	3391.9
32.5°	7844.3	5801.4	3352.9	3337.4	3454.3	3571.3	3571.3	3485.5	3321.8	3165.8	3158.0
35°	8234.2	5637.6	3204.8	3275.0	3376.3	3430.9	3446.5	3321.8	3142.4	2994.3	2978.7
37.5°	8616.3	5497.3	3142.4	3197.0	3290.6	3337.4	3290.6	3165.8	3048.8	2924.1	2924.1
40°	9208.9	5411.5	3064.4	3142.4	3220.4	3228.2	3142.4	3048.8	3064.4	2994.3	2986.5
42.5°	9856.1	5403.7	3033.2	3087.8	3142.4	3126.8	3002.1	3002.1	3025.4	2892.9	2861.7
45°	10596.9	5512.9	3033.2	3009.9	3041.0	2994.3	2924.1	2908.5	2853.9	2659.0	2651.2
47.5°	11368.8	5778.0	3048.8	2900.7	2892.9	2877.3	2846.1	2791.5	2627.8	2464.0	2440.6
50°	11977.0	6144.5	3095.6	2760.3	2729.1	2783.7	2729.1	2635.6	2448.4	2292.5	2269.1
52.5°	12702.2	6511.0	3064.4	2588.8	2549.8	2690.2	2635.6	2503.0	2362.7	2269.1	2245.7
55°	13466.4	6893.0	2939.7	2354.9	2386.0	2573.2	2557.6	2409.4	2237.9	2113.1	2097.5
57.5°	14230.5	7376.5	2729.1	2152.1	2269.1	2503.0	2440.6	2261.3	2144.3	2058.6	2043.0
60°	15400.2	8070.5	2425.0	1941.6	2152.1	2354.9	2253.5	2198.9	2074.1	2004.0	1965.0
62.5°	16912.9	9224.5	2027.4	1746.7	1988.4	2175.5	2167.7	2105.3	1996.2	1918.2	1894.8
65°	19065.0	10324.0	1660.9	1559.5	1777.8	1957.2	2050.8	1996.2	1887.0	1801.2	1793.4
67.5°	*19478.3*	*9224.5*	*1380.2*	*1364.6*	*1543.9*	*1746.7*	*1926.0*	*1887.0*	*1715.5*	*1606.3*	*1590.7*
70°	16951.9	6588.9	1161.8	1177.4	1349.0	1528.3	1723.3	1629.7	1489.3	1427.0	1419.2
72.5°	15049.3	5661.0	974.7	1005.9	1130.6	1294.4	1411.4	1442.5	1341.2	1286.6	1263.2
75°	10846.4	4241.9	787.6	826.5	912.3	1005.9	1224.2	1278.8	1185.2	1130.6	1091.7
77.5°	4023.5	1770.0	584.8	623.8	686.2	818.7	990.3	1107.3	1037.1	1076.1	966.9
80°	966.9	623.8	428.9	421.1	483.4	616.0	787.6	873.3	803.1	764.2	662.8
82.5°	421.1	304.1	280.7	280.7	296.3	405.5	522.4	616.0	600.4	499.0	475.7
85°	156.0	132.6	132.6	140.4	140.4	187.1	280.7	327.5	296.3	257.3	249.5
87.5°	70.2	70.2	54.6	46.8	39.0	39.0	46.8	31.2	23.4	15.6	15.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)