Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1359556

Luminaire Tested: **GSS-SB6B-722-U-T2-HSS**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1359556
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6B-722-U-T2-HSS
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 219W 70CRI 2200K FIXTURE w/ TYPE II DISTRIBUTION OPTIC AND HOUSE SIDE SHIELD
Light Source:	(156) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	21097.4 lumens
Efficiency:	N/A
Efficacy:	96.3 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type II - Medium
BUG Rating:	B2 - U0 - G3


Input Watts (W):	219
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	8.7%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359556
CATALOG NUMBER: GSS-SB6B-722-U-T2-HSS

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 10.6 fc
Type II - Medium - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359556
CATALOG NUMBER: GSS-SB6B-722-U-T2-HSS

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1359556
CATALOG NUMBER: GSS-SB6B-722-U-T2-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2264.0	0.0	2264.0
	% Fixture	10.7	0.0	10.7
Street Side	Lumens	18833.4	0.0	18833.4
	% Fixture	89.3	0.0	89.3
Total	Lumens	21097.4	0.0	21097.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.6	1.3
10°-20°	774.7	3.7
20°-30°	1274.6	6.0
30°-40°	2226.2	10.6
40°-50°	3787.8	18.0
50°-60°	5463.2	25.9
60°-70°	5273.0	25.0
70°-80°	1937.0	9.2
80°-90°	76.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	21097.4	100.0
0°-180°	21097.4	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1359556
CATALOG NUMBER: GSS-SB6B-722-U-T2-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1738.4	8.2			
FM	(30°-60°)	10336.3	49.0			
FH	(60°-80°)	6696.8	31.7			G3/7500
FVH	(80°-90°)	62.0	0.3			G1/100
BL	(0°-30°)	595.5	2.8	B2/1000		
BM	(30°-60°)	1141.0	5.4	B2/2500		
BH	(60°-80°)	513.2	2.4	B2/1000		G2/1000
BVH	(80°-90°)	14.3	0.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3
Type II Medium



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359556
CATALOG NUMBER: GSS-SB6B-722-U-T2-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	78°	85°
0°	3157.8	3157.8	3157.8	3157.8	3157.8	3157.8	3157.8	3157.8	3157.8	*3157.8*	3157.8
2.5°	3494.9	3489.0	3500.8	3477.1	3483.0	3453.5	3388.4	3347.0	3293.8	*3258.3*	3216.9
5°	3749.2	3755.1	3743.2	3749.2	3731.4	3690.0	3654.5	3548.1	3459.4	*3423.9*	3335.2
7.5°	3831.9	3843.8	3843.8	3873.3	3891.1	3908.8	3879.3	3766.9	3648.6	*3601.3*	3453.5
10°	3831.9	3831.9	3873.3	3914.7	3997.5	4056.7	4050.7	4009.3	3861.5	*3790.6*	3625.0
12.5°	3725.5	3719.6	3772.8	3891.1	4003.4	4139.4	4240.0	4204.5	4068.5	*4015.3*	3772.8
15°	3429.8	3435.7	3536.3	3713.7	3938.4	4169.0	4340.5	4417.4	4322.8	*4240.0*	3997.5
17.5°	3039.5	3063.2	3181.5	3429.8	3766.9	4139.4	4464.7	4648.0	4588.9	*4512.0*	4216.3
20°	2897.6	2903.5	2968.6	3146.0	3530.4	4027.1	4500.2	4896.4	4943.7	*4819.5*	4452.9
22.5°	3116.4	3140.1	3116.4	3128.2	3370.7	3891.1	4535.7	5115.2	5286.7	*5168.4*	4736.7
25°	3518.5	3494.9	3429.8	3376.6	3418.0	3790.6	4553.4	5393.1	5718.3	*5617.8*	5109.3
27.5°	3973.9	3920.6	3867.4	3743.2	3660.5	3849.7	4612.5	5558.7	6120.5	*6043.6*	5446.3
30°	4677.6	4665.7	4506.1	4222.2	4015.3	4080.3	4707.1	5730.2	6581.7	*6487.1*	5789.3
32.5°	5505.5	5475.9	5268.9	4884.5	4517.9	4405.6	4896.4	5895.8	7096.2	*6930.6*	6232.8
35°	6333.4	6327.4	6203.3	5641.5	5144.7	4849.1	5233.4	6150.0	7693.5	*7575.2*	6711.8
37.5°	6995.7	7037.1	7113.9	6362.9	5883.9	5434.5	5682.9	6558.1	8444.5	*8361.7*	7315.0
40°	7545.6	7616.6	7717.1	7084.4	6569.9	6138.2	6292.0	7226.3	9349.2	*9337.4*	8036.4
42.5°	8018.7	8131.1	8048.3	7687.5	7214.5	6853.7	6960.2	7995.0	10330.9	*10384.1*	8864.3
45°	8574.6	8645.5	8651.4	8273.0	7835.4	7587.0	7764.4	8870.2	11466.3	*11531.3*	9745.4
47.5°	9183.7	9160.0	9201.4	8923.5	8527.3	8302.5	8621.9	9798.7	12501.1	*12731.8*	10644.3
50°	9668.6	9751.4	9816.4	9662.7	9296.0	9100.9	9467.5	10756.6	13524.2	*13790.3*	11495.8
52.5°	9721.8	9769.1	10100.2	10248.1	10230.3	9916.9	10342.7	11649.6	14399.4	*14813.3*	12187.7
55°	8953.0	9284.2	9828.2	10336.8	11005.0	11058.2	11176.5	12501.1	15168.1	*15842.3*	12779.1
57.5°	7356.4	7604.8	8556.8	9769.1	11052.3	12158.1	12619.4	13423.6	15954.6	*16693.8*	13465.0
60°	5008.7	4908.2	6019.9	8361.7	10342.7	12589.8	14559.0	15032.1	16794.3	*17787.8*	14204.2
62.5°	2720.2	2791.2	3477.1	5387.2	8261.2	11974.8	16220.7	17864.7	18308.2	*19295.7*	15061.7
65°	1744.5	1809.5	2235.3	3069.1	4837.2	9349.2	15901.4	20289.2	20253.7	*20998.8*	15741.7
67.5°	*1194.5*	*1224.1*	*1567.1*	*2176.2*	*2643.3*	*5150.7*	*12365.1*	*19680.1*	*21069.8*	*21424.6*	*15517.0*
70°	804.2	833.8	1111.7	1608.5	1898.2	2259.0	7368.2	16238.5	19579.6	*19804.3*	13731.1
72.5°	508.6	538.1	674.1	1076.3	1431.1	1277.3	3382.5	11324.3	16291.7	*16747.0*	11744.2
75°	289.8	307.5	419.9	745.1	904.8	839.7	910.7	7090.3	10940.0	*11135.1*	7817.6
77.5°	147.8	159.7	266.1	479.0	579.5	467.2	484.9	3086.8	3820.1	*3678.2*	2146.6
80°	71.0	82.8	165.6	289.8	378.5	266.1	283.8	697.8	916.6	*780.6*	502.6
82.5°	35.5	35.5	106.4	118.3	207.0	159.7	124.2	242.5	343.0	*348.9*	230.6
85°	23.7	17.7	29.6	41.4	47.3	65.0	71.0	100.5	112.4	*118.3*	88.7
87.5°	0.0	0.0	5.9	5.9	11.8	17.7	29.6	41.4	41.4	*47.3*	41.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359556
CATALOG NUMBER: GSS-SB6B-722-U-T2-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3157.8	3157.8	3157.8	3157.8	3157.8	3157.8	3157.8	3157.8	3157.8	3157.8	3157.8
2.5°	3193.3	3175.5	3063.2	2968.6	2885.8	2826.7	2749.8	2732.0	2684.7	2655.2	2661.1
5°	3246.5	3163.7	2956.7	2779.3	2584.2	2389.1	2217.6	2158.4	2040.2	1998.8	2010.6
7.5°	3311.6	3211.0	2874.0	2525.1	2188.0	1939.6	1697.2	1549.3	1431.1	1383.8	1377.8
10°	3435.7	3264.2	2773.4	2270.8	1803.6	1466.5	1253.7	1170.9	1129.5	1117.7	1117.7
12.5°	3565.8	3323.4	2637.4	1963.3	1425.2	1165.0	1082.2	1058.5	1046.7	1040.8	1040.8
15°	3695.9	3364.8	2442.3	1590.7	1159.0	1052.6	1017.1	1005.3	987.6	981.6	993.5
17.5°	3879.3	3394.3	2217.6	1301.0	1040.8	987.6	952.1	940.2	922.5	916.6	922.5
20°	4038.9	3441.7	1957.4	1111.7	969.8	928.4	881.1	857.5	851.5	845.6	845.6
22.5°	4228.1	3494.9	1655.8	1005.3	910.7	851.5	798.3	780.6	768.8	768.8	768.8
25°	4494.3	3536.3	1413.3	958.0	845.6	774.7	721.4	703.7	697.8	691.9	697.8
27.5°	4719.0	3536.3	1253.7	928.4	792.4	709.6	662.3	650.5	638.7	626.8	632.7
30°	4931.9	3459.4	1135.4	904.8	756.9	656.4	620.9	597.3	585.4	567.7	567.7
32.5°	5174.3	3388.4	1088.1	881.1	721.4	615.0	579.5	561.8	550.0	532.2	532.2
35°	5434.5	3264.2	1082.2	863.4	686.0	585.4	550.0	538.1	520.4	508.6	508.6
37.5°	5801.1	3187.4	1070.3	839.7	656.4	555.9	520.4	514.5	502.6	490.8	496.7
40°	6292.0	3181.5	1046.7	822.0	632.7	526.3	496.7	484.9	484.9	473.1	473.1
42.5°	6765.0	3205.1	1046.7	786.5	609.1	496.7	473.1	467.2	455.3	437.6	437.6
45°	7344.6	3293.8	1058.5	751.0	585.4	479.0	455.3	443.5	431.7	419.9	419.9
47.5°	7882.7	3406.2	1070.3	715.5	561.8	461.3	443.5	437.6	419.9	408.0	413.9
50°	8338.0	3542.2	1040.8	680.1	526.3	455.3	431.7	425.8	402.1	396.2	402.1
52.5°	8746.1	3625.0	952.1	644.6	490.8	443.5	419.9	413.9	390.3	384.4	378.5
55°	9059.5	3654.5	851.5	591.3	461.3	425.8	402.1	390.3	372.6	360.7	354.8
57.5°	9367.0	3536.3	721.4	520.4	425.8	396.2	378.5	366.6	343.0	319.3	313.4
60°	9721.8	3388.4	603.2	431.7	384.4	366.6	348.9	337.1	307.5	266.1	266.1
62.5°	10135.7	3317.5	479.0	354.8	337.1	319.3	319.3	307.5	260.2	218.8	212.9
65°	10443.2	2891.7	366.6	295.7	289.8	272.0	277.9	272.0	218.8	165.6	159.7
67.5°	*10076.6*	*2069.7*	*283.8*	*248.4*	*242.5*	*218.8*	*236.5*	*230.6*	*189.2*	*141.9*	*130.1*
70°	8604.1	1348.3	230.6	207.0	195.1	165.6	195.1	201.1	159.7	112.4	106.4
72.5°	7320.9	863.4	183.3	165.6	136.0	118.3	153.8	171.5	130.1	88.7	82.8
75°	5067.9	544.0	136.0	124.2	94.6	82.8	124.2	136.0	106.4	59.1	59.1
77.5°	1673.5	272.0	100.5	82.8	65.0	59.1	94.6	100.5	71.0	41.4	35.5
80°	319.3	130.1	71.0	53.2	47.3	35.5	59.1	53.2	29.6	23.7	23.7
82.5°	153.8	76.9	53.2	41.4	23.7	23.7	17.7	23.7	23.7	17.7	17.7
85°	71.0	47.3	35.5	23.7	17.7	11.8	11.8	17.7	17.7	17.7	11.8
87.5°	41.4	35.5	23.7	17.7	11.8	11.8	11.8	11.8	11.8	11.8	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)