Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1359172

Luminaire Tested: **GSS-SB6B-722-U-T2**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1359172
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6B-722-U-T2
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 219W 70CRI 2200K FIXTURE w/ TYPE II DISTRIBUTION OPTIC
Light Source:	(156) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	26481.9 lumens
Efficiency:	N/A
Efficacy:	120.9 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type II - Medium
BUG Rating:	B3 - U0 - G3


Input Watts (W):	219
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	8.7%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359172
CATALOG NUMBER: GSS-SB6B-722-U-T2

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 11.8 fc
Type II - Medium - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359172
CATALOG NUMBER: GSS-SB6B-722-U-T2

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1359172
CATALOG NUMBER: GSS-SB6B-722-U-T2

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	6067.6	0.0	6067.6
	% Fixture	22.9	0.0	22.9
Street Side	Lumens	20414.3	0.0	20414.3
	% Fixture	77.1	0.0	77.1
Total	Lumens	26481.9	0.0	26481.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	377.4	1.4
10°-20°	1136.3	4.3
20°-30°	1919.8	7.2
30°-40°	2961.7	11.2
40°-50°	4523.0	17.1
50°-60°	6253.8	23.6
60°-70°	6319.9	23.9
70°-80°	2780.5	10.5
80°-90°	209.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	26481.9	100.0
0°-180°	26481.9	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1359172
CATALOG NUMBER: GSS-SB6B-722-U-T2

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2066.1	7.8			
FM	(30°-60°)	10827.1	40.9			
FH	(60°-80°)	7415.0	28.0			G3/7500
FVH	(80°-90°)	106.1	0.4			G2/225
BL	(0°-30°)	1367.4	5.2	B3/2500		
BM	(30°-60°)	2911.4	11.0	B3/5000		
BH	(60°-80°)	1685.4	6.4	B3/2500		G3/2500
BVH	(80°-90°)	103.3	0.4			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3
Type II Medium



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359172
CATALOG NUMBER: GSS-SB6B-722-U-T2

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	79°	85°
0°	3949.8	3949.8	3949.8	3949.8	3949.8	3949.8	3949.8	3949.8	3949.8	*3949.8*	3949.8
2.5°	4133.1	4198.2	4198.2	4168.6	4156.8	4150.9	4109.5	4062.2	4044.5	*4014.9*	3997.1
5°	4387.4	4387.4	4399.2	4369.7	4387.4	4363.8	4304.6	4245.5	4174.5	*4121.3*	4097.7
7.5°	4411.1	4458.4	4487.9	4487.9	4523.4	4529.3	4499.7	4434.7	4346.0	*4263.2*	4221.8
10°	4434.7	4476.1	4476.1	4523.4	4600.3	4659.4	4677.1	4653.5	4511.6	*4452.4*	4369.7
12.5°	4381.5	4428.8	4446.5	4541.1	4647.6	4759.9	4842.7	4854.5	4765.8	*4659.4*	4535.2
15°	4198.2	4239.6	4310.5	4452.4	4641.7	4813.1	4972.8	5061.5	4961.0	*4884.1*	4712.6
17.5°	3949.8	3973.5	4091.8	4275.1	4535.2	4825.0	5102.9	5274.3	5250.7	*5150.2*	4949.1
20°	3926.2	3949.8	3985.3	4121.3	4422.9	4783.6	5185.6	5516.8	5581.8	*5428.1*	5179.7
22.5°	4127.2	4150.9	4150.9	4168.6	4357.8	4748.1	5268.4	5776.9	5924.8	*5794.7*	5475.4
25°	4405.1	4452.4	4399.2	4357.8	4422.9	4771.7	5315.7	6072.6	6362.3	*6202.7*	5806.5
27.5°	4801.3	4795.4	4748.1	4623.9	4606.2	4842.7	5445.8	6303.2	6782.1	*6616.6*	6149.5
30°	5351.2	5380.8	5274.3	5014.2	4895.9	5002.3	5623.2	6492.4	7225.6	*7089.6*	6474.7
32.5°	5972.1	5960.2	5830.2	5581.8	5292.1	5262.5	5788.8	6693.4	7734.1	*7562.7*	6882.7
35°	6640.2	6628.4	6587.0	6161.3	5782.9	5623.2	6054.9	6924.1	8325.4	*8183.5*	7361.6
37.5°	7243.4	7296.6	7420.7	6734.8	6332.8	6096.2	6397.8	7308.4	9082.3	*8875.3*	7941.1
40°	7757.8	7852.4	7970.6	7349.8	6847.2	6646.1	6853.1	7935.2	9892.4	*9768.2*	8638.8
42.5°	8230.8	8295.9	8284.0	7905.6	7474.0	7249.3	7426.7	8585.6	10938.9	*10850.2*	9496.2
45°	8810.3	8881.2	8851.7	8491.0	8059.3	7858.3	8177.6	9348.4	11932.3	*11944.1*	10306.3
47.5°	9377.9	9448.9	9431.1	9100.0	8686.1	8520.5	8958.1	10247.1	12890.2	*13049.9*	11187.3
50°	9910.1	9975.1	10010.6	9803.7	9443.0	9265.6	9720.9	11092.7	13818.5	*14179.2*	12026.9
52.5°	10057.9	10140.7	10383.1	10460.0	10300.3	10087.5	10418.6	11902.8	14616.8	*15154.9*	12837.0
55°	9573.1	9715.0	10235.3	10625.6	11098.6	11122.2	11145.9	12689.2	15314.5	*16035.9*	13576.1
57.5°	8727.5	8751.2	9360.2	10152.5	11276.0	12281.2	12399.4	13605.7	15994.5	*16893.3*	14309.3
60°	6853.1	6728.9	7716.4	9058.6	10637.4	12742.4	14398.0	15024.8	16840.1	*17928.0*	15190.3
62.5°	3671.9	3683.8	4499.7	6167.2	8810.3	12293.0	16112.8	17141.6	18075.9	*19270.3*	16497.1
65°	2306.0	2394.7	2856.0	3595.1	5333.5	9768.2	16219.2	19956.2	20033.0	*21221.5*	18135.0
67.5°	*1685.2*	*1708.8*	*2099.1*	*2637.2*	*3057.0*	*5729.6*	*13055.8*	*19991.7*	*21446.2*	*22593.3*	*18832.7*
70°	1253.5	1265.4	1543.3	1986.7	2229.2	2684.5	8319.5	17301.3	20713.0	*21280.7*	17088.4
72.5°	916.5	922.4	1070.2	1460.5	1756.1	1596.5	3908.5	12464.5	17987.2	*18998.3*	15373.6
75°	644.5	656.3	762.8	1011.1	1182.6	1111.6	1490.1	7793.3	12913.9	*12801.5*	10737.9
77.5°	484.9	490.8	561.7	715.5	804.2	727.3	839.6	3642.4	4612.1	*4162.7*	3388.1
80°	354.8	372.5	408.0	449.4	538.1	467.1	473.0	1022.9	1111.6	*975.6*	875.1
82.5°	189.2	212.9	272.0	272.0	313.4	277.9	248.3	455.3	478.9	*449.4*	390.3
85°	59.1	59.1	65.0	82.8	124.2	124.2	124.2	153.7	159.6	*159.6*	136.0
87.5°	11.8	11.8	11.8	11.8	17.7	23.7	35.5	47.3	53.2	*59.1*	59.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359172
CATALOG NUMBER: GSS-SB6B-722-U-T2

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3949.8	3949.8	3949.8	3949.8	3949.8	3949.8	3949.8	3949.8	3949.8	3949.8	3949.8
2.5°	3985.3	3943.9	3902.5	3831.6	3796.1	3742.9	3695.6	3671.9	3654.2	3648.3	3648.3
5°	4062.2	3997.1	3867.1	3742.9	3630.5	3530.0	3453.2	3394.0	3358.6	3329.0	3329.0
7.5°	4139.1	4050.4	3855.2	3636.5	3476.8	3352.6	3246.2	3210.7	3198.9	3169.3	3151.6
10°	4269.1	4127.2	3837.5	3524.1	3299.4	3193.0	3145.7	3133.9	3139.8	3145.7	3145.7
12.5°	4369.7	4215.9	3790.2	3382.2	3163.4	3104.3	3110.2	3139.8	3187.1	3181.2	3169.3
15°	4511.6	4281.0	3695.6	3216.6	3057.0	3057.0	3116.1	3181.2	3228.5	3258.0	3240.3
17.5°	4677.1	4357.8	3553.7	3062.9	2968.3	3021.5	3145.7	3210.7	3293.5	3311.2	3299.4
20°	4884.1	4422.9	3394.0	2915.1	2909.2	3021.5	3127.9	3222.6	3287.6	3305.3	3317.2
22.5°	5085.1	4482.0	3187.1	2808.6	2844.1	2986.0	3086.6	3187.1	3216.6	3234.4	3240.3
25°	5292.1	4541.1	2997.9	2725.9	2796.8	2938.7	3021.5	3062.9	3068.8	3057.0	3057.0
27.5°	5516.8	4547.1	2808.6	2660.8	2743.6	2867.8	2915.1	2926.9	2903.3	2820.5	2796.8
30°	5753.3	4487.9	2654.9	2601.7	2684.5	2785.0	2820.5	2785.0	2702.2	2584.0	2572.1
32.5°	5948.4	4399.2	2542.6	2530.7	2619.4	2708.1	2708.1	2643.1	2518.9	2400.7	2394.7
35°	6244.1	4275.1	2430.2	2483.4	2560.3	2601.7	2613.5	2518.9	2382.9	2270.6	2258.7
37.5°	6533.8	4168.6	2382.9	2424.3	2495.3	2530.7	2495.3	2400.7	2312.0	2217.4	2217.4
40°	6983.2	4103.6	2323.8	2382.9	2442.0	2448.0	2382.9	2312.0	2323.8	2270.6	2264.7
42.5°	7474.0	4097.7	2300.1	2341.5	2382.9	2371.1	2276.5	2276.5	2294.2	2193.7	2170.0
45°	8035.7	4180.4	2300.1	2282.4	2306.0	2270.6	2217.4	2205.5	2164.1	2016.3	2010.4
47.5°	8621.1	4381.5	2312.0	2199.6	2193.7	2181.9	2158.2	2116.8	1992.7	1868.5	1850.8
50°	9082.3	4659.4	2347.4	2093.2	2069.5	2110.9	2069.5	1998.6	1856.7	1738.4	1720.7
52.5°	9632.2	4937.3	2323.8	1963.1	1933.5	2040.0	1998.6	1898.1	1791.6	1720.7	1702.9
55°	10211.7	5227.0	2229.2	1785.7	1809.4	1951.3	1939.4	1827.1	1697.0	1602.4	1590.6
57.5°	10791.1	5593.6	2069.5	1632.0	1720.7	1898.1	1850.8	1714.8	1626.1	1561.0	1549.2
60°	11678.1	6119.9	1838.9	1472.3	1632.0	1785.7	1708.8	1667.4	1572.8	1519.6	1490.1
62.5°	12825.2	6995.0	1537.4	1324.5	1507.8	1649.7	1643.8	1596.5	1513.7	1454.6	1436.8
65°	14457.1	7828.7	1259.5	1182.6	1348.2	1484.1	1555.1	1513.7	1430.9	1365.9	1360.0
67.5°	*14770.5*	*6995.0*	*1046.6*	*1034.8*	*1170.8*	*1324.5*	*1460.5*	*1430.9*	*1300.8*	*1218.1*	*1206.2*
70°	12854.7	4996.4	881.0	892.9	1022.9	1158.9	1306.8	1235.8	1129.4	1082.1	1076.2
72.5°	11412.0	4292.8	739.1	762.8	857.4	981.5	1070.2	1093.9	1017.0	975.6	957.9
75°	8224.9	3216.6	597.2	626.8	691.8	762.8	928.3	969.7	898.8	857.4	827.8
77.5°	3051.1	1342.2	443.5	473.0	520.3	620.9	750.9	839.6	786.4	816.0	733.2
80°	733.2	473.0	325.2	319.3	366.6	467.1	597.2	662.2	609.0	579.5	502.6
82.5°	319.3	230.6	212.9	212.9	224.7	307.5	396.2	467.1	455.3	378.4	360.7
85°	118.3	100.5	100.5	106.4	106.4	141.9	212.9	248.3	224.7	195.1	189.2
87.5°	53.2	53.2	41.4	35.5	29.6	29.6	35.5	23.7	17.7	11.8	11.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)