Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1364145

Luminaire Tested: **GSS-SB1C-722-U-SLR**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1364145
Test Lab:	INNOVATION CENTER(G1)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB1C-722-U-SLR
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 1SQUARE 52W 70CRI 2200K FIXTURE w/ 90° Spill Light Eliminator RIGHT OPTIC
Light Source:	(26) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	5305.9 lumens
Efficiency:	N/A
Efficacy:	102.0 lumens/watt
Luminous Opening:	Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification:	Type IV - Short
BUG Rating:	B1 - U0 - G1


Input Watts (W):	52
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	10.1%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1364145
CATALOG NUMBER: GSS-SB1C-722-U-SLR

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 2.5 fc
Type IV - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1364145
CATALOG NUMBER: GSS-SB1C-722-U-SLR

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1364145
CATALOG NUMBER: GSS-SB1C-722-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1427.4	0.0	1427.4
	% Fixture	26.9	0.0	26.9
Street Side	Lumens	3878.5	0.0	3878.5
	% Fixture	73.1	0.0	73.1
Total	Lumens	5305.9	0.0	5305.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.5	1.6
10°-20°	256.0	4.8
20°-30°	396.2	7.5
30°-40°	491.6	9.3
40°-50°	718.8	13.5
50°-60°	1126.0	21.2
60°-70°	1336.0	25.2
70°-80°	779.2	14.7
80°-90°	118.5	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5305.9	100.0
0°-180°	5305.9	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1364145
CATALOG NUMBER: GSS-SB1C-722-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	398.8	7.5			
FM	(30°-60°)	1614.2	30.4			
FH	(60°-80°)	1768.6	33.3			G1/1800
FVH	(80°-90°)	97.0	1.8			G1/100
BL	(0°-30°)	337.0	6.4	B1/500		
BM	(30°-60°)	722.2	13.6	B1/1000		
BH	(60°-80°)	346.7	6.5	B1/500		G1/500
BVH	(80°-90°)	21.6	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1
Type IV Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1364145
CATALOG NUMBER: GSS-SB1C-722-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	846.0	846.0	846.0	846.0	846.0	846.0	846.0	846.0	846.0	846.0	846.0
2.5°	914.2	905.9	897.7	890.2	882.6	875.1	867.4	860.2	852.8	845.4	838.9
5°	976.4	961.8	947.3	931.9	916.8	901.8	886.9	872.8	858.8	844.1	831.5
7.5°	1039.4	1014.7	990.1	966.8	943.6	922.9	902.1	883.5	864.9	845.4	830.2
10°	1079.0	1049.5	1019.9	991.1	962.2	936.6	910.9	889.5	868.1	847.3	831.1
12.5°	1099.1	1069.7	1040.4	1008.1	975.8	947.1	918.4	894.8	871.3	848.6	832.8
15°	1108.8	1079.1	1049.5	1016.7	983.8	953.0	921.9	895.3	868.7	843.4	829.4
17.5°	1111.4	1083.6	1056.0	1021.0	985.9	950.6	915.5	884.4	853.6	824.0	812.0
20°	1119.8	1091.8	1063.8	1026.1	988.5	947.1	905.7	865.0	824.2	785.1	777.5
22.5°	1128.9	1103.2	1077.7	1036.3	995.0	944.4	893.8	842.7	791.5	744.8	737.7
25°	1143.2	1121.0	1098.8	1053.7	1008.5	944.1	879.8	816.1	752.4	698.8	698.1
27.5°	1164.0	1147.0	1130.0	1079.1	1028.4	946.6	864.9	788.8	712.6	657.9	661.1
30°	1193.1	1179.8	1166.5	1109.2	1051.7	951.9	852.3	765.1	678.0	624.8	628.3
32.5°	1228.8	1220.5	1212.2	1144.6	1077.0	957.9	838.9	744.3	649.8	600.8	600.8
35°	1289.2	1278.8	1268.4	1182.2	1096.2	956.5	816.8	720.7	624.4	586.5	578.5
37.5°	1365.7	1353.4	1341.1	1228.2	1115.3	952.4	789.6	694.5	599.5	569.6	554.3
40°	1478.6	1454.4	1430.0	1280.7	1131.5	943.4	755.2	663.2	571.2	547.6	528.4
42.5°	1636.9	1585.5	1534.0	1338.9	1143.5	927.7	711.7	626.0	540.1	523.6	499.8
45°	1833.5	1751.1	1668.7	1417.8	1166.8	916.9	667.0	588.1	509.3	494.4	470.8
47.5°	2021.7	1917.3	1813.0	1498.9	1184.7	904.3	623.9	550.4	477.3	460.0	437.9
50°	2239.7	2098.2	1956.8	1569.6	1182.4	882.9	583.3	517.0	450.5	426.9	405.1
52.5°	2519.3	2294.7	2069.9	1603.1	1136.1	839.0	542.1	486.9	431.8	401.6	378.3
55°	2853.4	2492.1	2130.7	1594.2	1057.8	780.9	503.7	461.7	419.4	389.3	361.8
57.5°	3194.1	2657.8	2121.6	1546.1	970.6	720.0	469.5	440.4	411.3	386.0	352.3
60°	3449.7	2732.0	2014.1	1430.7	847.3	643.1	438.9	418.5	398.1	378.3	344.5
62.5°	3343.9	2567.3	1790.7	1241.7	692.7	545.5	398.4	386.9	375.7	367.2	335.0
65°	*2987.1*	*2214.4*	*1441.6*	*974.0*	*506.3*	*428.7*	*351.0*	*348.5*	*346.2*	*343.9*	*317.3*
67.5°	2652.3	1901.8	1151.2	757.9	364.6	327.8	290.9	297.8	304.7	308.2	290.0
70°	2331.8	1615.6	899.5	580.8	262.1	249.1	236.2	246.4	256.7	255.6	246.8
72.5°	2001.6	1341.6	681.5	436.6	191.8	191.5	191.4	199.2	207.0	196.6	202.2
75°	1638.9	1071.2	503.5	323.6	143.8	142.9	142.1	151.3	160.6	164.8	168.4
77.5°	1090.0	702.8	315.6	209.2	102.8	103.5	104.1	114.2	124.3	136.2	136.9
80°	639.7	402.9	166.1	115.6	65.1	65.9	66.4	77.1	87.6	104.5	103.8
82.5°	319.9	201.9	84.1	62.2	40.2	40.4	40.5	45.7	50.9	60.3	62.9
85°	72.7	48.0	23.4	19.7	16.2	17.0	17.9	21.3	24.7	29.8	31.4
87.5°	5.8	5.7	5.4	5.3	5.2	5.4	5.8	6.5	7.1	7.8	9.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1364145
CATALOG NUMBER: GSS-SB1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	846.0	846.0	846.0	846.0	846.0	846.0	846.0	846.0	846.0	846.0	846.0
2.5°	831.9	825.0	819.6	814.2	809.6	804.8	799.2	793.5	789.5	785.3	782.6
5°	819.0	806.9	796.7	786.6	778.3	769.7	762.2	754.6	748.6	742.5	737.6
7.5°	815.0	800.0	786.9	773.6	762.5	751.3	742.0	732.5	723.5	714.7	709.0
10°	815.2	799.3	785.8	772.3	760.5	748.7	736.4	724.1	714.2	704.3	695.8
12.5°	819.6	806.5	797.0	787.6	776.7	765.8	751.2	736.4	723.0	709.8	699.3
15°	820.9	812.3	811.5	810.7	807.0	803.2	789.6	776.0	757.5	739.0	723.9
17.5°	810.9	809.7	822.6	835.4	842.8	850.2	840.7	831.1	805.2	779.2	756.8
20°	784.9	792.2	817.4	842.4	862.4	882.4	881.3	880.4	846.6	812.6	783.1
22.5°	748.6	759.4	792.2	825.0	853.8	882.6	890.0	897.3	864.1	830.7	794.4
25°	709.9	721.7	752.1	782.5	813.5	844.5	858.2	872.0	844.6	817.2	781.9
27.5°	672.4	683.8	706.4	729.0	753.9	778.8	794.3	809.7	793.0	776.2	747.7
30°	637.1	645.9	662.3	678.6	695.5	712.4	724.7	737.0	726.0	715.0	694.5
32.5°	604.6	608.3	619.0	629.6	642.2	654.6	661.5	668.3	659.7	651.1	637.6
35°	575.4	572.2	579.3	586.3	596.4	606.6	611.8	617.0	609.9	602.7	590.7
37.5°	546.0	537.5	540.8	544.0	552.7	561.2	568.6	576.1	570.9	565.8	555.5
40°	515.9	503.5	503.2	502.8	511.1	519.3	528.6	537.9	536.9	535.9	526.2
42.5°	484.0	468.2	466.5	464.8	473.0	481.2	491.0	500.9	502.8	504.8	496.7
45°	454.4	438.3	435.7	433.1	440.1	447.4	458.2	469.1	473.6	478.2	470.9
47.5°	424.1	410.0	408.5	406.8	414.2	421.7	433.7	445.7	450.5	455.5	450.5
50°	393.7	382.1	384.1	386.0	394.2	402.3	411.6	421.1	430.0	438.9	437.9
52.5°	369.7	361.0	367.1	373.1	380.5	388.0	397.7	407.4	416.8	426.3	427.7
55°	352.2	342.6	351.1	359.7	368.7	377.6	386.7	395.8	404.6	413.3	415.2
57.5°	338.8	325.4	334.0	342.6	352.3	362.0	371.1	380.2	390.4	400.7	402.3
60°	327.6	310.8	316.5	322.1	332.1	341.9	351.4	360.7	371.1	381.5	383.6
62.5°	313.0	290.9	291.7	292.2	303.5	314.7	322.5	330.2	340.1	350.1	353.1
65°	*293.5*	*269.9*	*267.3*	*264.7*	*275.4*	*286.1*	*292.2*	*298.4*	*307.0*	*315.6*	*318.6*
67.5°	269.1	248.1	242.8	237.5	247.3	257.2	262.2	267.3	273.1	279.0	282.4
70°	234.3	221.9	218.5	215.1	223.2	231.2	235.6	240.1	244.7	249.4	251.2
72.5°	199.3	196.6	194.1	191.8	197.9	204.0	207.7	211.5	215.9	220.3	221.4
75°	166.9	165.4	163.6	161.9	166.6	171.3	174.1	177.1	181.7	186.2	188.2
77.5°	133.5	130.0	128.2	126.1	130.4	134.7	137.4	140.1	143.9	147.7	148.2
80°	99.7	95.4	93.9	92.4	95.5	98.6	99.7	100.6	103.7	106.7	106.7
82.5°	62.9	62.9	62.0	61.0	60.3	59.7	58.4	57.1	60.2	63.3	64.4
85°	31.7	31.8	30.4	28.8	27.0	24.9	24.5	24.0	23.9	23.6	24.5
87.5°	9.9	10.6	11.4	11.9	12.7	13.2	12.8	12.3	11.8	11.4	10.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1364145
CATALOG NUMBER: GSS-SB1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	846.0	846.0	846.0	846.0	846.0	846.0	846.0	846.0	846.0	846.0	846.0
2.5°	779.9	778.6	777.3	776.2	775.3	774.7	775.3	776.2	777.3	778.6	779.9
5°	732.5	730.4	728.2	726.8	725.4	724.1	725.4	726.8	728.2	730.4	732.5
7.5°	703.3	699.9	696.6	694.1	691.6	690.3	691.6	694.1	696.6	699.9	703.3
10°	687.5	682.7	678.0	675.4	672.8	670.9	672.8	675.4	678.0	682.7	687.5
12.5°	688.8	682.8	677.1	673.2	669.3	667.0	669.3	673.2	677.1	682.8	688.8
15°	708.8	700.4	691.9	687.1	682.3	678.6	682.3	687.1	691.9	700.4	708.8
17.5°	734.4	722.2	710.1	705.8	701.4	699.4	701.4	705.8	710.1	722.2	734.4
20°	753.6	737.3	721.2	714.7	708.2	705.9	708.2	714.7	721.2	737.3	753.6
22.5°	758.1	738.9	719.5	713.4	707.2	704.6	707.2	713.4	719.5	738.9	758.1
25°	746.8	726.5	706.2	699.9	693.6	691.6	693.6	699.9	706.2	726.5	746.8
27.5°	719.1	701.2	683.2	676.6	669.8	665.7	669.8	676.6	683.2	701.2	719.1
30°	674.1	660.7	647.5	643.4	639.1	637.1	639.1	643.4	647.5	660.7	674.1
32.5°	624.1	615.8	607.5	604.8	602.1	600.8	602.1	604.8	607.5	615.8	624.1
35°	578.7	572.8	566.8	564.6	562.5	560.6	562.5	564.6	566.8	572.8	578.7
37.5°	545.3	538.2	531.0	527.1	523.2	520.3	523.2	527.1	531.0	538.2	545.3
40°	516.4	506.3	496.3	491.0	485.6	482.7	485.6	491.0	496.3	506.3	516.4
42.5°	488.5	476.9	465.2	457.0	449.0	443.8	449.0	457.0	465.2	476.9	488.5
45°	463.5	450.4	437.3	427.6	417.8	411.3	417.8	427.6	437.3	450.4	463.5
47.5°	445.7	434.4	423.0	414.5	405.9	399.7	405.9	414.5	423.0	434.4	445.7
50°	437.0	428.1	419.1	411.1	402.9	397.1	402.9	411.1	419.1	428.1	437.0
52.5°	429.2	422.8	416.3	409.3	402.3	397.1	402.3	409.3	416.3	422.8	429.2
55°	417.2	412.5	407.7	402.5	397.3	393.2	397.3	402.5	407.7	412.5	417.2
57.5°	403.8	398.9	393.8	389.9	386.0	384.1	386.0	389.9	393.8	398.9	403.8
60°	385.6	381.8	377.9	374.2	370.5	367.2	370.5	374.2	377.9	381.8	385.6
62.5°	356.2	354.4	352.7	348.5	344.5	340.0	344.5	348.5	352.7	354.4	356.2
65°	*321.5*	*320.6*	*319.9*	*316.9*	*314.0*	*308.8*	*314.0*	*316.9*	*319.9*	*320.6*	*321.5*
67.5°	285.7	284.0	282.2	279.1	276.1	275.1	276.1	279.1	282.2	284.0	285.7
70°	253.0	250.4	247.8	240.8	233.8	225.8	233.8	240.8	247.8	250.4	253.0
72.5°	222.5	218.5	214.4	206.2	197.9	189.5	197.9	206.2	214.4	218.5	222.5
75°	190.1	184.4	178.8	170.1	161.6	155.7	161.6	170.1	178.8	184.4	190.1
77.5°	149.0	144.0	139.1	133.9	128.7	125.9	128.7	133.9	139.1	144.0	149.0
80°	106.7	103.0	99.3	96.7	94.1	92.1	94.1	96.7	99.3	103.0	106.7
82.5°	65.5	63.8	62.3	59.4	56.4	54.5	56.4	59.4	62.3	63.8	65.5
85°	25.3	24.9	24.7	23.6	22.7	22.1	22.7	23.6	24.7	24.9	25.3
87.5°	9.3	8.6	7.8	7.3	6.7	6.5	6.7	7.3	7.8	8.6	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1364145
CATALOG NUMBER: GSS-SB1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	846.0	846.0	846.0	846.0	846.0	846.0	846.0	846.0	846.0	846.0	846.0
2.5°	782.6	785.3	789.5	793.5	799.2	804.8	809.6	814.2	819.6	825.0	831.9
5°	737.6	742.5	748.6	754.6	762.2	769.7	778.3	786.6	796.7	806.9	819.0
7.5°	709.0	714.7	723.5	732.5	742.0	751.3	762.5	773.6	786.9	800.0	815.0
10°	695.8	704.3	714.2	724.1	736.4	748.7	760.5	772.3	785.8	799.3	815.2
12.5°	699.3	709.8	723.0	736.4	751.2	765.8	776.7	787.6	797.0	806.5	819.6
15°	723.9	739.0	757.5	776.0	789.6	803.2	807.0	810.7	811.5	812.3	820.9
17.5°	756.8	779.2	805.2	831.1	840.7	850.2	842.8	835.4	822.6	809.7	810.9
20°	783.1	812.6	846.6	880.4	881.3	882.4	862.4	842.4	817.4	792.2	784.9
22.5°	794.4	830.7	864.1	897.3	890.0	882.6	853.8	825.0	792.2	759.4	748.6
25°	781.9	817.2	844.6	872.0	858.2	844.5	813.5	782.5	752.1	721.7	709.9
27.5°	747.7	776.2	793.0	809.7	794.3	778.8	753.9	729.0	706.4	683.8	672.4
30°	694.5	715.0	726.0	737.0	724.7	712.4	695.5	678.6	662.3	645.9	637.1
32.5°	637.6	651.1	659.7	668.3	661.5	654.6	642.2	629.6	619.0	608.3	604.6
35°	590.7	602.7	609.9	617.0	611.8	606.6	596.4	586.3	579.3	572.2	575.4
37.5°	555.5	565.8	570.9	576.1	568.6	561.2	552.7	544.0	540.8	537.5	546.0
40°	526.2	535.9	536.9	537.9	528.6	519.3	511.1	502.8	503.2	503.5	515.9
42.5°	496.7	504.8	502.8	500.9	491.0	481.2	473.0	464.8	466.5	468.2	484.0
45°	470.9	478.2	473.6	469.1	458.2	447.4	440.1	433.1	435.7	438.3	454.4
47.5°	450.5	455.5	450.5	445.7	433.7	421.7	414.2	406.8	408.5	410.0	424.1
50°	437.9	438.9	430.0	421.1	411.6	402.3	394.2	386.0	384.1	382.1	393.7
52.5°	427.7	426.3	416.8	407.4	397.7	388.0	380.5	373.1	367.1	361.0	369.7
55°	415.2	413.3	404.6	395.8	386.7	377.6	368.7	359.7	351.1	342.6	352.2
57.5°	402.3	400.7	390.4	380.2	371.1	362.0	352.3	342.6	334.0	325.4	338.8
60°	383.6	381.5	371.1	360.7	351.4	341.9	332.1	322.1	316.5	310.8	327.6
62.5°	353.1	350.1	340.1	330.2	322.5	314.7	303.5	292.2	291.7	290.9	313.0
65°	*318.6*	*315.6*	*307.0*	*298.4*	*292.2*	*286.1*	*275.4*	*264.7*	*267.3*	*269.9*	*293.5*
67.5°	282.4	279.0	273.1	267.3	262.2	257.2	247.3	237.5	242.8	248.1	269.1
70°	251.2	249.4	244.7	240.1	235.6	231.2	223.2	215.1	218.5	221.9	234.3
72.5°	221.4	220.3	215.9	211.5	207.7	204.0	197.9	191.8	194.1	196.6	199.3
75°	188.2	186.2	181.7	177.1	174.1	171.3	166.6	161.9	163.6	165.4	166.9
77.5°	148.2	147.7	143.9	140.1	137.4	134.7	130.4	126.1	128.2	130.0	133.5
80°	106.7	106.7	103.7	100.6	99.7	98.6	95.5	92.4	93.9	95.4	99.7
82.5°	64.4	63.3	60.2	57.1	58.4	59.7	60.3	61.0	62.0	62.9	62.9
85°	24.5	23.6	23.9	24.0	24.5	24.9	27.0	28.8	30.4	31.8	31.7
87.5°	10.4	11.4	11.8	12.3	12.8	13.2	12.7	11.9	11.4	10.6	9.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1364145
CATALOG NUMBER: GSS-SB1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	846.0	846.0	846.0	846.0	846.0	846.0	846.0	846.0	846.0	846.0	846.0
2.5°	838.9	845.4	852.8	860.2	867.4	875.1	882.6	890.2	897.7	905.9	914.2
5°	831.5	844.1	858.8	872.8	886.9	901.8	916.8	931.9	947.3	961.8	976.4
7.5°	830.2	845.4	864.9	883.5	902.1	922.9	943.6	966.8	990.1	1014.7	1039.4
10°	831.1	847.3	868.1	889.5	910.9	936.6	962.2	991.1	1019.9	1049.5	1079.0
12.5°	832.8	848.6	871.3	894.8	918.4	947.1	975.8	1008.1	1040.4	1069.7	1099.1
15°	829.4	843.4	868.7	895.3	921.9	953.0	983.8	1016.7	1049.5	1079.1	1108.8
17.5°	812.0	824.0	853.6	884.4	915.5	950.6	985.9	1021.0	1056.0	1083.6	1111.4
20°	777.5	785.1	824.2	865.0	905.7	947.1	988.5	1026.1	1063.8	1091.8	1119.8
22.5°	737.7	744.8	791.5	842.7	893.8	944.4	995.0	1036.3	1077.7	1103.2	1128.9
25°	698.1	698.8	752.4	816.1	879.8	944.1	1008.5	1053.7	1098.8	1121.0	1143.2
27.5°	661.1	657.9	712.6	788.8	864.9	946.6	1028.4	1079.1	1130.0	1147.0	1164.0
30°	628.3	624.8	678.0	765.1	852.3	951.9	1051.7	1109.2	1166.5	1179.8	1193.1
32.5°	600.8	600.8	649.8	744.3	838.9	957.9	1077.0	1144.6	1212.2	1220.5	1228.8
35°	578.5	586.5	624.4	720.7	816.8	956.5	1096.2	1182.2	1268.4	1278.8	1289.2
37.5°	554.3	569.6	599.5	694.5	789.6	952.4	1115.3	1228.2	1341.1	1353.4	1365.7
40°	528.4	547.6	571.2	663.2	755.2	943.4	1131.5	1280.7	1430.0	1454.4	1478.6
42.5°	499.8	523.6	540.1	626.0	711.7	927.7	1143.5	1338.9	1534.0	1585.5	1636.9
45°	470.8	494.4	509.3	588.1	667.0	916.9	1166.8	1417.8	1668.7	1751.1	1833.5
47.5°	437.9	460.0	477.3	550.4	623.9	904.3	1184.7	1498.9	1813.0	1917.3	2021.7
50°	405.1	426.9	450.5	517.0	583.3	882.9	1182.4	1569.6	1956.8	2098.2	2239.7
52.5°	378.3	401.6	431.8	486.9	542.1	839.0	1136.1	1603.1	2069.9	2294.7	2519.3
55°	361.8	389.3	419.4	461.7	503.7	780.9	1057.8	1594.2	2130.7	2492.1	2853.4
57.5°	352.3	386.0	411.3	440.4	469.5	720.0	970.6	1546.1	2121.6	2657.8	3194.1
60°	344.5	378.3	398.1	418.5	438.9	643.1	847.3	1430.7	2014.1	2732.0	3449.7
62.5°	335.0	367.2	375.7	386.9	398.4	545.5	692.7	1241.7	1790.7	2567.3	3343.9
65°	*317.3*	*343.9*	*346.2*	*348.5*	*351.0*	*428.7*	*506.3*	*974.0*	*1441.6*	*2214.4*	*2987.1*
67.5°	290.0	308.2	304.7	297.8	290.9	327.8	364.6	757.9	1151.2	1901.8	2652.3
70°	246.8	255.6	256.7	246.4	236.2	249.1	262.1	580.8	899.5	1615.6	2331.8
72.5°	202.2	196.6	207.0	199.2	191.4	191.5	191.8	436.6	681.5	1341.6	2001.6
75°	168.4	164.8	160.6	151.3	142.1	142.9	143.8	323.6	503.5	1071.2	1638.9
77.5°	136.9	136.2	124.3	114.2	104.1	103.5	102.8	209.2	315.6	702.8	1090.0
80°	103.8	104.5	87.6	77.1	66.4	65.9	65.1	115.6	166.1	402.9	639.7
82.5°	62.9	60.3	50.9	45.7	40.5	40.4	40.2	62.2	84.1	201.9	319.9
85°	31.4	29.8	24.7	21.3	17.9	17.0	16.2	19.7	23.4	48.0	72.7
87.5°	9.1	7.8	7.1	6.5	5.8	5.4	5.2	5.3	5.4	5.7	5.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1364145
CATALOG NUMBER: GSS-SB1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	846.0	846.0	846.0	846.0	846.0	846.0	846.0	846.0	*846.0*	846.0	846.0
2.5°	917.4	920.7	924.2	927.8	929.9	931.9	934.1	936.2	*938.2*	936.2	934.1
5°	991.1	1005.6	1015.5	1025.4	1032.9	1040.4	1044.7	1049.1	*1049.8*	1049.1	1044.7
7.5°	1056.8	1074.2	1089.2	1104.3	1113.9	1123.5	1129.0	1134.8	*1136.7*	1134.8	1129.0
10°	1099.3	1119.8	1134.4	1149.0	1158.0	1166.8	1171.2	1175.6	*1176.9*	1175.6	1171.2
12.5°	1118.7	1138.3	1149.5	1160.7	1166.4	1172.0	1174.1	1175.9	*1174.3*	1175.9	1174.1
15°	1120.4	1131.8	1136.6	1141.2	1138.5	1135.7	1131.6	1127.6	*1125.0*	1127.6	1131.6
17.5°	1115.4	1119.6	1110.9	1102.3	1086.7	1071.2	1059.5	1047.8	*1039.4*	1047.8	1059.5
20°	1113.3	1106.9	1083.8	1060.8	1031.6	1002.4	982.8	963.1	*951.1*	963.1	982.8
22.5°	1110.6	1092.3	1053.5	1014.7	974.8	934.9	912.3	889.9	*877.2*	889.9	912.3
25°	1111.8	1080.3	1027.8	975.5	928.6	881.7	857.2	832.8	*818.8*	832.8	857.2
27.5°	1115.9	1067.9	1003.0	938.2	887.3	836.3	813.0	789.6	*777.3*	789.6	813.0
30°	1129.4	1065.6	988.0	910.3	857.1	803.9	781.0	758.1	*744.8*	758.1	781.0
32.5°	1148.4	1067.9	981.0	894.1	839.8	785.7	763.8	742.0	*730.6*	742.0	763.8
35°	1187.3	1085.4	989.0	892.8	842.4	792.2	776.1	760.1	*753.9*	760.1	776.1
37.5°	1246.7	1127.6	1028.4	929.1	894.8	860.6	860.6	860.6	*865.5*	860.6	860.6
40°	1345.0	1211.3	1117.4	1023.6	1021.5	1019.7	1041.5	1063.4	*1073.1*	1063.4	1041.5
42.5°	1495.6	1354.4	1278.7	1202.9	1248.3	1293.7	1356.8	1419.8	*1461.1*	1419.8	1356.8
45°	1696.0	1558.4	1505.5	1452.7	1553.8	1654.7	1766.2	1877.6	*1956.8*	1877.6	1766.2
47.5°	1905.9	1790.0	1759.8	1729.7	1897.7	2065.8	2229.2	2392.5	*2488.8*	2392.5	2229.2
50°	2135.6	2031.4	2025.6	2019.7	2243.6	2467.4	2678.3	2889.1	*3006.6*	2889.1	2678.3
52.5°	2405.0	2290.5	2295.2	2299.6	2565.5	2831.4	3086.4	3341.3	*3473.7*	3341.3	3086.4
55°	2710.1	2566.7	2565.9	2565.1	2870.6	3176.3	3489.5	3803.0	*3979.8*	3803.0	3489.5
57.5°	3059.8	2925.5	2893.5	2861.5	3181.0	3500.3	3846.2	4192.3	*4378.1*	4192.3	3846.2
60°	3375.7	3301.8	3250.6	3199.6	3527.7	3855.8	4213.2	4570.4	*4755.7*	4570.4	4213.2
62.5°	3476.2	3608.4	3604.6	3600.9	3955.0	4309.1	4680.7	5052.6	*5219.0*	5052.6	4680.7
65°	*3198.0*	*3408.8*	*3553.9*	*3698.8*	*4126.9*	*4554.9*	*4942.1*	*5329.3*	*5499.3*	*5329.3*	*4942.1*
67.5°	2838.1	3024.1	3142.8	3261.5	3743.9	4226.3	4665.7	5105.0	*5280.0*	5105.0	4665.7
70°	2537.6	2743.4	2828.3	2913.1	3322.9	3732.6	4080.2	4427.7	*4496.2*	4427.7	4080.2
72.5°	2246.3	2491.1	2527.1	2563.0	2861.2	3159.4	3344.6	3529.7	*3380.3*	3529.7	3344.6
75°	1915.0	2191.0	2215.0	2239.0	2331.9	2425.0	2472.1	2519.3	*2434.3*	2519.3	2472.1
77.5°	1329.0	1568.2	1622.0	1675.9	1737.8	1799.8	1796.5	1793.3	*1673.9*	1793.3	1796.5
80°	826.7	1013.7	1020.7	1027.7	1074.2	1120.5	1167.8	1215.2	*1139.3*	1215.2	1167.8
82.5°	422.5	525.3	541.1	556.9	585.4	613.8	627.0	640.4	*576.1*	640.4	627.0
85°	99.4	126.1	151.9	177.8	207.6	237.5	234.1	230.7	*194.6*	230.7	234.1
87.5°	6.0	6.2	6.4	6.5	6.6	6.7	7.1	7.5	*7.8*	7.5	7.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1364145
CATALOG NUMBER: GSS-SB1C-722-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	846.0	846.0	846.0	846.0	846.0	846.0	846.0
2.5°	931.9	929.9	927.8	924.2	920.7	917.4	914.2
5°	1040.4	1032.9	1025.4	1015.5	1005.6	991.1	976.4
7.5°	1123.5	1113.9	1104.3	1089.2	1074.2	1056.8	1039.4
10°	1166.8	1158.0	1149.0	1134.4	1119.8	1099.3	1079.0
12.5°	1172.0	1166.4	1160.7	1149.5	1138.3	1118.7	1099.1
15°	1135.7	1138.5	1141.2	1136.6	1131.8	1120.4	1108.8
17.5°	1071.2	1086.7	1102.3	1110.9	1119.6	1115.4	1111.4
20°	1002.4	1031.6	1060.8	1083.8	1106.9	1113.3	1119.8
22.5°	934.9	974.8	1014.7	1053.5	1092.3	1110.6	1128.9
25°	881.7	928.6	975.5	1027.8	1080.3	1111.8	1143.2
27.5°	836.3	887.3	938.2	1003.0	1067.9	1115.9	1164.0
30°	803.9	857.1	910.3	988.0	1065.6	1129.4	1193.1
32.5°	785.7	839.8	894.1	981.0	1067.9	1148.4	1228.8
35°	792.2	842.4	892.8	989.0	1085.4	1187.3	1289.2
37.5°	860.6	894.8	929.1	1028.4	1127.6	1246.7	1365.7
40°	1019.7	1021.5	1023.6	1117.4	1211.3	1345.0	1478.6
42.5°	1293.7	1248.3	1202.9	1278.7	1354.4	1495.6	1636.9
45°	1654.7	1553.8	1452.7	1505.5	1558.4	1696.0	1833.5
47.5°	2065.8	1897.7	1729.7	1759.8	1790.0	1905.9	2021.7
50°	2467.4	2243.6	2019.7	2025.6	2031.4	2135.6	2239.7
52.5°	2831.4	2565.5	2299.6	2295.2	2290.5	2405.0	2519.3
55°	3176.3	2870.6	2565.1	2565.9	2566.7	2710.1	2853.4
57.5°	3500.3	3181.0	2861.5	2893.5	2925.5	3059.8	3194.1
60°	3855.8	3527.7	3199.6	3250.6	3301.8	3375.7	3449.7
62.5°	4309.1	3955.0	3600.9	3604.6	3608.4	3476.2	3343.9
65°	*4554.9*	*4126.9*	*3698.8*	*3553.9*	*3408.8*	*3198.0*	*2987.1*
67.5°	4226.3	3743.9	3261.5	3142.8	3024.1	2838.1	2652.3
70°	3732.6	3322.9	2913.1	2828.3	2743.4	2537.6	2331.8
72.5°	3159.4	2861.2	2563.0	2527.1	2491.1	2246.3	2001.6
75°	2425.0	2331.9	2239.0	2215.0	2191.0	1915.0	1638.9
77.5°	1799.8	1737.8	1675.9	1622.0	1568.2	1329.0	1090.0
80°	1120.5	1074.2	1027.7	1020.7	1013.7	826.7	639.7
82.5°	613.8	585.4	556.9	541.1	525.3	422.5	319.9
85°	237.5	207.6	177.8	151.9	126.1	99.4	72.7
87.5°	6.7	6.6	6.5	6.4	6.2	6.0	5.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)