Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360694

Luminaire Tested: **GSS-SB2D-722-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360694
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB2D-722-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 2SQUARE 147W 70CRI 2200K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(52) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	15501.4 lumens
Efficiency:	N/A
Efficacy:	105.5 lumens/watt
Luminous Opening:	Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	147
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	3.1%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360694
CATALOG NUMBER: GSS-SB2D-722-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 7.6 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360694
CATALOG NUMBER: GSS-SB2D-722-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360694
CATALOG NUMBER: GSS-SB2D-722-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	7750.7	0.0	7750.7
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	7750.7	0.0	7750.7
	% Fixture	50.0	0.0	50.0
Total	Lumens	15501.4	0.0	15501.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.6	1.9
10°-20°	901.0	5.8
20°-30°	1505.9	9.7
30°-40°	2076.8	13.4
40°-50°	2545.9	16.4
50°-60°	2983.4	19.2
60°-70°	3313.0	21.4
70°-80°	1801.6	11.6
80°-90°	78.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	15501.4	100.0
0°-180°	15501.4	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360694
CATALOG NUMBER: GSS-SB2D-722-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1351.3	8.7			
FM	(30°-60°)	3803.0	24.5			
FH	(60°-80°)	2557.3	16.5			G2/5000
FVH	(80°-90°)	39.0	0.3			G1/100
BL	(0°-30°)	1351.3	8.7	B3/2500		
BM	(30°-60°)	3803.0	24.5	B3/5000		
BH	(60°-80°)	2557.3	16.5	B4/5000		G4/5000
BVH	(80°-90°)	39.0	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360694
CATALOG NUMBER: GSS-SB2D-722-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	3054.2	3054.2	3054.2	3054.2	3054.2	3054.2	3054.2	3054.2	3054.2	3054.2	3054.2
2.5°	3057.5	3057.5	3047.4	3060.9	3054.2	3057.5	3060.9	3057.5	3054.2	3057.5	3060.9
5°	3074.5	3067.7	3074.5	3081.3	3071.1	3077.9	3074.5	3057.5	3067.7	3067.7	3067.7
7.5°	3105.1	3111.8	3105.1	3122.0	3111.8	3132.2	3111.8	3098.3	3094.9	3091.5	3091.5
10°	3118.6	3118.6	3115.2	3145.8	3152.6	3172.9	3159.3	3139.0	3128.8	3115.2	3101.7
12.5°	3081.3	3088.1	3105.1	3162.7	3189.9	3230.6	3220.4	3179.7	3149.2	3139.0	3118.6
15°	3040.6	3047.4	3081.3	3152.6	3217.0	3278.1	3274.7	3223.8	3186.5	3159.3	3128.8
17.5°	2976.1	2986.3	3033.8	3142.4	3257.8	3325.6	3346.0	3295.1	3254.4	3210.3	3169.5
20°	2867.5	2867.5	2952.3	3091.5	3251.0	3403.7	3458.0	3417.3	3369.7	3298.5	3244.2
22.5°	2745.3	2752.1	2837.0	3020.2	3247.6	3471.6	3576.8	3532.6	3485.1	3407.1	3325.6
25°	2623.2	2623.2	2718.2	2925.2	3203.5	3519.1	3715.9	3692.1	3597.1	3525.8	3420.6
27.5°	2511.2	2511.2	2613.0	2830.2	3128.8	3532.6	3855.0	3855.0	3749.8	3644.6	3529.2
30°	2378.8	2412.8	2528.2	2755.5	3060.9	3508.9	3956.8	4021.3	3926.3	3790.5	3620.9
32.5°	2266.9	2290.6	2409.4	2650.3	2962.5	3481.7	4072.2	4231.7	4133.3	3946.6	3756.6
35°	2134.5	2131.1	2266.9	2504.4	2823.4	3420.6	4163.8	4482.8	4387.8	4187.6	3929.7
37.5°	1961.4	1961.4	2100.6	2331.3	2691.0	3315.5	4238.5	4761.1	4689.8	4462.5	4187.6
40°	1774.8	1795.2	1917.3	2151.5	2531.6	3189.9	4238.5	4988.4	5025.8	4791.6	4506.6
42.5°	1639.1	1645.8	1757.8	1978.4	2355.1	3027.0	4184.2	5185.3	5297.3	5100.4	4730.5
45°	1496.5	1513.5	1608.5	1812.1	2171.8	2833.6	4089.2	5405.8	5585.7	5450.0	4964.7
47.5°	1323.5	1340.4	1449.0	1656.0	1998.8	2623.2	3929.7	5636.6	6013.3	5914.9	5382.1
50°	1123.2	1136.8	1238.6	1459.2	1805.3	2382.2	3729.5	5809.7	6440.9	6539.3	6013.3
52.5°	878.9	889.1	997.7	1211.5	1574.6	2151.5	3447.8	5914.9	6871.8	7218.0	6858.3
55°	631.2	648.2	743.2	919.6	1269.2	1842.7	3111.8	5969.2	7343.5	8022.2	7906.9
57.5°	454.7	461.5	526.0	661.7	943.4	1479.6	2680.9	5877.5	7767.7	8982.6	9223.5
60°	376.7	376.7	386.9	451.3	644.8	1045.2	2165.1	5538.2	8130.8	9953.1	10696.3
62.5°	346.1	346.1	352.9	363.1	424.2	678.7	1547.4	4849.3	8171.6	10886.4	12311.6
65°	315.6	315.6	322.4	329.2	342.7	441.2	933.2	3549.6	7374.1	10896.5	13180.4
67.5°	288.4	288.4	291.8	295.2	302.0	322.4	512.4	2151.5	5901.3	10608.1	13512.9
70°	261.3	261.3	261.3	257.9	268.1	271.5	339.4	1092.7	3946.6	9579.9	13353.4
72.5°	*230.8*	*230.8*	*227.4*	*220.6*	*224.0*	*224.0*	*251.1*	*536.2*	*2049.7*	*7615.0*	*12057.1*
75°	196.8	200.2	186.6	179.9	176.5	179.9	200.2	305.4	916.2	4618.6	9009.7
77.5°	166.3	173.1	152.7	139.1	135.7	135.7	156.1	190.0	393.6	1676.4	4038.3
80°	125.6	129.0	112.0	98.4	98.4	95.0	115.4	139.1	186.6	498.8	906.1
82.5°	71.3	71.3	64.5	57.7	54.3	57.7	78.1	95.0	115.4	176.5	247.7
85°	17.0	17.0	20.4	23.8	23.8	30.5	44.1	50.9	61.1	71.3	95.0
87.5°	3.4	3.4	3.4	6.8	10.2	10.2	17.0	23.8	30.5	37.3	40.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360694
CATALOG NUMBER: GSS-SB2D-722-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	3054.2	3054.2	*3054.2*
2.5°	3060.9	3064.3	*3060.9*
5°	3081.3	3074.5	*3064.3*
7.5°	3084.7	3088.1	*3091.5*
10°	3098.3	3111.8	*3091.5*
12.5°	3111.8	3101.7	*3094.9*
15°	3122.0	3118.6	*3098.3*
17.5°	3159.3	3145.8	*3142.4*
20°	3217.0	3213.6	*3203.5*
22.5°	3284.9	3278.1	*3274.7*
25°	3383.3	3359.6	*3346.0*
27.5°	3464.8	3444.4	*3437.6*
30°	3546.2	3505.5	*3505.5*
32.5°	3617.5	3607.3	*3600.5*
35°	3787.1	3736.2	*3743.0*
37.5°	3994.2	3943.2	*3899.1*
40°	4286.0	4218.1	*4191.0*
42.5°	4472.6	4404.8	*4411.6*
45°	4577.8	4459.1	*4428.5*
47.5°	4862.9	4713.6	*4672.9*
50°	5324.4	5141.2	*5090.3*
52.5°	6071.0	5775.7	*5707.9*
55°	7007.6	6644.5	*6576.6*
57.5°	8290.3	7808.4	*7662.5*
60°	9851.3	9254.1	*9033.5*
62.5°	11727.9	10991.6	*10781.2*
65°	13139.6	12525.4	*12199.6*
67.5°	14269.7	13764.0	*13607.9*
70°	14941.6	14965.3	*15006.1*
72.5°	*14164.5*	*14816.0*	*15128.2*
75°	10380.7	10886.4	*11371.6*
77.5°	4011.1	3617.5	*3502.1*
80°	648.2	607.4	*627.8*
82.5°	291.8	308.8	*325.8*
85°	190.0	220.6	*234.2*
87.5°	44.1	44.1	*44.1*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)