Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360693

Luminaire Tested: **GSS-SB2C-722-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360693
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB2C-722-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 2SQUARE 102W 70CRI 2200K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(52) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	11277.8 lumens
Efficiency:	N/A
Efficacy:	110.6 lumens/watt
Luminous Opening:	Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B3 - U0 - G3


Input Watts (W):	102
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	9.5%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360693
CATALOG NUMBER: GSS-SB2C-722-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 5.6 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360693
CATALOG NUMBER: GSS-SB2C-722-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360693
CATALOG NUMBER: GSS-SB2C-722-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	5638.9	0.0	5638.9
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	5638.9	0.0	5638.9
	% Fixture	50.0	0.0	50.0
Total	Lumens	11277.8	0.0	11277.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.1	1.9
10°-20°	655.5	5.8
20°-30°	1095.6	9.7
30°-40°	1510.9	13.4
40°-50°	1852.2	16.4
50°-60°	2170.5	19.2
60°-70°	2410.4	21.4
70°-80°	1310.8	11.6
80°-90°	56.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11277.8	100.0
0°-180°	11277.8	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360693
CATALOG NUMBER: GSS-SB2C-722-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	983.1	8.7			
FM	(30°-60°)	2766.9	24.5			
FH	(60°-80°)	1860.6	16.5			G2/5000
FVH	(80°-90°)	28.4	0.3			G1/100
BL	(0°-30°)	983.1	8.7	B2/1000		
BM	(30°-60°)	2766.9	24.5	B3/5000		
BH	(60°-80°)	1860.6	16.5	B3/2500		G3/2500
BVH	(80°-90°)	28.4	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360693
CATALOG NUMBER: GSS-SB2C-722-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	2222.0	2222.0	2222.0	2222.0	2222.0	2222.0	2222.0	2222.0	2222.0	2222.0	2222.0
2.5°	2224.5	2224.5	2217.1	2226.9	2222.0	2224.5	2226.9	2224.5	2222.0	2224.5	2226.9
5°	2236.8	2231.9	2236.8	2241.8	2234.4	2239.3	2236.8	2224.5	2231.9	2231.9	2231.9
7.5°	2259.0	2264.0	2259.0	2271.4	2264.0	2278.8	2264.0	2254.1	2251.6	2249.2	2249.2
10°	2268.9	2268.9	2266.4	2288.7	2293.6	2308.4	2298.5	2283.7	2276.3	2266.4	2256.6
12.5°	2241.8	2246.7	2259.0	2301.0	2320.8	2350.4	2343.0	2313.4	2291.1	2283.7	2268.9
15°	2212.1	2217.1	2241.8	2293.6	2340.5	2385.0	2382.5	2345.5	2318.3	2298.5	2276.3
17.5°	2165.2	2172.6	2207.2	2286.2	2370.1	2419.5	2434.3	2397.3	2367.7	2335.6	2306.0
20°	2086.2	2086.2	2147.9	2249.2	2365.2	2476.3	2515.8	2486.2	2451.6	2399.8	2360.3
22.5°	1997.3	2002.3	2064.0	2197.3	2362.7	2525.7	2602.2	2570.1	2535.6	2478.8	2419.5
25°	1908.5	1908.5	1977.6	2128.2	2330.6	2560.2	2703.4	2686.2	2617.0	2565.2	2488.7
27.5°	1827.0	1827.0	1901.1	2059.1	2276.3	2570.1	2804.7	2804.7	2728.1	2651.6	2567.7
30°	1730.7	1755.4	1839.3	2004.7	2226.9	2552.8	2878.7	2925.6	2856.5	2757.8	2634.3
32.5°	1649.2	1666.5	1752.9	1928.2	2155.3	2533.1	2962.7	3078.7	3007.1	2871.3	2733.1
35°	1552.9	1550.5	1649.2	1822.0	2054.1	2488.7	3029.3	3261.4	3192.3	3046.6	2859.0
37.5°	1427.0	1427.0	1528.2	1696.1	1957.8	2412.1	3083.7	3463.9	3412.0	3246.6	3046.6
40°	1291.2	1306.0	1394.9	1565.3	1841.8	2320.8	3083.7	3629.3	3656.4	3486.1	3278.7
42.5°	1192.5	1197.4	1278.9	1439.4	1713.4	2202.3	3044.2	3772.5	3854.0	3710.8	3441.6
45°	1088.8	1101.1	1170.3	1318.4	1580.1	2061.5	2975.0	3933.0	4063.8	3965.1	3612.0
47.5°	962.9	975.2	1054.2	1204.8	1454.2	1908.5	2859.0	4100.8	4374.9	4303.3	3915.7
50°	817.2	827.1	901.1	1061.6	1313.5	1733.2	2713.3	4226.8	4686.0	4757.6	4374.9
52.5°	639.4	646.9	725.9	881.4	1145.6	1565.3	2508.4	4303.3	4999.5	5251.3	4989.6
55°	459.2	471.6	540.7	669.1	923.4	1340.6	2264.0	4342.8	5342.7	5836.5	5752.5
57.5°	330.8	335.8	382.7	481.4	686.4	1076.4	1950.4	4276.1	5651.3	6535.2	6710.5
60°	274.0	274.0	281.5	328.4	469.1	760.4	1575.2	4029.2	5915.5	7241.3	7782.0
62.5°	251.8	251.8	256.8	264.2	308.6	493.8	1125.8	3528.1	5945.1	7920.2	8957.2
65°	229.6	229.6	234.5	239.5	249.4	321.0	678.9	2582.5	5364.9	7927.6	9589.2
67.5°	209.9	209.9	212.3	214.8	219.7	234.5	372.8	1565.3	4293.4	7717.8	9831.2
70°	190.1	190.1	190.1	187.6	195.0	197.5	246.9	795.0	2871.3	6969.7	9715.1
72.5°	*167.9*	*167.9*	*165.4*	*160.5*	*162.9*	*162.9*	*182.7*	*390.1*	*1491.2*	*5540.2*	*8772.0*
75°	143.2	145.7	135.8	130.9	128.4	130.9	145.7	222.2	666.6	3360.2	6554.9
77.5°	121.0	125.9	111.1	101.2	98.8	98.8	113.6	138.3	286.4	1219.6	2938.0
80°	91.3	93.8	81.5	71.6	71.6	69.1	83.9	101.2	135.8	362.9	659.2
82.5°	51.8	51.8	46.9	42.0	39.5	42.0	56.8	69.1	83.9	128.4	180.2
85°	12.3	12.3	14.8	17.3	17.3	22.2	32.1	37.0	44.4	51.8	69.1
87.5°	2.5	2.5	2.5	4.9	7.4	7.4	12.3	17.3	22.2	27.2	29.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360693
CATALOG NUMBER: GSS-SB2C-722-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	2222.0	2222.0	*2222.0*
2.5°	2226.9	2229.4	*2226.9*
5°	2241.8	2236.8	*2229.4*
7.5°	2244.2	2246.7	*2249.2*
10°	2254.1	2264.0	*2249.2*
12.5°	2264.0	2256.6	*2251.6*
15°	2271.4	2268.9	*2254.1*
17.5°	2298.5	2288.7	*2286.2*
20°	2340.5	2338.0	*2330.6*
22.5°	2389.9	2385.0	*2382.5*
25°	2461.5	2444.2	*2434.3*
27.5°	2520.7	2505.9	*2501.0*
30°	2580.0	2550.4	*2550.4*
32.5°	2631.8	2624.4	*2619.5*
35°	2755.3	2718.3	*2723.2*
37.5°	2905.9	2868.9	*2836.8*
40°	3118.2	3068.8	*3049.1*
42.5°	3254.0	3204.6	*3209.6*
45°	3330.5	3244.1	*3221.9*
47.5°	3537.9	3429.3	*3399.7*
50°	3873.7	3740.4	*3703.3*
52.5°	4416.9	4202.1	*4152.7*
55°	5098.3	4834.1	*4784.7*
57.5°	6031.5	5680.9	*5574.8*
60°	7167.2	6732.7	*6572.2*
62.5°	8532.5	7996.8	*7843.7*
65°	9559.6	9112.7	*8875.7*
67.5°	10381.7	10013.9	*9900.3*
70°	10870.6	10887.8	*10917.5*
72.5°	*10305.2*	*10779.2*	*11006.4*
75°	7552.4	7920.2	*8273.3*
77.5°	2918.2	2631.8	*2547.9*
80°	471.6	441.9	*456.7*
82.5°	212.3	224.7	*237.0*
85°	138.3	160.5	*170.4*
87.5°	32.1	32.1	*32.1*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)