Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360698

Luminaire Tested: **GSS-SB3D-722-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360698
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB3D-722-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 3SQUARE 219W 70CRI 2200K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(78) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	23350.9 lumens
Efficiency:	N/A
Efficacy:	106.6 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	219
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	2.5%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360698
CATALOG NUMBER: GSS-SB3D-722-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 11.5 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360698
CATALOG NUMBER: GSS-SB3D-722-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360698
CATALOG NUMBER: GSS-SB3D-722-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	11675.4	0.0	11675.4
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	11675.4	0.0	11675.4
	% Fixture	50.0	0.0	50.0
Total	Lumens	23350.9	0.0	23350.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	445.3	1.9
10°-20°	1357.2	5.8
20°-30°	2268.5	9.7
30°-40°	3128.4	13.4
40°-50°	3835.0	16.4
50°-60°	4494.1	19.2
60°-70°	4990.7	21.4
70°-80°	2713.9	11.6
80°-90°	117.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	23350.9	100.0
0°-180°	23350.9	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360698
CATALOG NUMBER: GSS-SB3D-722-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2035.5	8.7			
FM	(30°-60°)	5728.8	24.5			
FH	(60°-80°)	3852.3	16.5			G2/5000
FVH	(80°-90°)	58.8	0.3			G1/100
BL	(0°-30°)	2035.5	8.7	B3/2500		
BM	(30°-60°)	5728.8	24.5	B4/8500		
BH	(60°-80°)	3852.3	16.5	B4/5000		G4/5000
BVH	(80°-90°)	58.8	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360698
CATALOG NUMBER: GSS-SB3D-722-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	4600.7	4600.7	4600.7	4600.7	4600.7	4600.7	4600.7	4600.7	4600.7	4600.7	4600.7
2.5°	4605.8	4605.8	4590.5	4610.9	4600.7	4605.8	4610.9	4605.8	4600.7	4605.8	4610.9
5°	4631.4	4621.1	4631.4	4641.6	4626.3	4636.5	4631.4	4605.8	4621.1	4621.1	4621.1
7.5°	4677.4	4687.6	4677.4	4702.9	4687.6	4718.3	4687.6	4667.2	4662.0	4656.9	4656.9
10°	4697.8	4697.8	4692.7	4738.7	4748.9	4779.6	4759.2	4728.5	4713.2	4692.7	4672.3
12.5°	4641.6	4651.8	4677.4	4764.3	4805.2	4866.5	4851.2	4789.8	4743.8	4728.5	4697.8
15°	4580.2	4590.5	4641.6	4748.9	4846.1	4938.1	4933.0	4856.3	4800.1	4759.2	4713.2
17.5°	4483.1	4498.5	4570.0	4733.6	4907.4	5009.6	5040.3	4963.6	4902.3	4835.8	4774.5
20°	4319.5	4319.5	4447.3	4656.9	4897.2	5127.2	5209.0	5147.7	5076.1	4968.8	4887.0
22.5°	4135.5	4145.7	4273.5	4549.6	4892.1	5229.5	5387.9	5321.5	5249.9	5132.3	5009.6
25°	3951.5	3951.5	4094.6	4406.4	4825.6	5301.0	5597.5	5561.7	5418.6	5311.2	5152.8
27.5°	3782.8	3782.8	3936.2	4263.3	4713.2	5321.5	5807.1	5807.1	5648.6	5490.2	5316.4
30°	3583.4	3634.6	3808.4	4150.9	4610.9	5285.7	5960.5	6057.6	5914.5	5710.0	5454.4
32.5°	3414.7	3450.5	3629.4	3992.4	4462.7	5244.8	6134.3	6374.5	6226.3	5945.1	5658.9
35°	3215.4	3210.3	3414.7	3772.6	4253.1	5152.8	6272.3	6752.8	6609.7	6308.1	5919.6
37.5°	2954.7	2954.7	3164.3	3511.9	4053.7	4994.3	6384.7	7172.0	7064.6	6722.1	6308.1
40°	2673.5	2704.2	2888.2	3240.9	3813.5	4805.2	6384.7	7514.5	7570.7	7218.0	6788.6
42.5°	2469.0	2479.3	2648.0	2980.2	3547.6	4559.8	6303.0	7811.0	7979.7	7683.2	7126.0
45°	2254.3	2279.9	2423.0	2729.7	3271.6	4268.4	6159.8	8143.2	8414.2	8209.7	7478.7
47.5°	1993.6	2019.2	2182.8	2494.6	3010.9	3951.5	5919.6	8490.8	9058.3	8910.0	8107.4
50°	1692.0	1712.5	1865.8	2198.1	2719.5	3588.5	5618.0	8751.5	9702.4	9850.6	9058.3
52.5°	1324.0	1339.3	1502.9	1824.9	2371.9	3240.9	5193.7	8910.0	10351.6	10873.0	10331.1
55°	950.8	976.4	1119.5	1385.3	1911.8	2775.8	4687.6	8991.8	11062.1	12084.5	11910.7
57.5°	685.0	695.2	792.3	996.8	1421.1	2228.8	4038.4	8853.8	11701.1	13531.2	13894.1
60°	567.4	567.4	582.8	679.9	971.3	1574.5	3261.4	8342.6	12248.1	14993.2	16112.7
62.5°	521.4	521.4	531.6	547.0	639.0	1022.4	2331.0	7304.9	12309.4	16398.9	18545.9
65°	475.4	475.4	485.6	495.9	516.3	664.5	1405.8	5347.0	11108.1	16414.3	19854.6
67.5°	434.5	434.5	439.6	444.7	455.0	485.6	771.9	3240.9	8889.6	15979.8	20355.5
70°	393.6	393.6	393.6	388.5	403.8	409.0	511.2	1646.0	5945.1	14430.9	20115.3
72.5°	*347.6*	*347.6*	*342.5*	*332.3*	*337.4*	*337.4*	*378.3*	*807.7*	*3087.6*	*11471.1*	*18162.5*
75°	296.5	301.6	281.2	270.9	265.8	270.9	301.6	460.1	1380.2	6957.3	13572.1
77.5°	250.5	260.7	230.0	209.6	204.5	204.5	235.1	286.3	593.0	2525.3	6083.1
80°	189.1	194.3	168.7	148.2	148.2	143.1	173.8	209.6	281.2	751.4	1364.9
82.5°	107.3	107.3	97.1	86.9	81.8	86.9	117.6	143.1	173.8	265.8	373.2
85°	25.6	25.6	30.7	35.8	35.8	46.0	66.5	76.7	92.0	107.3	143.1
87.5°	5.1	5.1	5.1	10.2	15.3	15.3	25.6	35.8	46.0	56.2	61.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360698
CATALOG NUMBER: GSS-SB3D-722-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	4600.7	4600.7	*4600.7*
2.5°	4610.9	4616.0	*4610.9*
5°	4641.6	4631.4	*4616.0*
7.5°	4646.7	4651.8	*4656.9*
10°	4667.2	4687.6	*4656.9*
12.5°	4687.6	4672.3	*4662.0*
15°	4702.9	4697.8	*4667.2*
17.5°	4759.2	4738.7	*4733.6*
20°	4846.1	4841.0	*4825.6*
22.5°	4948.3	4938.1	*4933.0*
25°	5096.5	5060.8	*5040.3*
27.5°	5219.2	5188.6	*5178.3*
30°	5341.9	5280.6	*5280.6*
32.5°	5449.3	5433.9	*5423.7*
35°	5704.9	5628.2	*5638.4*
37.5°	6016.7	5940.0	*5873.6*
40°	6456.3	6354.1	*6313.2*
42.5°	6737.5	6635.2	*6645.5*
45°	6895.9	6717.0	*6671.0*
47.5°	7325.3	7100.4	*7039.1*
50°	8020.5	7744.5	*7667.8*
52.5°	9145.2	8700.4	*8598.2*
55°	10556.0	10009.1	*9906.8*
57.5°	12488.3	11762.4	*11542.6*
60°	14839.8	13940.1	*13607.8*
62.5°	17666.7	16557.4	*16240.5*
65°	19793.2	18868.0	*18377.2*
67.5°	21495.5	20733.8	*20498.7*
70°	22507.6	22543.4	*22604.8*
72.5°	*21337.0*	*22318.5*	*22788.8*
75°	15637.3	16398.9	*17129.9*
77.5°	6042.2	5449.3	*5275.5*
80°	976.4	915.0	*945.7*
82.5°	439.6	465.2	*490.7*
85°	286.3	332.3	*352.7*
87.5°	66.5	66.5	*66.5*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)