Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1359925

Luminaire Tested: **GSS-SB2C-722-U-T3**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1359925
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB2C-722-U-T3
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 2SQUARE 102W 70CRI 2200K FIXTURE w/ TYPE III DISTRIBUTION OPTIC
Light Source:	(52) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	11149.1 lumens
Efficiency:	N/A
Efficacy:	109.3 lumens/watt
Luminous Opening:	Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification:	Type III - Short
BUG Rating:	B2 - U0 - G2


Input Watts (W):	102
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	9.5%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359925
CATALOG NUMBER: GSS-SB2C-722-U-T3

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 4.9 fc
Type III - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359925
CATALOG NUMBER: GSS-SB2C-722-U-T3

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1359925
CATALOG NUMBER: GSS-SB2C-722-U-T3

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2637.7	0.0	2637.7
	% Fixture	23.7	0.0	23.7
Street Side	Lumens	8511.4	0.0	8511.4
	% Fixture	76.3	0.0	76.3
Total	Lumens	11149.1	0.0	11149.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.2	1.5
10°-20°	533.6	4.8
20°-30°	912.3	8.2
30°-40°	1323.5	11.9
40°-50°	1719.2	15.4
50°-60°	2329.4	20.9
60°-70°	2717.2	24.4
70°-80°	1339.7	12.0
80°-90°	105.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11149.1	100.0
0°-180°	11149.1	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1359925
CATALOG NUMBER: GSS-SB2C-722-U-T3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	951.1	8.5			
FM	(30°-60°)	4072.0	36.5			
FH	(60°-80°)	3433.1	30.8			G2/5000
FVH	(80°-90°)	55.2	0.5			G1/100
BL	(0°-30°)	664.0	6.0	B2/1000		
BM	(30°-60°)	1300.0	11.7	B2/2500		
BH	(60°-80°)	623.7	5.6	B2/1000		G2/1000
BVH	(80°-90°)	50.0	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G2
Type III Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359925
CATALOG NUMBER: GSS-SB2C-722-U-T3

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	52°	55°	65°	75°	85°
0°	1725.3	1725.3	1725.3	1725.3	1725.3	1725.3	1725.3	1725.3	1725.3	1725.3	1725.3
2.5°	1777.5	1775.0	1772.5	1762.6	1762.6	1765.1	1760.1	1762.6	1760.1	1747.7	1737.7
5°	1876.8	1854.4	1849.5	1844.5	1849.5	1834.6	1822.2	1814.7	1787.4	1779.9	1750.2
7.5°	1919.0	1921.5	1919.0	1909.0	1901.6	1901.6	1881.7	1871.8	1854.4	1824.6	1775.0
10°	1978.5	1976.1	1968.6	1973.6	1988.5	1963.7	1948.8	1941.3	1911.5	1869.3	1822.2
12.5°	2085.3	2067.9	2063.0	2055.5	2053.0	2038.1	2020.8	2023.2	1988.5	1923.9	1874.3
15°	2177.1	2157.3	2179.6	2164.7	2144.9	2122.5	2105.2	2090.3	2050.5	1991.0	1928.9
17.5°	2264.0	2254.1	2264.0	2264.0	2261.6	2224.3	2189.6	2177.1	2130.0	2063.0	1981.0
20°	2331.1	2331.1	2348.4	2348.4	2341.0	2318.7	2296.3	2281.4	2214.4	2127.5	2033.2
22.5°	2418.0	2378.2	2415.5	2418.0	2420.4	2403.1	2388.2	2368.3	2298.8	2194.5	2075.4
25°	2499.9	2467.6	2489.9	2475.0	2485.0	2492.4	2485.0	2477.5	2400.6	2281.4	2137.4
27.5°	2629.0	2596.7	2611.6	2576.8	2576.8	2569.4	2581.8	2591.7	2507.3	2365.8	2192.0
30°	2822.6	2785.4	2772.9	2730.7	2688.5	2671.2	2676.1	2693.5	2636.4	2447.7	2246.7
32.5°	2988.9	2969.1	2959.1	2924.4	2872.2	2792.8	2805.2	2805.2	2745.6	2507.3	2274.0
35°	3125.5	3120.5	3123.0	3075.8	3065.9	2936.8	2936.8	2931.8	2822.6	2586.8	2346.0
37.5°	3214.8	3187.5	3199.9	3217.3	3185.0	3098.2	3075.8	3063.4	2929.3	2671.2	2440.3
40°	3195.0	3175.1	3222.3	3254.6	3229.7	3212.3	3209.9	3185.0	3036.1	2777.9	2579.3
42.5°	3192.5	3175.1	3232.2	3267.0	3254.6	3281.9	3289.3	3306.7	3172.6	2946.7	2777.9
45°	3202.4	3195.0	3289.3	3334.0	3304.2	3341.4	3383.6	3398.5	3346.4	3152.8	3026.2
47.5°	3284.3	3274.4	3383.6	3435.8	3460.6	3525.1	3497.8	3522.7	3552.5	3445.7	3311.6
50°	3363.8	3373.7	3520.2	3569.8	3691.5	3780.8	3686.5	3726.2	3825.5	3785.8	3694.0
52.5°	3490.4	3492.9	3636.9	3761.0	3994.3	4078.7	3986.9	3991.9	4125.9	4200.4	4078.7
55°	3522.7	3550.0	3743.6	4001.8	4336.9	4396.5	4354.3	4336.9	4495.8	4597.6	4466.0
57.5°	3520.2	3505.3	3746.1	4103.6	4597.6	4808.6	4833.4	4786.3	4920.3	4962.5	4890.5
60°	3428.3	3458.1	3721.3	4175.6	4840.9	5310.1	5369.6	5307.6	5372.1	5384.5	5183.4
62.5°	3147.8	3157.7	3517.7	4178.0	5032.0	5727.1	5903.4	5833.9	5774.3	5620.4	5248.0
65°	2691.0	2673.6	3018.7	3833.0	5066.8	6129.3	6382.5	6382.5	5995.2	5699.8	5111.5
67.5°	2244.2	2216.9	2475.0	3125.5	4510.7	6305.5	6710.2	6578.6	6042.4	5754.4	4786.3
70°	1082.4	1159.3	1554.0	2211.9	3448.2	5325.0	6466.9	6516.5	6005.2	5583.1	4155.7
72.5°	387.3	369.9	558.6	948.3	1909.0	3475.5	5414.3	5851.2	5744.5	5091.6	3403.5
75°	178.7	181.2	233.4	330.2	618.1	1695.5	3443.2	4029.1	4920.3	4232.7	2547.0
77.5°	139.0	139.0	158.9	188.7	255.7	548.6	1760.1	2261.6	3180.1	2621.5	1213.9
80°	101.8	104.3	106.7	124.1	156.4	206.0	523.8	784.5	1159.3	841.6	394.7
82.5°	72.0	72.0	69.5	69.5	84.4	91.9	141.5	198.6	340.1	230.9	104.3
85°	29.8	34.8	29.8	29.8	29.8	37.2	44.7	52.1	74.5	64.5	44.7
87.5°	5.0	5.0	5.0	7.4	9.9	12.4	14.9	17.4	19.9	19.9	19.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1359925
CATALOG NUMBER: GSS-SB2C-722-U-T3

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1725.3	1725.3	1725.3	1725.3	1725.3	1725.3	1725.3	1725.3	1725.3	1725.3	1725.3
2.5°	1732.8	1732.8	1725.3	1712.9	1708.0	1700.5	1698.0	1695.5	1690.6	1700.5	1695.5
5°	1742.7	1732.8	1722.9	1703.0	1700.5	1688.1	1675.7	1673.2	1665.8	1673.2	1673.2
7.5°	1765.1	1750.2	1727.8	1708.0	1690.6	1688.1	1665.8	1645.9	1645.9	1648.4	1645.9
10°	1804.8	1787.4	1765.1	1727.8	1695.5	1665.8	1628.5	1603.7	1606.2	1606.2	1601.2
12.5°	1856.9	1832.1	1792.4	1737.7	1688.1	1640.9	1596.2	1588.8	1586.3	1591.3	1576.4
15°	1896.6	1874.3	1809.7	1747.7	1670.7	1623.6	1576.4	1559.0	1561.5	1556.5	1544.1
17.5°	1946.3	1911.5	1832.1	1740.2	1650.9	1606.2	1551.6	1514.3	1494.5	1496.9	1494.5
20°	1993.4	1943.8	1849.5	1740.2	1645.9	1566.5	1496.9	1447.3	1405.1	1397.6	1395.2
22.5°	2028.2	1978.5	1869.3	1742.7	1616.1	1521.8	1420.0	1355.4	1293.4	1283.4	1281.0
25°	2077.8	2013.3	1891.7	1725.3	1576.4	1447.3	1320.7	1248.7	1194.1	1184.2	1184.2
27.5°	2120.1	2050.5	1921.5	1708.0	1511.8	1345.5	1226.4	1154.4	1119.6	1102.2	1102.2
30°	2164.7	2087.8	1946.3	1655.8	1425.0	1243.7	1151.9	1104.7	1065.0	1047.6	1040.2
32.5°	2214.4	2149.8	1951.2	1603.7	1338.1	1176.7	1099.7	1060.0	1017.8	993.0	990.5
35°	2276.4	2229.3	1933.9	1526.7	1251.2	1124.6	1050.1	1005.4	963.2	938.4	943.3
37.5°	2375.7	2321.1	1881.7	1417.5	1179.2	1092.3	1010.4	945.8	896.2	856.5	858.9
40°	2522.2	2432.8	1804.8	1285.9	1127.1	1055.1	963.2	888.7	816.7	757.2	757.2
42.5°	2688.5	2532.1	1710.4	1164.3	1087.3	1007.9	913.6	819.2	717.4	655.4	652.9
45°	2874.7	2619.0	1601.2	1065.0	1022.8	950.8	849.0	715.0	647.9	615.7	613.2
47.5°	3123.0	2713.4	1472.1	978.1	948.3	893.7	752.2	655.4	615.7	590.8	588.4
50°	3356.3	2815.1	1365.4	893.7	868.9	826.7	685.2	630.6	598.3	578.4	573.5
52.5°	3626.9	2919.4	1246.2	811.8	779.5	722.4	670.3	618.1	588.4	573.5	568.5
55°	3895.0	3065.9	1114.6	737.3	700.1	675.2	655.4	610.7	580.9	571.0	563.5
57.5°	4200.4	3207.4	953.3	657.9	643.0	640.5	652.9	608.2	583.4	566.0	556.1
60°	4359.3	3269.4	784.5	585.9	588.4	603.2	643.0	608.2	568.5	538.7	526.3
62.5°	4304.6	3142.8	620.6	513.9	536.2	563.5	625.6	585.9	536.2	513.9	499.0
65°	4086.2	2926.9	484.1	451.8	489.1	513.9	583.4	553.6	503.9	481.6	479.1
67.5°	*3770.9*	*2552.0*	*392.2*	*397.2*	*434.4*	*466.7*	*546.1*	*533.7*	*476.6*	*461.7*	*461.7*
70°	3170.1	2050.5	322.7	347.5	379.8	414.6	518.8	501.5	441.9	434.4	434.4
72.5°	2477.5	1447.3	275.6	305.3	315.3	364.9	481.6	464.2	429.5	446.8	449.3
75°	1747.7	881.3	235.8	258.2	268.1	300.4	446.8	454.3	422.0	479.1	489.1
77.5°	794.4	387.3	183.7	203.6	216.0	255.7	384.8	422.0	364.9	364.9	345.1
80°	278.0	163.8	146.5	146.5	156.4	198.6	320.2	347.5	292.9	258.2	248.2
82.5°	101.8	89.4	109.2	109.2	99.3	121.6	213.5	230.9	211.0	183.7	181.2
85°	39.7	42.2	67.0	67.0	49.6	59.6	119.2	124.1	119.2	104.3	104.3
87.5°	17.4	17.4	19.9	19.9	17.4	14.9	22.3	22.3	14.9	9.9	5.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)