Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360702

Luminaire Tested: **GSS-SB4D-722-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360702
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB4D-722-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 4SQUARE 238W 70CRI 2200K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(104) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	26141.1 lumens
Efficiency:	N/A
Efficacy:	109.8 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	238
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	--
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360702
CATALOG NUMBER: GSS-SB4D-722-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 12.9 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360702
CATALOG NUMBER: GSS-SB4D-722-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360702
CATALOG NUMBER: GSS-SB4D-722-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	13070.6	0.0	13070.6
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	13070.6	0.0	13070.6
	% Fixture	50.0	0.0	50.0
Total	Lumens	26141.1	0.0	26141.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	498.5	1.9
10°-20°	1519.4	5.8
20°-30°	2539.6	9.7
30°-40°	3502.2	13.4
40°-50°	4293.3	16.4
50°-60°	5031.2	19.2
60°-70°	5587.0	21.4
70°-80°	3038.2	11.6
80°-90°	131.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	26141.1	100.0
0°-180°	26141.1	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360702
CATALOG NUMBER: GSS-SB4D-722-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2278.8	8.7			
FM	(30°-60°)	6413.4	24.5			
FH	(60°-80°)	4312.6	16.5			G2/5000
FVH	(80°-90°)	65.8	0.3			G1/100
BL	(0°-30°)	2278.8	8.7	B3/2500		
BM	(30°-60°)	6413.4	24.5	B4/8500		
BH	(60°-80°)	4312.6	16.5	B4/5000		G4/5000
BVH	(80°-90°)	65.8	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360702
CATALOG NUMBER: GSS-SB4D-722-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	5150.4	5150.4	5150.4	5150.4	5150.4	5150.4	5150.4	5150.4	5150.4	5150.4	5150.4
2.5°	5156.2	5156.2	5139.0	5161.9	5150.4	5156.2	5161.9	5156.2	5150.4	5156.2	5161.9
5°	5184.8	5173.3	5184.8	5196.2	5179.1	5190.5	5184.8	5156.2	5173.3	5173.3	5173.3
7.5°	5236.3	5247.7	5236.3	5264.9	5247.7	5282.1	5247.7	5224.8	5219.1	5213.4	5213.4
10°	5259.2	5259.2	5253.5	5305.0	5316.4	5350.7	5327.9	5293.5	5276.3	5253.5	5230.6
12.5°	5196.2	5207.7	5236.3	5333.6	5379.4	5448.0	5430.9	5362.2	5310.7	5293.5	5259.2
15°	5127.6	5139.0	5196.2	5316.4	5425.1	5528.1	5522.4	5436.6	5373.6	5327.9	5276.3
17.5°	5018.8	5036.0	5116.1	5299.2	5493.8	5608.3	5642.6	5556.8	5488.1	5413.7	5345.0
20°	4835.7	4835.7	4978.8	5213.4	5482.4	5739.9	5831.5	5762.8	5682.7	5562.5	5470.9
22.5°	4629.7	4641.1	4784.2	5093.2	5476.6	5854.3	6031.7	5957.4	5877.2	5745.6	5608.3
25°	4423.7	4423.7	4583.9	4933.0	5402.2	5934.5	6266.4	6226.3	6066.1	5945.9	5768.5
27.5°	4234.8	4234.8	4406.5	4772.8	5276.3	5957.4	6501.0	6501.0	6323.6	6146.2	5951.6
30°	4011.6	4068.9	4263.4	4646.9	5161.9	5917.3	6672.7	6781.4	6621.2	6392.3	6106.1
32.5°	3822.8	3862.8	4063.1	4469.4	4995.9	5871.5	6867.3	7136.2	6970.3	6655.5	6335.1
35°	3599.6	3593.9	3822.8	4223.4	4761.3	5768.5	7021.8	7559.7	7399.5	7061.8	6626.9
37.5°	3307.7	3307.7	3542.4	3931.5	4538.1	5591.1	7147.7	8029.0	7908.8	7525.4	7061.8
40°	2993.0	3027.3	3233.3	3628.2	4269.2	5379.4	7147.7	8412.4	8475.4	8080.5	7599.8
42.5°	2764.1	2775.5	2964.4	3336.3	3971.6	5104.7	7056.1	8744.3	8933.2	8601.3	7977.5
45°	2523.7	2552.3	2712.6	3055.9	3662.5	4778.5	6895.9	9116.3	9419.6	9190.7	8372.3
47.5°	2231.9	2260.5	2443.6	2792.7	3370.7	4423.7	6626.9	9505.4	10140.7	9974.7	9076.2
50°	1894.2	1917.1	2088.8	2460.8	3044.5	4017.4	6289.3	9797.3	10861.7	11027.7	10140.7
52.5°	1482.2	1499.4	1682.5	2043.0	2655.3	3628.2	5814.3	9974.7	11588.5	12172.2	11565.6
55°	1064.4	1093.0	1253.3	1550.9	2140.3	3107.4	5247.7	10066.3	12384.0	13528.5	13333.9
57.5°	766.8	778.3	887.0	1115.9	1590.9	2495.1	4521.0	9911.8	13099.3	15148.0	15554.4
60°	635.2	635.2	652.4	761.1	1087.3	1762.6	3651.1	9339.5	13711.6	16784.7	18038.0
62.5°	583.7	583.7	595.2	612.3	715.3	1144.5	2609.6	8177.8	13780.3	18358.5	20762.0
65°	532.2	532.2	543.7	555.1	578.0	744.0	1573.7	5986.0	12435.5	18375.7	22227.1
67.5°	486.4	486.4	492.2	497.9	509.3	543.7	864.1	3628.2	9951.8	17889.2	22787.9
70°	440.6	440.6	440.6	434.9	452.1	457.8	572.3	1842.7	6655.5	16155.2	22518.9
72.5°	*389.1*	*389.1*	*383.4*	*372.0*	*377.7*	*377.7*	*423.5*	*904.2*	*3456.5*	*12841.8*	*20332.8*
75°	331.9	337.6	314.7	303.3	297.6	303.3	337.6	515.0	1545.1	7788.6	15193.8
77.5°	280.4	291.9	257.5	234.6	228.9	228.9	263.2	320.5	663.8	2827.0	6810.0
80°	211.7	217.5	188.8	166.0	166.0	160.2	194.6	234.6	314.7	841.2	1528.0
82.5°	120.2	120.2	108.7	97.3	91.6	97.3	131.6	160.2	194.6	297.6	417.8
85°	28.6	28.6	34.3	40.1	40.1	51.5	74.4	85.8	103.0	120.2	160.2
87.5°	5.7	5.7	5.7	11.4	17.2	17.2	28.6	40.1	51.5	62.9	68.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360702
CATALOG NUMBER: GSS-SB4D-722-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	5150.4	5150.4	*5150.4*
2.5°	5161.9	5167.6	*5161.9*
5°	5196.2	5184.8	*5167.6*
7.5°	5202.0	5207.7	*5213.4*
10°	5224.8	5247.7	*5213.4*
12.5°	5247.7	5230.6	*5219.1*
15°	5264.9	5259.2	*5224.8*
17.5°	5327.9	5305.0	*5299.2*
20°	5425.1	5419.4	*5402.2*
22.5°	5539.6	5528.1	*5522.4*
25°	5705.6	5665.5	*5642.6*
27.5°	5842.9	5808.6	*5797.1*
30°	5980.2	5911.6	*5911.6*
32.5°	6100.4	6083.3	*6071.8*
35°	6386.6	6300.7	*6312.2*
37.5°	6735.6	6649.8	*6575.4*
40°	7227.8	7113.3	*7067.6*
42.5°	7542.5	7428.1	*7439.5*
45°	7720.0	7519.7	*7468.2*
47.5°	8200.7	7948.9	*7880.2*
50°	8979.0	8669.9	*8584.1*
52.5°	10237.9	9740.1	*9625.6*
55°	11817.4	11205.1	*11090.6*
57.5°	13980.6	13168.0	*12921.9*
60°	16613.1	15605.9	*15233.9*
62.5°	19777.7	18535.9	*18181.1*
65°	22158.4	21122.6	*20573.2*
67.5°	24064.0	23211.4	*22948.1*
70°	25197.1	25237.2	*25305.9*
72.5°	*23886.6*	*24985.4*	*25511.9*
75°	17505.8	18358.5	*19176.8*
77.5°	6764.3	6100.4	*5905.8*
80°	1093.0	1024.4	*1058.7*
82.5°	492.2	520.8	*549.4*
85°	320.5	372.0	*394.9*
87.5°	74.4	74.4	*74.4*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)