Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360697

Luminaire Tested: **GSS-SB3C-722-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360697
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB3C-722-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 3SQUARE 150W 70CRI 2200K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(78) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	16989.1 lumens
Efficiency:	N/A
Efficacy:	113.3 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	150
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	6.3%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360697
CATALOG NUMBER: GSS-SB3C-722-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 8.4 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360697
CATALOG NUMBER: GSS-SB3C-722-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360697
CATALOG NUMBER: GSS-SB3C-722-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	8494.5	0.0	8494.5
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	8494.5	0.0	8494.5
	% Fixture	50.0	0.0	50.0
Total	Lumens	16989.1	0.0	16989.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	324.0	1.9
10°-20°	987.5	5.8
20°-30°	1650.5	9.7
30°-40°	2276.1	13.4
40°-50°	2790.2	16.4
50°-60°	3269.7	19.2
60°-70°	3631.0	21.4
70°-80°	1974.5	11.6
80°-90°	85.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	16989.1	100.0
0°-180°	16989.1	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360697
CATALOG NUMBER: GSS-SB3C-722-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1481.0	8.7			
FM	(30°-60°)	4168.0	24.5			
FH	(60°-80°)	2802.8	16.5			G2/5000
FVH	(80°-90°)	42.8	0.3			G1/100
BL	(0°-30°)	1481.0	8.7	B3/2500		
BM	(30°-60°)	4168.0	24.5	B3/5000		
BH	(60°-80°)	2802.8	16.5	B4/5000		G4/5000
BVH	(80°-90°)	42.8	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360697
CATALOG NUMBER: GSS-SB3C-722-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	3347.3	3347.3	3347.3	3347.3	3347.3	3347.3	3347.3	3347.3	3347.3	3347.3	3347.3
2.5°	3351.0	3351.0	3339.8	3354.7	3347.3	3351.0	3354.7	3351.0	3347.3	3351.0	3354.7
5°	3369.6	3362.1	3369.6	3377.0	3365.9	3373.3	3369.6	3351.0	3362.1	3362.1	3362.1
7.5°	3403.1	3410.5	3403.1	3421.7	3410.5	3432.8	3410.5	3395.6	3391.9	3388.2	3388.2
10°	3417.9	3417.9	3414.2	3447.7	3455.1	3477.4	3462.6	3440.3	3429.1	3414.2	3399.3
12.5°	3377.0	3384.5	3403.1	3466.3	3496.0	3540.7	3529.5	3484.9	3451.4	3440.3	3417.9
15°	3332.4	3339.8	3377.0	3455.1	3525.8	3592.7	3589.0	3533.2	3492.3	3462.6	3429.1
17.5°	3261.7	3272.9	3325.0	3444.0	3570.4	3644.8	3667.1	3611.3	3566.7	3518.4	3473.7
20°	3142.7	3142.7	3235.7	3388.2	3563.0	3730.3	3789.9	3745.2	3693.2	3615.1	3555.5
22.5°	3008.8	3016.3	3109.2	3310.1	3559.3	3804.7	3920.0	3871.7	3819.6	3734.1	3644.8
25°	2874.9	2874.9	2979.1	3205.9	3510.9	3856.8	4072.5	4046.5	3942.3	3864.2	3748.9
27.5°	2752.2	2752.2	2863.8	3101.8	3429.1	3871.7	4225.0	4225.0	4109.7	3994.4	3868.0
30°	2607.2	2644.3	2770.8	3020.0	3354.7	3845.6	4336.6	4407.2	4303.1	4154.3	3968.4
32.5°	2484.4	2510.5	2640.6	2904.7	3246.9	3815.9	4463.0	4637.8	4530.0	4325.4	4117.1
35°	2339.4	2335.7	2484.4	2744.8	3094.4	3748.9	4563.4	4913.1	4808.9	4589.5	4306.8
37.5°	2149.7	2149.7	2302.2	2555.1	2949.3	3633.6	4645.3	5218.0	5139.9	4890.7	4589.5
40°	1945.1	1967.5	2101.3	2358.0	2774.5	3496.0	4645.3	5467.2	5508.1	5251.5	4939.1
42.5°	1796.4	1803.8	1926.5	2168.3	2581.1	3317.5	4585.8	5682.9	5805.7	5589.9	5184.6
45°	1640.2	1658.8	1762.9	1986.0	2380.3	3105.5	4481.6	5924.7	6121.8	5973.0	5441.2
47.5°	1450.5	1469.1	1588.1	1815.0	2190.6	2874.9	4306.8	6177.6	6590.4	6482.5	5898.6
50°	1231.1	1245.9	1357.5	1599.3	1978.6	2610.9	4087.4	6367.3	7059.0	7166.9	6590.4
52.5°	963.3	974.4	1093.4	1327.8	1725.7	2358.0	3778.7	6482.5	7531.4	7910.7	7516.5
55°	691.8	710.4	814.5	1007.9	1391.0	2019.5	3410.5	6542.1	8048.3	8792.2	8665.7
57.5°	498.4	505.8	576.5	725.2	1033.9	1621.6	2938.2	6441.6	8513.2	9844.7	10108.8
60°	412.8	412.8	424.0	494.7	706.6	1145.5	2372.8	6069.7	8911.2	10908.4	11722.9
62.5°	379.4	379.4	386.8	398.0	464.9	743.8	1696.0	5314.7	8955.8	11931.2	13493.2
65°	345.9	345.9	353.3	360.8	375.6	483.5	1022.8	3890.3	8081.8	11942.3	14445.3
67.5°	316.1	316.1	319.9	323.6	331.0	353.3	561.6	2358.0	6467.7	11626.2	14809.8
70°	286.4	286.4	286.4	282.7	293.8	297.5	371.9	1197.6	4325.4	10499.3	14635.0
72.5°	*252.9*	*252.9*	*249.2*	*241.7*	*245.5*	*245.5*	*275.2*	*587.6*	*2246.4*	*8345.9*	*13214.3*
75°	215.7	219.4	204.6	197.1	193.4	197.1	219.4	334.7	1004.2	5061.8	9874.4
77.5°	182.2	189.7	167.4	152.5	148.8	148.8	171.1	208.3	431.4	1837.3	4425.8
80°	137.6	141.3	122.7	107.9	107.9	104.1	126.5	152.5	204.6	546.7	993.0
82.5°	78.1	78.1	70.7	63.2	59.5	63.2	85.5	104.1	126.5	193.4	271.5
85°	18.6	18.6	22.3	26.0	26.0	33.5	48.3	55.8	66.9	78.1	104.1
87.5°	3.7	3.7	3.7	7.4	11.2	11.2	18.6	26.0	33.5	40.9	44.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360697
CATALOG NUMBER: GSS-SB3C-722-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	3347.3	3347.3	*3347.3*
2.5°	3354.7	3358.4	*3354.7*
5°	3377.0	3369.6	*3358.4*
7.5°	3380.7	3384.5	*3388.2*
10°	3395.6	3410.5	*3388.2*
12.5°	3410.5	3399.3	*3391.9*
15°	3421.7	3417.9	*3395.6*
17.5°	3462.6	3447.7	*3444.0*
20°	3525.8	3522.1	*3510.9*
22.5°	3600.2	3592.7	*3589.0*
25°	3708.0	3682.0	*3667.1*
27.5°	3797.3	3775.0	*3767.5*
30°	3886.6	3841.9	*3841.9*
32.5°	3964.7	3953.5	*3946.1*
35°	4150.6	4094.8	*4102.3*
37.5°	4377.5	4321.7	*4273.3*
40°	4697.3	4623.0	*4593.2*
42.5°	4901.9	4827.5	*4834.9*
45°	5017.2	4887.0	*4853.5*
47.5°	5329.6	5166.0	*5121.3*
50°	5835.4	5634.6	*5578.8*
52.5°	6653.6	6330.1	*6255.7*
55°	7680.1	7282.2	*7207.8*
57.5°	9086.0	8557.9	*8397.9*
60°	10796.8	10142.2	*9900.5*
62.5°	12853.5	12046.5	*11815.9*
65°	14400.7	13727.5	*13370.5*
67.5°	15639.2	15085.0	*14914.0*
70°	16375.6	16401.6	*16446.3*
72.5°	*15523.9*	*16238.0*	*16580.1*
75°	11377.0	11931.2	*12463.0*
77.5°	4396.1	3964.7	*3838.2*
80°	710.4	665.7	*688.1*
82.5°	319.9	338.4	*357.0*
85°	208.3	241.7	*256.6*
87.5°	48.3	48.3	*48.3*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)