Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360701

Luminaire Tested: **GSS-SB4C-722-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360701
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB4C-722-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 4SQUARE 204W 70CRI 2200K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(104) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	23618.5 lumens
Efficiency:	N/A
Efficacy:	115.8 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	204
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	9.5%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360701
CATALOG NUMBER: GSS-SB4C-722-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 11.6 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360701
CATALOG NUMBER: GSS-SB4C-722-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360701
CATALOG NUMBER: GSS-SB4C-722-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	11809.3	0.0	11809.3
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	11809.3	0.0	11809.3
	% Fixture	50.0	0.0	50.0
Total	Lumens	23618.5	0.0	23618.5
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	450.4	1.9
10°-20°	1372.8	5.8
20°-30°	2294.5	9.7
30°-40°	3164.3	13.4
40°-50°	3879.0	16.4
50°-60°	4545.6	19.2
60°-70°	5047.9	21.4
70°-80°	2745.0	11.6
80°-90°	119.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	23618.5	100.0
0°-180°	23618.5	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360701
CATALOG NUMBER: GSS-SB4C-722-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2058.9	8.7			
FM	(30°-60°)	5794.5	24.5			
FH	(60°-80°)	3896.4	16.5			G2/5000
FVH	(80°-90°)	59.5	0.3			G1/100
BL	(0°-30°)	2058.9	8.7	B3/2500		
BM	(30°-60°)	5794.5	24.5	B4/8500		
BH	(60°-80°)	3896.4	16.5	B4/5000		G4/5000
BVH	(80°-90°)	59.5	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360701
CATALOG NUMBER: GSS-SB4C-722-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	4653.4	4653.4	4653.4	4653.4	4653.4	4653.4	4653.4	4653.4	4653.4	4653.4	4653.4
2.5°	4658.6	4658.6	4643.1	4663.8	4653.4	4658.6	4663.8	4658.6	4653.4	4658.6	4663.8
5°	4684.5	4674.1	4684.5	4694.8	4679.3	4689.6	4684.5	4658.6	4674.1	4674.1	4674.1
7.5°	4731.0	4741.3	4731.0	4756.8	4741.3	4772.4	4741.3	4720.6	4715.5	4710.3	4710.3
10°	4751.7	4751.7	4746.5	4793.0	4803.4	4834.4	4813.7	4782.7	4767.2	4746.5	4725.8
12.5°	4694.8	4705.1	4731.0	4818.9	4860.3	4922.3	4906.8	4844.7	4798.2	4782.7	4751.7
15°	4632.8	4643.1	4694.8	4803.4	4901.6	4994.7	4989.5	4912.0	4855.1	4813.7	4767.2
17.5°	4534.5	4550.0	4622.4	4787.9	4963.7	5067.1	5098.1	5020.5	4958.5	4891.3	4829.2
20°	4369.1	4369.1	4498.3	4710.3	4953.3	5186.0	5268.7	5206.7	5134.3	5025.7	4943.0
22.5°	4182.9	4193.3	4322.5	4601.7	4948.2	5289.4	5449.7	5382.5	5310.1	5191.2	5067.1
25°	3996.8	3996.8	4141.6	4457.0	4880.9	5361.8	5661.7	5625.5	5480.7	5372.1	5211.8
27.5°	3826.2	3826.2	3981.3	4312.2	4767.2	5382.5	5873.7	5873.7	5713.4	5553.1	5377.3
30°	3624.5	3676.2	3852.0	4198.4	4663.8	5346.3	6028.8	6127.0	5982.2	5775.4	5516.9
32.5°	3453.9	3490.1	3671.0	4038.1	4513.8	5304.9	6204.6	6447.6	6297.6	6013.3	5723.7
35°	3252.2	3247.1	3453.9	3815.8	4301.8	5211.8	6344.2	6830.2	6685.4	6380.4	5987.4
37.5°	2988.5	2988.5	3200.5	3552.1	4100.2	5051.6	6457.9	7254.2	7145.6	6799.2	6380.4
40°	2704.2	2735.2	2921.3	3278.1	3857.2	4860.3	6457.9	7600.6	7657.5	7300.7	6866.4
42.5°	2497.3	2507.7	2678.3	3014.4	3588.3	4612.1	6375.2	7900.5	8071.1	7771.2	7207.7
45°	2280.2	2306.0	2450.8	2761.0	3309.1	4317.4	6230.4	8236.6	8510.6	8303.8	7564.4
47.5°	2016.5	2042.3	2207.8	2523.2	3045.4	3996.8	5987.4	8588.2	9162.1	9012.1	8200.4
50°	1711.4	1732.1	1887.2	2223.3	2750.7	3629.7	5682.4	8851.9	9813.6	9963.5	9162.1
52.5°	1339.2	1354.7	1520.1	1845.9	2399.1	3278.1	5253.2	9012.1	10470.2	10997.6	10449.5
55°	961.7	987.6	1132.3	1401.2	1933.8	2807.6	4741.3	9094.9	11188.9	12223.0	12047.2
57.5°	692.8	703.2	801.4	1008.2	1437.4	2254.3	4084.7	8955.3	11835.2	13686.3	14053.4
60°	573.9	573.9	589.4	687.7	982.4	1592.5	3298.8	8438.2	12388.5	15165.0	16297.4
62.5°	527.4	527.4	537.7	553.2	646.3	1034.1	2357.7	7388.6	12450.5	16586.9	18758.5
65°	480.9	480.9	491.2	501.5	522.2	672.2	1421.9	5408.3	11235.5	16602.4	20082.2
67.5°	439.5	439.5	444.7	449.8	460.2	491.2	780.7	3278.1	8991.5	16162.9	20588.9
70°	398.1	398.1	398.1	393.0	408.5	413.6	517.0	1664.9	6013.3	14596.3	20345.8
72.5°	*351.6*	*351.6*	*346.4*	*336.1*	*341.3*	*341.3*	*382.6*	*816.9*	*3123.0*	*11602.6*	*18370.7*
75°	299.9	305.1	284.4	274.0	268.9	274.0	305.1	465.3	1396.0	7037.0	13727.6
77.5°	253.4	263.7	232.7	212.0	206.8	206.8	237.8	289.5	599.8	2554.2	6152.9
80°	191.3	196.5	170.6	149.9	149.9	144.8	175.8	212.0	284.4	760.1	1380.5
82.5°	108.6	108.6	98.2	87.9	82.7	87.9	118.9	144.8	175.8	268.9	377.4
85°	25.9	25.9	31.0	36.2	36.2	46.5	67.2	77.6	93.1	108.6	144.8
87.5°	5.2	5.2	5.2	10.3	15.5	15.5	25.9	36.2	46.5	56.9	62.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360701
CATALOG NUMBER: GSS-SB4C-722-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	4653.4	4653.4	*4653.4*
2.5°	4663.8	4668.9	*4663.8*
5°	4694.8	4684.5	*4668.9*
7.5°	4700.0	4705.1	*4710.3*
10°	4720.6	4741.3	*4710.3*
12.5°	4741.3	4725.8	*4715.5*
15°	4756.8	4751.7	*4720.6*
17.5°	4813.7	4793.0	*4787.9*
20°	4901.6	4896.4	*4880.9*
22.5°	5005.0	4994.7	*4989.5*
25°	5155.0	5118.8	*5098.1*
27.5°	5279.1	5248.0	*5237.7*
30°	5403.2	5341.1	*5341.1*
32.5°	5511.7	5496.2	*5485.9*
35°	5770.3	5692.7	*5703.0*
37.5°	6085.7	6008.1	*5940.9*
40°	6530.3	6426.9	*6385.5*
42.5°	6814.7	6711.3	*6721.6*
45°	6975.0	6794.0	*6747.5*
47.5°	7409.3	7181.8	*7119.8*
50°	8112.5	7833.3	*7755.7*
52.5°	9250.0	8800.2	*8696.8*
55°	10677.0	10123.8	*10020.4*
57.5°	12631.5	11897.3	*11674.9*
60°	15009.9	14099.9	*13763.8*
62.5°	17869.2	16747.2	*16426.6*
65°	20020.1	19084.2	*18587.9*
67.5°	21741.9	20971.5	*20733.6*
70°	22765.6	22801.8	*22863.9*
72.5°	*21581.6*	*22574.3*	*23050.0*
75°	15816.5	16586.9	*17326.3*
77.5°	6111.5	5511.7	*5335.9*
80°	987.6	925.5	*956.5*
82.5°	444.7	470.5	*496.4*
85°	289.5	336.1	*356.8*
87.5°	67.2	67.2	*67.2*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)