Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360705

Luminaire Tested: **GSS-SB5C-722-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360705
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB5C-722-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 5SQUARE 252W 70CRI 2200K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(130) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	29507.2 lumens
Efficiency:	N/A
Efficacy:	117.1 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	252
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	7.9%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360705
CATALOG NUMBER: GSS-SB5C-722-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 14.5 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360705
CATALOG NUMBER: GSS-SB5C-722-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360705
CATALOG NUMBER: GSS-SB5C-722-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	14753.6	0.0	14753.6
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	14753.6	0.0	14753.6
	% Fixture	50.0	0.0	50.0
Total	Lumens	29507.2	0.0	29507.2
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	562.7	1.9
10°-20°	1715.1	5.8
20°-30°	2866.6	9.7
30°-40°	3953.2	13.4
40°-50°	4846.1	16.4
50°-60°	5679.0	19.2
60°-70°	6306.4	21.4
70°-80°	3429.4	11.6
80°-90°	148.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	29507.2	100.0
0°-180°	29507.2	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360705
CATALOG NUMBER: GSS-SB5C-722-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2572.2	8.7			
FM	(30°-60°)	7239.2	24.5			
FH	(60°-80°)	4867.9	16.5			G2/5000
FVH	(80°-90°)	74.3	0.3			G1/100
BL	(0°-30°)	2572.2	8.7	B4/5000		
BM	(30°-60°)	7239.2	24.5	B4/8500		
BH	(60°-80°)	4867.9	16.5	B4/5000		G4/5000
BVH	(80°-90°)	74.3	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360705
CATALOG NUMBER: GSS-SB5C-722-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	5813.6	5813.6	5813.6	5813.6	5813.6	5813.6	5813.6	5813.6	5813.6	5813.6	5813.6
2.5°	5820.1	5820.1	5800.7	5826.6	5813.6	5820.1	5826.6	5820.1	5813.6	5820.1	5826.6
5°	5852.4	5839.5	5852.4	5865.3	5845.9	5858.9	5852.4	5820.1	5839.5	5839.5	5839.5
7.5°	5910.5	5923.5	5910.5	5942.8	5923.5	5962.2	5923.5	5897.6	5891.2	5884.7	5884.7
10°	5936.4	5936.4	5929.9	5988.1	6001.0	6039.7	6013.9	5975.1	5955.8	5929.9	5904.1
12.5°	5865.3	5878.2	5910.5	6020.4	6072.0	6149.5	6130.2	6052.7	5994.5	5975.1	5936.4
15°	5787.8	5800.7	5865.3	6001.0	6123.7	6240.0	6233.5	6136.6	6065.6	6013.9	5955.8
17.5°	5665.1	5684.5	5774.9	5981.6	6201.2	6330.4	6369.2	6272.3	6194.8	6110.8	6033.3
20°	5458.4	5458.4	5619.9	5884.7	6188.3	6479.0	6582.3	6504.8	6414.4	6278.7	6175.4
22.5°	5225.8	5238.7	5400.2	5749.1	6181.8	6608.2	6808.4	6724.5	6634.0	6485.4	6330.4
25°	4993.3	4993.3	5174.1	5568.2	6097.9	6698.6	7073.3	7028.1	6847.2	6711.5	6511.3
27.5°	4780.1	4780.1	4973.9	5387.3	5955.8	6724.5	7338.1	7338.1	7137.9	6937.6	6718.0
30°	4528.2	4592.8	4812.4	5245.2	5826.6	6679.2	7531.9	7654.6	7473.8	7215.4	6892.4
32.5°	4315.0	4360.2	4586.3	5045.0	5639.2	6627.6	7751.5	8055.1	7867.8	7512.5	7150.8
35°	4063.1	4056.6	4315.0	4767.2	5374.4	6511.3	7925.9	8533.1	8352.3	7971.2	7480.2
37.5°	3733.7	3733.7	3998.5	4437.8	5122.5	6311.0	8068.1	9062.8	8927.2	8494.4	7971.2
40°	3378.4	3417.1	3649.7	4095.4	4818.9	6072.0	8068.1	9495.6	9566.7	9121.0	8578.4
42.5°	3120.0	3132.9	3346.1	3766.0	4483.0	5762.0	7964.7	9870.3	10083.5	9708.8	9004.7
45°	2848.7	2881.0	3061.9	3449.4	4134.2	5393.8	7783.8	10290.2	10632.5	10374.1	9450.4
47.5°	2519.2	2551.5	2758.3	3152.3	3804.7	4993.3	7480.2	10729.4	11446.4	11259.1	10244.9
50°	2138.1	2164.0	2357.8	2777.6	3436.5	4534.6	7099.1	11058.9	12260.3	12447.7	11446.4
52.5°	1673.0	1692.4	1899.1	2306.1	2997.3	4095.4	6563.0	11259.1	13080.7	13739.6	13054.9
55°	1201.5	1233.8	1414.7	1750.6	2415.9	3507.6	5923.5	11362.5	13978.6	15270.5	15050.9
57.5°	865.6	878.5	1001.2	1259.6	1795.8	2816.4	5103.1	11188.0	14786.0	17098.6	17557.2
60°	717.0	717.0	736.4	859.1	1227.3	1989.6	4121.2	10542.1	15477.2	18946.0	20360.7
62.5°	658.9	658.9	671.8	691.2	807.5	1291.9	2945.6	9230.8	15554.7	20722.4	23435.5
65°	600.7	600.7	613.7	626.6	652.4	839.7	1776.4	6756.8	14036.7	20741.8	25089.1
67.5°	549.1	549.1	555.5	562.0	574.9	613.7	975.4	4095.4	11233.3	20192.7	25722.2
70°	497.4	497.4	497.4	490.9	510.3	516.8	646.0	2080.0	7512.5	18235.5	25418.6
72.5°	*439.3*	*439.3*	*432.8*	*419.9*	*426.3*	*426.3*	*478.0*	*1020.6*	*3901.6*	*14495.4*	*22951.0*
75°	374.7	381.1	355.3	342.4	335.9	342.4	381.1	581.4	1744.1	8791.5	17150.3
77.5°	316.5	329.4	290.7	264.8	258.4	258.4	297.1	361.7	749.3	3191.0	7686.9
80°	239.0	245.5	213.2	187.3	187.3	180.9	219.6	264.8	355.3	949.6	1724.7
82.5°	135.7	135.7	122.7	109.8	103.4	109.8	148.6	180.9	219.6	335.9	471.6
85°	32.3	32.3	38.8	45.2	45.2	58.1	84.0	96.9	116.3	135.7	180.9
87.5°	6.5	6.5	6.5	12.9	19.4	19.4	32.3	45.2	58.1	71.1	77.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360705
CATALOG NUMBER: GSS-SB5C-722-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	5813.6	5813.6	*5813.6*
2.5°	5826.6	5833.0	*5826.6*
5°	5865.3	5852.4	*5833.0*
7.5°	5871.8	5878.2	*5884.7*
10°	5897.6	5923.5	*5884.7*
12.5°	5923.5	5904.1	*5891.2*
15°	5942.8	5936.4	*5897.6*
17.5°	6013.9	5988.1	*5981.6*
20°	6123.7	6117.3	*6097.9*
22.5°	6252.9	6240.0	*6233.5*
25°	6440.2	6395.0	*6369.2*
27.5°	6595.3	6556.5	*6543.6*
30°	6750.3	6672.8	*6672.8*
32.5°	6885.9	6866.6	*6853.6*
35°	7208.9	7112.0	*7124.9*
37.5°	7603.0	7506.1	*7422.1*
40°	8158.5	8029.3	*7977.6*
42.5°	8513.8	8384.6	*8397.5*
45°	8714.0	8487.9	*8429.8*
47.5°	9256.6	8972.4	*8894.9*
50°	10135.1	9786.3	*9689.4*
52.5°	11556.2	10994.3	*10865.1*
55°	13339.1	12647.9	*12518.7*
57.5°	15780.8	14863.6	*14585.8*
60°	18752.2	17615.4	*17195.5*
62.5°	22324.4	20922.7	*20522.2*
65°	25011.6	23842.4	*23222.3*
67.5°	27162.7	26200.2	*25903.0*
70°	28441.7	28486.9	*28564.4*
72.5°	*26962.4*	*28202.7*	*28796.9*
75°	19759.9	20722.4	*21646.2*
77.5°	7635.3	6885.9	*6666.3*
80°	1233.8	1156.3	*1195.0*
82.5°	555.5	587.8	*620.1*
85°	361.7	419.9	*445.7*
87.5°	84.0	84.0	*84.0*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)