Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360325

Luminaire Tested: **GSS-SB6C-722-U-T3-HSS**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360325
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6C-722-U-T3-HSS
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 300W 70CRI 2200K FIXTURE w/ TYPE III DISTRIBUTION OPTIC AND HOUSE SIDE SHIELD
Light Source:	(156) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	26029.1 lumens
Efficiency:	N/A
Efficacy:	86.8 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type III - Short
BUG Rating:	B2 - U0 - G4


Input Watts (W):	300
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	6.3%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360325
CATALOG NUMBER: GSS-SB6C-722-U-T3-HSS

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 11.8 fc
Type III - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360325
CATALOG NUMBER: GSS-SB6C-722-U-T3-HSS

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360325
CATALOG NUMBER: GSS-SB6C-722-U-T3-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3112.3	0.0	3112.3
	% Fixture	12.0	0.0	12.0
Street Side	Lumens	22916.9	0.0	22916.9
	% Fixture	88.0	0.0	88.0
Total	Lumens	26029.1	0.0	26029.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	337.5	1.3
10°-20°	867.7	3.3
20°-30°	1546.8	5.9
30°-40°	2768.3	10.6
40°-50°	4360.7	16.8
50°-60°	6342.5	24.4
60°-70°	6900.8	26.5
70°-80°	2787.7	10.7
80°-90°	117.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	26029.1	100.0
0°-180°	26029.1	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360325
CATALOG NUMBER: GSS-SB6C-722-U-T3-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1835.4	7.1			
FM	(30°-60°)	11750.3	45.1			
FH	(60°-80°)	9236.1	35.5			G4/12000
FVH	(80°-90°)	95.0	0.4			G1/100
BL	(0°-30°)	916.5	3.5	B2/1000		
BM	(30°-60°)	1721.3	6.6	B2/2500		
BH	(60°-80°)	452.4	1.7	B1/500		G1/500
BVH	(80°-90°)	22.1	0.1			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G4
Type III Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360325
CATALOG NUMBER: GSS-SB6C-722-U-T3-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	51°	55°	65°	75°	85°
0°	3696.1	3696.1	3696.1	3696.1	3696.1	3696.1	*3696.1*	3696.1	3696.1	3696.1	3696.1
2.5°	3727.3	3719.5	3727.3	3696.1	3711.7	3719.5	*3735.1*	3711.7	3703.9	3711.7	3703.9
5°	3711.7	3703.9	3711.7	3719.5	3735.1	3758.5	*3750.7*	3750.7	3766.3	3735.1	3735.1
7.5°	3579.1	3571.3	3618.1	3633.7	3696.1	3750.7	*3813.1*	3789.7	3820.8	3813.1	3789.7
10°	3415.4	3392.0	3438.8	3524.5	3618.1	3758.5	*3820.8*	3836.4	3906.6	3937.8	3922.2
12.5°	3321.8	3298.4	3360.8	3423.2	3571.3	3742.9	*3852.0*	3891.0	3969.0	4031.4	4047.0
15°	3251.6	3275.0	3337.4	3454.4	3594.7	3774.1	*3867.6*	3945.6	4109.4	4171.7	4171.7
17.5°	3298.4	3290.6	3345.2	3462.2	3633.7	3813.1	*3953.4*	4031.4	4226.3	4312.1	4304.3
20°	3758.5	3711.7	3703.9	3641.5	3696.1	3906.6	*4078.2*	4156.1	4343.3	4460.3	4452.5
22.5°	4351.1	4397.9	4273.1	4132.8	3961.2	4031.4	*4210.7*	4319.9	4507.0	4631.8	4585.0
25°	5154.2	5130.9	5045.1	4764.4	4452.5	4304.3	*4397.9*	4507.0	4741.0	4842.3	4764.4
27.5°	6004.2	5902.8	5793.7	5403.8	4990.5	4717.6	*4733.2*	4803.4	5076.3	5138.7	4959.3
30°	6916.5	6932.1	6752.8	6222.5	5653.3	5240.0	*5208.8*	5240.0	5458.4	5450.6	5201.0
32.5°	7961.4	7922.4	7750.9	7181.6	6550.0	5871.6	*5793.7*	5739.1	5832.6	5746.9	5458.4
35°	8694.4	8733.4	8546.2	8171.9	7540.3	6698.2	*6511.0*	6378.5	6284.9	6191.3	5879.4
37.5°	9349.4	9302.6	9193.4	8982.9	8366.9	7594.9	*7236.2*	7119.3	6916.5	6659.2	6370.7
40°	9497.5	9474.1	9419.6	9427.4	9029.7	8429.3	*8171.9*	7961.4	7610.5	7400.0	7025.7
42.5°	9474.1	9552.1	9567.7	9630.1	9404.0	9255.8	*8990.7*	8788.0	8460.5	8203.1	7813.2
45°	9598.9	9731.5	9840.6	9895.2	9747.1	9731.5	*9762.7*	9669.1	9443.0	9177.8	8733.4
47.5°	9848.4	10074.6	10246.1	10363.1	10331.9	10589.2	*10425.5*	10402.1	10495.6	10238.3	9793.9
50°	10316.3	10378.7	10784.2	10955.7	11244.2	11618.5	*11298.8*	11376.8	11563.9	11587.3	10768.6
52.5°	10667.2	10721.8	11127.3	11634.1	12273.5	12686.8	*12398.3*	12390.5	12725.8	12819.3	11712.1
55°	10760.8	10885.5	11408.0	12289.1	13489.9	13911.0	*13708.3*	13638.1	14082.6	14246.3	12546.4
57.5°	10628.2	10675.0	11423.6	12694.6	14371.1	15283.4	*15345.8*	15127.4	15532.9	15571.9	13162.4
60°	9193.4	9396.2	10706.2	12951.9	15119.6	16772.8	*17100.3*	16975.5	17006.7	16936.5	13622.5
62.5°	6355.1	6394.1	8320.1	12679.0	15735.7	18277.7	*18823.5*	18730.0	18464.8	17802.0	13388.6
65°	3025.5	3236.0	4468.1	10729.6	15821.4	19424.0	*20484.4*	20546.8	19314.8	17809.8	12484.0
67.5°	*2082.0*	*2089.8*	*2378.3*	*7571.5*	*13419.8*	*19751.5*	*21373.4*	*21084.9*	*19236.8*	*17646.1*	*11376.8*
70°	1317.8	1224.2	1372.4	4319.9	9068.7	15509.5	*19065.3*	20079.0	18909.3	16577.8	9614.5
72.5°	522.4	561.4	647.2	1419.2	4444.7	8834.7	*12452.9*	15283.4	17053.5	14339.9	7509.1
75°	233.9	249.5	327.5	592.6	1146.3	3602.5	*4818.9*	6752.8	13645.9	11322.2	5318.0
77.5°	156.0	163.8	210.5	343.1	522.4	1005.9	*1762.3*	2066.4	8179.7	6191.3	2495.2
80°	93.6	101.4	140.4	210.5	288.5	358.7	*538.0*	623.8	2159.9	2050.8	686.2
82.5°	62.4	54.6	93.6	117.0	171.5	148.2	*171.5*	202.7	592.6	522.4	187.1
85°	23.4	23.4	39.0	46.8	62.4	78.0	*70.2*	85.8	140.4	140.4	85.8
87.5°	0.0	0.0	7.8	7.8	23.4	31.2	*39.0*	39.0	54.6	54.6	46.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360325
CATALOG NUMBER: GSS-SB6C-722-U-T3-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3696.1	3696.1	3696.1	3696.1	3696.1	3696.1	3696.1	3696.1	3696.1	3696.1	3696.1
2.5°	3711.7	3688.3	3696.1	3680.5	3688.3	3672.7	3641.5	3672.7	3649.3	3649.3	3672.7
5°	3735.1	3727.3	3703.9	3664.9	3641.5	3586.9	3501.1	3462.2	3423.2	3399.8	3415.4
7.5°	3813.1	3781.9	3742.9	3649.3	3524.5	3360.8	3189.2	2994.3	2846.1	2830.5	2776.0
10°	3914.4	3883.2	3797.5	3586.9	3329.6	2861.7	2487.5	2230.1	2074.2	1972.8	1933.8
12.5°	4047.0	4008.0	3852.0	3493.3	2861.7	2206.7	1762.3	1575.1	1520.5	1497.1	1489.4
15°	4171.7	4125.0	3852.0	3189.2	2315.9	1660.9	1434.8	1388.0	1380.2	1388.0	1380.2
17.5°	4288.7	4226.3	3813.1	2776.0	1777.9	1403.6	1349.0	1325.6	1317.8	1310.0	1310.0
20°	4429.1	4327.7	3703.9	2323.7	1466.0	1333.4	1310.0	1278.8	1278.8	1247.6	1255.4
22.5°	4561.6	4421.3	3493.3	1871.4	1349.0	1294.4	1271.0	1239.8	1224.2	1200.8	1200.8
25°	4694.2	4514.8	3243.8	1551.7	1278.8	1255.4	1232.0	1200.8	1161.9	1130.7	1130.7
27.5°	4889.1	4639.6	2947.5	1419.2	1239.8	1200.8	1177.4	1138.5	1091.7	1052.7	1052.7
30°	5107.5	4811.2	2705.8	1395.8	1224.2	1130.7	1091.7	1029.3	998.1	966.9	966.9
32.5°	5372.6	5045.1	2526.4	1434.8	1185.2	1037.1	974.7	912.3	888.9	888.9	888.9
35°	5762.5	5388.2	2331.5	1442.6	1138.5	943.5	842.1	779.8	779.8	811.0	811.0
37.5°	6284.9	5762.5	2230.1	1427.0	1099.5	849.9	733.0	686.2	678.4	709.6	709.6
40°	6885.3	6175.7	2269.1	1372.4	1044.9	756.4	647.2	608.2	600.4	608.2	616.0
42.5°	7540.3	6620.2	2362.7	1294.4	951.3	678.4	584.8	561.4	553.6	553.6	553.6
45°	8234.3	6924.3	2456.3	1216.4	857.7	616.0	545.8	530.2	522.4	522.4	522.4
47.5°	8897.1	7166.0	2393.9	1146.3	779.8	577.0	514.6	514.6	506.8	506.8	506.8
50°	9466.4	7142.6	2128.8	1076.1	694.0	545.8	499.0	491.3	491.3	483.5	483.5
52.5°	9786.1	6667.0	1715.5	998.1	616.0	514.6	483.5	475.7	467.9	460.1	460.1
55°	9910.8	6035.4	1333.4	881.1	561.4	491.3	467.9	460.1	444.5	436.7	428.9
57.5°	9692.5	5107.5	1029.3	701.8	514.6	460.1	444.5	436.7	421.1	397.7	389.9
60°	9248.0	4093.8	772.0	538.0	460.1	421.1	421.1	413.3	382.1	343.1	335.3
62.5°	8468.3	2939.7	584.8	436.7	397.7	382.1	397.7	382.1	335.3	280.7	272.9
65°	7368.8	1816.9	452.3	374.3	350.9	335.3	358.7	343.1	288.5	226.1	210.5
67.5°	*6160.1*	*927.9*	*350.9*	*319.7*	*296.3*	*280.7*	*304.1*	*304.1*	*249.5*	*187.1*	*179.3*
70°	4756.6	514.6	280.7	265.1	241.7	218.3	257.3	265.1	218.3	163.8	156.0
72.5°	3532.3	327.5	226.1	218.3	187.1	156.0	210.5	226.1	187.1	124.8	117.0
75°	2308.1	257.3	171.5	171.5	132.6	124.8	179.3	194.9	163.8	93.6	93.6
77.5°	1107.3	194.9	132.6	117.0	93.6	93.6	156.0	163.8	117.0	70.2	70.2
80°	366.5	132.6	93.6	78.0	62.4	62.4	124.8	93.6	62.4	54.6	54.6
82.5°	124.8	85.8	62.4	54.6	46.8	39.0	39.0	46.8	46.8	39.0	39.0
85°	62.4	54.6	46.8	39.0	31.2	31.2	31.2	31.2	39.0	39.0	39.0
87.5°	39.0	39.0	31.2	23.4	23.4	23.4	23.4	23.4	31.2	15.6	15.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)