Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1366469

Luminaire Tested: **GSS-SB6C-722-U-T3R**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1366469
Test Lab:	INNOVATION CENTER(G1)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6C-722-U-T3R
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 300W 70CRI 2200K FIXTURE w/ TYPE III ROADWAY DISTRIBUTION OPTIC
Light Source:	(156) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	35682.5 lumens
Efficiency:	N/A
Efficacy:	118.9 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type III - Medium
BUG Rating:	B3 - U0 - G4


Input Watts (W):	300
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	6.3%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1366469
CATALOG NUMBER: GSS-SB6C-722-U-T3R

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 15.4 fc
Type III - Medium - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1366469
CATALOG NUMBER: GSS-SB6C-722-U-T3R

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1366469
CATALOG NUMBER: GSS-SB6C-722-U-T3R

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	7973.7	0.0	7973.7
	% Fixture	22.3	0.0	22.3
Street Side	Lumens	27708.9	0.0	27708.9
	% Fixture	77.7	0.0	77.7
Total	Lumens	35682.5	0.0	35682.5
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	527.6	1.5
10°-20°	1506.4	4.2
20°-30°	2483.9	7.0
30°-40°	3813.5	10.7
40°-50°	5888.2	16.5
50°-60°	8132.9	22.8
60°-70°	8335.4	23.4
70°-80°	4720.9	13.2
80°-90°	273.7	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	35682.5	100.0
0°-180°	35682.5	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1366469
CATALOG NUMBER: GSS-SB6C-722-U-T3R

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2249.6	6.3			
FM	(30°-60°)	14130.5	39.6			
FH	(60°-80°)	11140.0	31.2			G4/12000
FVH	(80°-90°)	188.7	0.5			G2/225
BL	(0°-30°)	2268.4	6.4	B3/2500		
BM	(30°-60°)	3704.0	10.4	B3/5000		
BH	(60°-80°)	1916.3	5.4	B3/2500		G3/2500
BVH	(80°-90°)	85.0	0.2			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G4
Type III Medium



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1366469
CATALOG NUMBER: GSS-SB6C-722-U-T3R

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	80°	85°
0°	5451.1	5451.1	5451.1	5451.1	5451.1	5451.1	5451.1	5451.1	5451.1	*5451.1*	5451.1
2.5°	5068.3	5051.7	5043.3	5060.0	5084.9	5134.9	5193.1	5234.7	5334.6	*5392.9*	5442.8
5°	4802.0	4793.7	4793.7	4835.3	4876.9	4935.1	5018.4	5093.3	5243.1	*5359.6*	5442.8
7.5°	4485.7	4477.4	4477.4	4569.0	4652.2	4785.3	4918.5	5043.3	5226.4	*5376.2*	5509.4
10°	4152.8	4152.8	4169.5	4286.0	4427.5	4618.9	4843.6	5035.0	5268.0	*5442.8*	5625.9
12.5°	4011.4	4003.0	4011.4	4119.6	4261.0	4519.0	4777.0	5068.3	5351.3	*5576.0*	5792.3
15°	4044.7	4028.0	4011.4	4102.9	4211.1	4469.1	4777.0	5134.9	5492.7	*5709.1*	6008.7
17.5°	4219.4	4211.1	4161.2	4186.1	4261.0	4494.1	4818.6	5234.7	5634.2	*5892.2*	6216.8
20°	4560.6	4535.7	4460.8	4419.2	4427.5	4577.3	4893.5	5367.9	5767.4	*6075.3*	6441.5
22.5°	5126.6	5109.9	4985.1	4818.6	4710.4	4752.1	5026.7	5517.7	5950.5	*6241.7*	6699.5
25°	5875.6	5834.0	5642.5	5376.2	5126.6	5035.0	5193.1	5717.4	6125.2	*6441.5*	6940.8
27.5°	6674.5	6682.8	6508.1	6108.6	5675.8	5367.9	5409.5	5917.2	6325.0	*6607.9*	7148.9
30°	7606.6	7565.0	7373.6	6957.5	6325.0	5809.0	5634.2	6108.6	6508.1	*6774.4*	7398.6
32.5°	8838.3	8846.6	8505.4	7864.6	7074.0	6349.9	5925.5	6308.3	6716.1	*6990.8*	7706.5
35°	10328.0	10294.7	9886.9	9113.0	8039.4	6974.1	6300.0	6566.3	6965.8	*7273.7*	8064.3
37.5°	11659.6	11568.0	11326.7	10586.0	9254.4	7823.0	6807.7	6907.5	7356.9	*7681.5*	8597.0
40°	12849.7	12808.1	12766.5	12200.5	10644.3	8879.9	7473.5	7431.8	7839.6	*8264.1*	9254.4
42.5°	13831.7	13823.4	13840.0	13715.2	12342.0	10203.2	8405.6	8114.3	8522.1	*8954.8*	10028.4
45°	14547.4	14530.8	14705.6	14963.6	13998.2	11784.4	9504.1	8963.2	9387.6	*9878.6*	11010.4
47.5°	15313.1	15321.4	15562.8	15995.5	15612.7	13357.3	10752.5	10020.1	10402.9	*11027.1*	12183.9
50°	15612.7	15612.7	16186.9	16802.8	16911.0	15030.1	12242.1	11276.8	11667.9	*12333.7*	13365.7
52.5°	14963.6	15088.4	16095.4	17252.2	17759.9	16578.1	13815.1	12641.6	12974.5	*13831.7*	14539.1
55°	11335.0	11776.1	15396.3	17035.8	18076.1	17793.1	15379.7	14156.3	14522.5	*15371.3*	15745.9
57.5°	9787.1	9903.6	12075.7	16278.5	17676.6	18450.6	16827.8	15770.8	16103.7	*16935.9*	17002.5
60°	8605.3	8763.4	10095.0	14996.8	16886.0	18384.0	18034.5	17260.5	17726.6	*18783.5*	18275.8
62.5°	6974.1	7140.6	8264.1	11984.2	15845.7	17918.0	18974.9	18667.0	19108.1	*19990.2*	18800.1
65°	6141.9	6200.1	7007.4	9187.9	13931.6	17518.5	19457.6	19266.2	19457.6	*20198.3*	18533.8
67.5°	5118.2	5234.7	6017.0	7798.0	11251.8	16669.6	18741.9	19016.5	19965.3	*20697.6*	18733.6
68°	*4901.9*	*4985.1*	*5784.0*	*7456.8*	*10752.5*	*16361.7*	*18550.5*	*19033.2*	*20165.0*	*20797.5*	*18625.4*
70°	4003.0	4119.6	4827.0	6250.1	9013.1	13099.4	17801.5	19357.7	20306.5	*20589.4*	18034.5
72.5°	1980.7	2188.8	3328.9	4410.8	6508.1	9470.8	15604.4	18941.6	20015.2	*19840.4*	16786.1
75°	699.1	749.0	1556.3	2388.5	3154.2	6133.6	11035.4	17268.8	18350.7	*17327.1*	14073.1
77.5°	499.3	541.0	882.2	1206.7	1298.3	3079.3	7074.0	11418.2	10852.3	*8405.6*	6408.2
80°	391.1	424.4	657.5	674.1	649.1	1081.9	2413.5	3462.1	2438.4	*1531.3*	1106.9
82.5°	241.3	291.3	491.0	407.8	299.6	341.2	565.9	932.1	665.8	*424.4*	341.2
85°	91.5	116.5	224.7	158.1	99.9	133.2	191.4	249.7	191.4	*141.5*	124.8
87.5°	8.3	8.3	16.6	16.6	25.0	33.3	49.9	66.6	74.9	*74.9*	74.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1366469
CATALOG NUMBER: GSS-SB6C-722-U-T3R

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	5451.1	5451.1	5451.1	5451.1	5451.1	5451.1	5451.1	5451.1	5451.1	5451.1	5451.1
2.5°	5476.1	5501.1	5609.3	5667.5	5775.7	5858.9	5908.9	5933.8	5958.8	5975.4	5967.1
5°	5534.4	5609.3	5817.3	5975.4	6100.3	6183.5	6225.1	6258.4	6266.7	6283.4	6275.0
7.5°	5642.5	5759.1	6075.3	6258.4	6366.6	6399.9	6366.6	6349.9	6325.0	6300.0	6300.0
10°	5817.3	6000.4	6374.9	6508.1	6516.4	6466.5	6358.3	6233.4	6141.9	6108.6	6091.9
12.5°	6042.0	6300.0	6682.8	6716.1	6607.9	6374.9	6067.0	5809.0	5642.5	5517.7	5509.4
15°	6316.6	6616.3	6949.1	6849.3	6541.4	6050.3	5542.7	5176.5	4985.1	4876.9	4827.0
17.5°	6599.6	6982.4	7190.5	6915.9	6266.7	5467.8	4860.2	4569.0	4394.2	4335.9	4294.3
20°	6915.9	7282.0	7356.9	6816.0	5767.4	4818.6	4269.4	4086.3	4086.3	4069.6	4053.0
22.5°	7240.4	7590.0	7448.5	6541.4	5109.9	4177.8	3844.9	3911.5	4028.0	4061.3	4061.3
25°	7540.0	7856.3	7448.5	6050.3	4327.6	3653.5	3678.5	3836.6	3986.4	4069.6	4069.6
27.5°	7831.3	8022.7	7298.7	5359.6	3620.2	3387.2	3537.0	3728.4	3969.8	4094.6	4102.9
30°	8122.6	8147.6	7032.4	4477.4	3112.6	3195.8	3370.5	3620.2	3886.5	4044.7	4061.3
32.5°	8430.5	8264.1	6657.9	3603.6	2879.5	3012.7	3220.7	3420.5	3628.5	3745.0	3753.4
35°	8780.1	8372.3	6175.2	2929.5	2729.7	2887.8	3046.0	3112.6	3170.8	3237.4	3279.0
37.5°	9162.9	8513.7	5542.7	2588.2	2588.2	2771.3	2862.9	2729.7	2713.1	2704.8	2679.8
40°	9587.3	8663.5	4752.1	2413.5	2480.1	2646.5	2571.6	2413.5	2297.0	2172.1	2180.5
42.5°	10120.0	8855.0	3853.2	2330.3	2405.2	2546.6	2338.6	2147.2	1830.9	1747.7	1764.3
45°	10727.5	9096.3	3137.5	2255.4	2346.9	2455.1	2180.5	1814.3	1614.5	1697.8	1756.0
47.5°	11368.3	9412.6	2621.5	2197.1	2321.9	2346.9	2080.6	1664.5	1531.3	1714.4	1789.3
50°	12125.6	9703.8	2380.2	2138.8	2313.6	2313.6	1905.8	1639.5	1464.7	1622.9	1697.8
52.5°	12891.3	9986.8	2255.4	2072.3	2288.6	2305.3	1864.2	1606.2	1373.2	1423.1	1456.4
55°	13640.3	10144.9	2188.8	1980.7	2263.7	2263.7	1880.8	1548.0	1281.6	1281.6	1298.3
57.5°	14397.6	10253.1	2130.5	1872.5	2180.5	2138.8	1880.8	1506.3	1248.3	1215.1	1231.7
60°	15238.2	10319.7	2072.3	1747.7	2063.9	1989.0	1872.5	1473.1	1206.7	1156.8	1165.1
62.5°	15371.3	9853.6	1964.1	1614.5	1905.8	1864.2	1839.2	1431.4	1140.2	1040.3	1040.3
65°	14897.0	9154.6	1830.9	1448.1	1697.8	1739.4	1772.7	1381.5	1073.6	957.1	965.4
67.5°	14847.0	8630.3	1689.4	1298.3	1423.1	1581.2	1689.4	1298.3	973.7	873.8	865.5
68°	*14730.5*	*8438.8*	*1647.8*	*1265.0*	*1373.2*	*1548.0*	*1639.5*	*1265.0*	*957.1*	*857.2*	*857.2*
70°	13981.5	7606.6	1398.2	1115.2	1215.1	1265.0	1439.8	1123.5	857.2	774.0	782.3
72.5°	12525.1	6200.1	1073.6	907.1	973.7	973.7	1248.3	1040.3	782.3	707.4	707.4
75°	10444.5	4901.9	815.6	715.7	682.4	790.6	1015.3	940.4	690.8	632.5	607.5
77.5°	4743.7	2113.9	532.6	499.3	507.7	615.9	807.3	807.3	657.5	516.0	457.7
80°	1048.6	657.5	324.6	299.6	299.6	391.1	565.9	582.6	474.4	357.9	307.9
82.5°	349.5	266.3	199.7	183.1	174.8	208.1	349.5	382.8	283.0	208.1	208.1
85°	133.2	124.8	108.2	99.9	83.2	83.2	108.2	174.8	149.8	99.9	99.9
87.5°	66.6	66.6	58.3	41.6	33.3	25.0	16.6	16.6	16.6	25.0	16.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)