Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1367237

Luminaire Tested: **GSS-SB6C-722-U-T4W**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1367237
Test Lab:	INNOVATION CENTER(G1)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6C-722-U-T4W
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 300W 70CRI 2200K FIXTURE w/ TYPE IV WIDE DISTRIBUTION OPTIC
Light Source:	(156) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	34297.9 lumens
Efficiency:	N/A
Efficacy:	114.3 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type IV - Short
BUG Rating:	B3 - U0 - G5


Input Watts (W):	300
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	6.3%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1367237
CATALOG NUMBER: GSS-SB6C-722-U-T4W

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 12.5 fc
Type IV - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1367237
CATALOG NUMBER: GSS-SB6C-722-U-T4W

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1367237
CATALOG NUMBER: GSS-SB6C-722-U-T4W

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	8594.0	0.0	8594.0
	% Fixture	25.1	0.0	25.1
Street Side	Lumens	25703.9	0.0	25703.9
	% Fixture	74.9	0.0	74.9
Total	Lumens	34297.9	0.0	34297.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	409.0	1.2
10°-20°	1342.7	3.9
20°-30°	2310.4	6.7
30°-40°	3257.0	9.5
40°-50°	4507.0	13.1
50°-60°	6693.4	19.5
60°-70°	8945.5	26.1
70°-80°	6310.3	18.4
80°-90°	522.6	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	34297.9	100.0
0°-180°	34297.9	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1367237
CATALOG NUMBER: GSS-SB6C-722-U-T4W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2170.6	6.3			
FM	(30°-60°)	10220.0	29.8			
FH	(60°-80°)	12926.6	37.7			G5
FVH	(80°-90°)	386.7	1.1			G3/500
BL	(0°-30°)	1891.6	5.5	B3/2500		
BM	(30°-60°)	4237.4	12.4	B3/5000		
BH	(60°-80°)	2329.1	6.8	B3/2500		G3/2500
BVH	(80°-90°)	135.8	0.4			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G5
Type IV Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1367237
CATALOG NUMBER: GSS-SB6C-722-U-T4W

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	44°	45°	55°	65°	75°	85°
0°	4052.9	4052.9	4052.9	4052.9	4052.9	*4052.9*	4052.9	4052.9	4052.9	4052.9	4052.9
2.5°	4352.5	4327.6	4302.6	4294.3	4261.0	*4211.0*	4211.0	4194.4	4152.8	4119.5	4094.5
5°	4635.5	4643.8	4602.2	4568.9	4519.0	*4435.7*	4444.1	4369.2	4285.9	4194.4	4127.8
7.5°	4910.1	4910.1	4860.2	4818.6	4752.0	*4652.1*	4652.1	4535.6	4435.7	4310.9	4219.4
10°	5159.8	5143.1	5076.5	5026.6	4935.1	*4826.9*	4818.6	4702.0	4577.2	4435.7	4310.9
12.5°	5351.2	5351.2	5284.6	5201.4	5101.5	*4985.0*	4976.7	4851.8	4727.0	4577.2	4427.4
15°	5534.3	5492.7	5434.4	5326.2	5209.7	*5118.2*	5101.5	4993.3	4868.5	4735.3	4568.9
17.5°	5600.8	5584.2	5509.3	5401.1	5292.9	*5193.1*	5193.1	5093.2	5001.6	4868.5	4702.0
20°	5584.2	5559.2	5492.7	5401.1	5317.9	*5234.7*	5234.7	5159.8	5109.8	4985.0	4835.2
22.5°	5501.0	5476.0	5434.4	5351.2	5309.6	*5259.6*	5259.6	5218.0	5201.4	5126.5	4985.0
25°	5476.0	5459.4	5401.1	5326.2	5284.6	*5276.3*	5284.6	5292.9	5309.6	5251.3	5134.8
27.5°	5492.7	5492.7	5442.7	5367.8	5317.9	*5326.2*	5334.5	5384.5	5434.4	5401.1	5301.2
30°	5600.8	5575.9	5542.6	5467.7	5409.4	*5417.8*	5417.8	5517.6	5567.6	5525.9	5451.0
32.5°	5783.9	5759.0	5709.0	5550.9	5492.7	*5534.3*	5550.9	5634.1	5667.4	5625.8	5592.5
35°	6208.4	6233.3	6066.9	5783.9	5625.8	*5659.1*	5675.7	5734.0	5775.6	5759.0	5725.7
37.5°	6982.3	6990.7	6782.6	6274.9	5908.8	*5808.9*	5817.2	5900.4	5950.4	5892.1	5867.2
40°	7947.7	7956.0	7664.8	6974.0	6358.2	*6108.5*	6100.2	6116.8	6191.7	6091.9	6075.2
42.5°	8996.3	8879.8	8630.1	7839.5	7023.9	*6607.8*	6532.9	6483.0	6574.5	6449.7	6366.5
45°	9995.0	9911.8	9570.5	8755.0	7822.9	*7265.3*	7190.4	6940.7	7090.5	6990.7	6840.9
47.5°	10827.2	10760.6	10502.6	9745.3	8730.0	*8055.9*	7939.4	7548.2	7814.6	7764.6	7581.5
50°	11443.0	11376.5	11201.7	10735.7	9878.5	*8938.1*	8829.9	8355.5	8630.1	8721.7	8580.2
52.5°	11892.4	11875.8	11809.2	11734.3	11043.6	*9961.7*	9836.9	9246.0	9695.4	9870.1	9828.5
55°	12574.9	12541.6	12566.5	12691.4	12291.9	*11051.9*	10868.8	10178.1	10793.9	11118.5	11185.1
57.5°	13224.0	13224.0	13440.4	13764.9	13715.0	*12225.3*	12009.0	11268.3	12125.5	12283.6	12599.8
60°	13831.5	13889.8	14189.4	14905.1	15046.6	*13498.6*	13240.6	12524.9	13390.4	13565.2	14139.4
62.5°	13573.5	13715.0	14672.1	15828.8	16294.9	*14863.5*	14605.5	13906.4	14813.5	14605.5	15121.5
65°	12258.6	12475.0	13956.3	15887.1	17509.9	*16361.5*	16145.1	15462.7	15595.8	14763.6	15670.7
67.5°	10877.1	11193.4	12916.1	15179.7	17826.2	*17892.8*	17701.3	16419.7	15587.5	14930.0	16228.3
70°	*9637.1*	*9895.1*	*11925.7*	*15054.9*	*17351.8*	*18883.1*	*18841.5*	*16561.2*	*16036.9*	*15079.8*	*15878.8*
72.5°	6757.6	7115.5	9196.0	13898.1	17493.3	*17268.6*	17177.0	17551.5	16369.8	14530.6	14072.9
75°	2430.1	2571.6	4768.6	9404.1	13906.4	*16353.1*	16428.0	16261.6	16045.2	13015.9	10577.5
77.5°	724.0	774.0	1356.5	3728.4	7797.9	*13124.1*	13249.0	12807.9	12058.9	7847.8	4003.0
80°	391.1	424.4	640.8	1090.2	2921.1	*7406.8*	7748.0	6557.9	4344.2	2072.2	898.8
82.5°	191.4	208.1	332.9	532.6	1256.7	*2355.2*	2363.5	2097.2	1414.8	624.2	332.9
85°	66.6	74.9	108.2	199.7	432.8	*482.7*	482.7	449.4	416.1	307.9	149.8
87.5°	16.6	16.6	25.0	33.3	41.6	*49.9*	49.9	58.3	66.6	74.9	74.9
90°	0.0	0.0	0.0	0.0	0.0	*0.0*	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1367237
CATALOG NUMBER: GSS-SB6C-722-U-T4W

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	4052.9	4052.9	4052.9	4052.9	4052.9	4052.9	4052.9	4052.9	4052.9	4052.9	4052.9
2.5°	4077.9	4044.6	4019.6	3994.7	3978.0	3944.7	3936.4	3936.4	3928.1	3936.4	3928.1
5°	4102.9	4052.9	4011.3	3978.0	3961.4	3944.7	3944.7	3953.1	3944.7	3953.1	3944.7
7.5°	4152.8	4119.5	4077.9	4028.0	4019.6	4011.3	4019.6	4036.3	4044.6	4052.9	4036.3
10°	4252.7	4202.7	4144.5	4119.5	4102.9	4094.5	4119.5	4152.8	4161.1	4177.8	4161.1
12.5°	4369.2	4310.9	4269.3	4211.0	4211.0	4219.4	4244.3	4285.9	4310.9	4335.9	4310.9
15°	4502.3	4444.1	4385.8	4335.9	4327.6	4344.2	4385.8	4427.4	4435.7	4444.1	4427.4
17.5°	4635.5	4577.2	4502.3	4444.1	4435.7	4477.3	4494.0	4494.0	4477.3	4477.3	4452.4
20°	4768.6	4727.0	4652.1	4543.9	4577.2	4593.9	4543.9	4502.3	4477.3	4469.0	4444.1
22.5°	4926.7	4860.2	4776.9	4660.4	4685.4	4618.8	4527.3	4510.6	4485.7	4494.0	4469.0
25°	5076.5	5034.9	4901.8	4752.0	4685.4	4577.2	4519.0	4519.0	4494.0	4510.6	4502.3
27.5°	5251.3	5201.4	5018.3	4801.9	4627.1	4510.6	4502.3	4502.3	4460.7	4469.0	4460.7
30°	5426.1	5351.2	5109.8	4760.3	4485.7	4410.8	4435.7	4427.4	4410.8	4435.7	4452.4
32.5°	5575.9	5517.6	5159.8	4660.4	4310.9	4277.6	4294.3	4335.9	4377.5	4402.5	4435.7
35°	5734.0	5667.4	5201.4	4485.7	4119.5	4069.6	4061.2	4186.1	4261.0	4302.6	4327.6
37.5°	5900.4	5817.2	5226.3	4294.3	3936.4	3786.6	3811.6	3911.4	3994.7	4069.6	4127.8
40°	6125.1	6041.9	5259.6	4086.2	3745.0	3545.3	3512.0	3536.9	3595.2	3703.4	3761.6
42.5°	6458.0	6324.9	5259.6	3819.9	3470.4	3328.9	3212.4	3120.8	3087.5	3154.1	3187.4
45°	6915.8	6716.0	5226.3	3545.3	3154.1	3054.3	2862.8	2713.0	2579.9	2513.3	2496.7
47.5°	7673.1	7323.5	5193.1	3279.0	2854.5	2729.7	2496.7	2321.9	2130.5	1955.7	1914.1
50°	8688.4	8130.8	5201.4	3012.6	2554.9	2388.5	2180.4	1997.3	1772.6	1606.2	1581.2
52.5°	10028.3	9262.6	5251.3	2721.4	2263.6	2113.8	1939.1	1756.0	1531.3	1406.5	1398.1
55°	11584.5	10627.5	5426.1	2396.8	1997.3	1880.8	1756.0	1581.2	1389.8	1281.6	1265.0
57.5°	13398.8	12208.7	5775.6	2055.6	1756.0	1714.4	1614.5	1448.1	1289.9	1181.8	1165.1
60°	15188.0	13740.0	6041.9	1756.0	1564.6	1564.6	1473.0	1348.2	1131.8	1040.3	1023.6
62.5°	16020.3	14214.3	5534.3	1514.6	1414.8	1439.7	1381.5	1206.7	1140.1	1098.5	1073.6
65°	16220.0	13948.0	4161.1	1331.6	1289.9	1373.2	1281.6	1289.9	1231.7	1190.1	1165.1
67.5°	15978.6	13190.7	2663.1	1173.4	1198.4	1289.9	1414.8	1423.1	1231.7	1140.1	1123.5
70°	*14563.9*	*11567.9*	*1639.5*	*1040.3*	*1073.6*	*1273.3*	*1572.9*	*1339.9*	*1165.1*	*1090.2*	*1056.9*
72.5°	12150.4	9545.6	1148.5	915.4	915.4	1206.7	1414.8	1256.7	1073.6	1032.0	990.3
75°	8530.3	6458.0	840.5	765.6	765.6	940.4	1306.6	1148.5	1007.0	1023.6	1007.0
77.5°	2904.5	2097.2	607.5	590.9	565.9	807.3	1165.1	1098.5	932.1	882.2	815.6
80°	857.2	674.1	449.4	416.1	407.8	649.1	982.0	807.3	665.8	607.5	565.9
82.5°	332.9	299.6	291.3	266.3	258.0	432.8	649.1	557.6	499.3	416.1	407.8
85°	133.2	133.2	149.8	149.8	133.2	233.0	391.1	307.9	291.3	258.0	249.7
87.5°	66.6	66.6	58.3	41.6	41.6	49.9	41.6	41.6	41.6	41.6	41.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)