Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360727

Luminaire Tested: **GSS-SB5A-727-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360727
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB5A-727-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 5SQUARE 143W 70CRI 2700K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(130) 2700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	19943.3 lumens
Efficiency:	N/A
Efficacy:	139.5 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	143
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	10.5%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360727
CATALOG NUMBER: GSS-SB5A-727-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 9.8 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360727
CATALOG NUMBER: GSS-SB5A-727-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360727
CATALOG NUMBER: GSS-SB5A-727-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	9971.6	0.0	9971.6
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	9971.6	0.0	9971.6
	% Fixture	50.0	0.0	50.0
Total	Lumens	19943.3	0.0	19943.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	380.3	1.9
10°-20°	1159.2	5.8
20°-30°	1937.5	9.7
30°-40°	2671.9	13.4
40°-50°	3275.4	16.4
50°-60°	3838.3	19.2
60°-70°	4262.4	21.4
70°-80°	2317.9	11.6
80°-90°	100.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	19943.3	100.0
0°-180°	19943.3	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360727
CATALOG NUMBER: GSS-SB5A-727-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1738.5	8.7			
FM	(30°-60°)	4892.8	24.5			
FH	(60°-80°)	3290.1	16.5			G2/5000
FVH	(80°-90°)	50.2	0.3			G1/100
BL	(0°-30°)	1738.5	8.7	B3/2500		
BM	(30°-60°)	4892.8	24.5	B3/5000		
BH	(60°-80°)	3290.1	16.5	B4/5000		G4/5000
BVH	(80°-90°)	50.2	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360727
CATALOG NUMBER: GSS-SB5A-727-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	3929.3	3929.3	3929.3	3929.3	3929.3	3929.3	3929.3	3929.3	3929.3	3929.3	3929.3
2.5°	3933.7	3933.7	3920.6	3938.0	3929.3	3933.7	3938.0	3933.7	3929.3	3933.7	3938.0
5°	3955.5	3946.8	3955.5	3964.2	3951.1	3959.9	3955.5	3933.7	3946.8	3946.8	3946.8
7.5°	3994.8	4003.5	3994.8	4016.6	4003.5	4029.7	4003.5	3986.1	3981.7	3977.3	3977.3
10°	4012.3	4012.3	4007.9	4047.2	4055.9	4082.1	4064.7	4038.5	4025.4	4007.9	3990.4
12.5°	3964.2	3973.0	3994.8	4069.0	4104.0	4156.3	4143.2	4090.9	4051.6	4038.5	4012.3
15°	3911.9	3920.6	3964.2	4055.9	4138.9	4217.5	4213.1	4147.6	4099.6	4064.7	4025.4
17.5°	3828.9	3842.0	3903.1	4042.8	4191.3	4278.6	4304.8	4239.3	4186.9	4130.1	4077.8
20°	3689.2	3689.2	3798.3	3977.3	4182.5	4379.0	4448.9	4396.5	4335.3	4243.7	4173.8
22.5°	3532.0	3540.8	3649.9	3885.7	4178.2	4466.3	4601.7	4544.9	4483.8	4383.4	4278.6
25°	3374.8	3374.8	3497.1	3763.4	4121.4	4527.4	4780.7	4750.1	4627.9	4536.2	4400.8
27.5°	3230.8	3230.8	3361.7	3641.2	4025.4	4544.9	4959.7	4959.7	4824.3	4689.0	4540.5
30°	3060.5	3104.2	3252.6	3545.1	3938.0	4514.3	5090.6	5173.6	5051.4	4876.7	4658.4
32.5°	2916.4	2947.0	3099.8	3409.8	3811.4	4479.4	5239.1	5444.3	5317.7	5077.5	4833.1
35°	2746.2	2741.8	2916.4	3222.0	3632.4	4400.8	5357.0	5767.4	5645.1	5387.5	5055.7
37.5°	2523.5	2523.5	2702.5	2999.4	3462.2	4265.5	5453.0	6125.4	6033.7	5741.2	5387.5
40°	2283.4	2309.6	2466.7	2768.0	3257.0	4104.0	5453.0	6417.9	6465.9	6164.7	5797.9
42.5°	2108.7	2117.5	2261.5	2545.3	3029.9	3894.4	5383.2	6671.1	6815.2	6562.0	6086.1
45°	1925.4	1947.2	2069.4	2331.4	2794.2	3645.5	5260.9	6954.9	7186.3	7011.6	6387.3
47.5°	1702.7	1724.5	1864.2	2130.6	2571.5	3374.8	5055.7	7251.8	7736.4	7609.8	6924.3
50°	1445.1	1462.6	1593.6	1877.3	2322.7	3064.9	4798.1	7474.4	8286.5	8413.1	7736.4
52.5°	1130.8	1143.9	1283.6	1558.6	2025.8	2768.0	4435.8	7609.8	8841.0	9286.3	8823.5
55°	812.1	833.9	956.1	1183.2	1632.8	2370.7	4003.5	7679.6	9447.8	10321.0	10172.6
57.5°	585.0	593.8	676.7	851.4	1213.7	1903.5	3449.1	7561.7	9993.6	11556.6	11866.5
60°	484.6	484.6	497.7	580.7	829.5	1344.7	2785.4	7125.2	10460.7	12805.2	13761.3
62.5°	445.3	445.3	454.1	467.2	545.7	873.2	1990.9	6238.9	10513.1	14005.8	15839.5
65°	406.0	406.0	414.8	423.5	441.0	567.6	1200.6	4566.7	9487.1	14018.9	16957.2
67.5°	371.1	371.1	375.5	379.8	388.6	414.8	659.3	2768.0	7592.3	13647.8	17385.0
70°	336.2	336.2	336.2	331.8	344.9	349.3	436.6	1405.8	5077.5	12325.0	17179.8
72.5°	*296.9*	*296.9*	*292.5*	*283.8*	*288.1*	*288.1*	*323.1*	*689.8*	*2637.0*	*9797.1*	*15512.1*
75°	253.2	257.6	240.1	231.4	227.0	231.4	257.6	392.9	1178.8	5942.0	11591.5
77.5°	213.9	222.7	196.5	179.0	174.6	174.6	200.8	244.5	506.4	2156.8	5195.4
80°	161.5	165.9	144.1	126.6	126.6	122.2	148.4	179.0	240.1	641.8	1165.7
82.5°	91.7	91.7	83.0	74.2	69.9	74.2	100.4	122.2	148.4	227.0	318.7
85°	21.8	21.8	26.2	30.6	30.6	39.3	56.8	65.5	78.6	91.7	122.2
87.5°	4.4	4.4	4.4	8.7	13.1	13.1	21.8	30.6	39.3	48.0	52.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360727
CATALOG NUMBER: GSS-SB5A-727-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	3929.3	3929.3	*3929.3*
2.5°	3938.0	3942.4	*3938.0*
5°	3964.2	3955.5	*3942.4*
7.5°	3968.6	3973.0	*3977.3*
10°	3986.1	4003.5	*3977.3*
12.5°	4003.5	3990.4	*3981.7*
15°	4016.6	4012.3	*3986.1*
17.5°	4064.7	4047.2	*4042.8*
20°	4138.9	4134.5	*4121.4*
22.5°	4226.2	4217.5	*4213.1*
25°	4352.8	4322.2	*4304.8*
27.5°	4457.6	4431.4	*4422.7*
30°	4562.4	4510.0	*4510.0*
32.5°	4654.1	4641.0	*4632.2*
35°	4872.4	4806.9	*4815.6*
37.5°	5138.7	5073.2	*5016.4*
40°	5514.1	5426.8	*5391.9*
42.5°	5754.3	5666.9	*5675.7*
45°	5889.6	5736.8	*5697.5*
47.5°	6256.3	6064.2	*6011.9*
50°	6850.1	6614.3	*6548.9*
52.5°	7810.6	7430.8	*7343.5*
55°	9015.6	8548.4	*8461.1*
57.5°	10665.9	10046.0	*9858.2*
60°	12674.2	11905.8	*11622.0*
62.5°	15088.6	14141.2	*13870.5*
65°	16904.8	16114.6	*15695.4*
67.5°	18358.6	17708.1	*17507.3*
70°	19223.1	19253.6	*19306.0*
72.5°	*18223.3*	*19061.5*	*19463.2*
75°	13355.3	14005.8	*14630.2*
77.5°	5160.5	4654.1	*4505.6*
80°	833.9	781.5	*807.7*
82.5°	375.5	397.3	*419.1*
85°	244.5	283.8	*301.2*
87.5°	56.8	56.8	*56.8*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ

Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-727-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2672
CIE u':	0.2638
CIE v':	0.5276
Duv:	-0.0002
CIE x:	0.4619
CIE y:	0.4106
CIE z:	0.1275
Peak Wavelength (nm):	601
Dominant Wavelength (nm):	584
Purity:	61.88407
Rf:	67.9
Rg:	98.6

CRI (Ra):	71.1
R1:	68.3
R2:	79.8
R3:	91.2
R4:	69.4
R5:	66.5
R6:	72.6
R7:	77.0
R8:	44.1
R9:	-27.8
R10:	54.4
R11:	65.8
R12:	45.6
R13:	69.8
R14:	94.5
R15:	60.1



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2672K
CIE x = 0.4619
CIE y = 0.4106
Duv = -0.0002

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.02**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.71**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-3

TM-30-18


Summary


R_f = 67.9
R_g = 98.6
CIE R_a = 71.1
R_9 = -27.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	





REPORT NUMBER: SP1-2407-184-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-3

TM-30-18

Measure Comparisons





(END OF REPORT)