Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360690

Luminaire Tested: **GSS-SB1D-722-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360690
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB1D-722-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 1SQUARE 76W 70CRI 2200K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(26) 2200K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	7592 lumens
Efficiency:	N/A
Efficacy:	99.9 lumens/watt
Luminous Opening:	Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B3 - U0 - G3


Input Watts (W):	76
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	6.7%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360690
CATALOG NUMBER: GSS-SB1D-722-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 3.7 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360690
CATALOG NUMBER: GSS-SB1D-722-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360690
CATALOG NUMBER: GSS-SB1D-722-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3796.0	0.0	3796.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	3796.0	0.0	3796.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	7592.0	0.0	7592.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.8	1.9
10°-20°	441.3	5.8
20°-30°	737.5	9.7
30°-40°	1017.1	13.4
40°-50°	1246.9	16.4
50°-60°	1461.2	19.2
60°-70°	1622.6	21.4
70°-80°	882.4	11.6
80°-90°	38.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7592.0	100.0
0°-180°	7592.0	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360690
CATALOG NUMBER: GSS-SB1D-722-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	661.8	8.7			
FM	(30°-60°)	1862.6	24.5			
FH	(60°-80°)	1252.5	16.5			G1/1800
FVH	(80°-90°)	19.1	0.3			G1/100
BL	(0°-30°)	661.8	8.7	B2/1000		
BM	(30°-60°)	1862.6	24.5	B2/2500		
BH	(60°-80°)	1252.5	16.5	B3/2500		G3/2500
BVH	(80°-90°)	19.1	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360690
CATALOG NUMBER: GSS-SB1D-722-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	1495.8	1495.8	1495.8	1495.8	1495.8	1495.8	1495.8	1495.8	1495.8	1495.8	1495.8
2.5°	1497.5	1497.5	1492.5	1499.1	1495.8	1497.5	1499.1	1497.5	1495.8	1497.5	1499.1
5°	1505.8	1502.4	1505.8	1509.1	1504.1	1507.4	1505.8	1497.5	1502.4	1502.4	1502.4
7.5°	1520.7	1524.1	1520.7	1529.0	1524.1	1534.0	1524.1	1517.4	1515.7	1514.1	1514.1
10°	1527.4	1527.4	1525.7	1540.7	1544.0	1554.0	1547.3	1537.4	1532.4	1525.7	1519.1
12.5°	1509.1	1512.4	1520.7	1549.0	1562.3	1582.2	1577.2	1557.3	1542.3	1537.4	1527.4
15°	1489.2	1492.5	1509.1	1544.0	1575.6	1605.5	1603.8	1578.9	1560.6	1547.3	1532.4
17.5°	1457.6	1462.6	1485.8	1539.0	1595.5	1628.8	1638.7	1613.8	1593.9	1572.3	1552.3
20°	1404.4	1404.4	1445.9	1514.1	1592.2	1667.0	1693.6	1673.6	1650.4	1615.5	1588.9
22.5°	1344.6	1347.9	1389.4	1479.2	1590.5	1700.2	1751.7	1730.1	1706.9	1668.6	1628.8
25°	1284.7	1284.7	1331.3	1432.6	1568.9	1723.5	1819.9	1808.3	1761.7	1726.8	1675.3
27.5°	1229.9	1229.9	1279.7	1386.1	1532.4	1730.1	1888.0	1888.0	1836.5	1785.0	1728.5
30°	1165.1	1181.7	1238.2	1349.5	1499.1	1718.5	1937.9	1969.5	1922.9	1856.5	1773.4
32.5°	1110.2	1121.9	1180.0	1298.0	1450.9	1705.2	1994.4	2072.5	2024.3	1932.9	1839.8
35°	1045.4	1043.7	1110.2	1226.6	1382.8	1675.3	2039.3	2195.5	2149.0	2050.9	1924.6
37.5°	960.6	960.6	1028.8	1141.8	1318.0	1623.8	2075.8	2331.8	2296.9	2185.5	2050.9
40°	869.2	879.2	939.0	1053.7	1239.9	1562.3	2075.8	2443.1	2461.4	2346.7	2207.1
42.5°	802.7	806.1	860.9	968.9	1153.4	1482.5	2049.2	2539.5	2594.4	2498.0	2316.8
45°	732.9	741.3	787.8	887.5	1063.7	1387.8	2002.7	2647.6	2735.7	2669.2	2431.5
47.5°	648.2	656.5	709.7	811.1	978.9	1284.7	1924.6	2760.6	2945.1	2896.9	2635.9
50°	550.1	556.8	606.6	714.7	884.2	1166.7	1826.5	2845.3	3154.5	3202.7	2945.1
52.5°	430.5	435.4	488.6	593.3	771.2	1053.7	1688.6	2896.9	3365.6	3535.1	3358.9
55°	309.1	317.4	364.0	450.4	621.6	902.5	1524.1	2923.5	3596.6	3929.0	3872.5
57.5°	222.7	226.0	257.6	324.1	462.0	724.6	1313.0	2878.6	3804.3	4399.3	4517.3
60°	184.5	184.5	189.5	221.0	315.8	511.9	1060.4	2712.4	3982.2	4874.6	5238.6
62.5°	169.5	169.5	172.8	177.8	207.8	332.4	757.9	2375.0	4002.1	5331.7	6029.7
65°	154.6	154.6	157.9	161.2	167.9	216.1	457.1	1738.5	3611.5	5336.7	6455.2
67.5°	141.3	141.3	142.9	144.6	147.9	157.9	251.0	1053.7	2890.2	5195.4	6618.1
70°	128.0	128.0	128.0	126.3	131.3	133.0	166.2	535.2	1932.9	4691.8	6540.0
72.5°	*113.0*	*113.0*	*111.4*	*108.0*	*109.7*	*109.7*	*123.0*	*262.6*	*1003.8*	*3729.5*	*5905.1*
75°	96.4	98.1	91.4	88.1	86.4	88.1	98.1	149.6	448.7	2262.0	4412.6
77.5°	81.4	84.8	74.8	68.1	66.5	66.5	76.5	93.1	192.8	821.0	1977.8
80°	61.5	63.2	54.8	48.2	48.2	46.5	56.5	68.1	91.4	244.3	443.8
82.5°	34.9	34.9	31.6	28.3	26.6	28.3	38.2	46.5	56.5	86.4	121.3
85°	8.3	8.3	10.0	11.6	11.6	15.0	21.6	24.9	29.9	34.9	46.5
87.5°	1.7	1.7	1.7	3.3	5.0	5.0	8.3	11.6	15.0	18.3	19.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360690
CATALOG NUMBER: GSS-SB1D-722-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	1495.8	1495.8	*1495.8*
2.5°	1499.1	1500.8	*1499.1*
5°	1509.1	1505.8	*1500.8*
7.5°	1510.8	1512.4	*1514.1*
10°	1517.4	1524.1	*1514.1*
12.5°	1524.1	1519.1	*1515.7*
15°	1529.0	1527.4	*1517.4*
17.5°	1547.3	1540.7	*1539.0*
20°	1575.6	1573.9	*1568.9*
22.5°	1608.8	1605.5	*1603.8*
25°	1657.0	1645.4	*1638.7*
27.5°	1696.9	1686.9	*1683.6*
30°	1736.8	1716.8	*1716.8*
32.5°	1771.7	1766.7	*1763.4*
35°	1854.8	1829.9	*1833.2*
37.5°	1956.2	1931.2	*1909.6*
40°	2099.1	2065.9	*2052.6*
42.5°	2190.5	2157.3	*2160.6*
45°	2242.0	2183.9	*2168.9*
47.5°	2381.6	2308.5	*2288.6*
50°	2607.7	2517.9	*2493.0*
52.5°	2973.3	2828.7	*2795.5*
55°	3432.0	3254.2	*3221.0*
57.5°	4060.3	3824.3	*3752.8*
60°	4824.8	4532.3	*4424.2*
62.5°	5743.9	5383.2	*5280.2*
65°	6435.3	6134.4	*5974.9*
67.5°	6988.7	6741.1	*6664.6*
70°	7317.8	7329.4	*7349.4*
72.5°	*6937.2*	*7256.3*	*7409.2*
75°	5084.1	5331.7	*5569.4*
77.5°	1964.5	1771.7	*1715.2*
80°	317.4	297.5	*307.5*
82.5°	142.9	151.2	*159.6*
85°	93.1	108.0	*114.7*
87.5°	21.6	21.6	*21.6*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-722-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

Spectral Parameters

CCT (K):	2160
CIE u':	0.2927
CIE v':	0.5388
Duv:	0.0015
CIE x:	0.5130
CIE y:	0.4197
CIE z:	0.0674
Peak Wavelength (nm):	609
Dominant Wavelength (nm):	587
Purity:	79.96089
Rf:	70.6
Rg:	97.6

CRI (Ra):	71.9
R1:	68.7
R2:	82.6
R3:	95.5
R4:	66.4
R5:	65.4
R6:	75.9
R7:	77.2
R8:	43.5
R9:	-17.8
R10:	60.5
R11:	60.2
R12:	48.2
R13:	70.7
R14:	96.8
R15:	61.8



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2160K
CIE x = 0.5130
CIE y = 0.4197
Duv = 0.0015

Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 0.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.21**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	27	NR	620	966	NR	750	46	NR	880	1	NR
365	0	NR	495	42	NR	625	930	NR	755	39	NR	885	1	NR
370	0	NR	500	67	NR	630	888	NR	760	34	NR	890	1	NR
375	0	NR	505	101	NR	635	835	NR	765	30	NR	895	1	NR
380	0	NR	510	139	NR	640	778	NR	770	26	NR	900	1	NR
385	0	NR	515	183	NR	645	717	NR	775	22	NR	905	1	NR
390	0	NR	520	224	NR	650	656	NR	780	19	NR	910	1	NR
395	0	NR	525	262	NR	655	595	NR	785	17	NR	915	1	NR
400	1	NR	530	299	NR	660	536	NR	790	15	NR	920	1	NR
405	3	NR	535	332	NR	665	480	NR	795	13	NR	925	1	NR
410	7	NR	540	365	NR	670	425	NR	800	11	NR	930	1	NR
415	17	NR	545	400	NR	675	376	NR	805	10	NR	935	0	NR
420	36	NR	550	437	NR	680	332	NR	810	8	NR	940	0	NR
425	67	NR	555	479	NR	685	291	NR	815	8	NR	945	0	NR
430	105	NR	560	525	NR	690	255	NR	820	7	NR	950	0	NR
435	141	NR	565	579	NR	695	221	NR	825	6	NR	955	0	NR
440	169	NR	570	639	NR	700	192	NR	830	5	NR	960	0	NR
445	173	NR	575	703	NR	705	167	NR	835	4	NR	965	0	NR
450	136	NR	580	769	NR	710	144	NR	840	4	NR	970	0	NR
455	80	NR	585	832	NR	715	125	NR	845	3	NR	975	0	NR
460	45	NR	590	890	NR	720	109	NR	850	3	NR	980	0	NR
465	32	NR	595	937	NR	725	94	NR	855	3	NR	985	0	NR
470	23	NR	600	972	NR	730	81	NR	860	2	NR	990	0	NR
475	18	NR	605	992	NR	735	70	NR	865	2	NR	995	0	NR
480	18	NR	610	998	NR	740	61	NR	870	2	NR	1000	0	NR
485	20	NR	615	990	NR	745	53	NR	875	2	NR			


REPORT NUMBER: SP1-2407-184-2

TM-30-18


Summary


R_f = 70.6
R_g = 97.6
CIE R_a = 71.9
R_9 = -17.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 87	CES26 = 60	CES51 = 74	CES76 = 58
CES02 = 65	CES27 = 77	CES52 = 77	CES77 = 82
CES03 = 32	CES28 = 85	CES53 = 65	CES78 = 65
CES04 = 72	CES29 = 50	CES54 = 77	CES79 = 86
CES05 = 52	CES30 = 49	CES55 = 74	CES80 = 85
CES06 = 53	CES31 = 55	CES56 = 64	CES81 = 61
CES07 = 44	CES32 = 55	CES57 = 60	CES82 = 93
CES08 = 43	CES33 = 55	CES58 = 64	CES83 = 83
CES09 = 29	CES34 = 75	CES59 = 84	CES84 = 93
CES10 = 79	CES35 = 88	CES60 = 89	CES85 = 81
CES11 = 62	CES36 = 78	CES61 = 84	CES86 = 55
CES12 = 68	CES37 = 82	CES62 = 68	CES87 = 79
CES13 = 45	CES38 = 54	CES63 = 68	CES88 = 72
CES14 = 75	CES39 = 90	CES64 = 69	CES89 = 62
CES15 = 72	CES40 = 86	CES65 = 66	CES90 = 67
CES16 = 49	CES41 = 75	CES66 = 64	CES91 = 89
CES17 = 51	CES42 = 83	CES67 = 63	CES92 = 67
CES18 = 57	CES43 = 68	CES68 = 71	CES93 = 78
CES19 = 74	CES44 = 98	CES69 = 81	CES94 = 52
CES20 = 68	CES45 = 76	CES70 = 65	CES95 = 76
CES21 = 89	CES46 = 68	CES71 = 64	CES96 = 78
CES22 = 81	CES47 = 60	CES72 = 88	CES97 = 76
CES23 = 92	CES48 = 47	CES73 = 59	CES98 = 71
CES24 = 92	CES49 = 65	CES74 = 85	CES99 = 65
CES25 = 74	CES50 = 74	CES75 = 66	





REPORT NUMBER: SP1-2407-184-2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-2

TM-30-18

Measure Comparisons





(END OF REPORT)