Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360731

Luminaire Tested: **GSS-SB6A-727-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360731
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB6A-727-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 6SQUARE 170W 70CRI 2700K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(156) 2700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	23944.1 lumens
Efficiency:	N/A
Efficacy:	140.8 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B4 - U0 - G4


Input Watts (W):	170
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	12.0%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360731
CATALOG NUMBER: GSS-SB6A-727-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 11.8 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360731
CATALOG NUMBER: GSS-SB6A-727-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360731
CATALOG NUMBER: GSS-SB6A-727-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	11972.1	0.0	11972.1
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	11972.1	0.0	11972.1
	% Fixture	50.0	0.0	50.0
Total	Lumens	23944.1	0.0	23944.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	456.6	1.9
10°-20°	1391.7	5.8
20°-30°	2326.1	9.7
30°-40°	3207.9	13.4
40°-50°	3932.5	16.4
50°-60°	4608.3	19.2
60°-70°	5117.5	21.4
70°-80°	2782.9	11.6
80°-90°	120.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	23944.1	100.0
0°-180°	23944.1	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360731
CATALOG NUMBER: GSS-SB6A-727-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	2087.2	8.7			
FM	(30°-60°)	5874.4	24.5			
FH	(60°-80°)	3950.2	16.5			G2/5000
FVH	(80°-90°)	60.3	0.3			G1/100
BL	(0°-30°)	2087.2	8.7	B3/2500		
BM	(30°-60°)	5874.4	24.5	B4/8500		
BH	(60°-80°)	3950.2	16.5	B4/5000		G4/5000
BVH	(80°-90°)	60.3	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G4
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360731
CATALOG NUMBER: GSS-SB6A-727-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	4717.6	4717.6	4717.6	4717.6	4717.6	4717.6	4717.6	4717.6	4717.6	4717.6	4717.6
2.5°	4722.8	4722.8	4707.1	4728.1	4717.6	4722.8	4728.1	4722.8	4717.6	4722.8	4728.1
5°	4749.0	4738.6	4749.0	4759.5	4743.8	4754.3	4749.0	4722.8	4738.6	4738.6	4738.6
7.5°	4796.2	4806.7	4796.2	4822.4	4806.7	4838.1	4806.7	4785.7	4780.5	4775.2	4775.2
10°	4817.2	4817.2	4811.9	4859.1	4869.6	4901.1	4880.1	4848.6	4832.9	4811.9	4791.0
12.5°	4759.5	4770.0	4796.2	4885.3	4927.3	4990.2	4974.4	4911.5	4864.4	4848.6	4817.2
15°	4696.6	4707.1	4759.5	4869.6	4969.2	5063.5	5058.3	4979.7	4922.0	4880.1	4832.9
17.5°	4597.0	4612.8	4686.1	4853.9	5032.1	5136.9	5168.4	5089.8	5026.9	4958.7	4895.8
20°	4429.3	4429.3	4560.3	4775.2	5021.6	5257.5	5341.4	5278.5	5205.1	5095.0	5011.1
22.5°	4240.6	4251.1	4382.1	4665.2	5016.4	5362.3	5524.8	5456.7	5383.3	5262.7	5136.9
25°	4051.9	4051.9	4198.7	4518.4	4948.2	5435.7	5739.7	5703.0	5556.3	5446.2	5283.7
27.5°	3878.9	3878.9	4036.2	4371.6	4832.9	5456.7	5954.6	5954.6	5792.2	5629.7	5451.4
30°	3674.5	3726.9	3905.1	4256.3	4728.1	5420.0	6111.9	6211.5	6064.7	5855.1	5593.0
32.5°	3501.5	3538.2	3721.7	4093.8	4576.1	5378.1	6290.1	6536.5	6384.5	6096.2	5802.6
35°	3297.1	3291.8	3501.5	3868.4	4361.1	5283.7	6431.6	6924.4	6777.6	6468.3	6070.0
37.5°	3029.7	3029.7	3244.7	3601.1	4156.7	5121.2	6547.0	7354.2	7244.1	6892.9	6468.3
40°	2741.4	2772.9	2961.6	3323.3	3910.4	4927.3	6547.0	7705.4	7763.1	7401.4	6961.1
42.5°	2531.8	2542.3	2715.2	3055.9	3637.8	4675.7	6463.1	8009.4	8182.4	7878.4	7307.0
45°	2311.6	2337.8	2484.6	2799.1	3354.7	4376.9	6316.3	8350.1	8627.9	8418.3	7668.7
47.5°	2044.3	2070.5	2238.2	2558.0	3087.4	4051.9	6070.0	8706.6	9288.4	9136.4	8313.4
50°	1735.0	1756.0	1913.2	2254.0	2788.6	3679.7	5760.7	8973.9	9948.9	10100.9	9288.4
52.5°	1357.6	1373.3	1541.1	1871.3	2432.2	3323.3	5325.6	9136.4	10614.6	11149.2	10593.6
55°	975.0	1001.2	1147.9	1420.5	1960.4	2846.3	4806.7	9220.3	11343.2	12391.5	12213.3
57.5°	702.4	712.9	812.5	1022.1	1457.2	2285.4	4141.0	9078.7	11998.4	13875.0	14247.1
60°	581.8	581.8	597.6	697.2	995.9	1614.5	3344.2	8554.6	12559.3	15374.1	16522.0
62.5°	534.7	534.7	545.1	560.9	655.2	1048.4	2390.2	7490.5	12622.2	16815.6	19017.1
65°	487.5	487.5	498.0	508.5	529.4	681.4	1441.5	5482.9	11390.4	16831.3	20359.0
67.5°	445.6	445.6	450.8	456.0	466.5	498.0	791.5	3323.3	9115.4	16385.8	20872.7
70°	403.6	403.6	403.6	398.4	414.1	419.3	524.2	1687.8	6096.2	14797.5	20626.3
72.5°	*356.4*	*356.4*	*351.2*	*340.7*	*346.0*	*346.0*	*387.9*	*828.2*	*3166.0*	*11762.5*	*18624.0*
75°	304.0	309.3	288.3	277.8	272.6	277.8	309.3	471.8	1415.3	7134.0	13916.9
77.5°	256.8	267.3	235.9	214.9	209.7	209.7	241.1	293.5	608.0	2589.4	6237.7
80°	193.9	199.2	173.0	152.0	152.0	146.8	178.2	214.9	288.3	770.5	1399.6
82.5°	110.1	110.1	99.6	89.1	83.9	89.1	120.6	146.8	178.2	272.6	382.6
85°	26.2	26.2	31.5	36.7	36.7	47.2	68.1	78.6	94.4	110.1	146.8
87.5°	5.2	5.2	5.2	10.5	15.7	15.7	26.2	36.7	47.2	57.7	62.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360731
CATALOG NUMBER: GSS-SB6A-727-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	4717.6	4717.6	*4717.6*
2.5°	4728.1	4733.3	*4728.1*
5°	4759.5	4749.0	*4733.3*
7.5°	4764.8	4770.0	*4775.2*
10°	4785.7	4806.7	*4775.2*
12.5°	4806.7	4791.0	*4780.5*
15°	4822.4	4817.2	*4785.7*
17.5°	4880.1	4859.1	*4853.9*
20°	4969.2	4964.0	*4948.2*
22.5°	5074.0	5063.5	*5058.3*
25°	5226.0	5189.3	*5168.4*
27.5°	5351.8	5320.4	*5309.9*
30°	5477.6	5414.7	*5414.7*
32.5°	5587.7	5572.0	*5561.5*
35°	5849.8	5771.2	*5781.7*
37.5°	6169.6	6090.9	*6022.8*
40°	6620.3	6515.5	*6473.6*
42.5°	6908.6	6803.8	*6814.3*
45°	7071.1	6887.7	*6840.5*
47.5°	7511.4	7280.8	*7217.9*
50°	8224.3	7941.3	*7862.6*
52.5°	9377.5	8921.5	*8816.6*
55°	10824.2	10263.4	*10158.5*
57.5°	12805.6	12061.3	*11835.9*
60°	15216.8	14294.3	*13953.6*
62.5°	18115.5	16978.1	*16653.1*
65°	20296.1	19347.4	*18844.1*
67.5°	22041.6	21260.6	*21019.5*
70°	23079.5	23116.2	*23179.1*
72.5°	*21879.1*	*22885.5*	*23367.8*
75°	16034.6	16815.6	*17565.2*
77.5°	6195.8	5587.7	*5409.5*
80°	1001.2	938.3	*969.7*
82.5°	450.8	477.0	*503.2*
85°	293.5	340.7	*361.7*
87.5°	68.1	68.1	*68.1*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ

Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-727-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2672
CIE u':	0.2638
CIE v':	0.5276
Duv:	-0.0002
CIE x:	0.4619
CIE y:	0.4106
CIE z:	0.1275
Peak Wavelength (nm):	601
Dominant Wavelength (nm):	584
Purity:	61.88407
Rf:	67.9
Rg:	98.6

CRI (Ra):	71.1
R1:	68.3
R2:	79.8
R3:	91.2
R4:	69.4
R5:	66.5
R6:	72.6
R7:	77.0
R8:	44.1
R9:	-27.8
R10:	54.4
R11:	65.8
R12:	45.6
R13:	69.8
R14:	94.5
R15:	60.1



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2672K
CIE x = 0.4619
CIE y = 0.4106
Duv = -0.0002

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.02**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.71**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-3

TM-30-18


Summary


R_f = 67.9
R_g = 98.6
CIE R_a = 71.1
R_9 = -27.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	





REPORT NUMBER: SP1-2407-184-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-3

TM-30-18

Measure Comparisons





(END OF REPORT)