Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360715

Luminaire Tested: **GSS-SB2A-727-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360715
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB2A-727-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 2SQUARE 58W 70CRI 2700K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(52) 2700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	7622.6 lumens
Efficiency:	N/A
Efficacy:	131.4 lumens/watt
Luminous Opening:	Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B3 - U0 - G3


Input Watts (W):	58
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	9.0%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360715
CATALOG NUMBER: GSS-SB2A-727-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 3.8 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360715
CATALOG NUMBER: GSS-SB2A-727-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360715
CATALOG NUMBER: GSS-SB2A-727-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	3811.3	0.0	3811.3
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	3811.3	0.0	3811.3
	% Fixture	50.0	0.0	50.0
Total	Lumens	7622.6	0.0	7622.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.4	1.9
10°-20°	443.1	5.8
20°-30°	740.5	9.7
30°-40°	1021.2	13.4
40°-50°	1251.9	16.4
50°-60°	1467.0	19.2
60°-70°	1629.1	21.4
70°-80°	885.9	11.6
80°-90°	38.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7622.6	100.0
0°-180°	7622.6	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360715
CATALOG NUMBER: GSS-SB2A-727-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	664.5	8.7			
FM	(30°-60°)	1870.1	24.5			
FH	(60°-80°)	1257.5	16.5			G1/1800
FVH	(80°-90°)	19.2	0.3			G1/100
BL	(0°-30°)	664.5	8.7	B2/1000		
BM	(30°-60°)	1870.1	24.5	B2/2500		
BH	(60°-80°)	1257.5	16.5	B3/2500		G3/2500
BVH	(80°-90°)	19.2	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360715
CATALOG NUMBER: GSS-SB2A-727-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	1501.8	1501.8	1501.8	1501.8	1501.8	1501.8	1501.8	1501.8	1501.8	1501.8	1501.8
2.5°	1503.5	1503.5	1498.5	1505.2	1501.8	1503.5	1505.2	1503.5	1501.8	1503.5	1505.2
5°	1511.8	1508.5	1511.8	1515.2	1510.2	1513.5	1511.8	1503.5	1508.5	1508.5	1508.5
7.5°	1526.9	1530.2	1526.9	1535.2	1530.2	1540.2	1530.2	1523.5	1521.9	1520.2	1520.2
10°	1533.5	1533.5	1531.9	1546.9	1550.2	1560.2	1553.6	1543.6	1538.5	1531.9	1525.2
12.5°	1515.2	1518.5	1526.9	1555.2	1568.6	1588.6	1583.6	1563.6	1548.6	1543.6	1533.5
15°	1495.2	1498.5	1515.2	1550.2	1581.9	1612.0	1610.3	1585.3	1566.9	1553.6	1538.5
17.5°	1463.5	1468.5	1491.8	1545.2	1602.0	1635.3	1645.3	1620.3	1600.3	1578.6	1558.6
20°	1410.1	1410.1	1451.8	1520.2	1598.6	1673.7	1700.4	1680.4	1657.0	1622.0	1595.3
22.5°	1350.0	1353.3	1395.0	1485.1	1596.9	1707.1	1758.8	1737.1	1713.8	1675.4	1635.3
25°	1289.9	1289.9	1336.6	1438.4	1575.3	1730.4	1827.2	1815.5	1768.8	1733.8	1682.1
27.5°	1234.8	1234.8	1284.9	1391.7	1538.5	1737.1	1895.6	1895.6	1843.9	1792.2	1735.5
30°	1169.8	1186.4	1243.2	1355.0	1505.2	1725.4	1945.7	1977.4	1930.7	1863.9	1780.5
32.5°	1114.7	1126.4	1184.8	1303.3	1456.8	1712.1	2002.4	2080.9	2032.5	1940.7	1847.3
35°	1049.6	1047.9	1114.7	1231.5	1388.4	1682.1	2047.5	2204.4	2157.6	2059.2	1932.4
37.5°	964.5	964.5	1032.9	1146.4	1323.3	1630.3	2084.2	2341.2	2306.1	2194.3	2059.2
40°	872.7	882.7	942.8	1058.0	1244.9	1568.6	2084.2	2453.0	2471.4	2356.2	2216.0
42.5°	806.0	809.3	864.4	972.9	1158.1	1488.5	2057.5	2549.8	2604.8	2508.1	2326.2
45°	735.9	744.2	791.0	891.1	1068.0	1393.4	2010.8	2658.2	2746.7	2679.9	2441.3
47.5°	650.8	659.1	712.5	814.3	982.9	1289.9	1932.4	2771.7	2956.9	2908.6	2646.6
50°	552.3	559.0	609.1	717.5	887.8	1171.4	1833.9	2856.8	3167.2	3215.6	2956.9
52.5°	432.2	437.2	490.6	595.7	774.3	1058.0	1695.4	2908.6	3379.1	3549.3	3372.5
55°	310.4	318.7	365.4	452.2	624.1	906.1	1530.2	2935.3	3611.1	3944.8	3888.1
57.5°	223.6	226.9	258.6	325.4	463.9	727.6	1318.3	2890.2	3819.7	4417.1	4535.5
60°	185.2	185.2	190.2	221.9	317.1	514.0	1064.6	2723.3	3998.2	4894.3	5259.8
62.5°	170.2	170.2	173.5	178.6	208.6	333.7	760.9	2384.6	4018.2	5353.2	6054.1
65°	155.2	155.2	158.5	161.9	168.5	216.9	458.9	1745.5	3626.1	5358.2	6481.2
67.5°	141.8	141.8	143.5	145.2	148.5	158.5	252.0	1058.0	2901.9	5216.4	6644.8
70°	128.5	128.5	128.5	126.8	131.8	133.5	166.9	537.3	1940.7	4710.8	6566.3
72.5°	*113.5*	*113.5*	*111.8*	*108.5*	*110.1*	*110.1*	*123.5*	*263.7*	*1007.9*	*3744.6*	*5928.9*
75°	96.8	98.5	91.8	88.4	86.8	88.4	98.5	150.2	450.6	2271.1	4430.4
77.5°	81.8	85.1	75.1	68.4	66.7	66.7	76.8	93.4	193.6	824.3	1985.8
80°	61.7	63.4	55.1	48.4	48.4	46.7	56.7	68.4	91.8	245.3	445.5
82.5°	35.0	35.0	31.7	28.4	26.7	28.4	38.4	46.7	56.7	86.8	121.8
85°	8.3	8.3	10.0	11.7	11.7	15.0	21.7	25.0	30.0	35.0	46.7
87.5°	1.7	1.7	1.7	3.3	5.0	5.0	8.3	11.7	15.0	18.4	20.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360715
CATALOG NUMBER: GSS-SB2A-727-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	1501.8	1501.8	*1501.8*
2.5°	1505.2	1506.8	*1505.2*
5°	1515.2	1511.8	*1506.8*
7.5°	1516.9	1518.5	*1520.2*
10°	1523.5	1530.2	*1520.2*
12.5°	1530.2	1525.2	*1521.9*
15°	1535.2	1533.5	*1523.5*
17.5°	1553.6	1546.9	*1545.2*
20°	1581.9	1580.3	*1575.3*
22.5°	1615.3	1612.0	*1610.3*
25°	1663.7	1652.0	*1645.3*
27.5°	1703.7	1693.7	*1690.4*
30°	1743.8	1723.8	*1723.8*
32.5°	1778.8	1773.8	*1770.5*
35°	1862.3	1837.2	*1840.6*
37.5°	1964.1	1939.0	*1917.3*
40°	2107.6	2074.2	*2060.8*
42.5°	2199.4	2166.0	*2169.3*
45°	2251.1	2192.7	*2177.7*
47.5°	2391.3	2317.8	*2297.8*
50°	2618.2	2528.1	*2503.1*
52.5°	2985.3	2840.1	*2806.8*
55°	3445.9	3267.3	*3233.9*
57.5°	4076.6	3839.7	*3767.9*
60°	4844.2	4550.6	*4442.1*
62.5°	5767.0	5404.9	*5301.5*
65°	6461.2	6159.2	*5999.0*
67.5°	7016.9	6768.3	*6691.5*
70°	7347.3	7359.0	*7379.0*
72.5°	*6965.2*	*7285.6*	*7439.1*
75°	5104.6	5353.2	*5591.8*
77.5°	1972.4	1778.8	*1722.1*
80°	318.7	298.7	*308.7*
82.5°	143.5	151.9	*160.2*
85°	93.4	108.5	*115.1*
87.5°	21.7	21.7	*21.7*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ

Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-727-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2672
CIE u':	0.2638
CIE v':	0.5276
Duv:	-0.0002
CIE x:	0.4619
CIE y:	0.4106
CIE z:	0.1275
Peak Wavelength (nm):	601
Dominant Wavelength (nm):	584
Purity:	61.88407
Rf:	67.9
Rg:	98.6

CRI (Ra):	71.1
R1:	68.3
R2:	79.8
R3:	91.2
R4:	69.4
R5:	66.5
R6:	72.6
R7:	77.0
R8:	44.1
R9:	-27.8
R10:	54.4
R11:	65.8
R12:	45.6
R13:	69.8
R14:	94.5
R15:	60.1



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2672K
CIE x = 0.4619
CIE y = 0.4106
Duv = -0.0002

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.02**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.71**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-3

TM-30-18


Summary


R_f = 67.9
R_g = 98.6
CIE R_a = 71.1
R_9 = -27.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	





REPORT NUMBER: SP1-2407-184-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-3

TM-30-18

Measure Comparisons





(END OF REPORT)