Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1360719

Luminaire Tested: **GSS-SB3A-727-U-T1**

Issue Date: 02/18/2026

Report Generated By 670245763

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-08
Report Number:	P1360719
Test Lab:	INNOVATION CENTER(G3)
Issue Date:	02/18/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	McGRAW-EDISON
Catalog Number:	GSS-SB3A-727-U-T1
Description:	GALLEON II SLIM SITE HIGH DENSITY LED ARRAYS 3SQUARE 85W 70CRI 2700K FIXTURE w/ TYPE I DISTRIBUTION OPTIC
Light Source:	(78) 2700K CCT, 70 CRI LEDS
Ballast/Driver:	ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	11482.8 lumens
Efficiency:	N/A
Efficacy:	135.1 lumens/watt
Luminous Opening:	Rectangular (W 1.5' x L: 0.5' x H: 0')
IES Classification:	Type I - Short
BUG Rating:	B3 - U0 - G3


Input Watts (W):	85
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	0.98
Total Harmonic Distortion (THDi):	11.0%
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360719
CATALOG NUMBER: GSS-SB3A-727-U-T1

Iso-Footcandle Lines of Horizontal Illumination




Based on 20 foot mounting height. Maximum calculated value = 5.7 fc
Type I - Short - N/A

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360719
CATALOG NUMBER: GSS-SB3A-727-U-T1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


REPORT NUMBER: P1360719
CATALOG NUMBER: GSS-SB3A-727-U-T1

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	5741.4	0.0	5741.4
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	5741.4	0.0	5741.4
	% Fixture	50.0	0.0	50.0
Total	Lumens	11482.8	0.0	11482.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.0	1.9
10°-20°	667.4	5.8
20°-30°	1115.5	9.7
30°-40°	1538.4	13.4
40°-50°	1885.9	16.4
50°-60°	2210.0	19.2
60°-70°	2454.2	21.4
70°-80°	1334.6	11.6
80°-90°	57.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11482.8	100.0
0°-180°	11482.8	100.0



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

REPORT NUMBER: P1360719
CATALOG NUMBER: GSS-SB3A-727-U-T1

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit B	U	G
FL	(0°-30°)	1001.0	8.7			
FM	(30°-60°)	2817.1	24.5			
FH	(60°-80°)	1894.4	16.5			G2/5000
FVH	(80°-90°)	28.9	0.3			G1/100
BL	(0°-30°)	1001.0	8.7	B3/2500		
BM	(30°-60°)	2817.1	24.5	B3/5000		
BH	(60°-80°)	1894.4	16.5	B3/2500		G3/2500
BVH	(80°-90°)	28.9	0.3			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3
Type I Short



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360719
CATALOG NUMBER: GSS-SB3A-727-U-T1

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	80°
0°	2262.4	2262.4	2262.4	2262.4	2262.4	2262.4	2262.4	2262.4	2262.4	2262.4	2262.4
2.5°	2264.9	2264.9	2257.4	2267.4	2262.4	2264.9	2267.4	2264.9	2262.4	2264.9	2267.4
5°	2277.5	2272.4	2277.5	2282.5	2275.0	2280.0	2277.5	2264.9	2272.4	2272.4	2272.4
7.5°	2300.1	2305.1	2300.1	2312.7	2305.1	2320.2	2305.1	2295.1	2292.6	2290.0	2290.0
10°	2310.2	2310.2	2307.6	2330.3	2335.3	2350.4	2340.3	2325.2	2317.7	2307.6	2297.6
12.5°	2282.5	2287.5	2300.1	2342.8	2362.9	2393.1	2385.6	2355.4	2332.8	2325.2	2310.2
15°	2252.3	2257.4	2282.5	2335.3	2383.1	2428.3	2425.8	2388.1	2360.4	2340.3	2317.7
17.5°	2204.6	2212.1	2247.3	2327.7	2413.2	2463.5	2478.6	2440.9	2410.7	2378.0	2347.9
20°	2124.1	2124.1	2187.0	2290.0	2408.2	2521.3	2561.5	2531.4	2496.2	2443.4	2403.2
22.5°	2033.6	2038.7	2101.5	2237.3	2405.7	2571.6	2649.5	2616.8	2581.6	2523.8	2463.5
25°	1943.1	1943.1	2013.5	2166.9	2373.0	2606.8	2752.6	2735.0	2664.6	2611.8	2533.9
27.5°	1860.2	1860.2	1935.6	2096.5	2317.7	2616.8	2855.6	2855.6	2777.7	2699.8	2614.3
30°	1762.2	1787.3	1872.8	2041.2	2267.4	2599.2	2931.1	2978.8	2908.4	2807.9	2682.2
32.5°	1679.2	1696.8	1784.8	1963.3	2194.5	2579.1	3016.5	3134.7	3061.8	2923.5	2782.7
35°	1581.2	1578.6	1679.2	1855.2	2091.5	2533.9	3084.4	3320.7	3250.3	3102.0	2910.9
37.5°	1453.0	1453.0	1556.0	1727.0	1993.4	2456.0	3139.7	3526.8	3474.0	3305.6	3102.0
40°	1314.7	1329.8	1420.3	1593.7	1875.3	2362.9	3139.7	3695.2	3722.9	3549.4	3338.3
42.5°	1214.1	1219.2	1302.1	1465.5	1744.6	2242.3	3099.5	3841.0	3924.0	3778.2	3504.2
45°	1108.6	1121.1	1191.5	1342.4	1608.8	2099.0	3029.1	4004.4	4137.7	4037.1	3677.6
47.5°	980.4	992.9	1073.4	1226.7	1480.6	1943.1	2910.9	4175.4	4454.4	4381.5	3986.8
50°	832.1	842.1	917.5	1080.9	1337.3	1764.7	2762.6	4303.6	4771.1	4844.0	4454.4
52.5°	651.1	658.6	739.0	897.4	1166.4	1593.7	2554.0	4381.5	5090.4	5346.8	5080.3
55°	467.6	480.1	550.5	681.2	940.1	1365.0	2305.1	4421.7	5439.8	5942.5	5857.1
57.5°	336.8	341.9	389.6	490.2	698.8	1096.0	1985.9	4353.8	5754.0	6653.9	6832.4
60°	279.0	279.0	286.6	334.3	477.6	774.2	1603.8	4102.5	6023.0	7372.9	7923.4
62.5°	256.4	256.4	261.4	269.0	314.2	502.8	1146.3	3592.2	6053.2	8064.2	9119.9
65°	233.8	233.8	238.8	243.8	253.9	326.8	691.3	2629.4	5462.4	8071.7	9763.5
67.5°	213.7	213.7	216.2	218.7	223.7	238.8	379.6	1593.7	4371.4	7858.0	10009.8
70°	193.6	193.6	193.6	191.0	198.6	201.1	251.4	809.4	2923.5	7096.4	9891.7
72.5°	*170.9*	*170.9*	*168.4*	*163.4*	*165.9*	*165.9*	*186.0*	*397.2*	*1518.3*	*5640.9*	*8931.4*
75°	145.8	148.3	138.3	133.2	130.7	133.2	148.3	226.2	678.7	3421.2	6674.1
77.5°	123.2	128.2	113.1	103.1	100.6	100.6	115.6	140.8	291.6	1241.8	2991.4
80°	93.0	95.5	83.0	72.9	72.9	70.4	85.5	103.1	138.3	369.5	671.2
82.5°	52.8	52.8	47.8	42.7	40.2	42.7	57.8	70.4	85.5	130.7	183.5
85°	12.6	12.6	15.1	17.6	17.6	22.6	32.7	37.7	45.2	52.8	70.4
87.5°	2.5	2.5	2.5	5.0	7.5	7.5	12.6	17.6	22.6	27.7	30.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

REPORT NUMBER: P1360719
CATALOG NUMBER: GSS-SB3A-727-U-T1

CANDELA DISTRIBUTION (continued):

	85°	87.5°	90°
0°	2262.4	2262.4	*2262.4*
2.5°	2267.4	2269.9	*2267.4*
5°	2282.5	2277.5	*2269.9*
7.5°	2285.0	2287.5	*2290.0*
10°	2295.1	2305.1	*2290.0*
12.5°	2305.1	2297.6	*2292.6*
15°	2312.7	2310.2	*2295.1*
17.5°	2340.3	2330.3	*2327.7*
20°	2383.1	2380.5	*2373.0*
22.5°	2433.3	2428.3	*2425.8*
25°	2506.2	2488.6	*2478.6*
27.5°	2566.6	2551.5	*2546.4*
30°	2626.9	2596.7	*2596.7*
32.5°	2679.7	2672.1	*2667.1*
35°	2805.4	2767.7	*2772.7*
37.5°	2958.7	2921.0	*2888.3*
40°	3174.9	3124.6	*3104.5*
42.5°	3313.1	3262.9	*3267.9*
45°	3391.1	3303.1	*3280.5*
47.5°	3602.2	3491.6	*3461.5*
50°	3944.1	3808.4	*3770.7*
52.5°	4497.1	4278.4	*4228.2*
55°	5190.9	4922.0	*4871.7*
57.5°	6141.1	5784.2	*5676.1*
60°	7297.5	6855.0	*6691.6*
62.5°	8687.6	8142.1	*7986.2*
65°	9733.3	9278.3	*9037.0*
67.5°	10570.4	10195.8	*10080.2*
70°	11068.1	11085.7	*11115.9*
72.5°	*10492.5*	*10975.1*	*11206.4*
75°	7689.6	8064.2	*8423.6*
77.5°	2971.3	2679.7	*2594.2*
80°	480.1	450.0	*465.0*
82.5°	216.2	228.8	*241.3*
85°	140.8	163.4	*173.4*
87.5°	32.7	32.7	*32.7*
90°	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ

Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2407-184-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	10/15/2024
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	McGraw-Edison
Catalog Number:	**GSS-SB1A-727-U-5WQ**
Description:	GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2700K CCT 26 LEDS

Spectral Parameters

CCT (K):	2672
CIE u':	0.2638
CIE v':	0.5276
Duv:	-0.0002
CIE x:	0.4619
CIE y:	0.4106
CIE z:	0.1275
Peak Wavelength (nm):	601
Dominant Wavelength (nm):	584
Purity:	61.88407
Rf:	67.9
Rg:	98.6

CRI (Ra):	71.1
R1:	68.3
R2:	79.8
R3:	91.2
R4:	69.4
R5:	66.5
R6:	72.6
R7:	77.0
R8:	44.1
R9:	-27.8
R10:	54.4
R11:	65.8
R12:	45.6
R13:	69.8
R14:	94.5
R15:	60.1



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.2

REPORT NUMBER: SP1-2407-184-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2672K
CIE x = 0.4619
CIE y = 0.4106
Duv = -0.0002

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.02**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 1.71**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	52	NR	620	888	NR	750	27	NR	880	1	NR
365	0	NR	495	87	NR	625	834	NR	755	23	NR	885	1	NR
370	0	NR	500	135	NR	630	776	NR	760	20	NR	890	1	NR
375	0	NR	505	196	NR	635	712	NR	765	17	NR	895	0	NR
380	0	NR	510	258	NR	640	648	NR	770	15	NR	900	0	NR
385	1	NR	515	317	NR	645	583	NR	775	12	NR	905	0	NR
390	2	NR	520	368	NR	650	523	NR	780	11	NR	910	0	NR
395	4	NR	525	408	NR	655	465	NR	785	9	NR	915	0	NR
400	6	NR	530	443	NR	660	410	NR	790	8	NR	920	0	NR
405	11	NR	535	473	NR	665	360	NR	795	7	NR	925	0	NR
410	23	NR	540	498	NR	670	313	NR	800	6	NR	930	0	NR
415	51	NR	545	530	NR	675	272	NR	805	5	NR	935	0	NR
420	111	NR	550	563	NR	680	236	NR	810	4	NR	940	0	NR
425	214	NR	555	605	NR	685	203	NR	815	4	NR	945	0	NR
430	339	NR	560	651	NR	690	175	NR	820	3	NR	950	0	NR
435	467	NR	565	705	NR	695	150	NR	825	3	NR	955	0	NR
440	535	NR	570	765	NR	700	128	NR	830	3	NR	960	0	NR
445	372	NR	575	824	NR	705	110	NR	835	2	NR	965	0	NR
450	160	NR	580	882	NR	710	94	NR	840	2	NR	970	0	NR
455	89	NR	585	930	NR	715	80	NR	845	2	NR	975	0	NR
460	53	NR	590	968	NR	720	69	NR	850	1	NR	980	0	NR
465	31	NR	595	991	NR	725	59	NR	855	1	NR	985	0	NR
470	23	NR	600	999	NR	730	50	NR	860	1	NR	990	0	NR
475	21	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	23	NR	610	969	NR	740	36	NR	870	1	NR	1000	0	NR
485	32	NR	615	935	NR	745	31	NR	875	1	NR			


REPORT NUMBER: SP1-2407-184-3

TM-30-18


Summary


R_f = 67.9
R_g = 98.6
CIE R_a = 71.1
R_9 = -27.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2407-184-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 53	CES51 = 75	CES76 = 51
CES02 = 63	CES27 = 70	CES52 = 80	CES77 = 79
CES03 = 31	CES28 = 81	CES53 = 64	CES78 = 58
CES04 = 71	CES29 = 37	CES54 = 73	CES79 = 82
CES05 = 50	CES30 = 33	CES55 = 69	CES80 = 82
CES06 = 52	CES31 = 44	CES56 = 60	CES81 = 69
CES07 = 42	CES32 = 47	CES57 = 54	CES82 = 92
CES08 = 41	CES33 = 45	CES58 = 59	CES83 = 82
CES09 = 29	CES34 = 67	CES59 = 85	CES84 = 92
CES10 = 77	CES35 = 84	CES60 = 86	CES85 = 87
CES11 = 60	CES36 = 68	CES61 = 86	CES86 = 60
CES12 = 66	CES37 = 77	CES62 = 59	CES87 = 79
CES13 = 44	CES38 = 40	CES63 = 66	CES88 = 70
CES14 = 74	CES39 = 88	CES64 = 69	CES89 = 66
CES15 = 72	CES40 = 82	CES65 = 64	CES90 = 64
CES16 = 48	CES41 = 70	CES66 = 65	CES91 = 81
CES17 = 51	CES42 = 76	CES67 = 64	CES92 = 69
CES18 = 57	CES43 = 63	CES68 = 73	CES93 = 81
CES19 = 73	CES44 = 97	CES69 = 83	CES94 = 53
CES20 = 67	CES45 = 74	CES70 = 64	CES95 = 77
CES21 = 88	CES46 = 67	CES71 = 60	CES96 = 79
CES22 = 80	CES47 = 55	CES72 = 87	CES97 = 78
CES23 = 92	CES48 = 42	CES73 = 57	CES98 = 69
CES24 = 92	CES49 = 65	CES74 = 84	CES99 = 60
CES25 = 73	CES50 = 74	CES75 = 60	





REPORT NUMBER: SP1-2407-184-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2407-184-3

TM-30-18

Measure Comparisons





(END OF REPORT)